



A powerful and sustainable all-rounder for retail applications

GreenSpace Evo Projector

GreenSpace Evo Projector is a powerful and flexible projector for retail with a subtle and neutral design. The 3D printed housing is crafted from at least 65% recycled or bio-circular materials, while the heatsink is made from 85% recycled aluminium. Because of its circular design, the luminaire is upgradable, reusable, fully serviceable and recyclable. Combined with the high energy efficiency, this makes the GreenSpace Evo a sustainable projector choice. The PerfectAccent reflectors ensure a light effect with increased sparkle and improved shopper eye comfort. The OptiAccent (FPO) Lens technology for maximizing central light intensity. GreenSpace Evo also comes in state-of-the-art ultra-efficient variants and integrates seamlessly onto 3C- and DALI-tracks, CoreLine Trunking and Maxos fusion. Further customization of colors and textures is possible via Philips MyCreation

Benefits

- Blends into stores with a clean and neutral design
- More sparkle and enhanced shopper eye comfort with PerfectAccent reflectors
- Extend the useful life of the product with easy serviceability and upgradeability
- The recycled materials and high energy efficiency help further reduce the carbon footprint of the product

GreenSpace Evo Projector

Features

- Toolless access to the optics, LED and front glass
- Serviceable and upgradeable with standard tools
- Reduced carbon footprint due to high efficacy (ultra-efficient versions available)
- Equipped with state-of-the-art PerfectAccent reflectors or OptiAccent (FPO) Lens technology
- OptiAccent (FPO) Lens technology for maximizing central intensity, eliminating spill light/halo in compared to a traditional LED and reflector optical system, hence offering high contrast accentuation as opposed to a flat and vague light effect
- Very broad aiming flexibility, including upward lighting
- Connectivity options: Interact compatible DALI (DIA), Indoor positioning (DIA-VLC) and Wireless (WIA)
- Optional front glass (recommended for dusty environments)

Application

- Food and Large Retailers
- Fashion
- Petrol and Convenience

Warnings and Safety

- Cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden. For food preparation areas and areas with high levels of dust, the use of the optional front glass is strongly advised, as it can be cleaned with a (dry) microfiber cloth
- During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove

Versions



ST333T GreenSpace Evo Projector
black OptiAccent



ST333T GreenSpace Evo Projector
grey




ST333X2 GreenSpace Evo
Projector double spothead for
Maxos fusion, white


GreenSpace Evo Projector

Dimensional drawing


Flux	CCT	B (mm)
205	827/830/840/PW930/PW940/PC930	126
195	FMT/Rose	
275	827/CH/830/840/PW930/PW940/PC930	
395	827/CH/830/840/PW930/PW940	
275	FMT/Rose/FR	149
395	FR/PC930	
495	827/830/840/PW930/PW940	



Flux	CCT	B (mm)
205	827/830/840/PW930/PW940/PC930	126
195	FMT/Rose	
275	827/CH/830/840/PW930/PW940/PC930	
395	827/CH/830/840/PW930/PW940	
275	FMT/Rose/FR	149
395	FR/PC930	
495	827/830/840/PW930/PW940	




Trafo	Flux	CCT	Optic	A (mm)
PSU	ALL	ALL	FPO ALL	162
	205	840	HNB/HMB/HVB/HVVB/HOVL-H/HOVL-V	158
	495	PW930	NB/MB/WB/VVB/OVL-V	171
DIA	All			162
DIA-VLC	All			251
WIA	All			224



Flux	CCT	B (mm)
ALL FPO	ALL FPO	126
275	FMT/Rose/FR	126
395	FR/pc930	149
495		

Trafo	Flux	CCT	Optic	A (mm)
PSU	205	840	HNB/HMB/HVB/HVVB/HOVL-H/HOVL-V	158
	495	PW930	NB/MB/WB/VVB/OVL-V	171
	DIA	All		
DIA-VLC	All			253
WIA	All			224



Flux	CCT	B (mm)
275	FMT/Rose/FR	126
395	FR/pc930	149
495		

Product details



ST333T GreenSpace Evo Projector
grey



ST333T GreenSpace Evo Projector
white



ST333T GreenSpace Evo Projector
black

GreenSpace Evo Projector

General Information

Driver included	Yes
-----------------	-----

Operating and Electrical

Protection class IEC	Safety class II
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable

Mechanical and Housing

Mech. impact protection code	IK02
Ingress protection code	IP20

Emergency Operation

Central Emergency	No
-------------------	----

Approval and Application

Ambient temperature range	+10 to +25 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

General Information

Order Code	Full Product Name	Number of gear units
910505104594	ST333T 20S/PC930 PSU NB WH481	1 unit
910505104596	ST333T 27S/827 PSU WB WH481	1 unit
910505104597	ST333T 27S/830 PSU WB WH481	1 unit
910505104598	ST333T 27S/840 PSU WB WH481	1 unit
910505104601	ST333T 27S/PW930 UE PSU HWB WH481	1 unit
910505104602	ST333T 27S/PW930 UE DIA-VLC HWB WH481	1 unit
910505104605	ST333T 27S/CH DIA MB FG WH481	1 unit
910505104606	ST333T 27S/FMT DIA MB FG WH481	1 unit
910505104607	ST333T 27S/ROSE WIA MB FG WH481	1 unit
910505104608	ST333T 27S/FR WIA MB FG WH481	1 unit
910505104609	ST333T 39S/830 PSU WB WH481	1 unit
910505104610	ST333T 39S/830 DIA-VLC WB WH481	1 unit
910505104614	ST333T 39S/PW930 UE PSU HWB WH481	1 unit
910505104615	ST333T 39S/PW930 UE DIA-VLC HWB WH481	1 unit
910505104616	ST333T 49S/830 PSU WB WH481	1 unit
910505104984	ST333T 20S/PC930 PSU FPO12 BK482	1 unit
910505104986	ST333T 27S/PC930 PSU FPO18 BK482	1 unit
910505104989	ST333T 27S/PC930 PSU FPO24 BK482	1 unit
910505104999	ST333T 35S/PC930 PSU FPO36 BK482	1 unit
910505104622	ST333Y2 27S/830 PSU WB WH481	2 units
910505104623	ST333Y2 27S/PW930 DIA HRCT WH481	2 units
910505104624	ST333Y2 39S/830 PSU WB WH481	2 units
910505104625	ST333Y2 39S/PW930 DIA HRCT WH481	2 units
910505104603	ST333T 27S/PW940 PSU HMB GR482	1 unit
910505104612	ST333T 39S/PW940 PSU WB GR482	1 unit
910505104983	ST333T 20S/PW930 PSU FPO12 WH481	1 unit
910505104985	ST333T 27S/PW930 PSU FPO18 WH481	1 unit
910505104987	ST333T 27S/PW930 PSU FPO24 WH481	1 unit
910505104988	ST333T 27S/PW930 WIA FPO24 WH481	1 unit
910505104990	ST333T 27S/PW930 PSU FPO30 WH481	1 unit
910505104996	ST333T 35S/PW930 PSU FPO28 WH481	1 unit
910505104997	ST333T 35S/PW930 PSU FPO36 WH481	1 unit
910505104998	ST333T 35S/PW930 WIA FPO36 WH481	1 unit
910505104592	ST333T 19S/FMT WIA HMB BK482	1 unit
910505104593	ST333T 19S/ROSE WIA HMB BK482	1 unit
910505104595	ST333T 20S/PW930 PSU HNB BK482	1 unit
910505104599	ST333T 27S/PW930 PSU HRCT BK482	1 unit
910505104604	ST333T 27S/PC930 PSU HMB FG BK482	1 unit
910505104611	ST333T 39S/PW930 PSU HRCT BK482	1 unit
910505104613	ST333T 39S/PC930 PSU WB BK482	1 unit
910505104617	ST333T 49S/PW930 PSU WB BK482	1 unit
910505104618	ST333X2 27S/830 PSU WB WH481	2 units
910505104620	ST333X2 39S/830 PSU WB WH481	2 units
910505104619	ST333X2 27S/PW930 DIA HMB BK482	2 units
910505104621	ST333X2 39S/PW930 DIA HMB BK482	2 units

Light Technical (1/2)

GreenSpace Evo Projector

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505104594	ST333T 20S/ PC930 PSU NB WH481	3000 K	>90	105 lm/W	2,100 lm
910505104596	ST333T 27S/827 PSU WB WH481	2700 K	80	133 lm/W	2,800 lm
910505104597	ST333T 27S/830 PSU WB WH481	3000 K	>80	144 lm/W	2,700 lm
910505104598	ST333T 27S/840 PSU WB WH481	4000 K	>80	149 lm/W	2,800 lm
910505104601	ST333T 27S/ PW930 UE PSU HWB WH481	3000 K	>90	155 lm/W	2,700 lm
910505104602	ST333T 27S/ PW930 UE DIA-VLC HWB WH481	3000 K	>90	144 lm/W	2,700 lm
910505104605	ST333T 27S/CH DIA MB FG WH481	2700 K	80	111 lm/W	2,600 lm
910505104606	ST333T 27S/FMT DIA MB FG WH481	3000 K	90	90.5 lm/W	2,400 lm
910505104607	ST333T 27S/ ROSE WIA MB FG WH481	2200 K	80	94.5 lm/W	2,700 lm
910505104608	ST333T 27S/FR WIA MB FG WH481	5000 K	90	117 lm/W	2,400 lm
910505104609	ST333T 39S/830 PSU WB WH481	3000 K	>80	143 lm/W	4,000 lm
910505104610	ST333T 39S/830 DIA- VLC WB WH481	3000 K	>80	133 lm/W	4,000 lm
910505104614	ST333T 39S/ PW930 UE PSU HWB WH481	3000 K	>90	155 lm/W	3,800 lm
910505104615	ST333T 39S/ PW930 UE DIA-VLC HWB WH481	3000 K	>90	143 lm/W	3,800 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505104616	ST333T 49S/830 PSU WB WH481	3000 K	>80	129 lm/W	4,900 lm
910505104984	ST333T 20S/ PC930 PSU FPO12 BK482	3000 K	>90	95 lm/W	1,900 lm
910505104986	ST333T 27S/ PC930 PSU FPO18 BK482	3000 K	>90	102 lm/W	2,600 lm
910505104989	ST333T 27S/ PC930 PSU FPO24 BK482	3000 K	>90	110 lm/W	2,700 lm
910505104999	ST333T 35S/ PC930 PSU FPO36 BK482	3000 K	>90	111 lm/W	3,500 lm
910505104622	ST333Y2 27S/830 PSU WB WH481	3000 K	>80	135 lm/W	5,400 lm
910505104623	ST333Y2 27S/ PW930 DIA HRCT WH481	3000 K	>90	123 lm/W	5,400 lm
910505104624	ST333Y2 39S/830 PSU WB WH481	3000 K	>80	136 lm/W	8,000 lm
910505104625	ST333Y2 39S/ PW930 DIA HRCT WH481	3000 K	>90	128 lm/W	7,400 lm
910505104603	ST333T 27S/ PW940 PSU HMB GR482	4000 K	>90	149 lm/W	2,800 lm
910505104612	ST333T 39S/ PW940 PSU WB GR482	4000 K	>90	143 lm/W	4,000 lm
910505104983	ST333T 20S/ PW930 PSU FPO12 WH481	3000 K	>90	108 lm/W	1,950 lm
910505104985	ST333T 27S/ PW930 PSU FPO18 WH481	3000 K	>90	113 lm/W	2,600 lm
910505104987	ST333T 27S/ PW930 PSU FPO24 WH481	3000 K	>90	123 lm/W	2,700 lm
910505104988	ST333T 27S/ PW930 WIA FPO24 WH481	3000 K	>90	108 lm/W	2,700 lm
910505104990	ST333T 27S/ PW930 PSU FPO30 WH481	3000 K	>90	117 lm/W	2,700 lm

GreenSpace Evo Projector

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505104996	ST333T 35S/ PW930 PSU FPO28 WH481	3000 K	>90	109 lm/W	3,600 lm
910505104997	ST333T 35S/ PW930 PSU FPO36 WH481	3000 K	>90	118 lm/W	3,600 lm
910505104998	ST333T 35S/ PW930 WIA FPO36 WH481	3000 K	>90	113 lm/W	3,600 lm
910505104592	ST333T 19S/FMT WIA HMB BK482	3000 K	90	101 lm/W	1,900 lm
910505104593	ST333T 19S/ ROSE WIA HMB BK482	2200 K	80	107 lm/W	2,200 lm
910505104595	ST333T 20S/ PW930 PSU HNB BK482	3000 K	>90	124 lm/W	2,200 lm
910505104599	ST333T 27S/ PW930 PSU HRCT BK482	3000 K	>90	129 lm/W	2,700 lm
910505104604	ST333T 27S/ PC930 PSU	3000 K	>90	117 lm/W	2,700 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	HMB FG BK482				
910505104611	ST333T 39S/ PW930 PSU HRCT BK482	3000 K	>90	132 lm/W	3,700 lm
910505104613	ST333T 39S/ PC930 PSU WB BK482	3000 K	>90	115 lm/W	3,900 lm
910505104617	ST333T 49S/ PW930 PSU WB BK482	3000 K	>90	122 lm/W	5,000 lm
910505104618	ST333X2 27S/830 PSU WB WH481	3000 K	>80	135 lm/W	5,400 lm
910505104620	ST333X2 39S/830 PSU WB WH481	3000 K	>80	136 lm/W	8,000 lm
910505104619	ST333X2 27S/ PW930 DIA HMB BK482	3000 K	>90	132 lm/W	5,800 lm
910505104621	ST333X2 39S/ PW930 DIA HMB BK482	3000 K	>90	131 lm/W	7,600 lm

Light Technical (2/2)

Order Code	Full Product Name	Optic type
910505104594	ST333T 20S/PC930 PSU NB WH481	Narrow beam
910505104596	ST333T 27S/827 PSU WB WH481	Wide beam
910505104597	ST333T 27S/830 PSU WB WH481	Wide beam
910505104598	ST333T 27S/840 PSU WB WH481	Wide beam
910505104601	ST333T 27S/PW930 UE PSU HWB WH481	High-reflective metal reflector Wide beam 40 to 80 degrees
910505104602	ST333T 27S/PW930 UE DIA-VLC HWB WH481	High-reflective metal reflector Wide beam 40 to 80 degrees
910505104605	ST333T 27S/CH DIA MB FG WH481	Medium beam
910505104606	ST333T 27S/FMT DIA MB FG WH481	Medium beam
910505104607	ST333T 27S/ROSE WIA MB FG WH481	Medium beam
910505104608	ST333T 27S/FR WIA MB FG WH481	Medium beam
910505104609	ST333T 39S/830 PSU WB WH481	Wide beam
910505104610	ST333T 39S/830 DIA-VLC WB WH481	Wide beam
910505104614	ST333T 39S/PW930 UE PSU HWB WH481	High-reflective metal reflector Wide beam 40 to 80 degrees
910505104615	ST333T 39S/PW930 UE DIA-VLC HWB WH481	High-reflective metal reflector Wide beam 40 to 80 degrees
910505104616	ST333T 49S/830 PSU WB WH481	Wide beam

Order Code	Full Product Name	Optic type
910505104984	ST333T 20S/PC930 PSU FPO12 BK482	Beam angle 12°
910505104986	ST333T 27S/PC930 PSU FPO18 BK482	Beam angle 18°
910505104989	ST333T 27S/PC930 PSU FPO24 BK482	Beam angle 24°
910505104999	ST333T 35S/PC930 PSU FPO36 BK482	Beam angle 36°
910505104622	ST333Y2 27S/830 PSU WB WH481	Wide beam
910505104623	ST333Y2 27S/PW930 DIA HRCT WH481	High-reflective metal reflector Rectangular beam
910505104624	ST333Y2 39S/830 PSU WB WH481	Wide beam
910505104625	ST333Y2 39S/PW930 DIA HRCT WH481	High-reflective metal reflector Rectangular beam
910505104603	ST333T 27S/PW940 PSU HMB GR482	High-reflective metal reflector Medium beam 20 to 40 degrees
910505104612	ST333T 39S/PW940 PSU WB GR482	Wide beam
910505104983	ST333T 20S/PW930 PSU FPO12 WH481	Beam angle 12°
910505104985	ST333T 27S/PW930 PSU FPO18 WH481	Beam angle 18°

GreenSpace Evo Projector

Order Code	Full Product Name	Optic type
910505104987	ST333T 27S/PW930 PSU FPO24 WH481	Beam angle 24°
910505104988	ST333T 27S/PW930 WIA FPO24 WH481	Beam angle 24°
910505104990	ST333T 27S/PW930 PSU FPO30 WH481	Beam angle 30°
910505104996	ST333T 35S/PW930 PSU FPO28 WH481	Beam angle 30°
910505104997	ST333T 35S/PW930 PSU FPO36 WH481	Beam angle 36°
910505104998	ST333T 35S/PW930 WIA FPO36 WH481	Beam angle 36°
910505104592	ST333T 19S/FMT WIA HMB BK482	High-reflective metal reflector Medium beam 20 to 40 degrees
910505104593	ST333T 19S/ROSE WIA HMB BK482	High-reflective metal reflector Medium beam 20 to 40 degrees

Order Code	Full Product Name	Optic type
910505104595	ST333T 20S/PW930 PSU HNB BK482	High-reflective metal reflector Narrow beam 10 to 20 degrees
910505104599	ST333T 27S/PW930 PSU HRCT BK482	High-reflective metal reflector Rectangular beam
910505104604	ST333T 27S/PC930 PSU HMB FG BK482	High-reflective metal reflector Medium beam 20 to 40 degrees
910505104611	ST333T 39S/PW930 PSU HRCT BK482	High-reflective metal reflector Rectangular beam
910505104613	ST333T 39S/PC930 PSU WB BK482	Wide beam
910505104617	ST333T 49S/PW930 PSU WB BK482	Wide beam
910505104618	ST333X2 27S/830 PSU WB WH481	Wide beam
910505104620	ST333X2 39S/830 PSU WB WH481	Wide beam
910505104619	ST333X2 27S/PW930 DIA HMB BK482	High-reflective metal reflector Medium beam 20 to 40 degrees
910505104621	ST333X2 39S/PW930 DIA HMB BK482	High-reflective metal reflector Medium beam 20 to 40 degrees

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Power Consumption
910505104594	ST333T 20S/PC930 PSU NB WH481	220 to 240 V	20 W
910505104596	ST333T 27S/827 PSU WB WH481	220 to 240 V	21 W
910505104597	ST333T 27S/830 PSU WB WH481	220 to 240 V	18.8 W
910505104598	ST333T 27S/840 PSU WB WH481	220 to 240 V	18.8 W
910505104601	ST333T 27S/PW930 UE PSU HWB WH481	220 to 240 V	17.4 W
910505104602	ST333T 27S/PW930 UE DIA-VLC HWB WH481	220 to 240 V	18.8 W
910505104605	ST333T 27S/CH DIA MB FG WH481	220 to 240 V	23.5 W
910505104606	ST333T 27S/FMT DIA MB FG WH481	220 to 240 V	26.5 W
910505104607	ST333T 27S/ROSE WIA MB FG WH481	220 to 240 V	28.5 W
910505104608	ST333T 27S/FR WIA MB FG WH481	220 to 240 V	20.5 W
910505104609	ST333T 39S/830 PSU WB WH481	220 to 240 V	28 W
910505104610	ST333T 39S/830 DIA-VLC WB WH481	220 to 240 V	30 W
910505104614	ST333T 39S/PW930 UE PSU HWB WH481	220 to 240 V	24.5 W
910505104615	ST333T 39S/PW930 UE DIA-VLC HWB WH481	220 to 240 V	26.5 W
910505104616	ST333T 49S/830 PSU WB WH481	220 to 240 V	38 W
910505104984	ST333T 20S/PC930 PSU FPO12 BK482	210 to 240 V	20 W
910505104986	ST333T 27S/PC930 PSU FPO18 BK482	210 to 240 V	25.5 W
910505104989	ST333T 27S/PC930 PSU FPO24 BK482	210 to 240 V	24.5 W
910505104999	ST333T 35S/PC930 PSU FPO36 BK482	210 to 240 V	31.5 W

Order Code	Full Product Name	Input Voltage	Power Consumption
910505104622	ST333Y2 27S/830 PSU WB WH481	220 to 240 V	40 W
910505104623	ST333Y2 27S/PW930 DIA HRCT WH481	220 to 240 V	44 W
910505104624	ST333Y2 39S/830 PSU WB WH481	220 to 240 V	59 W
910505104625	ST333Y2 39S/PW930 DIA HRCT WH481	220 to 240 V	58 W
910505104603	ST333T 27S/PW940 PSU HMB GR482	220 to 240 V	18.8 W
910505104612	ST333T 39S/PW940 PSU WB GR482	220 to 240 V	28 W
910505104983	ST333T 20S/PW930 PSU FPO12 WH481	210 to 240 V	18 W
910505104985	ST333T 27S/PW930 PSU FPO18 WH481	210 to 240 V	23 W
910505104987	ST333T 27S/PW930 PSU FPO24 WH481	210 to 240 V	22 W
910505104988	ST333T 27S/PW930 WIA FPO24 WH481	210 to 240 V	25 W
910505104990	ST333T 27S/PW930 PSU FPO30 WH481	210 to 240 V	23 W
910505104996	ST333T 35S/PW930 PSU FPO28 WH481	210 to 240 V	33 W
910505104997	ST333T 35S/PW930 PSU FPO36 WH481	210 to 240 V	30.5 W
910505104998	ST333T 35S/PW930 WIA FPO36 WH481	210 to 240 V	32 W
910505104592	ST333T 19S/FMT WIA HMB BK482	220 to 240 V	18.8 W
910505104593	ST333T 19S/ROSE WIA HMB BK482	220 to 240 V	20.5 W
910505104595	ST333T 20S/PW930 PSU HNB BK482	220 to 240 V	17.8 W

GreenSpace Evo Projector

Order Code	Full Product Name	Input Voltage	Power Consumption
910505104599	ST333T 27S/PW930 PSU HRCT BK482	220 to 240 V	21 W
910505104604	ST333T 27S/PC930 PSU HMB FG BK482	220 to 240 V	23 W
910505104611	ST333T 39S/PW930 PSU HRCT BK482	220 to 240 V	28 W
910505104613	ST333T 39S/PC930 PSU WB BK482	220 to 240 V	34 W

Order Code	Full Product Name	Input Voltage	Power Consumption
910505104617	ST333T 49S/PW930 PSU WB BK482	220 to 240 V	41 W
910505104618	ST333X2 27S/830 PSU WB WH481	220 to 240 V	40 W
910505104620	ST333X2 39S/830 PSU WB WH481	220 to 240 V	59 W
910505104619	ST333X2 27S/PW930 DIA HMB BK482	220 to 240 V	44 W
910505104621	ST333X2 39S/PW930 DIA HMB BK482	220 to 240 V	58 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
910505104594	ST333T 20S/PC930 PSU NB WH481	No
910505104596	ST333T 27S/827 PSU WB WH481	No
910505104597	ST333T 27S/830 PSU WB WH481	No
910505104598	ST333T 27S/840 PSU WB WH481	No
910505104601	ST333T 27S/PW930 UE PSU HWB WH481	No
910505104602	ST333T 27S/PW930 UE DIA-VLC HWB WH481	Yes
910505104605	ST333T 27S/CH DIA MB FG WH481	Yes
910505104606	ST333T 27S/FMT DIA MB FG WH481	Yes
910505104607	ST333T 27S/ROSE WIA MB FG WH481	Yes
910505104608	ST333T 27S/FR WIA MB FG WH481	Yes
910505104609	ST333T 39S/830 PSU WB WH481	No
910505104610	ST333T 39S/830 DIA-VLC WB WH481	Yes
910505104614	ST333T 39S/PW930 UE PSU HWB WH481	No
910505104615	ST333T 39S/PW930 UE DIA-VLC HWB WH481	Yes
910505104616	ST333T 49S/830 PSU WB WH481	No
910505104984	ST333T 20S/PC930 PSU FPO12 BK482	No
910505104986	ST333T 27S/PC930 PSU FPO18 BK482	No
910505104989	ST333T 27S/PC930 PSU FPO24 BK482	No
910505104999	ST333T 35S/PC930 PSU FPO36 BK482	No
910505104622	ST333Y2 27S/830 PSU WB WH481	No
910505104623	ST333Y2 27S/PW930 DIA HRCT WH481	Yes
910505104624	ST333Y2 39S/830 PSU WB WH481	No
910505104625	ST333Y2 39S/PW930 DIA HRCT WH481	Yes

Order Code	Full Product Name	Dimmable
910505104603	ST333T 27S/PW940 PSU HMB GR482	No
910505104612	ST333T 39S/PW940 PSU WB GR482	No
910505104983	ST333T 20S/PW930 PSU FPO12 WH481	No
910505104985	ST333T 27S/PW930 PSU FPO18 WH481	No
910505104987	ST333T 27S/PW930 PSU FPO24 WH481	No
910505104988	ST333T 27S/PW930 WIA FPO24 WH481	No
910505104990	ST333T 27S/PW930 PSU FPO30 WH481	No
910505104996	ST333T 35S/PW930 PSU FPO28 WH481	No
910505104997	ST333T 35S/PW930 PSU FPO36 WH481	No
910505104998	ST333T 35S/PW930 WIA FPO36 WH481	No
910505104592	ST333T 19S/FMT WIA HMB BK482	Yes
910505104593	ST333T 19S/ROSE WIA HMB BK482	Yes
910505104595	ST333T 20S/PW930 PSU HNB BK482	No
910505104599	ST333T 27S/PW930 PSU HRCT BK482	No
910505104604	ST333T 27S/PC930 PSU HMB FG BK482	No
910505104611	ST333T 39S/PW930 PSU HRCT BK482	No
910505104613	ST333T 39S/PC930 PSU WB BK482	No
910505104617	ST333T 49S/PW930 PSU WB BK482	No
910505104618	ST333X2 27S/830 PSU WB WH481	No
910505104620	ST333X2 39S/830 PSU WB WH481	No
910505104619	ST333X2 27S/PW930 DIA HMB BK482	Yes
910505104621	ST333X2 39S/PW930 DIA HMB BK482	Yes

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910505104594	ST333T 20S/PC930 PSU NB WH481	White
910505104596	ST333T 27S/827 PSU WB WH481	White
910505104597	ST333T 27S/830 PSU WB WH481	White
910505104598	ST333T 27S/840 PSU WB WH481	White
910505104601	ST333T 27S/PW930 UE PSU HWB WH481	White
910505104602	ST333T 27S/PW930 UE DIA-VLC HWB WH481	White
910505104605	ST333T 27S/CH DIA MB FG WH481	White
910505104606	ST333T 27S/FMT DIA MB FG WH481	White
910505104607	ST333T 27S/ROSE WIA MB FG WH481	White
910505104608	ST333T 27S/FR WIA MB FG WH481	White
910505104609	ST333T 39S/830 PSU WB WH481	White
910505104610	ST333T 39S/830 DIA-VLC WB WH481	White

Order Code	Full Product Name	Housing Color
910505104614	ST333T 39S/PW930 UE PSU HWB WH481	White
910505104615	ST333T 39S/PW930 UE DIA-VLC HWB WH481	White
910505104616	ST333T 49S/830 PSU WB WH481	White
910505104984	ST333T 20S/PC930 PSU FPO12 BK482	Black
910505104986	ST333T 27S/PC930 PSU FPO18 BK482	Black
910505104989	ST333T 27S/PC930 PSU FPO24 BK482	Black
910505104999	ST333T 35S/PC930 PSU FPO36 BK482	Black
910505104622	ST333Y2 27S/830 PSU WB WH481	White
910505104623	ST333Y2 27S/PW930 DIA HRCT WH481	White
910505104624	ST333Y2 39S/830 PSU WB WH481	White
910505104625	ST333Y2 39S/PW930 DIA HRCT WH481	White
910505104603	ST333T 27S/PW940 PSU HMB GR482	Gray

GreenSpace Evo Projector

Order Code	Full Product Name	Housing Color
910505104612	ST333T 39S/PW940 PSU WB GR482	Gray
910505104983	ST333T 20S/PW930 PSU FPO12 WH481	White
910505104985	ST333T 27S/PW930 PSU FPO18 WH481	White
910505104987	ST333T 27S/PW930 PSU FPO24 WH481	White
910505104988	ST333T 27S/PW930 WIA FPO24 WH481	White
910505104990	ST333T 27S/PW930 PSU FPO30 WH481	White
910505104996	ST333T 35S/PW930 PSU FPO28 WH481	White
910505104997	ST333T 35S/PW930 PSU FPO36 WH481	White
910505104998	ST333T 35S/PW930 WIA FPO36 WH481	White
910505104592	ST333T 19S/FMT WIA HMB BK482	Black
910505104593	ST333T 19S/ROSE WIA HMB BK482	Black

Order Code	Full Product Name	Housing Color
910505104595	ST333T 20S/PW930 PSU HNB BK482	Black
910505104599	ST333T 27S/PW930 PSU HRCT BK482	Black
910505104604	ST333T 27S/PC930 PSU HMB FG BK482	Black
910505104611	ST333T 39S/PW930 PSU HRCT BK482	Black
910505104613	ST333T 39S/PC930 PSU WB BK482	Black
910505104617	ST333T 49S/PW930 PSU WB BK482	Black
910505104618	ST333X2 27S/830 PSU WB WH481	White
910505104620	ST333X2 39S/830 PSU WB WH481	White
910505104619	ST333X2 27S/PW930 DIA HMB BK482	Black
910505104621	ST333X2 39S/PW930 DIA HMB BK482	Black

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505104594	ST333T 20S/PC930 PSU NB WH481	(0.422, 0.386)
910505104596	ST333T 27S/827 PSU WB WH481	(0.458, 0.410)
910505104597	ST333T 27S/830 PSU WB WH481	(0.434, 0.403)
910505104598	ST333T 27S/840 PSU WB WH481	(0.382,0.380)
910505104601	ST333T 27S/PW930 UE PSU HWB WH481	(0.422, 0.386)
910505104602	ST333T 27S/PW930 UE DIA-VLC HWB WH481	(0.422, 0.386)
910505104605	ST333T 27S/CH DIA MB FG WH481	(0.458, 0.410)
910505104606	ST333T 27S/FMT DIA MB FG WH481	(0.457,0.385)
910505104607	ST333T 27S/ROSE WIA MB FG WH481	(0.457,0.385)
910505104608	ST333T 27S/FR WIA MB FG WH481	(0.343,0.331)
910505104609	ST333T 39S/830 PSU WB WH481	(0.434, 0.403)
910505104610	ST333T 39S/830 DIA-VLC WB WH481	(0.434, 0.403)
910505104614	ST333T 39S/PW930 UE PSU HWB WH481	(0.422, 0.386)
910505104615	ST333T 39S/PW930 UE DIA-VLC HWB WH481	(0.422, 0.386)
910505104616	ST333T 49S/830 PSU WB WH481	(0.434, 0.403)
910505104984	ST333T 20S/PC930 PSU FPO12 BK482	(0.422, 0.386)
910505104986	ST333T 27S/PC930 PSU FPO18 BK482	(0.422, 0.386)
910505104989	ST333T 27S/PC930 PSU FPO24 BK482	(0.422, 0.386)
910505104999	ST333T 35S/PC930 PSU FPO36 BK482	(0.422, 0.386)
910505104622	ST333Y2 27S/830 PSU WB WH481	(0.434, 0.403)
910505104623	ST333Y2 27S/PW930 DIA HRCT WH481	(0.422, 0.386)
910505104624	ST333Y2 39S/830 PSU WB WH481	(0.434, 0.403)
910505104625	ST333Y2 39S/PW930 DIA HRCT WH481	(0.422, 0.386)

Order Code	Full Product Name	Initial chromaticity
910505104603	ST333T 27S/PW940 PSU HMB GR482	(0.374,0.364)
910505104612	ST333T 39S/PW940 PSU WB GR482	(0.374,0.364)
910505104983	ST333T 20S/PW930 PSU FPO12 WH481	(0.422, 0.386)
910505104985	ST333T 27S/PW930 PSU FPO18 WH481	(0.422, 0.386)
910505104987	ST333T 27S/PW930 PSU FPO24 WH481	(0.422, 0.386)
910505104988	ST333T 27S/PW930 WIA FPO24 WH481	(0.422, 0.386)
910505104990	ST333T 27S/PW930 PSU FPO30 WH481	(0.422, 0.386)
910505104996	ST333T 35S/PW930 PSU FPO28 WH481	(0.422, 0.386)
910505104997	ST333T 35S/PW930 PSU FPO36 WH481	(0.422, 0.386)
910505104998	ST333T 35S/PW930 WIA FPO36 WH481	(0.422, 0.386)
910505104592	ST333T 19S/FMT WIA HMB BK482	(0.457,0.385)
910505104593	ST333T 19S/ROSE WIA HMB BK482	(0.457,0.385)
910505104595	ST333T 20S/PW930 PSU HNB BK482	(0.422, 0.386)
910505104599	ST333T 27S/PW930 PSU HRCT BK482	(0.422, 0.386)
910505104604	ST333T 27S/PC930 PSU HMB FG BK482	(0.422, 0.386)
910505104611	ST333T 39S/PW930 PSU HRCT BK482	(0.422, 0.386)
910505104613	ST333T 39S/PC930 PSU WB BK482	(0.422, 0.386)
910505104617	ST333T 49S/PW930 PSU WB BK482	(0.422, 0.386)
910505104618	ST333X2 27S/830 PSU WB WH481	(0.434, 0.403)
910505104620	ST333X2 39S/830 PSU WB WH481	(0.434, 0.403)
910505104619	ST333X2 27S/PW930 DIA HMB BK482	(0.422, 0.386)
910505104621	ST333X2 39S/PW930 DIA HMB BK482	(0.422, 0.386)

Product Data


Order Code	Full Product Name	Product family code
910505104594	ST333T 20S/PC930 PSU NB WH481	ST333T
910505104596	ST333T 27S/827 PSU WB WH481	ST333T
910505104597	ST333T 27S/830 PSU WB WH481	ST333T
910505104598	ST333T 27S/840 PSU WB WH481	ST333T
910505104601	ST333T 27S/PW930 UE PSU HWB WH481	ST333T
910505104602	ST333T 27S/PW930 UE DIA-VLC HWB WH481	ST333T
910505104605	ST333T 27S/CH DIA MB FG WH481	ST333T
910505104606	ST333T 27S/FMT DIA MB FG WH481	ST333T
910505104607	ST333T 27S/ROSE WIA MB FG WH481	ST333T

Order Code	Full Product Name	Product family code
910505104608	ST333T 27S/FR WIA MB FG WH481	ST333T
910505104609	ST333T 39S/830 PSU WB WH481	ST333T
910505104610	ST333T 39S/830 DIA-VLC WB WH481	ST333T
910505104614	ST333T 39S/PW930 UE PSU HWB WH481	ST333T
910505104615	ST333T 39S/PW930 UE DIA-VLC HWB WH481	ST333T
910505104616	ST333T 49S/830 PSU WB WH481	ST333T
910505104984	ST333T 20S/PC930 PSU FPO12 BK482	ST333T
910505104986	ST333T 27S/PC930 PSU FPO18 BK482	ST333T
910505104989	ST333T 27S/PC930 PSU FPO24 BK482	ST333T


GreenSpace Evo Projector

Order Code	Full Product Name	Product family code	Order Code	Full Product Name	Product family code
910505104999	ST333T 35S/PC930 PSU FPO36 BK482	ST333T	910505104998	ST333T 35S/PW930 WIA FPO36 WH481	ST333T
910505104622	ST333Y2 27S/830 PSU WB WH481	ST333Y2	910505104592	ST333T 19S/FMT WIA HMB BK482	ST333T
910505104623	ST333Y2 27S/PW930 DIA HRCT WH481	ST333Y2	910505104593	ST333T 19S/ROSE WIA HMB BK482	ST333T
910505104624	ST333Y2 39S/830 PSU WB WH481	ST333Y2	910505104595	ST333T 20S/PW930 PSU HNB BK482	ST333T
910505104625	ST333Y2 39S/PW930 DIA HRCT WH481	ST333Y2	910505104599	ST333T 27S/PW930 PSU HRCT BK482	ST333T
910505104603	ST333T 27S/PW940 PSU HMB GR482	ST333T	910505104604	ST333T 27S/PC930 PSU HMB FG BK482	ST333T
910505104612	ST333T 39S/PW940 PSU WB GR482	ST333T	910505104611	ST333T 39S/PW930 PSU HRCT BK482	ST333T
910505104983	ST333T 20S/PW930 PSU FPO12 WH481	ST333T	910505104613	ST333T 39S/PC930 PSU WB BK482	ST333T
910505104985	ST333T 27S/PW930 PSU FPO18 WH481	ST333T	910505104617	ST333T 49S/PW930 PSU WB BK482	ST333T
910505104987	ST333T 27S/PW930 PSU FPO24 WH481	ST333T	910505104618	ST333X2 27S/830 PSU WB WH481	ST333X2
910505104988	ST333T 27S/PW930 WIA FPO24 WH481	ST333T	910505104620	ST333X2 39S/830 PSU WB WH481	ST333X2
910505104990	ST333T 27S/PW930 PSU FPO30 WH481	ST333T	910505104619	ST333X2 27S/PW930 DIA HMB BK482	ST333X2
910505104996	ST333T 35S/PW930 PSU FPO28 WH481	ST333T	910505104621	ST333X2 39S/PW930 DIA HMB BK482	ST333X2
910505104997	ST333T 35S/PW930 PSU FPO36 WH481	ST333T			


Polar Wide Diagrams




Polar Normal (separate) - 910505104987




Polar Normal (separate) - 910505104985




Polar Normal (separate) - 910505104988



Polar Normal (separate) - 910505104984




Polar Normal (separate) - 910505104989




Polar Normal (separate) - 910505104983


Polar Wide Diagrams




Polar Normal (separate) - 910505104990




Polar Normal (separate) - 910505104996




Polar Normal (separate) - 910505104999




Polar Normal (separate) - 910505104997




Polar Normal (separate) - 910505104998




Polar Normal (separate) - 910505104986




Polar Normal (separate) - ST333TI - 910505104625




Polar Normal (separate) - ST333TI - 910505104610




Polar Normal (separate) - ST333TI - 910505104594



Polar Normal (separate) - ST333TI - 910505104616




Polar Normal (separate) - ST333TI - 910505104607




Polar Normal (separate) - ST333TI - 910505104615

GreenSpace Evo Projector


Polar Wide Diagrams




Polar Normal (separate) - ST333TI - 910505104602




Polar Normal (separate) - ST333TI - 910505104592




Polar Normal (separate) - ST333TI - 910505104606




Polar Normal (separate) - ST333TI - 910505104599




Polar Normal (separate) - ST333TI - 910505104609




Polar Normal (separate) - ST333TI - 910505104593



Polar Normal (separate) - ST333TI - 910505104597




Polar Normal (separate) - ST333TI - 910505104624




Polar Normal (separate) - ST333TI - 910505104608


Polar Wide Diagrams




Polar Normal (separate) - ST333TI - 910505104604




Polar Normal (separate) - ST333TI - 910505104614




Polar Normal (separate) - ST333TI - 910505104620




Polar Normal (separate) - ST333TI - 910505104605




Polar Normal (separate) - ST333TI - 910505104601




Polar Normal (separate) - ST333TI - 910505104618



Polar Normal (separate) - ST333TI - 910505104611




Polar Normal (separate) - ST333TI - 910505104623




Polar Normal (separate) - ST333TI - 910505104612


Polar Wide Diagrams




Polar Normal (separate) - ST333TI - 910505104595




Polar Normal (separate) - ST333TI - 910505104622




Polar Normal (separate) - ST333TI - 910505104598




Polar Normal (separate) - ST333TI - 910505104603




Polar Normal (separate) - ST333TI - 910505104596




Polar Normal (separate) - ST333TI - 910505104617



Polar Normal (separate) - ST333TI - 910505104613



Polar Normal (separate) - ST333TI - 910505104619



Polar Normal (separate) - ST333TI - 910505104621

GreenSpace Evo Projector

