



The ultimate in retail flexibility and performance

With StyliD Evo, retailers can enjoy the superior quality of light and market-leading energy efficiency of PerfectAccent optics in a series of flexible and future-proof projectors. StyliD Evo projectors are easy to reconfigure with quick and easy optic upgrades that require no tools. They also support frequent changes in store layouts, as the StyliD Evo projector can be easily repositioned on the track or Maxos fusion backbone. Covering a wide range of lighting applications, from lower light levels in convenience formats to high-ceiling installations where very high light output is required, StyliD offers continuity for every retail concept. StyliD Evo can be mounted on 3C or DALI track (ST770T, ST780T), on Maxos fusion (ST770S, ST780S, ST770X), or into the ceiling with a semi-recessed version (ST770B). All StyliD Evo projectors with PerfectAccent reflectors are certified as a circular lighting product and offer multiple system integration and dimming options, including wired as well as wireless. For prolonged shelf life and better visual representation of food, reducing food waste and increasing sales, fresh food LED lighting recipes are available. Check out our Fashion and Food catalog pages to find out more about PremiumWhite, PremiumColor, Fresh Meat, Rosé, Frost and Champagne.

Benefits

- Attract shoppers with more sparkle and superior eye comfort
- Easy to reposition and upgrade for frequent store updates
- Best-in class efficacy to reduce carbon footprint and save on energy use
- Certified as circular lighting with PerfectAccent high-efficacy reflectors

Applications

- Convenience stores
- Supermarkets & hypermarkets
- Large Retail formats

Features

- Easy optic replacement or upgrades that require no tools
- Available with PerfectAccent high-efficacy reflectors
- Optional front glass (advised in dusty environments)
- Up to 6000 lm output for high installation heights
- Available with fresh food LED lighting recipes and LED flavors
- Wired (DALI) and wireless connectivity options
- High intensity oval beam allows increased luminaire spacing when lighting fresh food counters or wordmarks on the wall

- All photometrical data is calculated without optional front glass. Flux should be reduced by 3.5% when using a front glass
- Cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden. For food preparation areas and areas with high levels of dust, the use of the optional front glass is strongly advised, as it can be cleaned with a (dry) microfiber cloth.
- During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove

Versions



StyliD Evo Compact HR



StyliD Evo Compact ST770B
white, semi recessed



StyliD Evo Compact HR for
maxos fusion



StyliD Evo Compact ST770B
black, semi recessed



StyliD Evo Compact ST770X
white, Maxos fusion
integrated



StyliD Evo Performance HR



StyliD Evo Compact ST770X
black, Maxos fusion
integrated



StyliD Evo Performance
ST780T white, track version



StyliD Evo Performance HR
for maxos fusion



StyliD Evo Performance
ST780S black, Maxos fusion
version



StyliD Evo Compact ST770T
silver, track version



StyliD Evo Compact HR



StyliD Evo Performance
ST780T silver, track version



StyliD Evo Compact ST770S
white, Maxos fusion version



StyliD Evo Compact HR



StyliD Evo Compact ST770S
silver, Maxos fusion version



StyliD Evo Compact HR



StyliD Evo Performance HR



StyliD Evo Compact HR for
maxos fusion



StyliD Evo Performance
ST780S white, Maxos fusion
version



StyliD Evo Compact ST770T
white, track version



StyliD Evo Compact ST770T
black, track version



StyliD Evo Compact HR



StyliD Evo Performance HR




StyliD Evo Compact HR for
maxos fusion




StyliD Evo Performance HR
for maxos fusion


Dimensional drawing




StyliD Evo Compact Maxos fusion - Power supply unit with DALI interface, Visual Light Communication (VLC) - ready (integrated)
- Medium-beam reflector high reflectance - 24°




STYLID EVO COMPACT MF INTEGRATED - Power supply unit with SystemReady interface, InterAct ready - Oval horizontal beam - 20° x 68°




StyliD Evo Compact - Power supply unit - Medium beam - 24°




StyliD Evo Performance - Power supply unit - Medium beam - 24° -




StyliD Evo Compact - 24°




StyliD Evo Compact Maxos fusion - Power supply unit with DALI interface, Visual Light Communication (VLC) - ready (integrated)
- Wide beam - 36°




StyliD Evo Compact - Power supply unit with DALI interface, Visual Light Communication (VLC) - ready (integrated) - Oval horizontal beam - 20° x 68°




StyliD Evo Performance Maxos fusion - Power supply unit with DALI interface, Visual Light Communication (VLC) - ready (integrated) - Very wide beam - 60°



StyliD Evo Semi Recessed - Power supply unit external - Medium beam - 24°



StyliD Evo Performance - Power supply unit with DALI interface, Visual Light Communication (VLC) - ready (integrated) - Oval horizontal beam - 20° x 68° -



StyliD Evo Compact - Power supply unit with DALI interface, Visual Light Communication (VLC) - ready (integrated) - Oval vertical beam - 20° x 68°


Product details



Aiming indication, with marking for Indoor Positioning operation



StyliD Evo Compact black, side view



StyliD Evo Compact ST770X Mounting interface



StyliD Evo Performance black, side view



OptiShield protects the optical compartment from bugs and dust



StyliD Evo Compact HR



Aiming indication, with marking for Indoor Positioning operation



StyliD Evo Compact white, side view



StyliD Evo ST770B semi recessed installation rim



OptiShield protects the optical compartment from bugs and dust



StyliD Evo Performance HR



StyliD Evo Compact HR



Aiming indication, with marking for Indoor Positioning operation



StyliD Evo Performance in black, full rotation flexibility



StyliD Evo Compact in white, full rotation flexibility



StyliD Evo Compact white, front view



OptiShield protects the optical compartment from bugs and dust



StyliD Evo Performance HR



StyliD Evo Compact HR black



StyliD Evo Performance HR



Aiming indication, with marking for Indoor Positioning operation



StyliD Evo Performance white, side view



StyliD Evo Compact black, front view



StyliD Evo Performance white, front view



StyliD Evo Performance black, front view



OptiShield protects the optical compartment from bugs and dust



StyliD Evo Performance HR



StyliD Evo Compact HR white



StyliD Evo Exploded View



StyliD Evo Compact in black, full rotation flexibility



StyliD Evo Performance in white, full rotation flexibility

General Information

Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Number of light sources	1
Beam angle of light source	120 degree(s)

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No

Controls and Dimming

Embedded control	Visible light communication
------------------	-----------------------------

Mechanical and Housing

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	-

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.5
Ambient temperature range	+10 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance +/-10%

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h 1 %

General Information

Order Code	Full Product Name	Lamp family code
910505100730	ST770T LED27S/PW930 PSU HMB SI	-
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	-
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	LED27S
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	LED39S
910505101207	ST770B 17S/830 PSU-E MB FG WH	-
910505101208	ST770B 20S/830 PSU-E NB FG WH	-
910505101212	ST770B 27S/830 PSU-E MB FG WH	-
910505101213	ST770B 27S/840 PSU-E VWB FG WH	-
910505101214	ST770B 27S/930 PSU-E MB FG WH	-
910505101215	ST770B 27S/CH PSU-E MB FG WH	-
910505101216	ST770B 27S/FMT PSU-E MB FG WH	-
910505101217	ST770B 27S/FR PSU-E MB FG WH	-
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	-
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	-
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	-
910505101221	ST770B 39S/827 PSU-E WB FG WH	-
910505101223	ST770B 39S/830 PSU-E MB FG WH	-
910505101224	ST770B 39S/840 PSU-E VWB FG WH	-
910505101368	ST770S 39S/930 DIA-VLC HWB BK	-
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	-
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	-
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	-
910505101410	ST770X 17S/830 DIA MB FG WH	-
910505101411	ST770X 20S/830 DIA NB FG WH	-
910505101412	ST770X 27S/827 DIA WB FG WH	-
910505101413	ST770X 27S/830 DIA MB FG WH	-
910505101414	ST770X 27S/840 DIA VWB FG WH	-
910505101415	ST770X 27S/930 DIA OVL-H WH	-
910505101416	ST770X 27S/CH DIA MB FG WH	-
910505101417	ST770X 27S/FMT DIA MB FG WH	-
910505101418	ST770X 27S/FR DIA MB FG WH	-

Order Code	Full Product Name	Lamp family code
910505101421	ST770X 27S/ROSE DIA MB FG WH	-
910505101422	ST770X 39S/830 DIA MB FG WH	-
910505101423	ST770X 39S/930 DIA OVL-H WH	-
910505100749	ST780T LED49S/827 PSU HWB SI FG	-
910505100756	ST780T 60S/827 PSU HWB FG SI	-
910505101419	ST770X 27S/PC930 DIA MB FG BK	-
910505101420	ST770X 27S/PW930 DIA MB FG BK	-
910505101434	ST780T 39S/827 PSU NB FG WH	-
910505101435	ST780T 39S/830 PSU NB FG WH	-
910505101436	ST780T 39S/840 PSU NB FG WH	-
910505101437	ST780T 39S/930 PSU NB FG WH	-
910505101438	ST780T 49S/827 PSU WB FG WH	-
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	-
910505101441	ST780T 49S/830 PSU MB FG WH	-
910505101442	ST780T 49S/840 PSU VWB FG WH	-
910505101446	ST780T 60S/830 PSU MB FG WH	-
910505101447	ST780T 60S/840 PSU MB FG WH	-
910505101431	ST780S 60S/827 DIA-VLC HWB BK	-
910505101432	ST780S 60S/830 DIA-VLC HMB BK	-
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	-
910505101386	ST770T 27S/930 PSU MB FG SI	-
910505101390	ST770T 27S/PC930 PSU MB FG SI	-
910505101392	ST770T 27S/PW930 PSU MB FG SI	-
910505100743	ST770T LED49S/830 PSU HMB SI	-
910505101443	ST780T 49S/930 PSU MB FG SI	-
910505101444	ST780T 49S/PW930 PSU MB FG SI	-
910505101445	ST780T 60S/827 PSU WB FG SI	-
910505101228	ST770S 17S/827 PSU WB FG WH	-
910505101229	ST770S 17S/830 PSU MB FG WH	-
910505101230	ST770S 17S/840 PSU VWB FG WH	-
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	-
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	-
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	-
910505101371	ST770S 39S/PW930 PSU VWB FG WH	-
910505100723	ST770T 20S/830 PSU HNB WH	-
910505100724	ST770T 27S/830 PSU HMB WH	-
910505100725	ST770T LED27S/827 PSU HWB WH	-
910505100736	ST770T 39S/830 PSU HMB WH	-
910505100737	ST770T LED39S/827 PSU HWB WH	-
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	-
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	-
910505102315	ST770T 27S/ROSE WIA WB FG WH	-

Order Code	Full Product Name	Lamp family code
910505102316	ST770T 39S/PW930 WIA WB WH	-
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	-
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	-
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	-
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	-
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	-
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	-
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	-
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	-
910505101425	ST780S 39S/827 PSU NB FG WH	-
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	-
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	-
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	-
910505101379	ST770T 20S/830 PSU NB FG WH	-
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	-
910505101381	ST770T 27S/827 PSU WB FG WH	-
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	-
910505101384	ST770T 27S/830 PSU MB FG WH	-
910505101385	ST770T 27S/840 PSU VWB FG WH	-
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	-
910505101395	ST770T 39S/827 PSU WB FG WH	-
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	-
910505101398	ST770T 39S/830 PSU MB FG WH	-
910505101399	ST770T 39S/840 PSU MB FG WH	-
910505101378	ST770T 17S/930 PSU MB FG BK	-
910505101387	ST770T 27S/CH PSU MB FG BK	-
910505101388	ST770T 27S/FMT PSU MB FG BK	-
910505101389	ST770T 27S/FR PSU MB FG BK	-
910505101393	ST770T 27S/ROSE PSU MB FG BK	-
910505101401	ST770T 39S/930 PSU MB FG BK	-
910505101402	ST770T 39S/PC930 PSU MB FG BK	-
910505101403	ST770T 39S/PW930 PSU MB FG BK	-
910505100722	ST770T LED17S/930 PSU HMB BK	-
910505100731	ST770T LED27S/CH PSU HMB BK FG	-
910505100732	ST770T 27S/FR PSU HMB FG BK	-
910505100733	ST770T 27S/FMT PSU HMB FG BK	-
910505100747	ST780T 39S/830 PSU HNB WH	-
910505100748	ST780T 49S/830 PSU HMB WH	-
910505100755	ST780T LED60S/830 PSU HMB WH	-
910505100721	ST770S LED17S/830 PSU HMB WH FG	-
910505101429	ST780S 49S/930 DIA-VLC HWB WH	-
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	-

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)	Optic type
910505100730	ST770T LED27S/PW930 PSU HMB SI	2,700 lm	3000 K	138 lm/W	>90	High-reflective metal reflector Medium beam 20 to 40 degrees
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	3,900 lm	3000 K	142 lm/W	>80	High-reflective metal reflector Oval - Horizontal beam
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	2,700 lm	3000 K	136 lm/W	>80	Oval horizontal beam
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	3,900 lm	3000 K	127 lm/W	>90	Oval horizontal beam
910505101207	ST770B 17S/830 PSU-E MB FG WH	1,700 lm	3000 K	144 lm/W	>80	Medium beam
910505101208	ST770B 20S/830 PSU-E NB FG WH	2,000 lm	3000 K	120 lm/W	>80	Narrow beam
910505101212	ST770B 27S/830 PSU-E MB FG WH	2,700 lm	3000 K	136 lm/W	>80	Medium beam
910505101213	ST770B 27S/840 PSU-E VWB FG WH	2,700 lm	4000 K	142 lm/W	>80	Very wide beam
910505101214	ST770B 27S/930 PSU-E MB FG WH	2,700 lm	3000 K	132 lm/W	>90	Medium beam
910505101215	ST770B 27S/CH PSU-E MB FG WH	2,700 lm	2700 K	130 lm/W	>80	Medium beam
910505101216	ST770B 27S/FMT PSU-E MB FG WH	2,700 lm	3000 K	78 lm/W	>90	Medium beam
910505101217	ST770B 27S/FR PSU-E MB FG WH	3,000 lm	5000 K	94 lm/W	>90	Medium beam
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	2,700 lm	3000 K	114 lm/W	>90	Medium beam
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	2,700 lm	3000 K	134 lm/W	>90	Medium beam
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	2,800 lm	2200 K	90 lm/W	>80	Medium beam
910505101221	ST770B 39S/827 PSU-E WB FG WH	3,900 lm	2700 K	132 lm/W	>80	Wide beam
910505101223	ST770B 39S/830 PSU-E MB FG WH	3,900 lm	3000 K	142 lm/W	>80	Medium beam
910505101224	ST770B 39S/840 PSU-E VWB FG WH	3,900 lm	4000 K	147 lm/W	>80	Very wide beam
910505101368	ST770S 39S/930 DIA-VLC HWB BK	3,900 lm	3000 K	129 lm/W	>90	High-reflective metal reflector Wide beam 40 to 80 degrees
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	2,700 lm	2700 K	125 lm/W	>80	Wide beam
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	2,700 lm	3000 K	131 lm/W	>80	Medium beam
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	2,700 lm	3000 K	131 lm/W	>80	Oval horizontal beam
910505101410	ST770X 17S/830 DIA MB FG WH	1,700 lm	3000 K	144 lm/W	>80	Medium beam
910505101411	ST770X 20S/830 DIA NB FG WH	2,000 lm	3000 K	121 lm/W	>80	Narrow beam
910505101412	ST770X 27S/827 DIA WB FG WH	2,700 lm	2700 K	130 lm/W	>80	Wide beam
910505101413	ST770X 27S/830 DIA MB FG WH	2,700 lm	3000 K	136 lm/W	>80	Medium beam
910505101414	ST770X 27S/840 DIA VWB FG WH	2,700 lm	4000 K	142 lm/W	>80	Very wide beam
910505101415	ST770X 27S/930 DIA OVL-H WH	2,700 lm	3000 K	133 lm/W	>90	Oval horizontal beam
910505101416	ST770X 27S/CH DIA MB FG WH	2,700 lm	2700 K	131 lm/W	>80	Medium beam
910505101417	ST770X 27S/FMT DIA MB FG WH	2,700 lm	3000 K	81 lm/W	>90	Medium beam
910505101418	ST770X 27S/FR DIA MB FG WH	3,000 lm	5000 K	95 lm/W	>90	Medium beam
910505101421	ST770X 27S/ROSE DIA MB FG WH	2,800 lm	2200 K	96 lm/W	>80	Medium beam
910505101422	ST770X 39S/830 DIA MB FG WH	3,900 lm	3000 K	142 lm/W	>80	Medium beam
910505101423	ST770X 39S/930 DIA OVL-H WH	3,900 lm	3000 K	128 lm/W	>90	Oval horizontal beam
910505100749	ST780T LED49S/827 PSU HWB SI FG	4,900 lm	2700 K	133 lm/W	>80	High-reflective metal reflector Wide beam 40 to 80 degrees

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)	Optic type
910505100756	ST780T 60S/827 PSU HWB FG SI	6,000 lm	2700 K	138 lm/W	>80	High-reflective metal reflector Wide beam 40 to 80 degrees
910505101419	ST770X 27S/PC930 DIA MB FG BK	2,700 lm	3000 K	116 lm/W	>90	Medium beam
910505101420	ST770X 27S/PW930 DIA MB FG BK	2,700 lm	3000 K	134 lm/W	>90	Medium beam
910505101434	ST780T 39S/827 PSU NB FG WH	3,900 lm	2700 K	133 lm/W	>80	Narrow beam
910505101435	ST780T 39S/830 PSU NB FG WH	3,900 lm	3000 K	139 lm/W	>80	Narrow beam
910505101436	ST780T 39S/840 PSU NB FG WH	3,900 lm	4000 K	144 lm/W	>80	Narrow beam
910505101437	ST780T 39S/930 PSU NB FG WH	3,900 lm	3000 K	131 lm/W	>90	Narrow beam
910505101438	ST780T 49S/827 PSU WB FG WH	4,900 lm	2700 K	139 lm/W	>80	Wide beam
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	4,900 lm	3000 K	128 lm/W	>80	Oval horizontal beam
910505101441	ST780T 49S/830 PSU MB FG WH	4,900 lm	3000 K	139 lm/W	>80	Medium beam
910505101442	ST780T 49S/840 PSU VWB FG WH	4,900 lm	4000 K	139 lm/W	>80	Very wide beam
910505101446	ST780T 60S/830 PSU MB FG WH	6,000 lm	3000 K	135 lm/W	>80	Medium beam
910505101447	ST780T 60S/840 PSU MB FG WH	6,000 lm	4000 K	152 lm/W	>80	Medium beam
910505101431	ST780S 60S/827 DIA-VLC HWB BK	6,000 lm	2700 K	135 lm/W	>80	High-reflective metal reflector Wide beam 40 to 80 degrees
910505101432	ST780S 60S/830 DIA-VLC HMB BK	6,000 lm	3000 K	139 lm/W	>80	High-reflective metal reflector Medium beam 20 to 40 degrees
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	6,000 lm	4000 K	146 lm/W	>80	Very wide beam
910505101386	ST770T 27S/930 PSU MB FG SI	2,700 lm	3000 K	132 lm/W	>90	Medium beam
910505101390	ST770T 27S/PC930 PSU MB FG SI	2,700 lm	3000 K	114 lm/W	>90	Medium beam
910505101392	ST770T 27S/PW930 PSU MB FG SI	2,700 lm	3000 K	134 lm/W	>90	Medium beam
910505100743	ST770T LED49S/830 PSU HMB SI	4,900 lm	3000 K	139 lm/W	>80	High-reflective metal reflector Medium beam 20 to 40 degrees
910505101443	ST780T 49S/930 PSU MB FG SI	4,900 lm	3000 K	132 lm/W	>90	Medium beam
910505101444	ST780T 49S/PW930 PSU MB FG SI	4,900 lm	3000 K	132 lm/W	>90	Medium beam
910505101445	ST780T 60S/827 PSU WB FG SI	6,000 lm	2700 K	138 lm/W	>80	Wide beam
910505101228	ST770S 17S/827 PSU WB FG WH	1,700 lm	2700 K	138 lm/W	>80	Wide beam
910505101229	ST770S 17S/830 PSU MB FG WH	1,700 lm	3000 K	144 lm/W	>80	Medium beam
910505101230	ST770S 17S/840 PSU VWB FG WH	1,700 lm	4000 K	150 lm/W	>80	Very wide beam
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	2,700 lm	2700 K	125 lm/W	>80	Wide beam
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	2,700 lm	3000 K	131 lm/W	>80	Medium beam
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	2,700 lm	4000 K	136 lm/W	>80	Very wide beam
910505101371	ST770S 39S/PW930 PSU VWB FG WH	3,900 lm	3000 K	130 lm/W	>90	Very wide beam
910505100723	ST770T 20S/830 PSU HNB WH	2,000 lm	3000 K	124 lm/W	>80	High-reflective metal reflector Narrow beam 10 to 20 degrees
910505100724	ST770T 27S/830 PSU HMB WH	2,700 lm	3000 K	141 lm/W	>80	High-reflective metal reflector Medium beam 20 to 40 degrees

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)	Optic type
910505100725	ST770T LED27S/827 PSU HWB WH	2,700 lm	2700 K	135 lm/W	>80	High-reflective metal reflector Wide beam 40 to 80 degrees
910505100736	ST770T 39S/830 PSU HMB WH	3,900 lm	3000 K	146 lm/W	>80	High-reflective metal reflector Medium beam 20 to 40 degrees
910505100737	ST770T LED39S/827 PSU HWB WH	3,900 lm	2700 K	139 lm/W	>80	High-reflective metal reflector Wide beam 40 to 80 degrees
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	2,700 lm	3000 K	133 lm/W	>80	High-reflective metal reflector Oval - Horizontal beam
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	2,700 lm	3000 K	130 lm/W	>90	High-reflective metal reflector Medium beam 20 to 40 degrees
910505102315	ST770T 27S/ROSE WIA WB FG WH	2,800 lm	2200 K	93 lm/W	>80	Wide beam
910505102316	ST770T 39S/PW930 WIA WB WH	3,900 lm	3000 K	127 lm/W	>90	Wide beam
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	3,900 lm	2700 K	129 lm/W	>80	Wide beam
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	3,900 lm	3000 K	138 lm/W	>80	Medium beam
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	3,900 lm	4000 K	142 lm/W	>80	Very wide beam
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	4,900 lm	3000 K	133 lm/W	>80	High-reflective metal reflector Oval - Vertical beam
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	4,900 lm	3000 K	133 lm/W	>80	High-reflective metal reflector Oval - Horizontal beam
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	3,900 lm	3000 K	116 lm/W	>90	High-reflective metal reflector very wide beam >80 degrees
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	4,000 lm	3000 K	134 lm/W	>90	High-reflective metal reflector very wide beam >80 degrees
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	4,900 lm	3000 K	132 lm/W	>90	High-reflective metal reflector Medium beam 20 to 40 degrees
910505101425	ST780S 39S/827 PSU NB FG WH	3,900 lm	2700 K	133 lm/W	>80	Narrow beam
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	4,900 lm	2700 K	133 lm/W	>80	Wide beam
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	4,900 lm	3000 K	128 lm/W	>80	Medium beam
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	4,900 lm	4000 K	133 lm/W	>80	Very wide beam
910505101379	ST770T 20S/830 PSU NB FG WH	2,000 lm	3000 K	120 lm/W	>80	Narrow beam
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	2,700 lm	2700 K	125 lm/W	>80	Oval vertical beam
910505101381	ST770T 27S/827 PSU WB FG WH	2,700 lm	2700 K	131 lm/W	>80	Wide beam
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	2,700 lm	3000 K	131 lm/W	>80	Oval horizontal beam
910505101384	ST770T 27S/830 PSU MB FG WH	2,700 lm	3000 K	136 lm/W	>80	Medium beam
910505101385	ST770T 27S/840 PSU VWB FG WH	2,700 lm	4000 K	142 lm/W	>80	Very wide beam
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	3,900 lm	2700 K	129 lm/W	>80	Oval vertical beam
910505101395	ST770T 39S/827 PSU WB FG WH	3,900 lm	2700 K	132 lm/W	>80	Wide beam
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	3,900 lm	3000 K	138 lm/W	>80	Oval horizontal beam
910505101398	ST770T 39S/830 PSU MB FG WH	3,900 lm	3000 K	142 lm/W	>80	Medium beam
910505101399	ST770T 39S/840 PSU MB FG WH	3,900 lm	4000 K	147 lm/W	>80	Medium beam
910505101378	ST770T 17S/930 PSU MB FG BK	1,700 lm	3000 K	135 lm/W	>90	Medium beam
910505101387	ST770T 27S/CH PSU MB FG BK	2,700 lm	2700 K	131 lm/W	>80	Medium beam

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)	Optic type
910505101388	ST770T 27S/FMT PSU MB FG BK	2,700 lm	3000 K	78 lm/W	>90	Medium beam
910505101389	ST770T 27S/FR PSU MB FG BK	3,000 lm	5000 K	94 lm/W	>90	Medium beam
910505101393	ST770T 27S/ROSE PSU MB FG BK	2,800 lm	2200 K	90 lm/W	>80	Medium beam
910505101401	ST770T 39S/930 PSU MB FG BK	3,900 lm	3000 K	127 lm/W	>90	Medium beam
910505101402	ST770T 39S/PC930 PSU MB FG BK	3,900 lm	3000 K	115 lm/W	>90	Medium beam
910505101403	ST770T 39S/PW930 PSU MB FG BK	3,900 lm	3000 K	130 lm/W	>90	Medium beam
910505100722	ST770T LED17S/930 PSU HMB BK	1,700 lm	3000 K	135 lm/W	>90	High-reflective metal reflector Medium beam 20 to 40 degrees
910505100731	ST770T LED27S/CH PSU HMB BK FG	2,700 lm	2700 K	135 lm/W	>80	High-reflective metal reflector Medium beam 20 to 40 degrees
910505100732	ST770T 27S/FR PSU HMB FG BK	2,700 lm	5000 K	98 lm/W	>90	High-reflective metal reflector Medium beam 20 to 40 degrees
910505100733	ST770T 27S/FMT PSU HMB FG BK	2,700 lm	3000 K	81 lm/W	>90	High-reflective metal reflector Medium beam 20 to 40 degrees
910505100747	ST780T 39S/830 PSU HNB WH	3,900 lm	3000 K	143 lm/W	>80	High-reflective metal reflector Narrow beam 10 to 20 degrees
910505100748	ST780T 49S/830 PSU HMB WH	4,900 lm	3000 K	139 lm/W	>80	High-reflective metal reflector Medium beam 20 to 40 degrees
910505100755	ST780T LED60S/830 PSU HMB WH	6,000 lm	3000 K	143 lm/W	>80	High-reflective metal reflector Medium beam 20 to 40 degrees
910505100721	ST770S LED17S/830 PSU HMB WH FG	1,700 lm	3000 K	149 lm/W	>80	High-reflective metal reflector Medium beam 20 to 40 degrees
910505101429	ST780S 49S/930 DIA-VLC HWB WH	4,900 lm	3000 K	137 lm/W	>90	High-reflective metal reflector Wide beam 40 to 80 degrees
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	4,900 lm	3000 K	132 lm/W	>90	High-reflective metal reflector Medium beam 20 to 40 degrees

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Protection class IEC
910505100730	ST770T LED27S/PW930 PSU HMB SI	19.8 W	Safety class II
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	29.5 W	Safety class II
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	19.6 W	Safety class II
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	31 W	Safety class II
910505101207	ST770B 17S/830 PSU-E MB FG WH	11.8 W	Safety class II
910505101208	ST770B 20S/830 PSU-E NB FG WH	16.6 W	Safety class II
910505101212	ST770B 27S/830 PSU-E MB FG WH	19.6 W	Safety class II
910505101213	ST770B 27S/840 PSU-E VWB FG WH	19.6 W	Safety class II
910505101214	ST770B 27S/930 PSU-E MB FG WH	19.8 W	Safety class II

Order Code	Full Product Name	Power Consumption	Protection class IEC
910505101215	ST770B 27S/CH PSU-E MB FG WH	19.8 W	Safety class II
910505101216	ST770B 27S/FMT PSU-E MB FG WH	35 W	Safety class II
910505101217	ST770B 27S/FR PSU-E MB FG WH	32.5 W	Safety class II
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	24.5 W	Safety class II
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	19.8 W	Safety class II
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	31 W	Safety class II
910505101221	ST770B 39S/827 PSU-E WB FG WH	31 W	Safety class II
910505101223	ST770B 39S/830 PSU-E MB FG WH	29 W	Safety class II
910505101224	ST770B 39S/840 PSU-E VWB FG WH	29 W	Safety class II
910505101368	ST770S 39S/930 DIA-VLC HWB BK	31.5 W	Safety class II
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	20.5 W	Safety class II
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	20.5 W	Safety class II
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	20.5 W	Safety class II
910505101410	ST770X 17S/830 DIA MB FG WH	11.8 W	Safety class I
910505101411	ST770X 20S/830 DIA NB FG WH	16.4 W	Safety class I
910505101412	ST770X 27S/827 DIA WB FG WH	19.6 W	Safety class I
910505101413	ST770X 27S/830 DIA MB FG WH	19.6 W	Safety class I
910505101414	ST770X 27S/840 DIA VWB FG WH	19.6 W	Safety class I
910505101415	ST770X 27S/930 DIA OVL-H WH	19.8 W	Safety class I
910505101416	ST770X 27S/CH DIA MB FG WH	19.6 W	Safety class I
910505101417	ST770X 27S/FMT DIA MB FG WH	34 W	Safety class I
910505101418	ST770X 27S/FR DIA MB FG WH	32 W	Safety class I
910505101421	ST770X 27S/ROSE DIA MB FG WH	29 W	Safety class I
910505101422	ST770X 39S/830 DIA MB FG WH	29 W	Safety class I
910505101423	ST770X 39S/930 DIA OVL-H WH	30.5 W	Safety class I
910505100749	ST780T LED49S/827 PSU HWB SI FG	37.5 W	Safety class II
910505100756	ST780T 60S/827 PSU HWB FG SI	44 W	Safety class II
910505101419	ST770X 27S/PC930 DIA MB FG BK	24 W	Safety class I
910505101420	ST770X 27S/PW930 DIA MB FG BK	19.8 W	Safety class I
910505101434	ST780T 39S/827 PSU NB FG WH	29 W	Safety class II
910505101435	ST780T 39S/830 PSU NB FG WH	29 W	Safety class II
910505101436	ST780T 39S/840 PSU NB FG WH	27 W	Safety class II
910505101437	ST780T 39S/930 PSU NB FG WH	29 W	Safety class II
910505101438	ST780T 49S/827 PSU WB FG WH	37.5 W	Safety class II
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	39 W	Safety class II
910505101441	ST780T 49S/830 PSU MB FG WH	37.5 W	Safety class II
910505101442	ST780T 49S/840 PSU VWB FG WH	37.5 W	Safety class II
910505101446	ST780T 60S/830 PSU MB FG WH	46 W	Safety class II
910505101447	ST780T 60S/840 PSU MB FG WH	39.5 W	Safety class II
910505101431	ST780S 60S/827 DIA-VLC HWB BK	45 W	Safety class II
910505101432	ST780S 60S/830 DIA-VLC HMB BK	45 W	Safety class II
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	41 W	Safety class II

Order Code	Full Product Name	Power Consumption	Protection class IEC
910505101386	ST770T 27S/930 PSU MB FG SI	19.8 W	Safety class II
910505101390	ST770T 27S/PC930 PSU MB FG SI	24.5 W	Safety class II
910505101392	ST770T 27S/PW930 PSU MB FG SI	19.8 W	Safety class II
910505100743	ST770T LED49S/830 PSU HMB SI	37.5 W	Safety class II
910505101443	ST780T 49S/930 PSU MB FG SI	38 W	Safety class II
910505101444	ST780T 49S/PW930 PSU MB FG SI	38 W	Safety class II
910505101445	ST780T 60S/827 PSU WB FG SI	46 W	Safety class II
910505101228	ST770S 17S/827 PSU WB FG WH	11.8 W	Safety class II
910505101229	ST770S 17S/830 PSU MB FG WH	11.8 W	Safety class II
910505101230	ST770S 17S/840 PSU VWB FG WH	11.8 W	Safety class II
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	20.5 W	Safety class II
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	20.5 W	Safety class II
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	20.5 W	Safety class II
910505101371	ST770S 39S/PW930 PSU VWB FG WH	31 W	Safety class II
910505100723	ST770T 20S/830 PSU HNB WH	16.6 W	Safety class II
910505100724	ST770T 27S/830 PSU HMB WH	19.6 W	Safety class II
910505100725	ST770T LED27S/827 PSU HWB WH	19.6 W	Safety class II
910505100736	ST770T 39S/830 PSU HMB WH	29 W	Safety class II
910505100737	ST770T LED39S/827 PSU HWB WH	29 W	Safety class II
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	20.5 W	Safety class II
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	20.5 W	Safety class II
910505102315	ST770T 27S/ROSE WIA WB FG WH	30 W	Safety class II
910505102316	ST770T 39S/PW930 WIA WB WH	32 W	Safety class II
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	31.5 W	Safety class II
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	29.5 W	Safety class II
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	29.5 W	Safety class II
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	39 W	Safety class II
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	39 W	Safety class II
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	35.5 W	Safety class II
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	29.5 W	Safety class II
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	39.5 W	Safety class II
910505101425	ST780S 39S/827 PSU NB FG WH	29 W	Safety class II
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	39 W	Safety class II
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	39 W	Safety class II
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	39 W	Safety class II
910505101379	ST770T 20S/830 PSU NB FG WH	16.6 W	Safety class II
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	20.5 W	Safety class II
910505101381	ST770T 27S/827 PSU WB FG WH	19.6 W	Safety class II
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	20.5 W	Safety class II
910505101384	ST770T 27S/830 PSU MB FG WH	19.6 W	Safety class II
910505101385	ST770T 27S/840 PSU VWB FG WH	19.6 W	Safety class II
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	31.5 W	Safety class II

Order Code	Full Product Name	Power Consumption	Protection class IEC
910505101395	ST770T 39S/827 PSU WB FG WH	31 W	Safety class II
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	29.5 W	Safety class II
910505101398	ST770T 39S/830 PSU MB FG WH	29 W	Safety class II
910505101399	ST770T 39S/840 PSU MB FG WH	29 W	Safety class II
910505101378	ST770T 17S/930 PSU MB FG BK	11.8 W	Safety class II
910505101387	ST770T 27S/CH PSU MB FG BK	19.6 W	Safety class II
910505101388	ST770T 27S/FMT PSU MB FG BK	35 W	Safety class II
910505101389	ST770T 27S/FR PSU MB FG BK	32.5 W	Safety class II
910505101393	ST770T 27S/ROSE PSU MB FG BK	31 W	Safety class II
910505101401	ST770T 39S/930 PSU MB FG BK	31 W	Safety class II
910505101402	ST770T 39S/PC930 PSU MB FG BK	35 W	Safety class II
910505101403	ST770T 39S/PW930 PSU MB FG BK	31 W	Safety class II
910505100722	ST770T LED17S/930 PSU HMB BK	11.8 W	Safety class II
910505100731	ST770T LED27S/CH PSU HMB BK FG	19.6 W	Safety class II
910505100732	ST770T 27S/FR PSU HMB FG BK	28.5 W	Safety class II
910505100733	ST770T 27S/FMT PSU HMB FG BK	35 W	Safety class II
910505100747	ST780T 39S/830 PSU HNB WH	27 W	Safety class II
910505100748	ST780T 49S/830 PSU HMB WH	37.5 W	Safety class II
910505100755	ST780T LED60S/830 PSU HMB WH	44 W	Safety class II
910505100721	ST770S LED17S/830 PSU HMB WH FG	11.8 W	Safety class II
910505101429	ST780S 49S/930 DIA-VLC HWB WH	39.5 W	Safety class II
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	39.5 W	Safety class II

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
910505100730	ST770T LED27S/PW930 PSU HMB SI	No	Not applicable
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	Yes	1%
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	No	-
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	No	-
910505101207	ST770B 17S/830 PSU-E MB FG WH	No	Not applicable
910505101208	ST770B 20S/830 PSU-E NB FG WH	No	Not applicable
910505101212	ST770B 27S/830 PSU-E MB FG WH	No	Not applicable
910505101213	ST770B 27S/840 PSU-E VWB FG WH	No	Not applicable
910505101214	ST770B 27S/930 PSU-E MB FG WH	No	Not applicable
910505101215	ST770B 27S/CH PSU-E MB FG WH	No	Not applicable
910505101216	ST770B 27S/FMT PSU-E MB FG WH	No	Not applicable
910505101217	ST770B 27S/FR PSU-E MB FG WH	No	Not applicable
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	No	Not applicable
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	No	Not applicable
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	No	Not applicable
910505101221	ST770B 39S/827 PSU-E WB FG WH	No	Not applicable
910505101223	ST770B 39S/830 PSU-E MB FG WH	No	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
910505101224	ST770B 39S/840 PSU-E VWB FG WH	No	Not applicable
910505101368	ST770S 39S/930 DIA-VLC HWB BK	Yes	1%
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	Yes	1%
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	Yes	1%
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	Yes	1%
910505101410	ST770X 17S/830 DIA MB FG WH	Yes	1%
910505101411	ST770X 20S/830 DIA NB FG WH	Yes	1%
910505101412	ST770X 27S/827 DIA WB FG WH	Yes	1%
910505101413	ST770X 27S/830 DIA MB FG WH	Yes	1%
910505101414	ST770X 27S/840 DIA VWB FG WH	Yes	1%
910505101415	ST770X 27S/930 DIA OVL-H WH	Yes	1%
910505101416	ST770X 27S/CH DIA MB FG WH	Yes	1%
910505101417	ST770X 27S/FMT DIA MB FG WH	Yes	1%
910505101418	ST770X 27S/FR DIA MB FG WH	Yes	1%
910505101421	ST770X 27S/ROSE DIA MB FG WH	Yes	1%
910505101422	ST770X 39S/830 DIA MB FG WH	Yes	1%
910505101423	ST770X 39S/930 DIA OVL-H WH	Yes	1%
910505100749	ST780T LED49S/827 PSU HWB SI FG	No	Not applicable
910505100756	ST780T 60S/827 PSU HWB FG SI	No	Not applicable
910505101419	ST770X 27S/PC930 DIA MB FG BK	Yes	1%
910505101420	ST770X 27S/PW930 DIA MB FG BK	Yes	1%
910505101434	ST780T 39S/827 PSU NB FG WH	No	Not applicable
910505101435	ST780T 39S/830 PSU NB FG WH	No	Not applicable
910505101436	ST780T 39S/840 PSU NB FG WH	No	Not applicable
910505101437	ST780T 39S/930 PSU NB FG WH	No	Not applicable
910505101438	ST780T 49S/827 PSU WB FG WH	No	Not applicable
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	Yes	1%
910505101441	ST780T 49S/830 PSU MB FG WH	No	Not applicable
910505101442	ST780T 49S/840 PSU VWB FG WH	No	Not applicable
910505101446	ST780T 60S/830 PSU MB FG WH	No	Not applicable
910505101447	ST780T 60S/840 PSU MB FG WH	No	Not applicable
910505101431	ST780S 60S/827 DIA-VLC HWB BK	Yes	1%
910505101432	ST780S 60S/830 DIA-VLC HMB BK	Yes	1%
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	Yes	1%
910505101386	ST770T 27S/930 PSU MB FG SI	No	Not applicable
910505101390	ST770T 27S/PC930 PSU MB FG SI	No	Not applicable
910505101392	ST770T 27S/PW930 PSU MB FG SI	No	Not applicable
910505100743	ST770T LED49S/830 PSU HMB SI	No	Not applicable
910505101443	ST780T 49S/930 PSU MB FG SI	No	Not applicable
910505101444	ST780T 49S/PW930 PSU MB FG SI	No	Not applicable
910505101445	ST780T 60S/827 PSU WB FG SI	No	Not applicable
910505101228	ST770S 17S/827 PSU WB FG WH	No	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
910505101229	ST770S 17S/830 PSU MB FG WH	No	Not applicable
910505101230	ST770S 17S/840 PSU VWB FG WH	No	Not applicable
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	Yes	1%
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	Yes	1%
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	Yes	1%
910505101371	ST770S 39S/PW930 PSU VWB FG WH	No	Not applicable
910505100723	ST770T 20S/830 PSU HNB WH	No	Not applicable
910505100724	ST770T 27S/830 PSU HMB WH	No	Not applicable
910505100725	ST770T LED27S/827 PSU HWB WH	No	Not applicable
910505100736	ST770T 39S/830 PSU HMB WH	No	Not applicable
910505100737	ST770T LED39S/827 PSU HWB WH	No	Not applicable
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	Yes	1%
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	Yes	1%
910505102315	ST770T 27S/ROSE WIA WB FG WH	Yes	Not applicable
910505102316	ST770T 39S/PW930 WIA WB WH	Yes	Not applicable
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	Yes	1%
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	Yes	1%
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	Yes	1%
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	Yes	1%
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	Yes	1%
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	Yes	1%
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	Yes	1%
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	Yes	1%
910505101425	ST780S 39S/827 PSU NB FG WH	No	Not applicable
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	Yes	1%
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	Yes	1%
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	Yes	1%
910505101379	ST770T 20S/830 PSU NB FG WH	No	Not applicable
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	Yes	1%
910505101381	ST770T 27S/827 PSU WB FG WH	No	Not applicable
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	Yes	1%
910505101384	ST770T 27S/830 PSU MB FG WH	No	Not applicable
910505101385	ST770T 27S/840 PSU VWB FG WH	No	Not applicable
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	Yes	1%
910505101395	ST770T 39S/827 PSU WB FG WH	No	Not applicable
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	Yes	1%
910505101398	ST770T 39S/830 PSU MB FG WH	No	Not applicable
910505101399	ST770T 39S/840 PSU MB FG WH	No	Not applicable
910505101378	ST770T 17S/930 PSU MB FG BK	No	Not applicable
910505101387	ST770T 27S/CH PSU MB FG BK	No	Not applicable
910505101388	ST770T 27S/FMT PSU MB FG BK	No	Not applicable
910505101389	ST770T 27S/FR PSU MB FG BK	No	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
910505101393	ST770T 27S/ROSE PSU MB FG BK	No	Not applicable
910505101401	ST770T 39S/930 PSU MB FG BK	No	Not applicable
910505101402	ST770T 39S/PC930 PSU MB FG BK	No	Not applicable
910505101403	ST770T 39S/PW930 PSU MB FG BK	No	Not applicable
910505100722	ST770T LED17S/930 PSU HMB BK	No	Not applicable
910505100731	ST770T LED27S/CH PSU HMB BK FG	No	Not applicable
910505100732	ST770T 27S/FR PSU HMB FG BK	No	Not applicable
910505100733	ST770T 27S/FMT PSU HMB FG BK	No	Not applicable
910505100747	ST780T 39S/830 PSU HNB WH	No	Not applicable
910505100748	ST780T 49S/830 PSU HMB WH	No	Not applicable
910505100755	ST780T LED60S/830 PSU HMB WH	No	Not applicable
910505100721	ST770S LED17S/830 PSU HMB WH FG	No	Not applicable
910505101429	ST780S 49S/930 DIA-VLC HWB WH	Yes	1%
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	Yes	1%

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910505100730	ST770T LED27S/PW930 PSU HMB SI	Silver
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	Silver
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	White
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	White
910505101207	ST770B 17S/830 PSU-E MB FG WH	White
910505101208	ST770B 20S/830 PSU-E NB FG WH	White
910505101212	ST770B 27S/830 PSU-E MB FG WH	White
910505101213	ST770B 27S/840 PSU-E VWB FG WH	White
910505101214	ST770B 27S/930 PSU-E MB FG WH	White
910505101215	ST770B 27S/CH PSU-E MB FG WH	White
910505101216	ST770B 27S/FMT PSU-E MB FG WH	White
910505101217	ST770B 27S/FR PSU-E MB FG WH	White
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	White
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	White
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	White
910505101221	ST770B 39S/827 PSU-E WB FG WH	White
910505101223	ST770B 39S/830 PSU-E MB FG WH	White
910505101224	ST770B 39S/840 PSU-E VWB FG WH	White
910505101368	ST770S 39S/930 DIA-VLC HWB BK	Black
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	Black
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	Black
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	Black
910505101410	ST770X 17S/830 DIA MB FG WH	White
910505101411	ST770X 20S/830 DIA NB FG WH	White
910505101412	ST770X 27S/827 DIA WB FG WH	White

Order Code	Full Product Name	Housing Color
910505101413	ST770X 27S/830 DIA MB FG WH	White
910505101414	ST770X 27S/840 DIA VWB FG WH	White
910505101415	ST770X 27S/930 DIA OVL-H WH	White
910505101416	ST770X 27S/CH DIA MB FG WH	White
910505101417	ST770X 27S/FMT DIA MB FG WH	White
910505101418	ST770X 27S/FR DIA MB FG WH	White
910505101421	ST770X 27S/ROSE DIA MB FG WH	White
910505101422	ST770X 39S/830 DIA MB FG WH	White
910505101423	ST770X 39S/930 DIA OVL-H WH	White
910505100749	ST780T LED49S/827 PSU HWB SI FG	Silver
910505100756	ST780T 60S/827 PSU HWB FG SI	Silver
910505101419	ST770X 27S/PC930 DIA MB FG BK	Black
910505101420	ST770X 27S/PW930 DIA MB FG BK	Black
910505101434	ST780T 39S/827 PSU NB FG WH	White
910505101435	ST780T 39S/830 PSU NB FG WH	White
910505101436	ST780T 39S/840 PSU NB FG WH	White
910505101437	ST780T 39S/930 PSU NB FG WH	White
910505101438	ST780T 49S/827 PSU WB FG WH	White
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	White
910505101441	ST780T 49S/830 PSU MB FG WH	White
910505101442	ST780T 49S/840 PSU VWB FG WH	White
910505101446	ST780T 60S/830 PSU MB FG WH	White
910505101447	ST780T 60S/840 PSU MB FG WH	White
910505101431	ST780S 60S/827 DIA-VLC HWB BK	Black
910505101432	ST780S 60S/830 DIA-VLC HMB BK	Black
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	Black
910505101386	ST770T 27S/930 PSU MB FG SI	Silver
910505101390	ST770T 27S/PC930 PSU MB FG SI	Silver
910505101392	ST770T 27S/PW930 PSU MB FG SI	Silver
910505100743	ST770T LED49S/830 PSU HMB SI	Silver
910505101443	ST780T 49S/930 PSU MB FG SI	Silver
910505101444	ST780T 49S/PW930 PSU MB FG SI	Silver
910505101445	ST780T 60S/827 PSU WB FG SI	Silver
910505101228	ST770S 17S/827 PSU WB FG WH	White
910505101229	ST770S 17S/830 PSU MB FG WH	White
910505101230	ST770S 17S/840 PSU VWB FG WH	White
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	White
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	White
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	White
910505101371	ST770S 39S/PW930 PSU VWB FG WH	White
910505100723	ST770T 20S/830 PSU HNB WH	White
910505100724	ST770T 27S/830 PSU HMB WH	White

Order Code	Full Product Name	Housing Color
910505100725	ST770T LED27S/827 PSU HWB WH	White
910505100736	ST770T 39S/830 PSU HMB WH	White
910505100737	ST770T LED39S/827 PSU HWB WH	White
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	White
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	White
910505102315	ST770T 27S/ROSE WIA WB FG WH	Black
910505102316	ST770T 39S/PW930 WIA WB WH	Black
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	Silver
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	Silver
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	Silver
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	White
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	Black
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	Black
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	Black
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	White
910505101425	ST780S 39S/827 PSU NB FG WH	White
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	White
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	White
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	White
910505101379	ST770T 20S/830 PSU NB FG WH	White
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	White
910505101381	ST770T 27S/827 PSU WB FG WH	White
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	White
910505101384	ST770T 27S/830 PSU MB FG WH	White
910505101385	ST770T 27S/840 PSU VWB FG WH	White
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	White
910505101395	ST770T 39S/827 PSU WB FG WH	White
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	White
910505101398	ST770T 39S/830 PSU MB FG WH	White
910505101399	ST770T 39S/840 PSU MB FG WH	White
910505101378	ST770T 17S/930 PSU MB FG BK	Black
910505101387	ST770T 27S/CH PSU MB FG BK	Black
910505101388	ST770T 27S/FMT PSU MB FG BK	Black
910505101389	ST770T 27S/FR PSU MB FG BK	Black
910505101393	ST770T 27S/ROSE PSU MB FG BK	Black
910505101401	ST770T 39S/930 PSU MB FG BK	Black
910505101402	ST770T 39S/PC930 PSU MB FG BK	Black
910505101403	ST770T 39S/PW930 PSU MB FG BK	Black
910505100722	ST770T LED17S/930 PSU HMB BK	Black
910505100731	ST770T LED27S/CH PSU HMB BK FG	Black
910505100732	ST770T 27S/FR PSU HMB FG BK	Black
910505100733	ST770T 27S/FMT PSU HMB FG BK	Black

Order Code	Full Product Name	Housing Color
910505100747	ST780T 39S/830 PSU HNB WH	White
910505100748	ST780T 49S/830 PSU HMB WH	White
910505100755	ST780T LED60S/830 PSU HMB WH	White
910505100721	ST770S LED17S/830 PSU HMB WH FG	White
910505101429	ST780S 49S/930 DIA-VLC HWB WH	White
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	White

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505100730	ST770T LED27S/PW930 PSU HMB SI	(0.422,0.386)<2
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	(0.434,0.403)<3
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	(0.434,0.403)<3
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	(0.434,0.403)<2
910505101207	ST770B 17S/830 PSU-E MB FG WH	(0.434,0.403)<3
910505101208	ST770B 20S/830 PSU-E NB FG WH	(0.434,0.403)<3
910505101212	ST770B 27S/830 PSU-E MB FG WH	(0.434,0.403)<3
910505101213	ST770B 27S/840 PSU-E VWB FG WH	(0.382,0.380)<3
910505101214	ST770B 27S/930 PSU-E MB FG WH	(0.434,0.403)<2
910505101215	ST770B 27S/CH PSU-E MB FG WH	(0.458,0.410)<3
910505101216	ST770B 27S/FMT PSU-E MB FG WH	(0.457,0.385)<3
910505101217	ST770B 27S/FR PSU-E MB FG WH	(0.343,0.331)<3
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	(0.422,0.386)<2
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	(0.422,0.386)<2
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	(0.478,0.382)<2
910505101221	ST770B 39S/827 PSU-E WB FG WH	(0.458,0.410)<3
910505101223	ST770B 39S/830 PSU-E MB FG WH	(0.434,0.403)<3
910505101224	ST770B 39S/840 PSU-E VWB FG WH	(0.382,0.380)<3
910505101368	ST770S 39S/930 DIA-VLC HWB BK	(0.434,0.403)<2
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	(0.458,0.410)<3
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	(0.434,0.403)<3
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	(0.434,0.403)<3
910505101410	ST770X 17S/830 DIA MB FG WH	(0.434,0.403)<3
910505101411	ST770X 20S/830 DIA NB FG WH	(0.434,0.403)<3
910505101412	ST770X 27S/827 DIA WB FG WH	(0.458,0.410)<3
910505101413	ST770X 27S/830 DIA MB FG WH	(0.434,0.403)<3
910505101414	ST770X 27S/840 DIA VWB FG WH	(0.382,0.380)<3
910505101415	ST770X 27S/930 DIA OVL-H WH	(0.434,0.403)<2
910505101416	ST770X 27S/CH DIA MB FG WH	(0.458,0.410)<3
910505101417	ST770X 27S/FMT DIA MB FG WH	(0.457,0.385)<3
910505101418	ST770X 27S/FR DIA MB FG WH	(0.343,0.331)<3
910505101421	ST770X 27S/ROSE DIA MB FG WH	(0.478,0.382)<2
910505101422	ST770X 39S/830 DIA MB FG WH	(0.434,0.403)<3

Order Code	Full Product Name	Initial chromaticity
910505101423	ST770X 39S/930 DIA OVL-H WH	(0.434,0.403)<2
910505100749	ST780T LED49S/827 PSU HWB SI FG	(0.458,0.410)<3
910505100756	ST780T 60S/827 PSU HWB FG SI	(0.458,0.410)<3
910505101419	ST770X 27S/PC930 DIA MB FG BK	(0.422,0.386)<2
910505101420	ST770X 27S/PW930 DIA MB FG BK	(0.422,0.386)<2
910505101434	ST780T 39S/827 PSU NB FG WH	(0.458,0.410)<3
910505101435	ST780T 39S/830 PSU NB FG WH	(0.434,0.403)<3
910505101436	ST780T 39S/840 PSU NB FG WH	(0.382,0.380)<3
910505101437	ST780T 39S/930 PSU NB FG WH	(0.434,0.403)<2
910505101438	ST780T 49S/827 PSU WB FG WH	(0.458,0.410)<3
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	(0.434,0.403)<3
910505101441	ST780T 49S/830 PSU MB FG WH	(0.434,0.403)<3
910505101442	ST780T 49S/840 PSU VWB FG WH	(0.382,0.380)<3
910505101446	ST780T 60S/830 PSU MB FG WH	(0.434,0.403)<3
910505101447	ST780T 60S/840 PSU MB FG WH	(0.382,0.380)<3
910505101431	ST780S 60S/827 DIA-VLC HWB BK	(0.458,0.410)<3
910505101432	ST780S 60S/830 DIA-VLC HMB BK	(0.434,0.403)<3
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	(0.382,0.380)<3
910505101386	ST770T 27S/930 PSU MB FG SI	(0.434,0.403)<2
910505101390	ST770T 27S/PC930 PSU MB FG SI	(0.422,0.386)<2
910505101392	ST770T 27S/PW930 PSU MB FG SI	(0.422,0.386)<2
910505100743	ST770T LED49S/830 PSU HMB SI	(0.434,0.403)<3
910505101443	ST780T 49S/930 PSU MB FG SI	(0.434,0.403)<2
910505101444	ST780T 49S/PW930 PSU MB FG SI	(0.422,0.386)<2
910505101445	ST780T 60S/827 PSU WB FG SI	(0.458,0.410)<3
910505101228	ST770S 17S/827 PSU WB FG WH	(0.458,0.410)<3
910505101229	ST770S 17S/830 PSU MB FG WH	(0.434,0.403)<3
910505101230	ST770S 17S/840 PSU VWB FG WH	(0.382,0.380)<3
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	(0.458,0.410)<3
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	(0.434,0.403)<3
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	(0.382,0.380)<3
910505101371	ST770S 39S/PW930 PSU VWB FG WH	(0.422,0.386)<2
910505100723	ST770T 20S/830 PSU HNB WH	(0.434,0.403)<3
910505100724	ST770T 27S/830 PSU HMB WH	(0.434,0.403)<3
910505100725	ST770T LED27S/827 PSU HWB WH	(0.458,0.410)<3
910505100736	ST770T 39S/830 PSU HMB WH	(0.434,0.403)<3
910505100737	ST770T LED39S/827 PSU HWB WH	(0.458,0.410)<3
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	(0.434,0.403)<3
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	(0.422,0.386)<2
910505102315	ST770T 27S/ROSE WIA WB FG WH	(0.478,0.382)<2
910505102316	ST770T 39S/PW930 WIA WB WH	(0.422,0.386)<2
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	(0.458,0.410)<3

Order Code	Full Product Name	Initial chromaticity
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	(0.434,0.403)<3
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	(0.382,0.380)<3
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	(0.434,0.403)<3
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	(0.434,0.403)<3
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	(0.422,0.386)<2
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	(0.422,0.386)<2
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	(0.422,0.386)<2
910505101425	ST780S 39S/827 PSU NB FG WH	(0.458,0.410)<3
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	(0.458,0.410)<3
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	(0.434,0.403)<3
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	(0.382,0.380)<3
910505101379	ST770T 20S/830 PSU NB FG WH	(0.434,0.403)<3
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	(0.458,0.410)<3
910505101381	ST770T 27S/827 PSU WB FG WH	(0.458,0.410)<3
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	(0.434,0.403)<3
910505101384	ST770T 27S/830 PSU MB FG WH	(0.434,0.403)<3
910505101385	ST770T 27S/840 PSU VWB FG WH	(0.382,0.380)<3
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	(0.458,0.410)<3
910505101395	ST770T 39S/827 PSU WB FG WH	(0.458,0.410)<3
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	(0.434,0.403)<3
910505101398	ST770T 39S/830 PSU MB FG WH	(0.434,0.403)<3
910505101399	ST770T 39S/840 PSU MB FG WH	(0.382,0.380)<3
910505101378	ST770T 17S/930 PSU MB FG BK	(0.434,0.403)<2
910505101387	ST770T 27S/CH PSU MB FG BK	(0.458,0.410)<3
910505101388	ST770T 27S/FMT PSU MB FG BK	(0.457,0.385)<3
910505101389	ST770T 27S/FR PSU MB FG BK	(0.343,0.331)<3
910505101393	ST770T 27S/ROSE PSU MB FG BK	(0.478,0.382)<2
910505101401	ST770T 39S/930 PSU MB FG BK	(0.434,0.403)<2
910505101402	ST770T 39S/PC930 PSU MB FG BK	(0.422,0.386)<2
910505101403	ST770T 39S/PW930 PSU MB FG BK	(0.422,0.386)<2
910505100722	ST770T LED17S/930 PSU HMB BK	(0.434,0.403)<2
910505100731	ST770T LED27S/CH PSU HMB BK FG	(0.458,0.410)<3
910505100732	ST770T 27S/FR PSU HMB FG BK	(0.343,0.331)<3
910505100733	ST770T 27S/FMT PSU HMB FG BK	(0.457,0.385)<3
910505100747	ST780T 39S/830 PSU HNB WH	(0.434,0.403)<3
910505100748	ST780T 49S/830 PSU HMB WH	(0.434,0.403)<3
910505100755	ST780T LED60S/830 PSU HMB WH	(0.434,0.403)<3
910505100721	ST770S LED17S/830 PSU HMB WH FG	(0.434,0.403)<3
910505101429	ST780S 49S/930 DIA-VLC HWB WH	(0.434,0.403)<2
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	(0.422,0.386)<2


Product Data

Order Code	Full Product Name	Product family code
910505100730	ST770T LED27S/PW930 PSU HMB SI	ST770T
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	ST770T
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	ST770B
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	ST770B
910505101207	ST770B 17S/830 PSU-E MB FG WH	ST770B
910505101208	ST770B 20S/830 PSU-E NB FG WH	ST770B
910505101212	ST770B 27S/830 PSU-E MB FG WH	ST770B
910505101213	ST770B 27S/840 PSU-E VWB FG WH	ST770B
910505101214	ST770B 27S/930 PSU-E MB FG WH	ST770B
910505101215	ST770B 27S/CH PSU-E MB FG WH	ST770B
910505101216	ST770B 27S/FMT PSU-E MB FG WH	ST770B
910505101217	ST770B 27S/FR PSU-E MB FG WH	ST770B
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	ST770B
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	ST770B
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	ST770B
910505101221	ST770B 39S/827 PSU-E WB FG WH	ST770B
910505101223	ST770B 39S/830 PSU-E MB FG WH	ST770B
910505101224	ST770B 39S/840 PSU-E VWB FG WH	ST770B
910505101368	ST770S 39S/930 DIA-VLC HWB BK	ST770S
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	ST770B
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	ST770B
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	ST770B
910505101410	ST770X 17S/830 DIA MB FG WH	ST770X
910505101411	ST770X 20S/830 DIA NB FG WH	ST770X
910505101412	ST770X 27S/827 DIA WB FG WH	ST770X
910505101413	ST770X 27S/830 DIA MB FG WH	ST770X
910505101414	ST770X 27S/840 DIA VWB FG WH	ST770X
910505101415	ST770X 27S/930 DIA OVL-H WH	ST770X
910505101416	ST770X 27S/CH DIA MB FG WH	ST770X
910505101417	ST770X 27S/FMT DIA MB FG WH	ST770X
910505101418	ST770X 27S/FR DIA MB FG WH	ST770X
910505101421	ST770X 27S/ROSE DIA MB FG WH	ST770X
910505101422	ST770X 39S/830 DIA MB FG WH	ST770X
910505101423	ST770X 39S/930 DIA OVL-H WH	ST770X
910505100749	ST780T LED49S/827 PSU HWB SI FG	ST780T
910505100756	ST780T 60S/827 PSU HWB FG SI	ST780T
910505101419	ST770X 27S/PC930 DIA MB FG BK	ST770X
910505101420	ST770X 27S/PW930 DIA MB FG BK	ST770X
910505101434	ST780T 39S/827 PSU NB FG WH	ST780T
910505101435	ST780T 39S/830 PSU NB FG WH	ST780T
910505101436	ST780T 39S/840 PSU NB FG WH	ST780T

Order Code	Full Product Name	Product family code
910505101437	ST780T 39S/930 PSU NB FG WH	ST780T
910505101438	ST780T 49S/827 PSU WB FG WH	ST780T
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	ST780T
910505101441	ST780T 49S/830 PSU MB FG WH	ST780T
910505101442	ST780T 49S/840 PSU VWB FG WH	ST780T
910505101446	ST780T 60S/830 PSU MB FG WH	ST780T
910505101447	ST780T 60S/840 PSU MB FG WH	ST780T
910505101431	ST780S 60S/827 DIA-VLC HVB BK	ST780S
910505101432	ST780S 60S/830 DIA-VLC HMB BK	ST780S
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	ST780S
910505101386	ST770T 27S/930 PSU MB FG SI	ST770T
910505101390	ST770T 27S/PC930 PSU MB FG SI	ST770T
910505101392	ST770T 27S/PW930 PSU MB FG SI	ST770T
910505100743	ST770T LED49S/830 PSU HMB SI	ST770T
910505101443	ST780T 49S/930 PSU MB FG SI	ST780T
910505101444	ST780T 49S/PW930 PSU MB FG SI	ST780T
910505101445	ST780T 60S/827 PSU WB FG SI	ST780T
910505101228	ST770S 17S/827 PSU WB FG WH	ST770S
910505101229	ST770S 17S/830 PSU MB FG WH	ST770S
910505101230	ST770S 17S/840 PSU VWB FG WH	ST770S
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	ST770S
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	ST770S
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	ST770S
910505101371	ST770S 39S/PW930 PSU VWB FG WH	ST770S
910505100723	ST770T 20S/830 PSU HNB WH	ST770T
910505100724	ST770T 27S/830 PSU HMB WH	ST770T
910505100725	ST770T LED27S/827 PSU HVB WH	ST770T
910505100736	ST770T 39S/830 PSU HMB WH	ST770T
910505100737	ST770T LED39S/827 PSU HVB WH	ST770T
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	ST770T
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	ST770T
910505102315	ST770T 27S/ROSE WIA WB FG WH	ST770T
910505102316	ST770T 39S/PW930 WIA WB WH	ST770T
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	ST770S
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	ST770S
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	ST770S
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	ST770T
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	ST780T
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	ST770S
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	ST770S
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	ST770S
910505101425	ST780S 39S/827 PSU NB FG WH	ST780S

Order Code	Full Product Name	Product family code
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	ST780S
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	ST780S
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	ST780S
910505101379	ST770T 20S/830 PSU NB FG WH	ST770T
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	ST770T
910505101381	ST770T 27S/827 PSU WB FG WH	ST770T
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	ST770T
910505101384	ST770T 27S/830 PSU MB FG WH	ST770T
910505101385	ST770T 27S/840 PSU VWB FG WH	ST770T
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	ST770T
910505101395	ST770T 39S/827 PSU WB FG WH	ST770T
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	ST770T
910505101398	ST770T 39S/830 PSU MB FG WH	ST770T
910505101399	ST770T 39S/840 PSU MB FG WH	ST770T
910505101378	ST770T 17S/930 PSU MB FG BK	ST770T
910505101387	ST770T 27S/CH PSU MB FG BK	ST770T
910505101388	ST770T 27S/FMT PSU MB FG BK	ST770T
910505101389	ST770T 27S/FR PSU MB FG BK	ST770T
910505101393	ST770T 27S/ROSE PSU MB FG BK	ST770T
910505101401	ST770T 39S/930 PSU MB FG BK	ST770T
910505101402	ST770T 39S/PC930 PSU MB FG BK	ST770T
910505101403	ST770T 39S/PW930 PSU MB FG BK	ST770T
910505100722	ST770T LED17S/930 PSU HMB BK	ST770T
910505100731	ST770T LED27S/CH PSU HMB BK FG	ST770T
910505100732	ST770T 27S/FR PSU HMB FG BK	ST770T
910505100733	ST770T 27S/FMT PSU HMB FG BK	ST770T
910505100747	ST780T 39S/830 PSU HNB WH	ST780T
910505100748	ST780T 49S/830 PSU HMB WH	ST780T
910505100755	ST780T LED60S/830 PSU HMB WH	ST780T
910505100721	ST770S LED17S/830 PSU HMB WH FG	ST770S
910505101429	ST780S 49S/930 DIA-VLC HWB WH	ST780S
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	ST780S


Polar normal diagrams



ST770TI - 910500465998

ST770TI - 910505101405


ST770TI - 910505101224



ST770TI - 910505101371

ST780TI - 910505101439


ST770TI - 910505101410




ST770TI - 910505101392

ST770TI - 910505101402


ST770TI - 910505101213




ST770TI - 910505101423




ST770TI - 910505101232




ST770TI - 910505101391




ST770TI - 910505101207




ST780TI - 910505101426




ST770TI - 910505101367




ST780TI - 910505101431




ST780TI - 910505101440




ST770TI - 910505101403




ST780TI - 910505101447




ST770TI - 910505101395




ST770TI - 910505101394




ST770TI - 910505101216




ST770TI - 910505100731




ST770TI - 910505101397




ST780TI - 910505101428




ST770TI - 910505101368




ST770TI - 910505101369




ST770TI - 910505101419




ST770TI - 910505101413




ST770TI - 910505101414




ST770TI - 910505101377




ST770TI - 910505101387




ST770TI - 910505101418




ST770TI - 910505101380




ST770TI - 910505101384




ST770TI - 910505101411




ST770TI - 910505101386




ST780TI - 910505101433




ST780TI - 910505101437




ST770TI - 910505101208




ST780TI - 910505101430




ST770TI - 910505101383




ST770TI - 910505101212




ST770TI - 910505101228




ST780TI - 910505101438




ST770TI - 910505101381




ST780TI - 910505101445




ST770TI - 910505101421




ST770TI - 910505102316




ST770TI - 910505101417




ST770TI - 910505101396












ST780TI - 910505101425





















ST770TI - 910505101388




ST770TI - 910505101214












ST770TI - 910505101218




ST770TI - 910505101420




ST780TI - 910505101436




ST770TI - 910505101220




ST780TI - 910505101443




ST770TI - 910505101379




ST770TI - 910505101398




ST770TI - 910505101399




ST780TI - 910505101429




ST770TI - 910505101209




ST770TI - 910505101217




ST770TI - 910505101230




ST770TI - 910505101229




ST770TI - 910505101385




ST770TI - 910505101412




ST780TI - 910505101434




ST780TI - 910505101444




ST780TI - 910505101446




ST770TI - 910505100014




ST770TI - 910505100723




ST770TI - 910505100721




ST770TI - 910505100722




ST770TI - 910505100724




ST770TI - 910505100725




ST770TI - 910505100730




ST770TI - 910505100732




ST770TI - 910505100743




ST780TI - 910505100747




ST780TI - 910505100748




ST770TI - 910505100737




ST770TI - 910505100736



ST780TI - 910505100755



ST780TI - 910505100756



ST780TI - 910505100749