



The ultimate in retail flexibility and performance

StyliD Evo

With StyliD Evo, retailers can enjoy the superior quality of light and market-leading energy efficiency of PerfectAccent optics in a series of flexible and future-proof projectors. StyliD Evo projectors are easy to reconfigure with quick and easy optic upgrades that require no tools. They also support frequent changes in store layouts, as the StyliD Evo projector can be easily repositioned on the track or Maxos fusion backbone. Covering a wide range of lighting applications, from lower light levels in convenience formats to high-ceiling installations where very high light output is required, StyliD offers continuity for every retail concept. StyliD Evo can be mounted on 3C or DALI track (ST770T, ST780T), on Maxos fusion (ST770S, ST780S, ST770X), or into the ceiling with a semi-recessed version (ST770B). All StyliD Evo projectors with PerfectAccent reflectors are certified as a circular lighting product and offer multiple system integration and dimming options, including wired as well as wireless. For prolonged shelf life and better visual representation of food, reducing food waste and increasing sales, fresh food LED lighting recipes are available. Check out our Fashion and Food catalog pages to find out more about PremiumWhite, PremiumColor, Fresh Meat, Rosé, Frost and Champagne.

Benefits

- Attract shoppers with more sparkle and superior eye comfort
- Easy to reposition and upgrade for frequent store updates
- Best-in class efficacy to reduce carbon footprint and save on energy use
- Certified as circular lighting with PerfectAccent high-efficacy reflectors

Features

- Easy optic replacement or upgrades that require no tools
- Available with PerfectAccent high-efficacy reflectors
- Optional front glass (advised in dusty environments)
- Up to 6000 lm output for high installation heights
- Available with fresh food LED lighting recipes and LED flavors
- Wired (DALI) and wireless connectivity options
- High intensity oval beam allows increased luminaire spacing when lighting fresh food counters or wordmarks on the wall

Application

- Convenience stores
- Supermarkets & hypermarkets
- Large Retail formats

Warnings and Safety

- All photometrical data is calculated without optional front glass. Flux should be reduced by 3.5% when using a front glass
- Cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden. For food preparation areas and areas with high levels of dust, the use of the optional front glass is strongly advised, as it can be cleaned with a (dry) microfiber cloth.
- During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove

Versions



StyliD Evo Compact HR for maxos fusion



StyliD Evo Compact ST770X black, Maxos fusion integrated



StyliD Evo Performance ST780T white, track version



StyliD Evo Performance HR for maxos fusion

Versions



StyliD Evo Performance ST780S
black, Maxos fusion version



StyliD Evo Compact HR



StyliD Evo Performance ST780T
silver, track version



StyliD Evo Compact ST770S silver,
Maxos fusion version



StyliD Evo Compact HR



StyliD Evo Performance HR











StyliD Evo Performance ST780S
white, Maxos fusion version






StyliD Evo Compact HR for maxos
fusion

Dimensional drawing



Dimensional drawing




Product details



Aiming indication, with marking for Indoor Positioning operation



StyliD Evo Compact black, side view



StyliD Evo Compact ST770X
Mounting interface



StyliD Evo Performance black, side view

Product details



OptiShield protects the optical compartment from bugs and dust



StyliD Evo Compact HR




Aiming indication, with marking for Indoor Positioning operation



StyliD Evo Compact white, side view



StyliD Evo ST770B semi recessed installation rim



OptiShield protects the optical compartment from bugs and dust



StyliD Evo Performance HR



StyliD Evo Compact HR

Product details



Aiming indication, with marking for Indoor Positioning operation



StyliD Evo Performance in black, full rotation flexibility



StyliD Evo Compact in white, full rotation flexibility



StyliD Evo Compact white, front view



OptiShield protects the optical compartment from bugs and dust



StyliD Evo Performance HR



StyliD Evo Compact HR black



StyliD Evo Performance HR

Product details



Aiming indication, with marking for Indoor Positioning operation



StyliD Evo Performance white, side view



StyliD Evo Compact black, front view



StyliD Evo Performance white, front view



StyliD Evo Performance black, front view



OptiShield protects the optical compartment from bugs and dust



StyliD Evo Performance HR



StyliD Evo Compact HR white

StyliD Evo

Product details

StyliD Evo Exploded View



StyliD Evo Compact in black, full rotation flexibility



StyliD Evo Performance in white, full rotation flexibility



General Information	
Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Mechanical and Housing	
Optical cover type	-
Mech. impact protection code	IK02
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	+10 to +35 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.5
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Lamp family code
910505100730	ST770T LED27S/PW930 PSU HMB SI	-
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	-
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	LED27S
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	LED39S
910505101207	ST770B 17S/830 PSU-E MB FG WH	-
910505101208	ST770B 20S/830 PSU-E NB FG WH	-
910505101212	ST770B 27S/830 PSU-E MB FG WH	-
910505101213	ST770B 27S/840 PSU-E VWB FG WH	-
910505101214	ST770B 27S/930 PSU-E MB FG WH	-
910505101215	ST770B 27S/CH PSU-E MB FG WH	-
910505101216	ST770B 27S/FMT PSU-E MB FG WH	-
910505101217	ST770B 27S/FR PSU-E MB FG WH	-
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	-
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	-
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	-
910505101221	ST770B 39S/827 PSU-E WB FG WH	-
910505101223	ST770B 39S/830 PSU-E MB FG WH	-
910505101224	ST770B 39S/840 PSU-E VWB FG WH	-
910505101368	ST770S 39S/930 DIA-VLC HWB BK	-
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	-
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	-
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	-
910505101410	ST770X 17S/830 DIA MB FG WH	-
910505101411	ST770X 20S/830 DIA NB FG WH	-
910505101412	ST770X 27S/827 DIA WB FG WH	-
910505101413	ST770X 27S/830 DIA MB FG WH	-
910505101414	ST770X 27S/840 DIA VWB FG WH	-
910505101415	ST770X 27S/930 DIA OVL-H WH	-
910505101416	ST770X 27S/CH DIA MB FG WH	-
910505101417	ST770X 27S/FMT DIA MB FG WH	-
910505101418	ST770X 27S/FR DIA MB FG WH	-
910505101421	ST770X 27S/ROSE DIA MB FG WH	-
910505101422	ST770X 39S/830 DIA MB FG WH	-
910505101423	ST770X 39S/930 DIA OVL-H WH	-
910505100749	ST780T LED49S/827 PSU HWB SI FG	-
910505100756	ST780T 60S/827 PSU HWB FG SI	-
910505101419	ST770X 27S/PC930 DIA MB FG BK	-
910505101420	ST770X 27S/PW930 DIA MB FG BK	-
910505101434	ST780T 39S/827 PSU NB FG WH	-
910505101435	ST780T 39S/830 PSU NB FG WH	-
910505101436	ST780T 39S/840 PSU NB FG WH	-
910505101437	ST780T 39S/930 PSU NB FG WH	-
910505101438	ST780T 49S/827 PSU WB FG WH	-
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	-
910505101441	ST780T 49S/830 PSU MB FG WH	-
910505101442	ST780T 49S/840 PSU VWB FG WH	-
910505101446	ST780T 60S/830 PSU MB FG WH	-
910505101447	ST780T 60S/840 PSU MB FG WH	-
910505101431	ST780S 60S/827 DIA-VLC HWB BK	-
910505101432	ST780S 60S/830 DIA-VLC HMB BK	-
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	-

Order Code	Full Product Name	Lamp family code
910505101386	ST770T 27S/930 PSU MB FG SI	-
910505101390	ST770T 27S/PC930 PSU MB FG SI	-
910505101392	ST770T 27S/PW930 PSU MB FG SI	-
910505100743	ST770T LED49S/830 PSU HMB SI	-
910505101443	ST780T 49S/930 PSU MB FG SI	-
910505101444	ST780T 49S/PW930 PSU MB FG SI	-
910505101445	ST780T 60S/827 PSU WB FG SI	-
910505101228	ST770S 17S/827 PSU WB FG WH	-
910505101229	ST770S 17S/830 PSU MB FG WH	-
910505101230	ST770S 17S/840 PSU VWB FG WH	-
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	-
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	-
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	-
910505101371	ST770S 39S/PW930 PSU VWB FG WH	-
910505100723	ST770T 20S/830 PSU HNB WH	-
910505100724	ST770T 27S/830 PSU HMB WH	-
910505100725	ST770T LED27S/827 PSU HWB WH	-
910505100736	ST770T 39S/830 PSU HMB WH	-
910505100737	ST770T LED39S/827 PSU HWB WH	-
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	-
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	-
910505102315	ST770T 27S/ROSE WIA WB FG WH	-
910505102316	ST770T 39S/PW930 WIA WB WH	-
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	-
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	-
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	-
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	-
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	-
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	-
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	-
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	-
910505101425	ST780S 39S/827 PSU NB FG WH	-
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	-
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	-
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	-
910505101379	ST770T 20S/830 PSU NB FG WH	-
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	-
910505101381	ST770T 27S/827 PSU WB FG WH	-
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	-
910505101384	ST770T 27S/830 PSU MB FG WH	-
910505101385	ST770T 27S/840 PSU VWB FG WH	-
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	-
910505101395	ST770T 39S/827 PSU WB FG WH	-
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	-
910505101398	ST770T 39S/830 PSU MB FG WH	-
910505101399	ST770T 39S/840 PSU MB FG WH	-
910505101378	ST770T 17S/930 PSU MB FG BK	-
910505101387	ST770T 27S/CH PSU MB FG BK	-
910505101388	ST770T 27S/FMT PSU MB FG BK	-
910505101389	ST770T 27S/FR PSU MB FG BK	-
910505101393	ST770T 27S/ROSE PSU MB FG BK	-
910505101401	ST770T 39S/930 PSU MB FG BK	-

Order Code	Full Product Name	Lamp family code
910505101402	ST770T 39S/PC930 PSU MB FG BK	-
910505101403	ST770T 39S/PW930 PSU MB FG BK	-
910505100722	ST770T LED17S/930 PSU HMB BK	-
910505100731	ST770T LED27S/CH PSU HMB BK FG	-
910505100732	ST770T 27S/FR PSU HMB FG BK	-
910505100733	ST770T 27S/FMT PSU HMB FG BK	-
910505100747	ST780T 39S/830 PSU HNB WH	-
910505100748	ST780T 49S/830 PSU HMB WH	-
910505100755	ST780T LED60S/830 PSU HMB WH	-
910505100721	ST770S LED17S/830 PSU HMB WH FG	-
910505101429	ST780S 49S/930 DIA-VLC HWB WH	-
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	-

Light Technical (1/2)

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505100730	ST770T LED27S/PW930 PSU HMB SI	3000 K	>90	138 lm/W	2,700 lm
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	3000 K	>80	142 lm/W	3,900 lm
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	3000 K	>80	136 lm/W	2,700 lm
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	3000 K	>90	127 lm/W	3,900 lm
910505101207	ST770B 17S/830 PSU-E MB FG WH	3000 K	>80	144 lm/W	1,700 lm
910505101208	ST770B 20S/830 PSU-E NB FG WH	3000 K	>80	120 lm/W	2,000 lm
910505101212	ST770B 27S/830 PSU-E MB FG WH	3000 K	>80	136 lm/W	2,700 lm
910505101213	ST770B 27S/840 PSU-E VWB FG WH	4000 K	>80	142 lm/W	2,700 lm
910505101214	ST770B 27S/930 PSU-E MB FG WH	3000 K	>90	132 lm/W	2,700 lm
910505101215	ST770B 27S/CH PSU-E MB FG WH	2700 K	>80	130 lm/W	2,700 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505101216	ST770B 27S/FMT PSU-E MB FG WH	3000 K	>90	78 lm/W	2,700 lm
910505101217	ST770B 27S/FR PSU-E MB FG WH	5000 K	>90	94 lm/W	3,000 lm
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	3000 K	>90	114 lm/W	2,700 lm
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	3000 K	>90	134 lm/W	2,700 lm
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	2200 K	>80	90 lm/W	2,800 lm
910505101221	ST770B 39S/827 PSU-E WB FG WH	2700 K	>80	132 lm/W	3,900 lm
910505101223	ST770B 39S/830 PSU-E MB FG WH	3000 K	>80	142 lm/W	3,900 lm
910505101224	ST770B 39S/840 PSU-E VWB FG WH	4000 K	>80	147 lm/W	3,900 lm
910505101368	ST770S 39S/930 DIA-VLC HWB BK	3000 K	>90	129 lm/W	3,900 lm
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	2700 K	>80	125 lm/W	2,700 lm
910505101210	ST770B 27S/830 DIA-	3000 K	>80	131 lm/W	2,700 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	VLC-E MB FG BK				
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	3000 K	>80	131 lm/W	2,700 lm
910505101410	ST770X 17S/830 DIA MB FG WH	3000 K	>80	144 lm/W	1,700 lm
910505101411	ST770X 20S/830 DIA NB FG WH	3000 K	>80	121 lm/W	2,000 lm
910505101412	ST770X 27S/827 DIA WB FG WH	2700 K	>80	130 lm/W	2,700 lm
910505101413	ST770X 27S/830 DIA MB FG WH	3000 K	>80	136 lm/W	2,700 lm
910505101414	ST770X 27S/840 DIA VWB FG WH	4000 K	>80	142 lm/W	2,700 lm
910505101415	ST770X 27S/930 DIA OVL-H WH	3000 K	>90	133 lm/W	2,700 lm
910505101416	ST770X 27S/CH DIA MB FG WH	2700 K	>80	131 lm/W	2,700 lm
910505101417	ST770X 27S/FMT DIA MB FG WH	3000 K	>90	81 lm/W	2,700 lm
910505101418	ST770X 27S/FR DIA MB FG WH	5000 K	>90	95 lm/W	3,000 lm
910505101421	ST770X 27S/ROSE DIA MB FG WH	2200 K	>80	96 lm/W	2,800 lm
910505101422	ST770X 39S/830 DIA MB FG WH	3000 K	>80	142 lm/W	3,900 lm
910505101423	ST770X 39S/930 DIA OVL-H WH	3000 K	>90	128 lm/W	3,900 lm
910505100749	ST780T LED49S/827 PSU HWB SI FG	2700 K	>80	133 lm/W	4,900 lm
910505100756	ST780T 60S/827 PSU HWB FG SI	2700 K	>80	138 lm/W	6,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505101419	ST770X 27S/PC930 DIA MB FG BK	3000 K	>90	116 lm/W	2,700 lm
910505101420	ST770X 27S/PW930 DIA MB FG BK	3000 K	>90	134 lm/W	2,700 lm
910505101434	ST780T 39S/827 PSU NB FG WH	2700 K	>80	133 lm/W	3,900 lm
910505101435	ST780T 39S/830 PSU NB FG WH	3000 K	>80	139 lm/W	3,900 lm
910505101436	ST780T 39S/840 PSU NB FG WH	4000 K	>80	144 lm/W	3,900 lm
910505101437	ST780T 39S/930 PSU NB FG WH	3000 K	>90	131 lm/W	3,900 lm
910505101438	ST780T 49S/827 PSU WB FG WH	2700 K	>80	139 lm/W	4,900 lm
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	3000 K	>80	128 lm/W	4,900 lm
910505101441	ST780T 49S/830 PSU MB FG WH	3000 K	>80	139 lm/W	4,900 lm
910505101442	ST780T 49S/840 PSU VWB FG WH	4000 K	>80	139 lm/W	4,900 lm
910505101446	ST780T 60S/830 PSU MB FG WH	3000 K	>80	135 lm/W	6,000 lm
910505101447	ST780T 60S/840 PSU MB FG WH	4000 K	>80	152 lm/W	6,000 lm
910505101431	ST780S 60S/827 DIA-VLC HWB BK	2700 K	>80	135 lm/W	6,000 lm
910505101432	ST780S 60S/830 DIA-VLC HMB BK	3000 K	>80	139 lm/W	6,000 lm
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	4000 K	>80	146 lm/W	6,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505101386	ST770T 27S/930 PSU MB FG SI	3000 K	>90	132 lm/W	2,700 lm
910505101390	ST770T 27S/PC930 PSU MB FG SI	3000 K	>90	114 lm/W	2,700 lm
910505101392	ST770T 27S/PW930 PSU MB FG SI	3000 K	>90	134 lm/W	2,700 lm
910505100743	ST770T LED49S/830 PSU HMB SI	3000 K	>80	139 lm/W	4,900 lm
910505101443	ST780T 49S/930 PSU MB FG SI	3000 K	>90	132 lm/W	4,900 lm
910505101444	ST780T 49S/PW930 PSU MB FG SI	3000 K	>90	132 lm/W	4,900 lm
910505101445	ST780T 60S/827 PSU WB FG SI	2700 K	>80	138 lm/W	6,000 lm
910505101228	ST770S 17S/827 PSU WB FG WH	2700 K	>80	138 lm/W	1,700 lm
910505101229	ST770S 17S/830 PSU MB FG WH	3000 K	>80	144 lm/W	1,700 lm
910505101230	ST770S 17S/840 PSU VWB FG WH	4000 K	>80	150 lm/W	1,700 lm
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	2700 K	>80	125 lm/W	2,700 lm
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	3000 K	>80	131 lm/W	2,700 lm
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	4000 K	>80	136 lm/W	2,700 lm
910505101371	ST770S 39S/PW930 PSU VWB FG WH	3000 K	>90	130 lm/W	3,900 lm
910505100723	ST770T 20S/830 PSU HNB WH	3000 K	>80	124 lm/W	2,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505100724	ST770T 27S/830 PSU HMB WH	3000 K	>80	141 lm/W	2,700 lm
910505100725	ST770T LED27S/827 PSU HWB WH	2700 K	>80	135 lm/W	2,700 lm
910505100736	ST770T 39S/830 PSU HMB WH	3000 K	>80	146 lm/W	3,900 lm
910505100737	ST770T LED39S/827 PSU HWB WH	2700 K	>80	139 lm/W	3,900 lm
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	3000 K	>80	133 lm/W	2,700 lm
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	3000 K	>90	130 lm/W	2,700 lm
910505102315	ST770T 27S/ROSE WIA WB FG WH	2200 K	>80	93 lm/W	2,800 lm
910505102316	ST770T 39S/PW930 WIA WB WH	3000 K	>90	127 lm/W	3,900 lm
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	2700 K	>80	129 lm/W	3,900 lm
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	3000 K	>80	138 lm/W	3,900 lm
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	4000 K	>80	142 lm/W	3,900 lm
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	3000 K	>80	133 lm/W	4,900 lm
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	3000 K	>80	133 lm/W	4,900 lm
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	3000 K	>90	116 lm/W	3,900 lm
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	3000 K	>90	134 lm/W	4,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505101377	ST770S 49S/ PW930 DIA- VLC HMB WH	3000 K	>90	132 lm/W	4,900 lm
910505101425	ST780S 39S/827 PSU NB FG WH	2700 K	>80	133 lm/W	3,900 lm
910505101426	ST780S 49S/827 DIA- VLC WB FG WH	2700 K	>80	133 lm/W	4,900 lm
910505101427	ST780S 49S/830 DIA- VLC MB FG WH	3000 K	>80	128 lm/W	4,900 lm
910505101428	ST780S 49S/840 DIA- VLC VWB FG WH	4000 K	>80	133 lm/W	4,900 lm
910505101379	ST770T 20S/830 PSU NB FG WH	3000 K	>80	120 lm/W	2,000 lm
910505101380	ST770T 27S/827 DIA- VLC OVL-V WH	2700 K	>80	125 lm/W	2,700 lm
910505101381	ST770T 27S/827 PSU WB FG WH	2700 K	>80	131 lm/W	2,700 lm
910505101383	ST770T 27S/830 DIA- VLC OVL-H WH	3000 K	>80	131 lm/W	2,700 lm
910505101384	ST770T 27S/830 PSU MB FG WH	3000 K	>80	136 lm/W	2,700 lm
910505101385	ST770T 27S/840 PSU VWB FG WH	4000 K	>80	142 lm/W	2,700 lm
910505101394	ST770T 39S/827 DIA- VLC OVL-V WH	2700 K	>80	129 lm/W	3,900 lm
910505101395	ST770T 39S/827 PSU WB FG WH	2700 K	>80	132 lm/W	3,900 lm
910505101397	ST770T 39S/830 DIA- VLC OVL-H WH	3000 K	>80	138 lm/W	3,900 lm
910505101398	ST770T 39S/830 PSU MB FG WH	3000 K	>80	142 lm/W	3,900 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505101399	ST770T 39S/840 PSU MB FG WH	4000 K	>80	147 lm/W	3,900 lm
910505101378	ST770T 17S/930 PSU MB FG BK	3000 K	>90	135 lm/W	1,700 lm
910505101387	ST770T 27S/CH PSU MB FG BK	2700 K	>80	131 lm/W	2,700 lm
910505101388	ST770T 27S/FMT PSU MB FG BK	3000 K	>90	78 lm/W	2,700 lm
910505101389	ST770T 27S/FR PSU MB FG BK	5000 K	>90	94 lm/W	3,000 lm
910505101393	ST770T 27S/ ROSE PSU MB FG BK	2200 K	>80	90 lm/W	2,800 lm
910505101401	ST770T 39S/930 PSU MB FG BK	3000 K	>90	127 lm/W	3,900 lm
910505101402	ST770T 39S/ PC930 PSU MB FG BK	3000 K	>90	115 lm/W	3,900 lm
910505101403	ST770T 39S/ PW930 PSU MB FG BK	3000 K	>90	130 lm/W	3,900 lm
910505100722	ST770T LED17S/930 PSU HMB BK	3000 K	>90	135 lm/W	1,700 lm
910505100731	ST770T LED27S/CH PSU HMB BK FG	2700 K	>80	135 lm/W	2,700 lm
910505100732	ST770T 27S/FR PSU HMB FG BK	5000 K	>90	98 lm/W	2,700 lm
910505100733	ST770T 27S/FMT PSU HMB FG BK	3000 K	>90	81 lm/W	2,700 lm
910505100747	ST780T 39S/830 PSU HNB WH	3000 K	>80	143 lm/W	3,900 lm
910505100748	ST780T 49S/830 PSU HMB WH	3000 K	>80	139 lm/W	4,900 lm
910505100755	ST780T LED60S/830 PSU HMB WH	3000 K	>80	143 lm/W	6,000 lm
910505100721	ST770S LED17S/830	3000 K	>80	149 lm/W	1,700 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	PSU HMB WH FG				
910505101429	ST780S 49S/930 DIA-VLC HWB WH	3000 K	>90	137 lm/W	4,900 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	3000 K	>90	132 lm/W	4,900 lm

Light Technical (2/2)

Order Code	Full Product Name	Number of light sources	Optic type
910505100730	ST770T LED27S/PW930 PSU HMB SI	-	High-reflective metal reflector Medium beam 20 to 40 degrees
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	-	High-reflective metal reflector Oval - Horizontal beam
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	1	Oval horizontal beam
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	1	Oval horizontal beam
910505101207	ST770B 17S/830 PSU-E MB FG WH	-	Medium beam
910505101208	ST770B 20S/830 PSU-E NB FG WH	-	Narrow beam
910505101212	ST770B 27S/830 PSU-E MB FG WH	-	Medium beam
910505101213	ST770B 27S/840 PSU-E VWB FG WH	-	Very wide beam
910505101214	ST770B 27S/930 PSU-E MB FG WH	-	Medium beam
910505101215	ST770B 27S/CH PSU-E MB FG WH	-	Medium beam
910505101216	ST770B 27S/FMT PSU-E MB FG WH	-	Medium beam
910505101217	ST770B 27S/FR PSU-E MB FG WH	-	Medium beam
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	-	Medium beam
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	-	Medium beam
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	-	Medium beam
910505101221	ST770B 39S/827 PSU-E WB FG WH	-	Wide beam
910505101223	ST770B 39S/830 PSU-E MB FG WH	-	Medium beam

Order Code	Full Product Name	Number of light sources	Optic type
910505101224	ST770B 39S/840 PSU-E VWB FG WH	-	Very wide beam
910505101368	ST770S 39S/930 DIA-VLC HWB BK	-	High-reflective metal reflector Wide beam 40 to 80 degrees
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	-	Wide beam
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	-	Medium beam
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	-	Oval horizontal beam
910505101410	ST770X 17S/830 DIA MB FG WH	-	Medium beam
910505101411	ST770X 20S/830 DIA NB FG WH	-	Narrow beam
910505101412	ST770X 27S/827 DIA WB FG WH	-	Wide beam
910505101413	ST770X 27S/830 DIA MB FG WH	-	Medium beam
910505101414	ST770X 27S/840 DIA VWB FG WH	-	Very wide beam
910505101415	ST770X 27S/930 DIA OVL-H WH	-	Oval horizontal beam
910505101416	ST770X 27S/CH DIA MB FG WH	-	Medium beam
910505101417	ST770X 27S/FMT DIA MB FG WH	-	Medium beam
910505101418	ST770X 27S/FR DIA MB FG WH	-	Medium beam
910505101421	ST770X 27S/ROSE DIA MB FG WH	-	Medium beam
910505101422	ST770X 39S/830 DIA MB FG WH	-	Medium beam
910505101423	ST770X 39S/930 DIA OVL-H WH	-	Oval horizontal beam
910505100749	ST780T LED49S/827 PSU HWB SI FG	-	High-reflective metal reflector Wide beam 40 to 80 degrees
910505100756	ST780T 60S/827 PSU HWB FG SI	-	High-reflective metal reflector Wide beam 40 to 80 degrees
910505101419	ST770X 27S/PC930 DIA MB FG BK	-	Medium beam
910505101420	ST770X 27S/PW930 DIA MB FG BK	-	Medium beam
910505101434	ST780T 39S/827 PSU NB FG WH	-	Narrow beam
910505101435	ST780T 39S/830 PSU NB FG WH	-	Narrow beam
910505101436	ST780T 39S/840 PSU NB FG WH	-	Narrow beam
910505101437	ST780T 39S/930 PSU NB FG WH	-	Narrow beam

Order Code	Full Product Name	Number of	
		light sources	Optic type
910505101438	ST780T 49S/827 PSU WB FG WH	-	Wide beam
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	-	Oval horizontal beam
910505101441	ST780T 49S/830 PSU MB FG WH	-	Medium beam
910505101442	ST780T 49S/840 PSU VWB FG WH	-	Very wide beam
910505101446	ST780T 60S/830 PSU MB FG WH	-	Medium beam
910505101447	ST780T 60S/840 PSU MB FG WH	-	Medium beam
910505101431	ST780S 60S/827 DIA-VLC HWB BK	-	High-reflective metal reflector Wide beam 40 to 80 degrees
910505101432	ST780S 60S/830 DIA-VLC HMB BK	-	High-reflective metal reflector Medium beam 20 to 40 degrees
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	-	Very wide beam
910505101386	ST770T 27S/930 PSU MB FG SI	-	Medium beam
910505101390	ST770T 27S/PC930 PSU MB FG SI	-	Medium beam
910505101392	ST770T 27S/PW930 PSU MB FG SI	-	Medium beam
910505100743	ST770T LED49S/830 PSU HMB SI	-	High-reflective metal reflector Medium beam 20 to 40 degrees
910505101443	ST780T 49S/930 PSU MB FG SI	-	Medium beam
910505101444	ST780T 49S/PW930 PSU MB FG SI	-	Medium beam
910505101445	ST780T 60S/827 PSU WB FG SI	-	Wide beam
910505101228	ST770S 17S/827 PSU WB FG WH	-	Wide beam
910505101229	ST770S 17S/830 PSU MB FG WH	-	Medium beam
910505101230	ST770S 17S/840 PSU VWB FG WH	-	Very wide beam
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	-	Wide beam
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	-	Medium beam
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	-	Very wide beam
910505101371	ST770S 39S/PW930 PSU VWB FG WH	-	Very wide beam
910505100723	ST770T 20S/830 PSU HNB WH	-	High-reflective metal reflector Narrow beam 10 to 20 degrees
910505100724	ST770T 27S/830 PSU HMB WH	-	High-reflective metal reflector Medium beam 20 to 40 degrees

Order Code	Full Product Name	Number of	
		light sources	Optic type
910505100725	ST770T LED27S/827 PSU HWB WH	-	High-reflective metal reflector Wide beam 40 to 80 degrees
910505100736	ST770T 39S/830 PSU HMB WH	-	High-reflective metal reflector Medium beam 20 to 40 degrees
910505100737	ST770T LED39S/827 PSU HWB WH	-	High-reflective metal reflector Wide beam 40 to 80 degrees
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	-	High-reflective metal reflector Oval - Horizontal beam
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	-	High-reflective metal reflector Medium beam 20 to 40 degrees
910505102315	ST770T 27S/ROSE WIA WB FG WH	-	Wide beam
910505102316	ST770T 39S/PW930 WIA WB WH	-	Wide beam
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	-	Wide beam
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	-	Medium beam
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	-	Very wide beam
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	-	High-reflective metal reflector Oval - Vertical beam
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	-	High-reflective metal reflector Oval - Horizontal beam
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	-	High-reflective metal reflector very wide beam >80 degrees
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	-	High-reflective metal reflector very wide beam >80 degrees
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	-	High-reflective metal reflector Medium beam 20 to 40 degrees
910505101425	ST780S 39S/827 PSU NB FG WH	-	Narrow beam
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	-	Wide beam
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	-	Medium beam
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	-	Very wide beam
910505101379	ST770T 20S/830 PSU NB FG WH	-	Narrow beam

Order Code	Full Product Name	Number of	
		light sources	Optic type
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	-	Oval vertical beam
910505101381	ST770T 27S/827 PSU WB FG WH	-	Wide beam
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	-	Oval horizontal beam
910505101384	ST770T 27S/830 PSU MB FG WH	-	Medium beam
910505101385	ST770T 27S/840 PSU VWB FG WH	-	Very wide beam
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	-	Oval vertical beam
910505101395	ST770T 39S/827 PSU WB FG WH	-	Wide beam
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	-	Oval horizontal beam
910505101398	ST770T 39S/830 PSU MB FG WH	-	Medium beam
910505101399	ST770T 39S/840 PSU MB FG WH	-	Medium beam
910505101378	ST770T 17S/930 PSU MB FG BK	-	Medium beam
910505101387	ST770T 27S/CH PSU MB FG BK	-	Medium beam
910505101388	ST770T 27S/FMT PSU MB FG BK	-	Medium beam
910505101389	ST770T 27S/FR PSU MB FG BK	-	Medium beam
910505101393	ST770T 27S/ROSE PSU MB FG BK	-	Medium beam
910505101401	ST770T 39S/930 PSU MB FG BK	-	Medium beam
910505101402	ST770T 39S/PC930 PSU MB FG BK	-	Medium beam
910505101403	ST770T 39S/PW930 PSU MB FG BK	-	Medium beam
910505100722	ST770T LED17S/930 PSU HMB BK	-	High-reflective metal reflector Medium beam 20 to 40 degrees
910505100731	ST770T LED27S/CH PSU HMB BK FG	-	High-reflective metal reflector Medium

Order Code	Full Product Name	Number of	
		light sources	Optic type
910505100732	ST770T 27S/FR PSU HMB FG BK	-	beam 20 to 40 degrees
910505100733	ST770T 27S/FMT PSU HMB FG BK	-	High-reflective metal reflector Medium beam 20 to 40 degrees
910505100747	ST780T 39S/830 PSU HNB WH	-	High-reflective metal reflector Narrow beam 10 to 20 degrees
910505100748	ST780T 49S/830 PSU HMB WH	-	High-reflective metal reflector Medium beam 20 to 40 degrees
910505100755	ST780T LED60S/830 PSU HMB WH	-	High-reflective metal reflector Medium beam 20 to 40 degrees
910505100721	ST770S LED17S/830 PSU HMB WH FG	-	High-reflective metal reflector Medium beam 20 to 40 degrees
910505101429	ST780S 49S/930 DIA-VLC HWB WH	-	High-reflective metal reflector Wide beam 40 to 80 degrees
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	-	High-reflective metal reflector Medium beam 20 to 40 degrees

Operating and Electrical

Order Code	Full Product Name	Protection class	Power
		IEC	Consumption
910505100730	ST770T LED27S/PW930 PSU HMB SI	Safety class II	19.8 W
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	Safety class II	29.5 W
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	Safety class II	19.6 W
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	Safety class II	31 W
910505101207	ST770B 17S/830 PSU-E MB FG WH	Safety class II	11.8 W
910505101208	ST770B 20S/830 PSU-E NB FG WH	Safety class II	16.6 W

Order Code	Full Product Name	Protection class	Power
		IEC	Consumption
910505101212	ST770B 27S/830 PSU-E MB FG WH	Safety class II	19.6 W
910505101213	ST770B 27S/840 PSU-E VWB FG WH	Safety class II	19.6 W
910505101214	ST770B 27S/930 PSU-E MB FG WH	Safety class II	19.8 W
910505101215	ST770B 27S/CH PSU-E MB FG WH	Safety class II	19.8 W
910505101216	ST770B 27S/FMT PSU-E MB FG WH	Safety class II	35 W
910505101217	ST770B 27S/FR PSU-E MB FG WH	Safety class II	32.5 W

Order Code	Full Product Name	Protection class IEC	Power Consumption
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	Safety class II	24.5 W
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	Safety class II	19.8 W
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	Safety class II	31 W
910505101221	ST770B 39S/827 PSU-E WB FG WH	Safety class II	31 W
910505101223	ST770B 39S/830 PSU-E MB FG WH	Safety class II	29 W
910505101224	ST770B 39S/840 PSU-E VWB FG WH	Safety class II	29 W
910505101368	ST770S 39S/930 DIA-VLC HWP BK	Safety class II	31.5 W
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	Safety class II	20.5 W
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	Safety class II	20.5 W
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	Safety class II	20.5 W
910505101410	ST770X 17S/830 DIA MB FG WH	Safety class I	11.8 W
910505101411	ST770X 20S/830 DIA NB FG WH	Safety class I	16.4 W
910505101412	ST770X 27S/827 DIA WB FG WH	Safety class I	19.6 W
910505101413	ST770X 27S/830 DIA MB FG WH	Safety class I	19.6 W
910505101414	ST770X 27S/840 DIA VWB FG WH	Safety class I	19.6 W
910505101415	ST770X 27S/930 DIA OVL-H WH	Safety class I	19.8 W
910505101416	ST770X 27S/CH DIA MB FG WH	Safety class I	19.6 W
910505101417	ST770X 27S/FMT DIA MB FG WH	Safety class I	34 W
910505101418	ST770X 27S/FR DIA MB FG WH	Safety class I	32 W
910505101421	ST770X 27S/ROSE DIA MB FG WH	Safety class I	29 W
910505101422	ST770X 39S/830 DIA MB FG WH	Safety class I	29 W
910505101423	ST770X 39S/930 DIA OVL-H WH	Safety class I	30.5 W
910505100749	ST780T LED49S/827 PSU HWP SI FG	Safety class II	37.5 W
910505100756	ST780T 60S/827 PSU HWP FG SI	Safety class II	44 W
910505101419	ST770X 27S/PC930 DIA MB FG BK	Safety class I	24 W

Order Code	Full Product Name	Protection class IEC	Power Consumption
910505101420	ST770X 27S/PW930 DIA MB FG BK	Safety class I	19.8 W
910505101434	ST780T 39S/827 PSU NB FG WH	Safety class II	29 W
910505101435	ST780T 39S/830 PSU NB FG WH	Safety class II	29 W
910505101436	ST780T 39S/840 PSU NB FG WH	Safety class II	27 W
910505101437	ST780T 39S/930 PSU NB FG WH	Safety class II	29 W
910505101438	ST780T 49S/827 PSU WB FG WH	Safety class II	37.5 W
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	Safety class II	39 W
910505101441	ST780T 49S/830 PSU MB FG WH	Safety class II	37.5 W
910505101442	ST780T 49S/840 PSU VWB FG WH	Safety class II	37.5 W
910505101446	ST780T 60S/830 PSU MB FG WH	Safety class II	46 W
910505101447	ST780T 60S/840 PSU MB FG WH	Safety class II	39.5 W
910505101431	ST780S 60S/827 DIA-VLC HWP BK	Safety class II	45 W
910505101432	ST780S 60S/830 DIA-VLC HWP BK	Safety class II	45 W
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	Safety class II	41 W
910505101386	ST770T 27S/930 PSU MB FG SI	Safety class II	19.8 W
910505101390	ST770T 27S/PC930 PSU MB FG SI	Safety class II	24.5 W
910505101392	ST770T 27S/PW930 PSU MB FG SI	Safety class II	19.8 W
910505100743	ST770T LED49S/830 PSU HWP SI	Safety class II	37.5 W
910505101443	ST780T 49S/930 PSU MB FG SI	Safety class II	38 W
910505101444	ST780T 49S/PW930 PSU MB FG SI	Safety class II	38 W
910505101445	ST780T 60S/827 PSU WB FG SI	Safety class II	46 W
910505101228	ST770S 17S/827 PSU WB FG WH	Safety class II	11.8 W
910505101229	ST770S 17S/830 PSU MB FG WH	Safety class II	11.8 W
910505101230	ST770S 17S/840 PSU VWB FG WH	Safety class II	11.8 W
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	Safety class II	20.5 W

Order Code	Full Product Name	Protection class IEC	Power Consumption
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	Safety class II	20.5 W
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	Safety class II	20.5 W
910505101371	ST770S 39S/PW930 PSU VWB FG WH	Safety class II	31 W
910505100723	ST770T 20S/830 PSU HNB WH	Safety class II	16.6 W
910505100724	ST770T 27S/830 PSU HMB WH	Safety class II	19.6 W
910505100725	ST770T LED27S/827 PSU HNB WH	Safety class II	19.6 W
910505100736	ST770T 39S/830 PSU HMB WH	Safety class II	29 W
910505100737	ST770T LED39S/827 PSU HNB WH	Safety class II	29 W
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	Safety class II	20.5 W
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	Safety class II	20.5 W
910505102315	ST770T 27S/ROSE WIA WB FG WH	Safety class II	30 W
910505102316	ST770T 39S/PW930 WIA WB WH	Safety class II	32 W
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	Safety class II	31.5 W
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	Safety class II	29.5 W
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	Safety class II	29.5 W
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	Safety class II	39 W
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	Safety class II	39 W
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	Safety class II	35.5 W
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	Safety class II	29.5 W
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	Safety class II	39.5 W
910505101425	ST780S 39S/827 PSU NB FG WH	Safety class II	29 W
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	Safety class II	39 W
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	Safety class II	39 W
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	Safety class II	39 W
910505101379	ST770T 20S/830 PSU NB FG WH	Safety class II	16.6 W

Order Code	Full Product Name	Protection class IEC	Power Consumption
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	Safety class II	20.5 W
910505101381	ST770T 27S/827 PSU WB FG WH	Safety class II	19.6 W
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	Safety class II	20.5 W
910505101384	ST770T 27S/830 PSU MB FG WH	Safety class II	19.6 W
910505101385	ST770T 27S/840 PSU VWB FG WH	Safety class II	19.6 W
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	Safety class II	31.5 W
910505101395	ST770T 39S/827 PSU WB FG WH	Safety class II	31 W
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	Safety class II	29.5 W
910505101398	ST770T 39S/830 PSU MB FG WH	Safety class II	29 W
910505101399	ST770T 39S/840 PSU MB FG WH	Safety class II	29 W
910505101378	ST770T 17S/930 PSU MB FG BK	Safety class II	11.8 W
910505101387	ST770T 27S/CH PSU MB FG BK	Safety class II	19.6 W
910505101388	ST770T 27S/FMT PSU MB FG BK	Safety class II	35 W
910505101389	ST770T 27S/FR PSU MB FG BK	Safety class II	32.5 W
910505101393	ST770T 27S/ROSE PSU MB FG BK	Safety class II	31 W
910505101401	ST770T 39S/930 PSU MB FG BK	Safety class II	31 W
910505101402	ST770T 39S/PC930 PSU MB FG BK	Safety class II	35 W
910505101403	ST770T 39S/PW930 PSU MB FG BK	Safety class II	31 W
910505100722	ST770T LED17S/930 PSU HMB BK	Safety class II	11.8 W
910505100731	ST770T LED27S/CH PSU HMB BK FG	Safety class II	19.6 W
910505100732	ST770T 27S/FR PSU HMB FG BK	Safety class II	28.5 W
910505100733	ST770T 27S/FMT PSU HMB FG BK	Safety class II	35 W
910505100747	ST780T 39S/830 PSU HNB WH	Safety class II	27 W
910505100748	ST780T 49S/830 PSU HMB WH	Safety class II	37.5 W
910505100755	ST780T LED60S/830 PSU HMB WH	Safety class II	44 W

Order Code	Full Product Name	Protection class IEC	Power Consumption
910505100721	ST770S LED17S/830 PSU HMB WH FG	Safety class II	11.8 W
910505101429	ST780S 49S/930 DIA-VLC HMB WH	Safety class II	39.5 W

Order Code	Full Product Name	Protection class IEC	Power Consumption
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	Safety class II	39.5 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505100730	ST770T LED27S/PW930 PSU HMB SI	No	-	Not applicable
910505101396	ST770T 39S/830 DIA- VLC HOVL-H SI	Yes	Visible light communication	1%
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	No	-	-
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	No	-	-
910505101207	ST770B 17S/830 PSU-E MB FG WH	No	-	Not applicable
910505101208	ST770B 20S/830 PSU-E NB FG WH	No	-	Not applicable
910505101212	ST770B 27S/830 PSU-E MB FG WH	No	-	Not applicable
910505101213	ST770B 27S/840 PSU-E VWB FG WH	No	-	Not applicable
910505101214	ST770B 27S/930 PSU-E MB FG WH	No	-	Not applicable
910505101215	ST770B 27S/CH PSU-E MB FG WH	No	-	Not applicable
910505101216	ST770B 27S/FMT PSU-E MB FG WH	No	-	Not applicable
910505101217	ST770B 27S/FR PSU-E MB FG WH	No	-	Not applicable
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	No	-	Not applicable
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	No	-	Not applicable
910505101220	ST770B 27S/ROSE PSU- E MB FG WH	No	-	Not applicable
910505101221	ST770B 39S/827 PSU-E WB FG WH	No	-	Not applicable
910505101223	ST770B 39S/830 PSU-E MB FG WH	No	-	Not applicable
910505101224	ST770B 39S/840 PSU-E VWB FG WH	No	-	Not applicable
910505101368	ST770S 39S/930 DIA- VLC HMB BK	Yes	-	1%
910505101209	ST770B 27S/827 DIA- VLC-E WB FG BK	Yes	Visible light communication	1%
910505101210	ST770B 27S/830 DIA- VLC-E MB FG BK	Yes	Visible light communication	1%

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505101211	ST770B 27S/830 DIA- VLC-E OVL-H BK	Yes	Visible light communication	1%
910505101410	ST770X 17S/830 DIA MB FG WH	Yes	-	1%
910505101411	ST770X 20S/830 DIA NB FG WH	Yes	-	1%
910505101412	ST770X 27S/827 DIA WB FG WH	Yes	-	1%
910505101413	ST770X 27S/830 DIA MB FG WH	Yes	-	1%
910505101414	ST770X 27S/840 DIA VWB FG WH	Yes	-	1%
910505101415	ST770X 27S/930 DIA OVL-H WH	Yes	-	1%
910505101416	ST770X 27S/CH DIA MB FG WH	Yes	-	1%
910505101417	ST770X 27S/FMT DIA MB FG WH	Yes	-	1%
910505101418	ST770X 27S/FR DIA MB FG WH	Yes	-	1%
910505101421	ST770X 27S/ROSE DIA MB FG WH	Yes	-	1%
910505101422	ST770X 39S/830 DIA MB FG WH	Yes	-	1%
910505101423	ST770X 39S/930 DIA OVL-H WH	Yes	-	1%
910505100749	ST780T LED49S/827 PSU HMB SI FG	No	-	Not applicable
910505100756	ST780T 60S/827 PSU HMB FG SI	No	-	Not applicable
910505101419	ST770X 27S/PC930 DIA MB FG BK	Yes	-	1%
910505101420	ST770X 27S/PW930 DIA MB FG BK	Yes	-	1%
910505101434	ST780T 39S/827 PSU NB FG WH	No	-	Not applicable
910505101435	ST780T 39S/830 PSU NB FG WH	No	-	Not applicable
910505101436	ST780T 39S/840 PSU NB FG WH	No	-	Not applicable
910505101437	ST780T 39S/930 PSU NB FG WH	No	-	Not applicable

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505101438	ST780T 49S/827 PSU WB FG WH	No	-	Not applicable
910505101440	ST780T 49S/830 DIA- VLC OVL-H WH	Yes	Visible light communication	1%
910505101441	ST780T 49S/830 PSU MB FG WH	No	-	Not applicable
910505101442	ST780T 49S/840 PSU VWB FG WH	No	-	Not applicable
910505101446	ST780T 60S/830 PSU MB FG WH	No	-	Not applicable
910505101447	ST780T 60S/840 PSU MB FG WH	No	-	Not applicable
910505101431	ST780S 60S/827 DIA- VLC HWB BK	Yes	Visible light communication	1%
910505101432	ST780S 60S/830 DIA- VLC HMB BK	Yes	Visible light communication	1%
910505101433	ST780S 60S/840 DIA- VLC VWB FG BK	Yes	Visible light communication	1%
910505101386	ST770T 27S/930 PSU MB FG SI	No	-	Not applicable
910505101390	ST770T 27S/PC930 PSU MB FG SI	No	-	Not applicable
910505101392	ST770T 27S/PW930 PSU MB FG SI	No	-	Not applicable
910505100743	ST770T LED49S/830 PSU HMB SI	No	-	Not applicable
910505101443	ST780T 49S/930 PSU MB FG SI	No	-	Not applicable
910505101444	ST780T 49S/PW930 PSU MB FG SI	No	-	Not applicable
910505101445	ST780T 60S/827 PSU WB FG SI	No	-	Not applicable
910505101228	ST770S 17S/827 PSU WB FG WH	No	-	Not applicable
910505101229	ST770S 17S/830 PSU MB FG WH	No	-	Not applicable
910505101230	ST770S 17S/840 PSU VWB FG WH	No	-	Not applicable
910505101231	ST770S 27S/827 DIA- VLC WB FG WH	Yes	Visible light communication	1%
910505101232	ST770S 27S/830 DIA- VLC MB FG WH	Yes	-	1%
910505101364	ST770S 27S/840 DIA- VLC VWB FG WH	Yes	Visible light communication	1%
910505101371	ST770S 39S/PW930 PSU VWB FG WH	No	-	Not applicable
910505100723	ST770T 20S/830 PSU HNB WH	No	-	Not applicable
910505100724	ST770T 27S/830 PSU HMB WH	No	-	Not applicable

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505100725	ST770T LED27S/827 PSU HWB WH	No	-	Not applicable
910505100736	ST770T 39S/830 PSU HMB WH	No	-	Not applicable
910505100737	ST770T LED39S/827 PSU HWB WH	No	-	Not applicable
910505101382	ST770T 27S/830 DIA- VLC HOVL-H WH	Yes	Visible light communication	1%
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	Yes	-	1%
910505102315	ST770T 27S/ROSE WIA WB FG WH	Yes	-	Not applicable
910505102316	ST770T 39S/PW930 WIA WB WH	Yes	-	Not applicable
910505101365	ST770S 39S/827 DIA- VLC WB FG SI	Yes	Visible light communication	1%
910505101366	ST770S 39S/830 DIA- VLC MB FG SI	Yes	Visible light communication	1%
910505101367	ST770S 39S/840 DIA- VLC VWB FG SI	Yes	-	1%
910505101405	ST770T 49S/830 DIA- VLC HOVL-V WH	Yes	-	1%
910505101439	ST780T 49S/830 DIA- VLC HOVL-H BK	Yes	Visible light communication	1%
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	Yes	-	1%
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	Yes	Visible light communication	1%
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	Yes	-	1%
910505101425	ST780S 39S/827 PSU NB FG WH	No	-	Not applicable
910505101426	ST780S 49S/827 DIA- VLC WB FG WH	Yes	Visible light communication	1%
910505101427	ST780S 49S/830 DIA- VLC MB FG WH	Yes	Visible light communication	1%
910505101428	ST780S 49S/840 DIA- VLC VWB FG WH	Yes	Visible light communication	1%
910505101379	ST770T 20S/830 PSU NB FG WH	No	-	Not applicable
910505101380	ST770T 27S/827 DIA- VLC OVL-V WH	Yes	-	1%
910505101381	ST770T 27S/827 PSU WB FG WH	No	-	Not applicable
910505101383	ST770T 27S/830 DIA- VLC OVL-H WH	Yes	-	1%
910505101384	ST770T 27S/830 PSU MB FG WH	No	-	Not applicable
910505101385	ST770T 27S/840 PSU VWB FG WH	No	-	Not applicable

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	Yes	-	1%
910505101395	ST770T 39S/827 PSU WB FG WH	No	-	Not applicable
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	Yes	-	1%
910505101398	ST770T 39S/830 PSU MB FG WH	No	-	Not applicable
910505101399	ST770T 39S/840 PSU MB FG WH	No	-	Not applicable
910505101378	ST770T 17S/930 PSU MB FG BK	No	-	Not applicable
910505101387	ST770T 27S/CH PSU MB FG BK	No	-	Not applicable
910505101388	ST770T 27S/FMT PSU MB FG BK	No	-	Not applicable
910505101389	ST770T 27S/FR PSU MB FG BK	No	-	Not applicable
910505101393	ST770T 27S/ROSE PSU MB FG BK	No	-	Not applicable
910505101401	ST770T 39S/930 PSU MB FG BK	No	-	Not applicable
910505101402	ST770T 39S/PC930 PSU MB FG BK	No	-	Not applicable

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910505100730	ST770T LED27S/PW930 PSU HMB SI	Silver
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	Silver
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	White
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	White
910505101207	ST770B 17S/830 PSU-E MB FG WH	White
910505101208	ST770B 20S/830 PSU-E NB FG WH	White
910505101212	ST770B 27S/830 PSU-E MB FG WH	White
910505101213	ST770B 27S/840 PSU-E VWB FG WH	White
910505101214	ST770B 27S/930 PSU-E MB FG WH	White
910505101215	ST770B 27S/CH PSU-E MB FG WH	White
910505101216	ST770B 27S/FMT PSU-E MB FG WH	White
910505101217	ST770B 27S/FR PSU-E MB FG WH	White
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	White
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	White
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	White
910505101221	ST770B 39S/827 PSU-E WB FG WH	White
910505101223	ST770B 39S/830 PSU-E MB FG WH	White
910505101224	ST770B 39S/840 PSU-E VWB FG WH	White
910505101368	ST770S 39S/930 DIA-VLC HWB BK	Black
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	Black
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	Black
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	Black
910505101410	ST770X 17S/830 DIA MB FG WH	White

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505101403	ST770T 39S/PW930 PSU MB FG BK	No	-	Not applicable
910505100722	ST770T LED17S/930 PSU HMB BK	No	-	Not applicable
910505100731	ST770T LED27S/CH PSU HMB BK FG	No	-	Not applicable
910505100732	ST770T 27S/FR PSU HMB FG BK	No	-	Not applicable
910505100733	ST770T 27S/FMT PSU HMB FG BK	No	-	Not applicable
910505100747	ST780T 39S/830 PSU HNB WH	No	-	Not applicable
910505100748	ST780T 49S/830 PSU HMB WH	No	-	Not applicable
910505100755	ST780T LED60S/830 PSU HMB WH	No	-	Not applicable
910505100721	ST770S LED17S/830 PSU HMB WH FG	No	-	Not applicable
910505101429	ST780S 49S/930 DIA-VLC HWB WH	Yes	Visible light communication	1%
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	Yes	Visible light communication	1%

Order Code	Full Product Name	Housing Color
910505101411	ST770X 20S/830 DIA NB FG WH	White
910505101412	ST770X 27S/827 DIA WB FG WH	White
910505101413	ST770X 27S/830 DIA MB FG WH	White
910505101414	ST770X 27S/840 DIA VWB FG WH	White
910505101415	ST770X 27S/930 DIA OVL-H WH	White
910505101416	ST770X 27S/CH DIA MB FG WH	White
910505101417	ST770X 27S/FMT DIA MB FG WH	White
910505101418	ST770X 27S/FR DIA MB FG WH	White
910505101421	ST770X 27S/ROSE DIA MB FG WH	White
910505101422	ST770X 39S/830 DIA MB FG WH	White
910505101423	ST770X 39S/930 DIA OVL-H WH	White
910505100749	ST780T LED49S/827 PSU HWB SI FG	Silver
910505100756	ST780T 60S/827 PSU HWB FG SI	Silver
910505101419	ST770X 27S/PC930 DIA MB FG BK	Black
910505101420	ST770X 27S/PW930 DIA MB FG BK	Black
910505101434	ST780T 39S/827 PSU NB FG WH	White
910505101435	ST780T 39S/830 PSU NB FG WH	White
910505101436	ST780T 39S/840 PSU NB FG WH	White
910505101437	ST780T 39S/930 PSU NB FG WH	White
910505101438	ST780T 49S/827 PSU WB FG WH	White
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	White
910505101441	ST780T 49S/830 PSU MB FG WH	White
910505101442	ST780T 49S/840 PSU VWB FG WH	White

Order Code	Full Product Name	Housing Color
910505101446	ST780T 60S/830 PSU MB FG WH	White
910505101447	ST780T 60S/840 PSU MB FG WH	White
910505101431	ST780S 60S/827 DIA-VLC HWB BK	Black
910505101432	ST780S 60S/830 DIA-VLC HMB BK	Black
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	Black
910505101386	ST770T 27S/930 PSU MB FG SI	Silver
910505101390	ST770T 27S/PC930 PSU MB FG SI	Silver
910505101392	ST770T 27S/PW930 PSU MB FG SI	Silver
910505100743	ST770T LED49S/830 PSU HMB SI	Silver
910505101443	ST780T 49S/930 PSU MB FG SI	Silver
910505101444	ST780T 49S/PW930 PSU MB FG SI	Silver
910505101445	ST780T 60S/827 PSU WB FG SI	Silver
910505101228	ST770S 17S/827 PSU WB FG WH	White
910505101229	ST770S 17S/830 PSU MB FG WH	White
910505101230	ST770S 17S/840 PSU VWB FG WH	White
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	White
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	White
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	White
910505101371	ST770S 39S/PW930 PSU VWB FG WH	White
910505100723	ST770T 20S/830 PSU HNB WH	White
910505100724	ST770T 27S/830 PSU HMB WH	White
910505100725	ST770T LED27S/827 PSU HWB WH	White
910505100736	ST770T 39S/830 PSU HMB WH	White
910505100737	ST770T LED39S/827 PSU HWB WH	White
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	White
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	White
910505102315	ST770T 27S/ROSE WIA WB FG WH	Black
910505102316	ST770T 39S/PW930 WIA WB WH	Black
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	Silver
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	Silver
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	Silver
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	White
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	Black
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	Black
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	Black

Order Code	Full Product Name	Housing Color
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	White
910505101425	ST780S 39S/827 PSU NB FG WH	White
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	White
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	White
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	White
910505101379	ST770T 20S/830 PSU NB FG WH	White
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	White
910505101381	ST770T 27S/827 PSU WB FG WH	White
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	White
910505101384	ST770T 27S/830 PSU MB FG WH	White
910505101385	ST770T 27S/840 PSU VWB FG WH	White
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	White
910505101395	ST770T 39S/827 PSU WB FG WH	White
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	White
910505101398	ST770T 39S/830 PSU MB FG WH	White
910505101399	ST770T 39S/840 PSU MB FG WH	White
910505101378	ST770T 17S/930 PSU MB FG BK	Black
910505101387	ST770T 27S/CH PSU MB FG BK	Black
910505101388	ST770T 27S/FMT PSU MB FG BK	Black
910505101389	ST770T 27S/FR PSU MB FG BK	Black
910505101393	ST770T 27S/ROSE PSU MB FG BK	Black
910505101401	ST770T 39S/930 PSU MB FG BK	Black
910505101402	ST770T 39S/PC930 PSU MB FG BK	Black
910505101403	ST770T 39S/PW930 PSU MB FG BK	Black
910505100722	ST770T LED17S/930 PSU HMB BK	Black
910505100731	ST770T LED27S/CH PSU HMB BK FG	Black
910505100732	ST770T 27S/FR PSU HMB FG BK	Black
910505100733	ST770T 27S/FMT PSU HMB FG BK	Black
910505100747	ST780T 39S/830 PSU HNB WH	White
910505100748	ST780T 49S/830 PSU HMB WH	White
910505100755	ST780T LED60S/830 PSU HMB WH	White
910505100721	ST770S LED17S/830 PSU HMB WH FG	White
910505101429	ST780S 49S/930 DIA-VLC HWB WH	White
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	White

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505100730	ST770T LED27S/PW930 PSU HMB SI	(0.422,0.386)<2
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	(0.434,0.403)<3
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	(0.434,0.403)<3
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	(0.434,0.403)<2
910505101207	ST770B 17S/830 PSU-E MB FG WH	(0.434,0.403)<3
910505101208	ST770B 20S/830 PSU-E NB FG WH	(0.434,0.403)<3
910505101212	ST770B 27S/830 PSU-E MB FG WH	(0.434,0.403)<3
910505101213	ST770B 27S/840 PSU-E VWB FG WH	(0.382,0.380)<3
910505101214	ST770B 27S/930 PSU-E MB FG WH	(0.434,0.403)<2
910505101215	ST770B 27S/CH PSU-E MB FG WH	(0.458,0.410)<3
910505101216	ST770B 27S/FMT PSU-E MB FG WH	(0.457,0.385)<3
910505101217	ST770B 27S/FR PSU-E MB FG WH	(0.343,0.331)<3
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	(0.422,0.386)<2

Order Code	Full Product Name	Initial chromaticity
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	(0.422,0.386)<2
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	(0.478,0.382)<2
910505101221	ST770B 39S/827 PSU-E WB FG WH	(0.458,0.410)<3
910505101223	ST770B 39S/830 PSU-E MB FG WH	(0.434,0.403)<3
910505101224	ST770B 39S/840 PSU-E VWB FG WH	(0.382,0.380)<3
910505101368	ST770S 39S/930 DIA-VLC HWB BK	(0.434,0.403)<2
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	(0.458,0.410)<3
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	(0.434,0.403)<3
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	(0.434,0.403)<3
910505101410	ST770X 17S/830 DIA MB FG WH	(0.434,0.403)<3
910505101411	ST770X 20S/830 DIA NB FG WH	(0.434,0.403)<3
910505101412	ST770X 27S/827 DIA WB FG WH	(0.458,0.410)<3
910505101413	ST770X 27S/830 DIA MB FG WH	(0.434,0.403)<3

Order Code	Full Product Name	Initial chromaticity
910505101414	ST770X 27S/840 DIA VWB FG WH	(0.382,0.380)<3
910505101415	ST770X 27S/930 DIA OVL-H WH	(0.434,0.403)<2
910505101416	ST770X 27S/CH DIA MB FG WH	(0.458,0.410)<3
910505101417	ST770X 27S/FMT DIA MB FG WH	(0.457,0.385)<3
910505101418	ST770X 27S/FR DIA MB FG WH	(0.343,0.331)<3
910505101421	ST770X 27S/ROSE DIA MB FG WH	(0.478,0.382)<2
910505101422	ST770X 39S/830 DIA MB FG WH	(0.434,0.403)<3
910505101423	ST770X 39S/930 DIA OVL-H WH	(0.434,0.403)<2
910505100749	ST780T LED49S/827 PSU HWB SI FG	(0.458,0.410)<3
910505100756	ST780T 60S/827 PSU HWB FG SI	(0.458,0.410)<3
910505101419	ST770X 27S/PC930 DIA MB FG BK	(0.422,0.386)<2
910505101420	ST770X 27S/PW930 DIA MB FG BK	(0.422,0.386)<2
910505101434	ST780T 39S/827 PSU NB FG WH	(0.458,0.410)<3
910505101435	ST780T 39S/830 PSU NB FG WH	(0.434,0.403)<3
910505101436	ST780T 39S/840 PSU NB FG WH	(0.382,0.380)<3
910505101437	ST780T 39S/930 PSU NB FG WH	(0.434,0.403)<2
910505101438	ST780T 49S/827 PSU WB FG WH	(0.458,0.410)<3
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	(0.434,0.403)<3
910505101441	ST780T 49S/830 PSU MB FG WH	(0.434,0.403)<3
910505101442	ST780T 49S/840 PSU VWB FG WH	(0.382,0.380)<3
910505101446	ST780T 60S/830 PSU MB FG WH	(0.434,0.403)<3
910505101447	ST780T 60S/840 PSU MB FG WH	(0.382,0.380)<3
910505101431	ST780S 60S/827 DIA-VLC HWB BK	(0.458,0.410)<3
910505101432	ST780S 60S/830 DIA-VLC HMB BK	(0.434,0.403)<3
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	(0.382,0.380)<3
910505101386	ST770T 27S/930 PSU MB FG SI	(0.434,0.403)<2
910505101390	ST770T 27S/PC930 PSU MB FG SI	(0.422,0.386)<2
910505101392	ST770T 27S/PW930 PSU MB FG SI	(0.422,0.386)<2
910505100743	ST770T LED49S/830 PSU HMB SI	(0.434,0.403)<3
910505101443	ST780T 49S/930 PSU MB FG SI	(0.434,0.403)<2
910505101444	ST780T 49S/PW930 PSU MB FG SI	(0.422,0.386)<2
910505101445	ST780T 60S/827 PSU WB FG SI	(0.458,0.410)<3
910505101228	ST770S 17S/827 PSU WB FG WH	(0.458,0.410)<3
910505101229	ST770S 17S/830 PSU MB FG WH	(0.434,0.403)<3
910505101230	ST770S 17S/840 PSU VWB FG WH	(0.382,0.380)<3
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	(0.458,0.410)<3
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	(0.434,0.403)<3
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	(0.382,0.380)<3
910505101371	ST770S 39S/PW930 PSU VWB FG WH	(0.422,0.386)<2
910505100723	ST770T 20S/830 PSU HNB WH	(0.434,0.403)<3
910505100724	ST770T 27S/830 PSU HMB WH	(0.434,0.403)<3
910505100725	ST770T LED27S/827 PSU HWB WH	(0.458,0.410)<3
910505100736	ST770T 39S/830 PSU HMB WH	(0.434,0.403)<3
910505100737	ST770T LED39S/827 PSU HWB WH	(0.458,0.410)<3
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	(0.434,0.403)<3

Order Code	Full Product Name	Initial chromaticity
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	(0.422,0.386)<2
910505102315	ST770T 27S/ROSE WIA WB FG WH	(0.478,0.382)<2
910505102316	ST770T 39S/PW930 WIA WB WH	(0.422,0.386)<2
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	(0.458,0.410)<3
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	(0.434,0.403)<3
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	(0.382,0.380)<3
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	(0.434,0.403)<3
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	(0.434,0.403)<3
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	(0.422,0.386)<2
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	(0.422,0.386)<2
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	(0.422,0.386)<2
910505101425	ST780S 39S/827 PSU NB FG WH	(0.458,0.410)<3
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	(0.458,0.410)<3
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	(0.434,0.403)<3
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	(0.382,0.380)<3
910505101379	ST770T 20S/830 PSU NB FG WH	(0.434,0.403)<3
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	(0.458,0.410)<3
910505101381	ST770T 27S/827 PSU WB FG WH	(0.458,0.410)<3
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	(0.434,0.403)<3
910505101384	ST770T 27S/830 PSU MB FG WH	(0.434,0.403)<3
910505101385	ST770T 27S/840 PSU VWB FG WH	(0.382,0.380)<3
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	(0.458,0.410)<3
910505101395	ST770T 39S/827 PSU WB FG WH	(0.458,0.410)<3
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	(0.434,0.403)<3
910505101398	ST770T 39S/830 PSU MB FG WH	(0.434,0.403)<3
910505101399	ST770T 39S/840 PSU MB FG WH	(0.382,0.380)<3
910505101378	ST770T 17S/930 PSU MB FG BK	(0.434,0.403)<2
910505101387	ST770T 27S/CH PSU MB FG BK	(0.458,0.410)<3
910505101388	ST770T 27S/FMT PSU MB FG BK	(0.457,0.385)<3
910505101389	ST770T 27S/FR PSU MB FG BK	(0.343,0.331)<3
910505101393	ST770T 27S/ROSE PSU MB FG BK	(0.478,0.382)<2
910505101401	ST770T 39S/930 PSU MB FG BK	(0.434,0.403)<2
910505101402	ST770T 39S/PC930 PSU MB FG BK	(0.422,0.386)<2
910505101403	ST770T 39S/PW930 PSU MB FG BK	(0.422,0.386)<2
910505100722	ST770T LED17S/930 PSU HMB BK	(0.434,0.403)<2
910505100731	ST770T LED27S/CH PSU HMB BK FG	(0.458,0.410)<3
910505100732	ST770T 27S/FR PSU HMB FG BK	(0.343,0.331)<3
910505100733	ST770T 27S/FMT PSU HMB FG BK	(0.457,0.385)<3
910505100747	ST780T 39S/830 PSU HNB WH	(0.434,0.403)<3
910505100748	ST780T 49S/830 PSU HMB WH	(0.434,0.403)<3
910505100755	ST780T LED60S/830 PSU HMB WH	(0.434,0.403)<3
910505100721	ST770S LED17S/830 PSU HMB WH FG	(0.434,0.403)<3
910505101429	ST780S 49S/930 DIA-VLC HWB WH	(0.434,0.403)<2
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	(0.422,0.386)<2

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h
910505100730	ST770T LED27S/PW930 PSU HMB SI	-
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	-
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	1 %

Order Code	Full Product Name	Driver failure rate at 5000 h
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	1 %
910505101207	ST770B 17S/830 PSU-E MB FG WH	-
910505101208	ST770B 20S/830 PSU-E NB FG WH	-

Order Code	Full Product Name	Driver failure rate at 5000 h
910505101212	ST770B 27S/830 PSU-E MB FG WH	-
910505101213	ST770B 27S/840 PSU-E VWB FG WH	-
910505101214	ST770B 27S/930 PSU-E MB FG WH	-
910505101215	ST770B 27S/CH PSU-E MB FG WH	-
910505101216	ST770B 27S/FMT PSU-E MB FG WH	-
910505101217	ST770B 27S/FR PSU-E MB FG WH	-
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	-
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	-
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	-
910505101221	ST770B 39S/827 PSU-E WB FG WH	-
910505101223	ST770B 39S/830 PSU-E MB FG WH	-
910505101224	ST770B 39S/840 PSU-E VWB FG WH	-
910505101368	ST770S 39S/930 DIA-VLC HWB BK	-
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	-
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	-
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	-
910505101410	ST770X 17S/830 DIA MB FG WH	-
910505101411	ST770X 20S/830 DIA NB FG WH	-
910505101412	ST770X 27S/827 DIA WB FG WH	-
910505101413	ST770X 27S/830 DIA MB FG WH	-
910505101414	ST770X 27S/840 DIA VWB FG WH	-
910505101415	ST770X 27S/930 DIA OVL-H WH	-
910505101416	ST770X 27S/CH DIA MB FG WH	-
910505101417	ST770X 27S/FMT DIA MB FG WH	-
910505101418	ST770X 27S/FR DIA MB FG WH	-
910505101421	ST770X 27S/ROSE DIA MB FG WH	-
910505101422	ST770X 39S/830 DIA MB FG WH	-
910505101423	ST770X 39S/930 DIA OVL-H WH	-
910505100749	ST780T LED49S/827 PSU HWB SI FG	-
910505100756	ST780T 60S/827 PSU HWB FG SI	-
910505101419	ST770X 27S/PC930 DIA MB FG BK	-
910505101420	ST770X 27S/PW930 DIA MB FG BK	-
910505101434	ST780T 39S/827 PSU NB FG WH	-
910505101435	ST780T 39S/830 PSU NB FG WH	-
910505101436	ST780T 39S/840 PSU NB FG WH	-
910505101437	ST780T 39S/930 PSU NB FG WH	-
910505101438	ST780T 49S/827 PSU WB FG WH	-
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	-
910505101441	ST780T 49S/830 PSU MB FG WH	-
910505101442	ST780T 49S/840 PSU VWB FG WH	-
910505101446	ST780T 60S/830 PSU MB FG WH	-
910505101447	ST780T 60S/840 PSU MB FG WH	-
910505101431	ST780S 60S/827 DIA-VLC HWB BK	-
910505101432	ST780S 60S/830 DIA-VLC HMB BK	-
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	-
910505101386	ST770T 27S/930 PSU MB FG SI	-
910505101390	ST770T 27S/PC930 PSU MB FG SI	-
910505101392	ST770T 27S/PW930 PSU MB FG SI	-
910505100743	ST770T LED49S/830 PSU HMB SI	-
910505101443	ST780T 49S/930 PSU MB FG SI	-
910505101444	ST780T 49S/PW930 PSU MB FG SI	-
910505101445	ST780T 60S/827 PSU WB FG SI	-

Order Code	Full Product Name	Driver failure rate at 5000 h
910505101228	ST770S 17S/827 PSU WB FG WH	-
910505101229	ST770S 17S/830 PSU MB FG WH	-
910505101230	ST770S 17S/840 PSU VWB FG WH	-
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	-
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	-
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	-
910505101371	ST770S 39S/PW930 PSU VWB FG WH	-
910505100723	ST770T 20S/830 PSU HNB WH	-
910505100724	ST770T 27S/830 PSU HMB WH	-
910505100725	ST770T LED27S/827 PSU HWB WH	-
910505100736	ST770T 39S/830 PSU HMB WH	-
910505100737	ST770T LED39S/827 PSU HWB WH	-
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	-
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	-
910505102315	ST770T 27S/ROSE WIA WB FG WH	-
910505102316	ST770T 39S/PW930 WIA WB WH	-
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	-
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	-
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	-
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	-
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	-
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	-
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	-
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	-
910505101425	ST780S 39S/827 PSU NB FG WH	-
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	-
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	-
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	-
910505101379	ST770T 20S/830 PSU NB FG WH	-
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	-
910505101381	ST770T 27S/827 PSU WB FG WH	-
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	-
910505101384	ST770T 27S/830 PSU MB FG WH	-
910505101385	ST770T 27S/840 PSU VWB FG WH	-
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	-
910505101395	ST770T 39S/827 PSU WB FG WH	-
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	-
910505101398	ST770T 39S/830 PSU MB FG WH	-
910505101399	ST770T 39S/840 PSU MB FG WH	-
910505101378	ST770T 17S/930 PSU MB FG BK	-
910505101387	ST770T 27S/CH PSU MB FG BK	-
910505101388	ST770T 27S/FMT PSU MB FG BK	-
910505101389	ST770T 27S/FR PSU MB FG BK	-
910505101393	ST770T 27S/ROSE PSU MB FG BK	-
910505101401	ST770T 39S/930 PSU MB FG BK	-
910505101402	ST770T 39S/PC930 PSU MB FG BK	-
910505101403	ST770T 39S/PW930 PSU MB FG BK	-
910505100722	ST770T LED17S/930 PSU HMB BK	-
910505100731	ST770T LED27S/CH PSU HMB BK FG	-
910505100732	ST770T 27S/FR PSU HMB FG BK	-
910505100733	ST770T 27S/FMT PSU HMB FG BK	-
910505100747	ST780T 39S/830 PSU HNB WH	-

Order Code	Full Product Name	Driver failure rate at 5000 h
910505100748	ST780T 49S/830 PSU HMB WH	-
910505100755	ST780T LED60S/830 PSU HMB WH	-
910505100721	ST770S LED17S/830 PSU HMB WH FG	-

Order Code	Full Product Name	Driver failure rate at 5000 h
910505101429	ST780S 49S/930 DIA-VLC HWB WH	-
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	-

Product Data




Order Code	Full Product Name	Product family code
910505100730	ST770T LED27S/PW930 PSU HMB SI	ST770T
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	ST770T
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	ST770B
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	ST770B
910505101207	ST770B 17S/830 PSU-E MB FG WH	ST770B
910505101208	ST770B 20S/830 PSU-E NB FG WH	ST770B
910505101212	ST770B 27S/830 PSU-E MB FG WH	ST770B
910505101213	ST770B 27S/840 PSU-E VWB FG WH	ST770B
910505101214	ST770B 27S/930 PSU-E MB FG WH	ST770B
910505101215	ST770B 27S/CH PSU-E MB FG WH	ST770B
910505101216	ST770B 27S/FMT PSU-E MB FG WH	ST770B
910505101217	ST770B 27S/FR PSU-E MB FG WH	ST770B
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	ST770B
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	ST770B
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	ST770B
910505101221	ST770B 39S/827 PSU-E WB FG WH	ST770B
910505101223	ST770B 39S/830 PSU-E MB FG WH	ST770B
910505101224	ST770B 39S/840 PSU-E VWB FG WH	ST770B
910505101368	ST770S 39S/930 DIA-VLC HWB BK	ST770S
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	ST770B
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	ST770B
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	ST770B
910505101410	ST770X 17S/830 DIA MB FG WH	ST770X
910505101411	ST770X 20S/830 DIA NB FG WH	ST770X
910505101412	ST770X 27S/827 DIA WB FG WH	ST770X
910505101413	ST770X 27S/830 DIA MB FG WH	ST770X
910505101414	ST770X 27S/840 DIA VWB FG WH	ST770X
910505101415	ST770X 27S/930 DIA OVL-H WH	ST770X
910505101416	ST770X 27S/CH DIA MB FG WH	ST770X
910505101417	ST770X 27S/FMT DIA MB FG WH	ST770X
910505101418	ST770X 27S/FR DIA MB FG WH	ST770X
910505101421	ST770X 27S/ROSE DIA MB FG WH	ST770X
910505101422	ST770X 39S/830 DIA MB FG WH	ST770X
910505101423	ST770X 39S/930 DIA OVL-H WH	ST770X
910505100749	ST780T LED49S/827 PSU HWB SI FG	ST780T
910505100756	ST780T 60S/827 PSU HWB FG SI	ST780T
910505101419	ST770X 27S/PC930 DIA MB FG BK	ST770X
910505101420	ST770X 27S/PW930 DIA MB FG BK	ST770X
910505101434	ST780T 39S/827 PSU NB FG WH	ST780T
910505101435	ST780T 39S/830 PSU NB FG WH	ST780T
910505101436	ST780T 39S/840 PSU NB FG WH	ST780T
910505101437	ST780T 39S/930 PSU NB FG WH	ST780T
910505101438	ST780T 49S/827 PSU WB FG WH	ST780T
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	ST780T
910505101441	ST780T 49S/830 PSU MB FG WH	ST780T

Order Code	Full Product Name	Product family code
910505101442	ST780T 49S/840 PSU VWB FG WH	ST780T
910505101446	ST780T 60S/830 PSU MB FG WH	ST780T
910505101447	ST780T 60S/840 PSU MB FG WH	ST780T
910505101431	ST780S 60S/827 DIA-VLC HWB BK	ST780S
910505101432	ST780S 60S/830 DIA-VLC HMB BK	ST780S
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	ST780S
910505101386	ST770T 27S/930 PSU MB FG SI	ST770T
910505101390	ST770T 27S/PC930 PSU MB FG SI	ST770T
910505101392	ST770T 27S/PW930 PSU MB FG SI	ST770T
910505100743	ST770T LED49S/830 PSU HMB SI	ST770T
910505101443	ST780T 49S/930 PSU MB FG SI	ST780T
910505101444	ST780T 49S/PW930 PSU MB FG SI	ST780T
910505101445	ST780T 60S/827 PSU WB FG SI	ST780T
910505101228	ST770S 17S/827 PSU WB FG WH	ST770S
910505101229	ST770S 17S/830 PSU MB FG WH	ST770S
910505101230	ST770S 17S/840 PSU VWB FG WH	ST770S
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	ST770S
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	ST770S
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	ST770S
910505101371	ST770S 39S/PW930 PSU VWB FG WH	ST770S
910505100723	ST770T 20S/830 PSU HNB WH	ST770T
910505100724	ST770T 27S/830 PSU HMB WH	ST770T
910505100725	ST770T LED27S/827 PSU HWB WH	ST770T
910505100736	ST770T 39S/830 PSU HMB WH	ST770T
910505100737	ST770T LED39S/827 PSU HWB WH	ST770T
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	ST770T
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	ST770T
910505102315	ST770T 27S/ROSE WIA WB FG WH	ST770T
910505102316	ST770T 39S/PW930 WIA WB WH	ST770T
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	ST770S
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	ST770S
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	ST770S
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	ST770T
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	ST780T
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	ST770S
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	ST770S
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	ST770S
910505101425	ST780S 39S/827 PSU NB FG WH	ST780S
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	ST780S
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	ST780S
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	ST780S
910505101379	ST770T 20S/830 PSU NB FG WH	ST770T
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	ST770T
910505101381	ST770T 27S/827 PSU WB FG WH	ST770T
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	ST770T

Order Code	Full Product Name	Product family code
910505101384	ST770T 27S/830 PSU MB FG WH	ST770T
910505101385	ST770T 27S/840 PSU VWB FG WH	ST770T
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	ST770T
910505101395	ST770T 39S/827 PSU WB FG WH	ST770T
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	ST770T
910505101398	ST770T 39S/830 PSU MB FG WH	ST770T
910505101399	ST770T 39S/840 PSU MB FG WH	ST770T
910505101378	ST770T 17S/930 PSU MB FG BK	ST770T
910505101387	ST770T 27S/CH PSU MB FG BK	ST770T
910505101388	ST770T 27S/FMT PSU MB FG BK	ST770T
910505101389	ST770T 27S/FR PSU MB FG BK	ST770T
910505101393	ST770T 27S/ROSE PSU MB FG BK	ST770T
910505101401	ST770T 39S/930 PSU MB FG BK	ST770T

Order Code	Full Product Name	Product family code
910505101402	ST770T 39S/PC930 PSU MB FG BK	ST770T
910505101403	ST770T 39S/PW930 PSU MB FG BK	ST770T
910505100722	ST770T LED17S/930 PSU HMB BK	ST770T
910505100731	ST770T LED27S/CH PSU HMB BK FG	ST770T
910505100732	ST770T 27S/FR PSU HMB FG BK	ST770T
910505100733	ST770T 27S/FMT PSU HMB FG BK	ST770T
910505100747	ST780T 39S/830 PSU HNB WH	ST780T
910505100748	ST780T 49S/830 PSU HMB WH	ST780T
910505100755	ST780T LED60S/830 PSU HMB WH	ST780T
910505100721	ST770S LED17S/830 PSU HMB WH FG	ST770S
910505101429	ST780S 49S/930 DIA-VLC HWB WH	ST780S
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	ST780S




Polar Wide Diagrams



Polar Normal (separate) - ST770T1 - 910500465998

Polar Normal (separate) - ST770T1 - 910505101405

Polar Normal (separate) - ST770T1 - 910505101224




Polar Normal (separate) - ST770T1 - 910505101371


Polar Normal (separate) - ST780T1 - 910505101439

Polar Normal (separate) - ST770T1 - 910505101410


Polar Wide Diagrams




Polar Normal (separate) - ST770TI - 910505101392




Polar Normal (separate) - ST770TI - 910505101402




Polar Normal (separate) - ST770TI - 910505101213




Polar Normal (separate) - ST770TI - 910505101423




Polar Normal (separate) - ST770TI - 910505101232




Polar Normal (separate) - ST770TI - 910505101391



Polar Normal (separate) - ST770TI - 910505101207




Polar Normal (separate) - ST780TI - 910505101426




Polar Normal (separate) - ST770TI - 910505101367


Polar Wide Diagrams




Polar Normal (separate) - ST780TI - 910505101431




Polar Normal (separate) - ST780TI - 910505101440




Polar Normal (separate) - ST770TI - 910505101403




Polar Normal (separate) - ST780TI - 910505101447




Polar Normal (separate) - ST770TI - 910505101395




Polar Normal (separate) - ST770TI - 910505101394



Polar Normal (separate) - ST770TI - 910505101216




Polar Normal (separate) - ST770TI - 910505100731




Polar Normal (separate) - ST770TI - 910505101397


Polar Wide Diagrams




Polar Normal (separate) - ST780TI - 910505101428




Polar Normal (separate) - ST770TI - 910505101368




Polar Normal (separate) - ST770TI - 910505101369




Polar Normal (separate) - ST770TI - 910505101419




Polar Normal (separate) - ST770TI - 910505101413




Polar Normal (separate) - ST770TI - 910505101414



Polar Normal (separate) - ST770TI - 910505101377




Polar Normal (separate) - ST770TI - 910505101387




Polar Normal (separate) - ST770TI - 910505101418


Polar Wide Diagrams




Polar Normal (separate) - ST770TI - 910505101380




Polar Normal (separate) - ST770TI - 910505101384




Polar Normal (separate) - ST770TI - 910505101411




Polar Normal (separate) - ST770TI - 910505101386




Polar Normal (separate) - ST780TI - 910505101433




Polar Normal (separate) - ST780TI - 910505101437



Polar Normal (separate) - ST770TI - 910505101208






Polar Normal (separate) - ST780TI - 910505101430



Polar Normal (separate) - ST770TI - 910505101383




Polar Wide Diagrams



Polar Normal (separate) - ST770TI - 910505101212

Polar Normal (separate) - ST770TI - 910505101228




Polar Normal (separate) - ST780TI - 910505101438



Polar Normal (separate) - ST770TI - 910505101381

Polar Normal (separate) - ST780TI - 910505101445

Polar Normal (separate) - ST770TI - 910505101421




Polar Normal (separate) - ST770TI - 910505102316


Polar Normal (separate) - ST770TI - 910505101417

Polar Normal (separate) - ST770TI - 910505101396


Polar Wide Diagrams




Polar Normal (separate) - ST780TI - 910505101425




Polar Normal (separate) - ST770TI - 910505101388




Polar Normal (separate) - ST770TI - 910505101214




Polar Normal (separate) - ST770TI - 910505101370




Polar Normal (separate) - ST770TI - 910505101390




Polar Normal (separate) - ST770TI - 910505101382



Polar Normal (separate) - ST770TI - 910505101221




Polar Normal (separate) - ST780TI - 910505101432




Polar Normal (separate) - ST770TI - 910505101416


Polar Wide Diagrams




Polar Normal (separate) - ST770TI - 910505101219




Polar Normal (separate) - ST780TI - 910505101435




Polar Normal (separate) - ST780TI - 910505101441




Polar Normal (separate) - ST770TI - 910505101364




Polar Normal (separate) - ST770TI - 910505101215




Polar Normal (separate) - ST780TI - 910505101427



Polar Normal (separate) - ST770TI - 910505100733




Polar Normal (separate) - ST770TI - 910505101231




Polar Normal (separate) - ST770TI - 910505101223


Polar Wide Diagrams



Polar Normal (separate) - ST770TI - 910505101366




Polar Normal (separate) - ST770TI - 910505101378




Polar Normal (separate) - ST770TI - 910505101415

Polar Normal (separate) - ST770TI - 910505101422




Polar Normal (separate) - ST770TI - 910505101210




Polar Normal (separate) - ST770TI - 910505101389

Polar Normal (separate) - ST770TI - 910505101211




Polar Normal (separate) - ST770TI - 910505101393




Polar Normal (separate) - ST770TI - 910505101401


Polar Wide Diagrams




Polar Normal (separate) - ST780TI - 910505101442




Polar Normal (separate) - ST770TI - 910505102315




Polar Normal (separate) - ST770TI - 910505101365




Polar Normal (separate) - ST770TI - 910505101218




Polar Normal (separate) - ST770TI - 910505101420




Polar Normal (separate) - ST780TI - 910505101436



Polar Normal (separate) - ST770TI - 910505101220






Polar Normal (separate) - ST780TI - 910505101443



Polar Normal (separate) - ST770TI - 910505101379




Polar Wide Diagrams



Polar Normal (separate) - ST770TI - 910505101398

Polar Normal (separate) - ST770TI - 910505101399




Polar Normal (separate) - ST780TI - 910505101429



Polar Normal (separate) - ST770TI - 910505101209

Polar Normal (separate) - ST770TI - 910505101217

Polar Normal (separate) - ST770TI - 910505101230




Polar Normal (separate) - ST770TI - 910505101229


Polar Normal (separate) - ST770TI - 910505101385

Polar Normal (separate) - ST770TI - 910505101412


Polar Wide Diagrams




Polar Normal (separate) - ST780TI - 910505101434




Polar Normal (separate) - ST780TI - 910505101444




Polar Normal (separate) - ST780TI - 910505101446




Polar Normal (separate) - ST770TI - 910505100014




Polar Normal (separate) - ST770TI - 910505100723




Polar Normal (separate) - ST770TI - 910505100721



Polar Normal (separate) - ST770TI - 910505100722






Polar Normal (separate) - ST770TI - 910505100724



Polar Normal (separate) - ST770TI - 910505100725




Polar Wide Diagrams



Polar Normal (separate) - ST770TI - 910505100730

Polar Normal (separate) - ST770TI - 910505100732




Polar Normal (separate) - ST770TI - 910505100743



Polar Normal (separate) - ST780TI - 910505100747

Polar Normal (separate) - ST780TI - 910505100748

Polar Normal (separate) - ST770TI - 910505100737




Polar Normal (separate) - ST770TI - 910505100736

Polar Normal (separate) - ST780TI - 910505100755

Polar Normal (separate) - ST780TI - 910505100756

Polar Wide Diagrams



Polar Normal (separate) - ST780TI - 910505100749

