



# Product Description

## Ecoclick Starters

Range of premium-quality glow switch starters for igniting fluorescent lamps with electromagnetic ballast.

### Benefits

- The only starter that offers fast, easy installation with no need to use any extra tools
- No irritation – even firmly stuck starters can be removed easily
- Eco-friendly, recyclable concept (free of lead and radioactivity)
- More than 25% longer lamp life; lower maintenance costs compared with lower-quality, non-IEC-compliant starters
- Optimal connectivity through brass components and oxidation-resistant brass pins
- Flame-retardant components and UV-resistant canister for additional safety and secure ignition (validated by Underwriters Laboratories UL)

### Features

- Redesigned canister top with 2 installation notches into which the pins of another starter fit perfectly (patented innovation)
- Radioactive-free (patented) and lead-free (RoHS-compliant)
- Premium reliability with 10,000 safe switches
- 2-pin igniter in plastic (flame-retardant polycarbonate) canister with high-quality radio-interference suppression capacitor
- Well-defined preheat and peak voltage ensure proper ignition

## Ecoclick Starters

### Application

- Ignite fluorescent lamps of all brands with conventional electromagnetic ballast using TL-D (T8), TL (T12), TL mini and PL-L lamps
- S2 Ecoclick starters are suitable for:
  - 110/130V, 4-22W single applications
  - 220/240V, 4-6-8-15-18-22W single applications
  - 220/240V, 4-22W series applications
- S10 Ecoclick starters are suitable for 220/240V, 4-65W single applications
- S10 Ecoclick starter is required for 220/240V, 13W single application
- S2 Ecoclick starter is recommended for 220/240V, 18W single application for optimum performance

### Versions




LPPR STARTER PHL 0003



LPPR STARTER PHL 0004

### Dimensional drawing



Product	C (max)	E (max)
S10 4-65W SIN 220-240V WH EUR/1000	40.3 mm	21.5 mm
S10 4-65W SIN 220-240V WH EUR/20X10CT	40.3 mm	21.5 mm
S2 4-22W SER 220-240V WH EUR BOX/20X10	40.3 mm	21.5 mm
S2 4-22W SER 220-240V WH EUR/1000	40.3 mm	21.5 mm

### Operating and Electrical

Voltage (nom.)	220-240 V
----------------	-----------

### Mechanical and Housing

Housing Colour	White
----------------	-------

### Operating and Electrical

Order Code	Full Product Name	Power Consumption
69769128	S10 4-65W SIN 220-240V WH EUR/1000	4 W

Order Code	Full Product Name	Power Consumption
69769131	S10 4-65W SIN 220-240V WH EUR/20X10CT	4 W

## Ecoclick Starters

Order Code	Full Product Name	Power Consumption
69750928	S2 4-22W SER 220-240V WH EUR/1000	22 W

Order Code	Full Product Name	Power Consumption
69750931	S2 4-22W SER 220-240V WH EUR BOX/20X10	22 W



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

[www.lighting.philips.com](http://www.lighting.philips.com)  
2023, August 2 - data subject to change