



Attractive LED alternative to popular incandescents.

A-Shape LED

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

Benefits

- This bulb is the perfect replacement for your matted incandescent bulbs
- Lower maintenance costs

Features

- Easy retrofit with existing lamp holders
- Long lifetime
- Instant full light on upon switching on
- UV- and IR-free light
- Free of mercury and hazardous materials – RoHS Compliant

Application

- Ideal for decorative and ambient lighting in retail outlets, hotels, restaurants, multi-unit residences and government buildings.

A-Shape LED

Versions



LEDbulb E A19 E26 FR



LEDbulb E26 A9 FR



LEDbulb A19 E26 FR





LEDbulb A19 E26 FR T20



LEDBulb CorePro E27 A60 8,5W

Dimensional drawing







Product	D	C
EcoHome LEDBulb 4W E27 3000K A60 1PF AR	60 mm	107 mm
EcoHome LEDBulb 4W E27 6500K A60 1PF AR	60 mm	107 mm
LEDBulb 11W E27 3000K W A19 1PF/6	60 mm	109 mm
LEDBulb 11W E27 6500K W A19 1PF/6	60 mm	109 mm
LEDBulb 14W E27 3000K W A19 1PF/6	60 mm	109 mm
LEDBulb 14W E27 3000K W A19 2PF/6	60 mm	109 mm
LEDBulb 14W E27 6500K W A19 1PF/6	60 mm	109 mm
LEDBulb 14W E27 6500K W A19 2PF/6	60 mm	109 mm

Product	D	C
10A19/LED/950/FR/P/E26/ND 4/2CT	60 mm	106 mm

A-Shape LED

Dimensional drawing



Product	D	C
8.8A19/AMB/927/ND D2D 6/1FB T20	61.5 mm	109.8 mm




Product	D	C
LEDGlobe13-100W G30 E27 CDL W ND MX	95 mm	137 mm
LEDGlobe13-100W G30 E27 WW W ND MX	95 mm	137 mm
LEDGlobe13-175W G95 E27 CDL100-240V BR	95 mm	137 mm
LEDGlobe13-175W G95 E27 WW 100-240V BR	95 mm	137 mm

Product	D	C
13.5A19/LED/950/FR/P/E26/ND 4/2CT	60 mm	117 mm
14A19/LED/927/FR/P/E26/ND 4/2CT	60 mm	117 mm

Product	D	C
LEDBulb 6W E27 3000K W A19 1PF/6	60 mm	107 mm
LEDBulb 6W E27 3000K W A19 2PF/6	60 mm	107 mm
LEDBulb 6W E27 6500K W A19 1PF/6	60 mm	107 mm
LEDBulb 6W E27 6500K W A19 2PF/6	60 mm	107 mm
LEDBulb 9W E27 3000K W A19 1PF/6	60 mm	107 mm
LEDBulb 9W E27 3000K W A19 2PF/6	60 mm	107 mm
LEDBulb 9W E27 6500K W A19 1PF/6	60 mm	107 mm
LEDBulb 9W E27 6500K W A19 2PF/6	60 mm	107 mm

A-Shape LED

Dimensional drawing



Product	D	C
8.8A19/AMB/950 DIM 120V LA	62.5 mm	111.5 mm

Product	D	C
10A19/LED/927/FR/P/E26/ND 4/2CT	60 mm	104 mm

Product	D	C
LEDbulb 8.5-70W A60 E27 927 DIM 1PF/10	60 mm	110 mm

General Information	
Switching Cycle	50,000
Operating and Electrical	
Starting Time (Nom)	0.5 s
Mechanical and Housing	
Bulb Finish	Frosted
Approval and Application	
Ambient temperature range	-20 to +45 °C

General Information

A-Shape LED

Order Code	Full Product Name	Cap-Base	Rated		Nominal lifetime
			Lifetime (Hours)		
929003005303	10A19/LED/950/FR/P/E26/ND 4/2CT	E26	11,000 hour(s)		11,000 hour(s)
929003004803	10A19/LED/927/FR/P/E26/ND 4/2CT	E26	11,000 hour(s)		11,000 hour(s)
929003651971	EcoHome LEDBulb 4W E27 3000K A60 1PF AR	E27	-		10,000 hour(s)
929003652071	EcoHome LEDBulb 4W E27 6500K A60 1PF AR	E27	-		10,000 hour(s)
929003797713	LEDBulb 11W E27 3000K W A19 1PF/6	E27	-		15,000 hour(s)
929003797813	LEDBulb 11W E27 6500K W A19 1PF/6	E27	-		15,000 hour(s)
929003797913	LEDBulb 14W E27 3000K W A19 1PF/6	E27	-		15,000 hour(s)
929003797923	LEDBulb 14W E27 3000K W A19 2PF/6	E27	-		15,000 hour(s)
929003798013	LEDBulb 14W E27 6500K W A19 1PF/6	E27	-		15,000 hour(s)
929003798023	LEDBulb 14W E27 6500K W A19 2PF/6	E27	-		15,000 hour(s)
929002333611	8.8A19/AMB/927/ND D2D 6/1FB T20	E26	-		15,000 hour(s)
929001940941	8.8A19/AMB/927-22 WG 120V LA	E26	-		15,000 hour(s)
929002036341	8.8A19/AMB/950 DIM 120V LA	E26	-		15,000 hour(s)
929003797313	LEDBulb 6W E27 3000K W A19 1PF/6	E27	-		15,000 hour(s)

Order Code	Full Product Name	Cap-Base	Rated		Nominal lifetime
			Lifetime (Hours)		
929003797323	LEDBulb 6W E27 3000K W A19 2PF/6	E27	-		15,000 hour(s)
929003797413	LEDBulb 6W E27 6500K W A19 1PF/6	E27	-		15,000 hour(s)
929003797423	LEDBulb 6W E27 6500K W A19 2PF/6	E27	-		15,000 hour(s)
929003797513	LEDBulb 9W E27 3000K W A19 1PF/6	E27	-		15,000 hour(s)
929003797523	LEDBulb 9W E27 3000K W A19 2PF/6	E27	-		15,000 hour(s)
929003797613	LEDBulb 9W E27 6500K W A19 1PF/6	E27	-		15,000 hour(s)
929003797623	LEDBulb 9W E27 6500K W A19 2PF/6	E27	-		15,000 hour(s)
929002069111	LEDbulb 8.5-70W A60 E27 927 DIM 1PF/10	E27	-		15,000 hour(s)
929003005403	14A19/LED/927/FR/P/E26/ND 4/2CT	E26	11,000 hour(s)		11,000 hour(s)
929003005603	13.5A19/LED/950/FR/P/E26/ND 4/2CT	E26	11,000 hour(s)		11,000 hour(s)
929002441871	LEDGlobe13-175W G95 E27 WW 100-240V BR	E27	-		15,000 hour(s)
929002441891	LEDGlobe13-100W G30 E27 WW W ND MX	E27	-		15,000 hour(s)
929002441971	LEDGlobe13-175W G95 E27 CDL100-240V BR	E27	-		15,000 hour(s)
929002441991	LEDGlobe13-100W G30 E27 CDL W ND MX	E27	-		15,000 hour(s)

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		Color rendering		LLMF At End Of Nominal Lifetime	
			Temperature (Nom)		index (CRI)	Color Code	(Nom)	Luminous Flux
929003005303	10A19/LED/950/FR/P/E26/ND 4/2CT	150 degree(s)	5000 K		90	950	0.7 %	1,000 lm
929003004803	10A19/LED/927/FR/P/E26/ND 4/2CT	150 degree(s)	2700 K		90	927	0.7 %	800 lm
929003651971	EcoHome LEDBulb 4W E27 3000K A60 1PF AR	150 degree(s)	3000 K		80	830	70 %	350 lm
929003652071	EcoHome LEDBulb 4W E27 6500K A60 1PF AR	150 degree(s)	6500 K		80	865	70 %	350 lm
929003797713	LEDBulb 11W E27 3000K W A19 1PF/6	150 degree(s)	3000 K		80	830	70 %	910 lm
929003797813	LEDBulb 11W E27 6500K W A19 1PF/6	150 degree(s)	6500 K		80	865	70 %	910 lm
929003797913	LEDBulb 14W E27 3000K W A19 1PF/6	150 degree(s)	3000 K		80	830	70 %	1,310 lm
929003797923	LEDBulb 14W E27 3000K W A19 2PF/6	150 degree(s)	3000 K		80	830	70 %	1,310 lm
929003798013	LEDBulb 14W E27 6500K W A19 1PF/6	150 degree(s)	6500 K		80	865	70 %	1,310 lm
929003798023	LEDBulb 14W E27 6500K W A19 2PF/6	150 degree(s)	6500 K		80	865	70 %	1,310 lm
929002333611	8.8A19/AMB/927/ND D2D 6/1FB T20	220 degree(s)	2700 K		90	927	70 %	800 lm
929001940941	8.8A19/AMB/927-22 WG 120V LA	250 degree(s)	2200 K		90	922-927	70 %	800 lm
929002036341	8.8A19/AMB/950 DIM 120V LA	250 degree(s)	5000 K		90	950	70 %	800 lm
929003797313	LEDBulb 6W E27 3000K W A19 1PF/6	150 degree(s)	3000 K		80	830	70 %	450 lm
929003797323	LEDBulb 6W E27 3000K W A19 2PF/6	150 degree(s)	3000 K		80	830	70 %	450 lm
929003797413	LEDBulb 6W E27 6500K W A19 1PF/6	150 degree(s)	6500 K		80	865	70 %	450 lm

A-Shape LED

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color	Color rendering	Color Code	LLMF At End Of	Luminous Flux
			Temperature (Nom)			Nominal Lifetime	
929003797423	LEDBulb 6W E27 6500K W A19 2PF/6	150 degree(s)	6500 K	80	865	70 %	450 lm
929003797513	LEDBulb 9W E27 3000K W A19 1PF/6	150 degree(s)	3000 K	80	830	70 %	800 lm
929003797523	LEDBulb 9W E27 3000K W A19 2PF/6	150 degree(s)	3000 K	80	830	70 %	800 lm
929003797613	LEDBulb 9W E27 6500K W A19 1PF/6	150 degree(s)	6500 K	80	865	70 %	800 lm
929003797623	LEDBulb 9W E27 6500K W A19 2PF/6	150 degree(s)	6500 K	80	865	70 %	800 lm
929002069111	LEDbulb 8.5-70W A60 E27 927 DIM 1PF/10	150 degree(s)	2700 K	90	927	70 %	806 lm
929003005403	14A19/LED/927/FR/P/E26/ND 4/2CT	150 degree(s)	2700 K	90	927	0.7 %	1,500 lm
929003005603	13.5A19/LED/950/FR/P/E26/ND 4/2CT	150 degree(s)	5000 K	90	950	0.7 %	1,500 lm
929002441871	LEDGlobe13-175W G95 E27 WW 100-240V BR	150 degree(s)	2700 K	80	827	70 %	1,521 lm
929002441891	LEDGlobe13-100W G30 E27 WW W ND MX	150 degree(s)	2700 K	80	827	70 %	1,521 lm
929002441971	LEDGlobe13-175W G95 E27 CDL100-240V BR	150 degree(s)	6500 K	80	865	70 %	1,521 lm
929002441991	LEDGlobe13-100W G30 E27 CDL W ND MX	150 degree(s)	6500 K	80	865	70 %	1,521 lm

Operating and Electrical

Order Code	Full Product Name	Input	Line	Power	Wattage
		Frequency	Frequency	Consumption	Equivalent
929003005303	10A19/LED/950/F R/P/E26/ND 4/2CT	60 Hz	60 Hz	10 W	75 W
929003004803	10A19/LED/927/F R/P/E26/ND 4/2CT	60 Hz	60 Hz	10 W	60 W
929003651971	EcoHome LEDBulb 4W E27 3000K A60 1PF AR	50 to 60 Hz	-	4 W	40 W
929003652071	EcoHome LEDBulb 4W E27 6500K A60 1PF AR	50 to 60 Hz	-	4 W	40 W
929003797713	LEDBulb 11W E27 3000K W A19 1PF/6	60 Hz	-	11 W	75 W
929003797813	LEDBulb 11W E27 6500K W A19 1PF/6	60 Hz	-	11 W	75 W
929003797913	LEDBulb 14W E27 3000K W A19 1PF/6	60 Hz	-	14 W	100 W
929003797923	LEDBulb 14W E27 3000K W A19 2PF/6	60 Hz	-	14 W	100 W
929003798013	LEDBulb 14W E27 6500K W A19 1PF/6	60 Hz	-	14 W	100 W
929003798023	LEDBulb 14W E27 6500K W A19 2PF/6	60 Hz	-	14 W	100 W

Order Code	Full Product Name	Input	Line	Power	Wattage
		Frequency	Frequency	Consumption	Equivalent
929002333611	8.8A19/AMB/927/ ND D2D 6/1FB T20	60 Hz	60 Hz	8.8 W	60 W
929001940941	8.8A19/AMB/ 927-22 WG 120V LA	60 Hz	60 Hz	8.8 W	60 W
929002036341	8.8A19/AMB/950 DIM 120V LA	60 Hz	60 Hz	8.8 W	60 W
929003797313	LEDBulb 6W E27 3000K W A19 1PF/6	60 Hz	-	6 W	40 W
929003797323	LEDBulb 6W E27 3000K W A19 2PF/6	60 Hz	-	6 W	40 W
929003797413	LEDBulb 6W E27 6500K W A19 1PF/6	60 Hz	-	6 W	40 W
929003797423	LEDBulb 6W E27 6500K W A19 2PF/6	60 Hz	-	6 W	40 W
929003797513	LEDBulb 9W E27 3000K W A19 1PF/6	60 Hz	-	9 W	60 W
929003797523	LEDBulb 9W E27 3000K W A19 2PF/6	60 Hz	-	9 W	60 W
929003797613	LEDBulb 9W E27 6500K W A19 1PF/6	60 Hz	-	9 W	60 W
929003797623	LEDBulb 9W E27 6500K W A19 2PF/6	60 Hz	-	9 W	60 W

A-Shape LED

		Input	Line	Power	Wattage
Order Code	Full Product Name	Frequency	Frequency	Consumption	Equivalent
929002069111	LEDbulb 8.5-70W	50 to 60	50 to 60	8.5 W	70 W
	A60 E27 927 DIM	Hz	Hz		
	1PF/10				
929003005403	14A19/LED/927/F	60 Hz	60 Hz	14 W	100 W
	R/P/E26/ND				
	4/2CT				
929003005603	13.5A19/LED/950/	60 Hz	60 Hz	13.5 W	100 W
	FR/P/E26/ND				
	4/2CT				
929002441871	LEDGlobe13-175W	50 to 60	50 to 60	13 W	175 W
	G95 E27 WW	Hz	Hz		
	100-240V BR				

		Input	Line	Power	Wattage
Order Code	Full Product Name	Frequency	Frequency	Consumption	Equivalent
929002441891	LEDGlobe13-100W	50 to 60	50 to 60	13 W	100 W
	G30 E27 WW W	Hz	Hz		
	ND MX				
929002441971	LEDGlobe13-175W	50 to 60	50 to 60	13 W	175 W
	G95 E27	Hz	Hz		
	CDL100-240V BR				
929002441991	LEDGlobe13-100W	50 to 60	50 to 60	13 W	100 W
	G30 E27 CDL W	Hz	Hz		
	ND MX				

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929003005303	10A19/LED/950/FR/P/E26/ND 4/2CT	95 °C
929003004803	10A19/LED/927/FR/P/E26/ND 4/2CT	85 °C
929003651971	EcoHome LEDBulb 4W E27 3000K A60 1PF AR	80 °C
929003652071	EcoHome LEDBulb 4W E27 6500K A60 1PF AR	80 °C
929003797713	LEDBulb 11W E27 3000K W A19 1PF/6	80 °C
929003797813	LEDBulb 11W E27 6500K W A19 1PF/6	80 °C
929003797913	LEDBulb 14W E27 3000K W A19 1PF/6	85 °C
929003797923	LEDBulb 14W E27 3000K W A19 2PF/6	85 °C
929003798013	LEDBulb 14W E27 6500K W A19 1PF/6	85 °C
929003798023	LEDBulb 14W E27 6500K W A19 2PF/6	85 °C
929002333611	8.8A19/AMB/927/ND D2D 6/1FB T20	95 °C
929001940941	8.8A19/AMB/927-22 WG 120V LA	85 °C
929002036341	8.8A19/AMB/950 DIM 120V LA	85 °C
929003797313	LEDBulb 6W E27 3000K W A19 1PF/6	75 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929003797323	LEDBulb 6W E27 3000K W A19 2PF/6	75 °C
929003797413	LEDBulb 6W E27 6500K W A19 1PF/6	75 °C
929003797423	LEDBulb 6W E27 6500K W A19 2PF/6	75 °C
929003797513	LEDBulb 9W E27 3000K W A19 1PF/6	80 °C
929003797523	LEDBulb 9W E27 3000K W A19 2PF/6	80 °C
929003797613	LEDBulb 9W E27 6500K W A19 1PF/6	80 °C
929003797623	LEDBulb 9W E27 6500K W A19 2PF/6	80 °C
929002069111	LEDbulb 8.5-70W A60 E27 927 DIM 1PF/10	85 °C
929003005403	14A19/LED/927/FR/P/E26/ND 4/2CT	95 °C
929003005603	13.5A19/LED/950/FR/P/E26/ND 4/2CT	95 °C
929002441871	LEDGlobe13-175W G95 E27 WW 100-240V BR	55 °C
929002441891	LEDGlobe13-100W G30 E27 WW W ND MX	55 °C
929002441971	LEDGlobe13-175W G95 E27 CDL100-240V BR	55 °C
929002441991	LEDGlobe13-100W G30 E27 CDL W ND MX	55 °C



Controls and Dimming

Order Code	Full Product Name	Dimmable
929003005303	10A19/LED/950/FR/P/E26/ND 4/2CT	No
929003004803	10A19/LED/927/FR/P/E26/ND 4/2CT	No
929003651971	EcoHome LEDBulb 4W E27 3000K A60 1PF AR	No
929003652071	EcoHome LEDBulb 4W E27 6500K A60 1PF AR	No
929003797713	LEDBulb 11W E27 3000K W A19 1PF/6	No
929003797813	LEDBulb 11W E27 6500K W A19 1PF/6	No
929003797913	LEDBulb 14W E27 3000K W A19 1PF/6	No
929003797923	LEDBulb 14W E27 3000K W A19 2PF/6	No
929003798013	LEDBulb 14W E27 6500K W A19 1PF/6	No
929003798023	LEDBulb 14W E27 6500K W A19 2PF/6	No
929002333611	8.8A19/AMB/927/ND D2D 6/1FB T20	No
929001940941	8.8A19/AMB/927-22 WG 120V LA	Only with specific dimmers
929002036341	8.8A19/AMB/950 DIM 120V LA	Only with specific dimmers











Order Code	Full Product Name	Dimmable
929003797313	LEDBulb 6W E27 3000K W A19 1PF/6	No
929003797323	LEDBulb 6W E27 3000K W A19 2PF/6	No
929003797413	LEDBulb 6W E27 6500K W A19 1PF/6	No
929003797423	LEDBulb 6W E27 6500K W A19 2PF/6	No
929003797513	LEDBulb 9W E27 3000K W A19 1PF/6	No
929003797523	LEDBulb 9W E27 3000K W A19 2PF/6	No
929003797613	LEDBulb 9W E27 6500K W A19 1PF/6	No
929003797623	LEDBulb 9W E27 6500K W A19 2PF/6	No
929002069111	LEDbulb 8.5-70W A60 E27 927 DIM 1PF/10	Yes
929003005403	14A19/LED/927/FR/P/E26/ND 4/2CT	No
929003005603	13.5A19/LED/950/FR/P/E26/ND 4/2CT	No
929002441871	LEDGlobe13-175W G95 E27 WW 100-240V BR	No
929002441891	LEDGlobe13-100W G30 E27 WW W ND MX	No
929002441971	LEDGlobe13-175W G95 E27 CDL100-240V BR	No
929002441991	LEDGlobe13-100W G30 E27 CDL W ND MX	No

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929003005303	10A19/LED/950/FR/P/E26/ND 4/2CT	A19
929003004803	10A19/LED/927/FR/P/E26/ND 4/2CT	A19
929003651971	EcoHome LEDBulb 4W E27 3000K A60 1PF AR	A60
929003652071	EcoHome LEDBulb 4W E27 6500K A60 1PF AR	A60
929003797713	LEDBulb 11W E27 3000K W A19 1PF/6	A19
929003797813	LEDBulb 11W E27 6500K W A19 1PF/6	A19
929003797913	LEDBulb 14W E27 3000K W A19 1PF/6	A19
929003797923	LEDBulb 14W E27 3000K W A19 2PF/6	A19
929003798013	LEDBulb 14W E27 6500K W A19 1PF/6	A19
929003798023	LEDBulb 14W E27 6500K W A19 2PF/6	A19
929002333611	8.8A19/AMB/927/ND D2D 6/1FB T20	A19
929001940941	8.8A19/AMB/927-22 WG 120V LA	A19
929002036341	8.8A19/AMB/950 DIM 120V LA	A19
929003797313	LEDBulb 6W E27 3000K W A19 1PF/6	A19
929003797323	LEDBulb 6W E27 3000K W A19 2PF/6	A19
929003797413	LEDBulb 6W E27 6500K W A19 1PF/6	A19
929003797423	LEDBulb 6W E27 6500K W A19 2PF/6	A19
929003797513	LEDBulb 9W E27 3000K W A19 1PF/6	A19
929003797523	LEDBulb 9W E27 3000K W A19 2PF/6	A19
929003797613	LEDBulb 9W E27 6500K W A19 1PF/6	A19
929003797623	LEDBulb 9W E27 6500K W A19 2PF/6	A19
929002069111	LEDbulb 8.5-70W A60 E27 927 DIM 1PF/10	A60
929003005403	14A19/LED/927/FR/P/E26/ND 4/2CT	A19
929003005603	13.5A19/LED/950/FR/P/E26/ND 4/2CT	A19
929002441871	LEDGlobe13-175W G95 E27 WW 100-240V BR	G95
929002441891	LEDGlobe13-100W G30 E27 WW W ND MX	G30
929002441971	LEDGlobe13-175W G95 E27 CDL100-240V BR	G95
929002441991	LEDGlobe13-100W G30 E27 CDL W ND MX	G30



A-Shape LED



A-Shape LED

