



The world's brightest fluorescent lighting

MASTER TL5 High Output

This TL5 lamp (tube diameter 16 mm) offers high light output. The TL5 HO lamp is optimized for installations requiring high light output and offers excellent lumen maintenance and color rendering. Application areas vary from offices and industry to schools and retail environments.

Benefits

- Allows system miniaturization and maximum luminaire design freedom
- Lamp lengths enable easy fitting into ceiling module systems
- Optimized for installations which need high luminous flux
- Virtually constant lumen level with excellent lumen maintenance
- Good color rendering

Features

- 40% thinner than TL-D lamps
- Designed for high light output and system miniaturization
- Highly efficient 3-band fluorescent coating in combination with precoating
- Specifically designed for operation with electronic gear and well-suited for dimming
- Maximum light output reached at approximately 35 °C in free-burning position if an electronic driver with cut-off feature is used
- Can be ignited from -15 to +50 °C

Application


- The combination of a compact lamp and high lumen package of the MASTER TL5 HO offers exciting opportunities for architectural lighting and customized solutions
- Offers economic solutions with high-ceiling lighting in shops, industry and department stores
- The high luminous flux gives optimal results in aesthetic pendants and furniture-mounted luminaires in offices, workshops, restaurants and reception areas

MASTER TL5 High Output

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 24W/840 SLV/40	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm
MASTER TL5 HO 24W/840 UNP/40	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm
MASTER TL5 HO 39W/840 SLV/40	17 mm	849.0 mm	856.1 mm	853.7 mm	863.2 mm
MASTER TL5 HO 49W/830 SLV/40	17 mm	1,449.0 mm	1,456.1 mm	1,453.7 mm	1,463.2 mm
MASTER TL5 HO 54W/840 SLV/40	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm
MASTER TL5 HO 54W/840 UNP/40	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm
MASTER TL5 HO 54W/865 SLV/40	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm
MASTER TL5 HO 80W/840 SLV/40	17 mm	1,449.0 mm	1,456.1 mm	1,453.7 mm	1,463.2 mm
MASTER TL5 HO 80W/865 SLV/40	17 mm	1,449.0 mm	1,456.1 mm	1,453.7 mm	1,463.2 mm

General Information	
Cap-Base	G5
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T5
Approval and Application	
Mercury (Hg) Content (Nom)	1.2 mg

Light Technical

Order Code	Full Product Name	Chromaticity	Chromaticity	Color		Luminous Efficacy (rated) (Nom)	Luminous Flux	
		Coordinate X (Nom)	Coordinate Y (Nom)	Correlated Color Temperature (Nom)	rendering index (CRI)			
927927583055	MASTER TL5 HO 49W/830 SLV/40	0.44	0.403	Warm White (WW)	3000 K	82	89 lm/W	4,375 lm
927928084018	MASTER TL5 HO 24W/840 UNP/40	0.38	0.38	Cool White (CW)	4000 K	82	76 lm/W	1,700 lm
927928084055	MASTER TL5 HO 24W/840 SLV/40	0.38	0.38	Cool White (CW)	4000 K	82	76 lm/W	1,700 lm

MASTER TL5 High Output

Order Code	Full Product Name	Chromaticity	Chromaticity	Color Designation	Correlated Color Temperature (Nom)	Color	Luminous Efficacy (rated) (Nom)	Luminous Flux
		Coordinate X (Nom)	Coordinate Y (Nom)			rendering index (CRI)		
927928584055	MASTER TL5 HO 39W/840 SLV/40	0.38	0.38	Cool White (CW)	4000 K	82	82 lm/W	3,100 lm
927929084018	MASTER TL5 HO 54W/840 UNP/40	0.38	0.38	Cool White (CW)	4000 K	80	83 lm/W	4,500 lm
927929084055	MASTER TL5 HO 54W/840 SLV/40	0.38	0.38	Cool White (CW)	4000 K	80	83 lm/W	4,500 lm
927929086555	MASTER TL5 HO 54W/865 SLV/40	0.313	0.337	Cool Daylight	6500 K	82	78 lm/W	4,200 lm
927929584057	MASTER TL5 HO 80W/840 SLV/40	0.38	0.38	Cool White (CW)	4000 K	81	82 lm/W	6,550 lm
927929586557	MASTER TL5 HO 80W/865 SLV/40	0.313	0.337	Cool Daylight	6500 K	82	79 lm/W	6,300 lm

Operating and Electrical

Order Code	Full Product Name	Lamp Current	
		(Nom)	Power Consumption
927927583055	MASTER TL5 HO 49W/830 SLV/40	0.255 A	49.3 W
927928084018	MASTER TL5 HO 24W/840 UNP/40	0.295 A	22.7 W
927928084055	MASTER TL5 HO 24W/840 SLV/40	0.295 A	22.7 W
927928584055	MASTER TL5 HO 39W/840 SLV/40	0.325 A	38.0 W
927929084018	MASTER TL5 HO 54W/840 UNP/40	0.455 A	54.4 W

Order Code	Full Product Name	Lamp Current	
		(Nom)	Power Consumption
927929084055	MASTER TL5 HO 54W/840 SLV/40	0.455 A	54.4 W
927929086555	MASTER TL5 HO 54W/865 SLV/40	0.455 A	54.4 W
927929584057	MASTER TL5 HO 80W/840 SLV/40	0.530 A	79.8 W
927929586557	MASTER TL5 HO 80W/865 SLV/40	0.530 A	79.8 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
927927583055	MASTER TL5 HO 49W/830 SLV/40	50 kWh
927928084018	MASTER TL5 HO 24W/840 UNP/40	23 kWh
927928084055	MASTER TL5 HO 24W/840 SLV/40	23 kWh
927928584055	MASTER TL5 HO 39W/840 SLV/40	38 kWh
927929084018	MASTER TL5 HO 54W/840 UNP/40	55 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
927929084055	MASTER TL5 HO 54W/840 SLV/40	55 kWh
927929086555	MASTER TL5 HO 54W/865 SLV/40	55 kWh
927929584057	MASTER TL5 HO 80W/840 SLV/40	80 kWh
927929586557	MASTER TL5 HO 80W/865 SLV/40	80 kWh

