



# Yellow, Red, Green and Blue fluorescent lighting

## TL-D Colored

This TL-D lamp (tube diameter 26 mm) helps to create special effects and atmospheres or attract attention by using red, green, blue and yellow light. Apart from using the specific colors, it is also possible to mix the colors to create white light. This lamp offers a high light output, thanks to the use of basic powders.

Application areas include shops and showrooms, bars and restaurants, demonstration areas, sign lighting and entertainment stores.

### Benefits

- Choice of attractive colors

### Features

- The fluorescent powders of Red and Yellow lamps are mixed with a pigment to filter out unwanted wavelengths
- Can be used with conventional or electronic gear
- Depending on the control gear, dimming is possible

### Application

- For color effects in stage lighting, shop-window lighting, festive lighting, bars, dance halls etc.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


# TL-D Colored

## Versions



LPPR TL-DCOL Red G13

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D Colored 18W Blue 1SL/25	28.0 mm	589.8 mm	596.9 mm	594.5 mm	604.0 mm
TL-D Colored 18W Green 1SL/25	28.0 mm	589.8 mm	596.9 mm	594.5 mm	604.0 mm
TL-D Colored 18W Red 1SL/25	28.0 mm	589.8 mm	596.9 mm	594.5 mm	604.0 mm
TL-D Colored 18W Yellow 1SL/25	28.0 mm	589.8 mm	596.9 mm	594.5 mm	604.0 mm
TL-D Colored 36W Blue 1SL/25	28.0 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm
TL-D Colored 36W Green 1SL/25	28.0 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm
TL-D Colored 36W Red 1SL/25	28.0 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm
TL-D Colored 36W Yellow 1SL/25	28.0 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm
TL-D Colored 58W Blue 1SL/25	28.0 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm
TL-D Colored 58W Green 1SL/25	28.0 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm
TL-D Colored 58W Red 1SL/25	28.0 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm
TL-D Colored 58W Yellow 1SL/25	28.0 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

### General Information

Cap-Base G13

### Controls and Dimming

Dimmable Yes

### Mechanical and Housing

Bulb Shape T8

# TL-D Colored

## Light Technical

Order Code	Full Product Name	Color Designation	Luminous Flux
928048001805	TL-D Colored 18W Blue 1SL/25	Blue (B)	400 lm
928048501805	TL-D Colored 36W Blue 1SL/25	Blue (B)	960 lm
928049001805	TL-D Colored 58W Blue 1SL/25	Blue (B)	1,600 lm
928048001705	TL-D Colored 18W Green 1SL/25	Green (G)	1,800 lm
928048501705	TL-D Colored 36W Green 1SL/25	Green (G)	4,300 lm
928049001705	TL-D Colored 58W Green 1SL/25	Green (G)	6,750 lm

Order Code	Full Product Name	Color Designation	Luminous Flux
928048001505	TL-D Colored 18W Red 1SL/25	Red (HO)	25 lm
928048501505	TL-D Colored 36W Red 1SL/25	Red (HO)	55 lm
928049001505	TL-D Colored 58W Red 1SL/25	Red (HO)	75 lm
928048001605	TL-D Colored 18W Yellow 1SL/25	Yellow	700 lm
928048501605	TL-D Colored 36W Yellow 1SL/25	Yellow	1,580 lm
928049001605	TL-D Colored 58W Yellow 1SL/25	Yellow	2,250 lm

## Operating and Electrical

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
928048001805	TL-D Colored 18W Blue 1SL/25	0.360 A	59 V	18.0 W
928048501805	TL-D Colored 36W Blue 1SL/25	0.440 A	103 V	36.0 W
928049001805	TL-D Colored 58W Blue 1SL/25	0.670 A	111 V	58.5 W
928048001705	TL-D Colored 18W Green 1SL/25	0.360 A	59 V	18.0 W
928048501705	TL-D Colored 36W Green 1SL/25	0.440 A	103 V	36.0 W
928049001705	TL-D Colored 58W Green 1SL/25	0.670 A	111 V	58.5 W

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
928048001505	TL-D Colored 18W Red 1SL/25	0.360 A	59 V	18.0 W
928048501505	TL-D Colored 36W Red 1SL/25	0.440 A	103 V	36.0 W
928049001505	TL-D Colored 58W Red 1SL/25	0.670 A	111 V	58.5 W
928048001605	TL-D Colored 18W Yellow 1SL/25	0.360 A	59 V	18.0 W
928048501605	TL-D Colored 36W Yellow 1SL/25	0.440 A	103 V	36.0 W
928049001605	TL-D Colored 58W Yellow 1SL/25	0.670 A	111 V	58.5 W

## Approval and Application

Order Code	Full Product Name	Energy Consumption	Mercury (Hg)
		kWh/1000 h	Content (Nom)
928048001805	TL-D Colored 18W Blue 1SL/25	23 kWh	13.0 mg
928048501805	TL-D Colored 36W Blue 1SL/25	45 kWh	13.0 mg
928049001805	TL-D Colored 58W Blue 1SL/25	71 kWh	13.0 mg
928048001705	TL-D Colored 18W Green 1SL/25	22 kWh	1.7 mg
928048501705	TL-D Colored 36W Green 1SL/25	42 kWh	1.7 mg
928049001705	TL-D Colored 58W Green 1SL/25	67 kWh	1.7 mg

Order Code	Full Product Name	Energy Consumption	Mercury (Hg)
		kWh/1000 h	Content (Nom)
928048001505	TL-D Colored 18W Red 1SL/25	26 kWh	13.0 mg
928048501505	TL-D Colored 36W Red 1SL/25	51 kWh	13.0 mg
928049001505	TL-D Colored 58W Red 1SL/25	82 kWh	13.0 mg
928048001605	TL-D Colored 18W Yellow 1SL/25	23 kWh	13.0 mg
928048501605	TL-D Colored 36W Yellow 1SL/25	44 kWh	13.0 mg

