

**PHILIPS**

**Lighting**



# Product Description

## TL-D Standard Colours

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

### Benefits

- Create atmospheres from warm white to cool daylight

### Features

- Standard colours with moderate colour rendering
- Available in various colour designations

### Application

- Suitable for use in a wide range of luminaires for TL-D fluorescent lamps, used in applications where colour rendering is not an important factor

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


### Versions



LPPR TL-DSTD G13

# TL-D Standard Colours

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W/54-765 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
TL-D 36W/54-765 1SL/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm
TL-D 58W/54-765 1SL/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

General Information	
Cap-Base	G13
Light Technical	
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	5.0 mg

## Light Technical

Order Code	Full Product Name	Color rendering index (CRI)	Luminous Flux
95043740	TL-D 18W/54-765 1SL/25	72	1,050 lm
95047540	TL-D 36W/54-765 1SL/25	75	2,500 lm

Order Code	Full Product Name	Color rendering index (CRI)	Luminous Flux
95051240	TL-D 58W/54-765 1SL/25	72	4,000 lm

## Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Voltage (Nom)	Power Consumption
95043740	TL-D 18W/54-765 1SL/25	0.360 A	59 V	18.0 W
95047540	TL-D 36W/54-765 1SL/25	0.440 A	103 V	36.0 W

Order Code	Full Product Name	Lamp Current (Nom)	Voltage (Nom)	Power Consumption
95051240	TL-D 58W/54-765 1SL/25	0.670 A	111 V	58.5 W

## Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
95043740	TL-D 18W/54-765 1SL/25	22 kWh
95047540	TL-D 36W/54-765 1SL/25	43 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
95051240	TL-D 58W/54-765 1SL/25	68 kWh

## TL-D Standard Colours



© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

[www.lighting.philips.com](http://www.lighting.philips.com)  
2025, December 13 - data subject to change