



# Product Description

## TL-D Standard Colours

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

### Benefits

- Create atmospheres from warm white to cool daylight
- Create atmospheres from warm white to cool daylight

### Features

- Standard colors with moderate color rendering
- Standard colours with moderate colour rendering
- Available in various color designations
- Available in various colour designations

### Application

- Suitable for use in a wide range of luminaires for TL-D fluorescent lamps, used in applications where color rendering is not an important factor
- Suitable for use in a wide range of luminaires for TL-D fluorescent lamps, used in applications where colour rendering is not an important factor

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


# TL-D Standard Colours

## Versions



LPPR TL-DSTD G13

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 10W/54-765 1SL/50	28 mm	331.5 mm	338.6 mm	336.2 mm	345.7 mm
TL-D 15W/54-765 1SL/50	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm

General Information	
Cap-Base	G13
Light Technical	
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg

## Light Technical

Order Code	Full Product Name	Color rendering index (CRI)	Luminous Flux
928024005436	TL-D 10W/54-765 1SL/50	75	390 lm

Order Code	Full Product Name	Color rendering index (CRI)	Luminous Flux
928024805436	TL-D 15W/54-765 1SL/50	72	725 lm

## Operating and Electrical

# TL-D Standard Colours

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
928024005436	TL-D 10W/54-765 1SL/50	0.230 A	46 V	10.0 W

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
928024805436	TL-D 15W/54-765 1SL/50	0.310 A	51 V	15.0 W

## Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
928024005436	TL-D 10W/54-765 1SL/50	-

Order Code	Full Product Name	Energy Consumption kWh/1000 h
928024805436	TL-D 15W/54-765 1SL/50	20 kWh

