



Philips TrueLine Wallmount: Stylish, comfortable, and adaptable bedhead light

KeyLine Wall-mounted

Introducing our new KeyLine Wall Mounted Luminaire! Made from robust extruded aluminum, this luminaire is perfect for use as mirror lighting in bathrooms. It is IP44 splash water protected and has comfortable low-glare optics. The luminaire is equipped with efficient LED technology and has a CRI90 rating for natural color rendering. With its sleek design and high-quality features, our KeyLine is the perfect choice for your bathroom lighting needs

Benefits

- High efficiency
- Robust and waterproof
- Comfortable low glare
- Long lifetime

Features

- Extruded aluminum body
- IP44 waterproof, IK06 protection
- Long lifetime: L90 50khrs, L80 100khrs
- Efficient high-gloss anti-glare optics (UGR<19 Comes with Environmental Product Declaration (EPD)

KeyLine Wall-mounted



Application

- Healthcare
- Hospitals and Care Centers

Warnings and Safety

- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

Dimensional drawing



Product details



KeyLine Wallmounted- WL350W-
detail



KeyLine Wallmounted- WL350W-
detail

KeyLine Wall-mounted

General Information

Driver included	Yes
Number of gear units	1 unit

Light Technical

Optic type	Medium beam
------------	-------------

Operating and Electrical

Protection class IEC	Safety class I
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No

Controls and Dimming

Embedded control	-
------------------	---

Mechanical and Housing

Housing Color	White RAL 9003
Mech. impact protection code	IK06
Ingress protection code	IP44

Emergency Operation

Central Emergency	No
Emergency lighting	-

Approval and Application

Ambient temperature range	+10 to +35 °C
CE mark	Yes
ENEC mark	-
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s

Initial Performance (IEC Compliant)

Initial chromaticity	(0.39, 0.38) SDCM <3
Luminous flux tolerance	+/-10%

Product Data

Product family code	WL350W
---------------------	--------

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505106577	WL350W 12S/930 PSD PCS L600 WH	3000 K	>90	116 lm/W	1,200 lm
910505106578	WL350W 18S/930 PSD PCS L900 WH	3000 K	>90	116 lm/W	1,800 lm
910505106579	WL350W 12S/940 PSD PCS L600 WH	4000 K	>90	126 lm/W	1,200 lm
910505106580	WL350W 18S/940 PSD PCS L900 WH	4000 K	>90	126 lm/W	1,800 lm
910505106581	WL350W 12S/840 PSU PCS L600 WH	4000 K	>80	132 lm/W	1,200 lm
910505106582	WL350W 18S/840 PSU PCS L900 WH	4000 K	>80	128 lm/W	1,800 lm
910505106583	WL350W 12S/830 PSU PCS L600 WH	4000 K	>80	133 lm/W	1,200 lm
910505106584	WL350W 18S/830 PSU PCS L900 WH	3000 K	>80	128 lm/W	1,800 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
910505106577	WL350W 12S/930 PSD PCS L600 WH	10 W	910505106581	WL350W 12S/840 PSU PCS L600 WH	9 W
910505106578	WL350W 18S/930 PSD PCS L900 WH	15 W	910505106582	WL350W 18S/840 PSU PCS L900 WH	14 W
910505106579	WL350W 12S/940 PSD PCS L600 WH	9 W	910505106583	WL350W 12S/830 PSU PCS L600 WH	9 W
910505106580	WL350W 18S/940 PSD PCS L900 WH	14 W	910505106584	WL350W 18S/830 PSU PCS L900 WH	14 W

Controls and Dimming

KeyLine Wall-mounted

Order Code	Full Product Name	Dimmable
910505106577	WL350W 12S/930 PSD PCS L600 WH	Yes
910505106578	WL350W 18S/930 PSD PCS L900 WH	Yes
910505106579	WL350W 12S/940 PSD PCS L600 WH	Yes
910505106580	WL350W 18S/940 PSD PCS L900 WH	Yes

Order Code	Full Product Name	Dimmable
910505106581	WL350W 12S/840 PSU PCS L600 WH	No
910505106582	WL350W 18S/840 PSU PCS L900 WH	No
910505106583	WL350W 12S/830 PSU PCS L600 WH	No
910505106584	WL350W 18S/830 PSU PCS L900 WH	Yes

