



Philips KeyLine Wallmount: Stylish, comfortable, and adaptable bedhead light

KeyLine Wall-mounted

Introducing our new KeyLine Wall Mounted Luminaire! Made from robust extruded aluminum, this luminaire is perfect for use as mirror lighting in bathrooms. It is IP44 splash water protected and has comfortable low-glare optics. The luminaire is equipped with efficient LED technology and has a CRI90 rating for natural color rendering. With its sleek design and high-quality features, our KeyLine is the perfect choice for your bathroom lighting needs

Benefits

- High efficiency
- Robust and waterproof
- Comfortable low glare
- Long lifetime

Features

- Extruded aluminum body
- IP44 waterproof, IK06 protection
- Long lifetime: L90 50khrs, L80 100khrs
- Efficient high-gloss anti-glare optics (UGR<19 Comes with Environmental Product Declaration (EPD)

KeyLine Wall-mounted

Application

- Healthcare
- Hospitals and Care Centers

Warnings and Safety


- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

Versions



KeyLine Wallmounted- WL350W

Dimensional drawing



Product details



KeyLine Wallmounted- WL350W-
detail



KeyLine Wallmounted- WL350W-
detail

KeyLine Wall-mounted

General Information

Driver included	Yes
Number of gear units	1 unit

Light Technical

Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>80
Optic type	Medium beam

Operating and Electrical

Protection class IEC	Safety class I
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No

Controls and Dimming

Dimmable	No
Embedded control	-

Mechanical and Housing

Housing Color	White RAL 9003
Mech. impact protection code	IK06
Ingress protection code	IP44

Emergency Operation

Central Emergency	No
Emergency lighting	-

Approval and Application

Ambient temperature range	+10 to +35 °C
CE mark	Yes
ENEC mark	-
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s

Initial Performance (IEC Compliant)

Initial chromaticity	(0.39, 0.38) SDCM <3
Luminous flux tolerance	+/-10%

Product Data

Product family code	WL350W
---------------------	--------

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
39027100	WL350W 12S/840 PSU PCS L600 WH	132 lm/W	1,200 lm
39028800	WL350W 18S/840 PSU PCS L900 WH	128 lm/W	1,800 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
39027100	WL350W 12S/840 PSU PCS L600 WH	9 W

Order Code	Full Product Name	Power Consumption
39028800	WL350W 18S/840 PSU PCS L900 WH	14 W

KeyLine Wall-mounted

