



Install smarter, finish sooner Choose long-lasting reliability and performance

CoreLine Waterproof

CoreLine waterproof delivers on the CoreLine promise of innovative, easy-to-use and high-quality luminaires. With its slim and stylish design, it retains the product architecture that the range is well-known and appreciated for. Installation is quick and easy, all thanks to its efficient design. CoreLine waterproof provides better wide-beam light distribution for straightforward and effective lighting. A direct replacement for traditional waterproof luminaires with fluorescent lamps ranging from 18W up to 58W, it delivers significant energy savings. Interact Ready luminaires with integrated wireless communications are also available in the CoreLine waterproof range, ready to be used with Interact connected lighting system.

Benefits

- Saves on energy and maintenance costs
- Supports fast and flexible installation thanks to smart WT120C G2 product architecture
- Ideal for general application projects with a robust design (IK08) and high water and dust-proof rating (IP65)

CoreLine Waterproof

Features

- Long lifetime and high efficiency: up to 100,000 hours with flux at 70% min. compared to initial level and efficiency up to 160lm/W
- Range of options available: L600/1200/1500, up to 12,000 lm, 4000K
- Uniform and wide-beam or opal light distribution
- Longer sliders, faster lock opening, tool-less electrical connections for easy and flexible installation
- Optional controls and versions available: DALI dimming, integrated wireless connectivity (Interact Ready), integrated movement sensors (MDU), emergency lighting (EL), waterproof external connector for easier installation (WEC), through wiring 1- and 3-phase (TW1/

Application

- Parking Garages
- Manufacturing
- Warehouses
- General lighting

Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

Versions



CoreLine Waterproof WT120C G2
PSU PCO -



PH All In CoreLine SPP e cat HR
911401814985






PH All In CoreLine SPP e cat HR
911401815085



CoreLine waterproof G2 (WT120C
G2), L1500

CoreLine Waterproof

Dimensional drawing




Product details



CoreLine waterproof All in L1500



CoreLine Waterproof WT120C G2
PCU-7DPP



CoreLine waterproof All in,
WT120C G2, easy lumen switch



CoreLine Waterproof WT120C G2
PCU-3DPP

CoreLine Waterproof

Product details



CoreLine Waterproof WT120C G2
PCU-10DPP




CoreLine Waterproof WT120C G2
PCU-9DPP



Product Detail Photo Coreline




CoreLine Waterproof WT120C G2
PCU-12DPP



CoreLine waterproof G2 (WT120C
G2),MDU, Motion Detection Unit



CoreLine waterproof All in L1500



CoreLine Waterproof WT120C G2
PCU-2DPP




CoreLine Waterproof WT120C G2
PCU-13DPP



CoreLine Waterproof WT120C G2
PCU-8DPP

CoreLine Waterproof

Product details



CoreLine waterproof G2 (WT120C G2),MDU, Motion Detection Unit



CoreLine Waterproof WT120C G2 PCU-11DPP



CoreLine waterproof G2 (WT120C G2),Emergency lighting, TrustSight

General Information	
Driver included	Yes
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Color rendering index (CRI)	>80
Operating and Electrical	
Protection class IEC	Safety class I
Line Frequency	50 or 60 Hz
Mechanical and Housing	
Mech. impact protection code	IK08
Ingress protection code	IP65
Approval and Application	
CE mark	Yes
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 30 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Lamp family code	Light source replaceable
910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	LED27S	No
910505100040	WT120C G2 LED27S/840 PSU MDU L1200	LED27S	No
910505100042	WT120C G2 LED27S/840 PSU ELB3 L1200	LED27S	No
910505100044	WT120C G2 LED27S/840 PSD L1200	LED27S	No
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	LED27S	No
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	LED40S	No
910505100048	WT120C G2 LED40S/840 PSU MDU L1200	LED40S	No
910505100049	WT120C G2 LED40S/840 PSU MDU TW3 L1200	LED40S	No
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	LED40S	No
910505100053	WT120C G2 LED40S/840 PSD L1200	LED40S	No
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	LED40S	No
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	LED40S	No
910505101269	WT120C G2 LED40S/840 WIA L1200	-	No
910505101270	WT120C G2 LED40S/840 WIA ELB3 L1200	-	No
911401535291	WT120C G2 LED27S/840 PSU TW3 L1200	-	No
911401535391	WT120C G2 LED40S/840 PSU TW3 L1200	-	No
911401815687	WT120C G2 LED60S/840 PSU L1200	-	-
911401815787	WT120C G2 LED80S/840 PSU L1200	-	-
911401816187	WT120C G2 LED60S/840 PSD L1200	-	-
911401816287	WT120C G2 LED80S/840 PSD L1200	-	-
911401823580	WT120C G2 LED27S/840 PSU L1200	-	No
911401823780	WT120C G2 LED40S/840 PSU L1200	-	No
911401824381	WT120C G2 LED40S/865 PSU L1200	-	No
911401824681	WT120C G2 LED37S/830 PSU L1200	-	No
911401826785	WT120C G2 LED27S/840 PSU L1200 BN	-	No

Order Code	Full Product Name	Lamp family code	Light source replaceable
911401826885	WT120C G2 LED40S/840 PSU L1200 BN	-	No
911401836980	WT120C G2 LED18S/840 PSU PCO L600	-	No
911401837080	WT120C G2 LED25S/840 PSU PCO L1200	-	No
911401837180	WT120C G2 LED31S/840 PSU PCO L1500	-	No
911401837280	WT120C G2 LED37S/840 PSU PCO L1200	-	No
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	-	No
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	-	No
911401814985	WT120C G2 LED27_45S/840 PSU L1200	-	No
910505100036	WT120C G2 LED19S/840 PSU MDU L600	LED27S	No
910505100038	WT120C G2 LED19S/840 PSD L600	LED19S	No
911401815487	WT120C G2 LED20S/840 PSU L600	-	-
911401815587	WT120C G2 LED40S/840 PSU L600	-	-
911401816087	WT120C G2 LED40S/840 PSD L600	-	-
911401823480	WT120C G2 LED19S/840 PSU L600	-	No
911401825885	WT120C G2 LED19S/840 PSU L600 BN	-	No
911401815085	WT120C G2 LED37_60S/840 PSU L1500	-	No
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	LED34S	No
910505100059	WT120C G2 LED34S/840 PSU MDU L1500	LED34S	No
910505100061	WT120C G2 LED34S/840 PSD L1500	LED34S	No
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	LED34S	No
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	LED34S	No
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	LED60S	No
910505100067	WT120C G2 LED60S/840 PSU MDU L1500	LED60S	No
910505100068	WT120C G2 LED60S/840 PSU MDU TW3 L1500	LED60S	No
910505100069	WT120C G2 LED60S/840 PSU WEC L1500	LED60S	No
910505100070	WT120C G2 LED60S/840 PSU TW1 WEC L1500	LED60S	No
910505100072	WT120C G2 LED60S/840 PSD L1500	LED60S	No
910505100073	WT120C G2 LED60S/840 PSU ELB3 L1500	LED60S	No
910505100076	WT120C G2 LED60S/840 PSD ELB3 L1500	LED60S	No
910505100077	WT120C G2 LED80S/840 PSU TW3 L1500	LED80S	No
910505100078	WT120C G2 LED80S/840 PSU MDU L1500	LED80S	No
910505100079	WT120C G2 LED80S/840 PSD L1500	LED80S	No
910505100080	WT120C G2 LED80S/840 PSU L1500 ELB3	LED80S	No
910505101271	WT120C G2 LED65S/840 WIA L1500	-	No
910505101272	WT120C G2 LED65S/840 WIA ELB3 L1500	-	No
910505101274	WT120C G2 LED65S/840 WIA TW3 L1500	-	No
910505103013	WT120C G2 LED80S/840 WIA L1500	-	No
910505103015	WT120C G2 LED80S/840 WIA TW3 L1500	-	No
911401535491	WT120C G2 LED34S/840 PSU TW3 L1500	-	No
911401535591	WT120C G2 LED60S/840 PSU TW3 L1500	-	No
911401535691	WT120C G2 LED80S/840 PSU TW3 L1500	-	No
911401815887	WT120C G2 LED100S/840 PSU L1500	-	-
911401815987	WT120C G2 LED120S/840 PSU L1500	-	-
911401816387	WT120C G2 LED100S/840 PSD L1500	-	-
911401816487	WT120C G2 LED120S/840 PSD L1500	-	-
911401823680	WT120C G2 LED34S/840 PSU L1500	-	No
911401823880	WT120C G2 LED60S/840 PSU L1500	-	No
911401823980	WT120C G2 LED80S/840 PSU L1500	-	No
911401824481	WT120C G2 LED34S/865 PSU L1500	-	No
911401824581	WT120C G2 LED60S/865 PSU L1500	-	No
911401824781	WT120C G2 LED55S/830 PSU L1500	-	No
911401825985	WT120C G2 LED34S/840 PSU L1500 BN	-	No

CoreLine Waterproof

Order Code	Full Product Name	Lamp family code	Light source replaceable
911401826085	WT120C G2 LED80S/840 PSU L1500 BN	-	No
911401826985	WT120C G2 LED60S/840 PSU L1500 BN	-	No

Light Technical (1/2)

Order Code	Full Product Name	All-in Type	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Order Code	Full Product Name	All-in Type	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	-	4000 K	126 lm/W	2,700 lm	911401535291	WT120C G2 LED27S/840 PSU TW3 L1200	-	4000 K	131 lm/W	2,700 lm
910505100040	WT120C G2 LED27S/840 PSU MDU L1200	-	4000 K	123 lm/W	2,700 lm	911401535391	WT120C G2 LED40S/840 PSU TW3 L1200	-	4000 K	140 lm/W	4,000 lm
910505100042	WT120C G2 LED27S/840 PSU ELB3 L1200	-	4000 K	104 lm/W	2,700 lm	911401815687	WT120C G2 LED60S/840 PSU L1200	-	4000 K	160 lm/W	6,000 lm
910505100044	WT120C G2 LED27S/840 PSD L1200	-	4000 K	123 lm/W	2,700 lm	911401815787	WT120C G2 LED80S/840 PSU L1200	-	4000 K	160 lm/W	8,000 lm
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	-	4000 K	100 lm/W	2,700 lm	911401816187	WT120C G2 LED60S/840 PSD L1200	-	4000 K	160 lm/W	6,000 lm
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	-	4000 K	133 lm/W	4,000 lm	911401816287	WT120C G2 LED80S/840 PSD L1200	-	4000 K	160 lm/W	8,000 lm
910505100048	WT120C G2 LED40S/840 PSU MDU L1200	-	4000 K	131 lm/W	4,000 lm	911401823580	WT120C G2 LED27S/840 PSU L1200	-	4000 K	131 lm/W	2,700 lm
910505100049	WT120C G2 LED40S/840 PSU MDU TW3 L1200	-	4000 K	133 lm/W	4,000 lm	911401823780	WT120C G2 LED40S/840 PSU L1200	-	4000 K	140 lm/W	4,000 lm
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-	4000 K	136 lm/W	4,000 lm	911401824381	WT120C G2 LED40S/865 PSU L1200	-	6500 K	140 lm/W	4,000 lm
910505100053	WT120C G2 LED40S/840 PSD L1200	-	4000 K	131 lm/W	4,000 lm	911401824681	WT120C G2 LED37S/830 PSU L1200	-	3000 K	130 lm/W	3,700 lm
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	-	4000 K	121 lm/W	4,000 lm	911401826785	WT120C G2 LED27S/840 PSU L1200 BN	-	4000 K	126 lm/W	2,700 lm
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	-	4000 K	113 lm/W	4,000 lm	911401826885	WT120C G2 LED40S/840 PSU L1200 BN	-	4000 K	140 lm/W	4,000 lm
910505101269	WT120C G2 LED40S/840 WIA L1200	-	4000 K	133 lm/W	4,000 lm	911401836980	WT120C G2 LED18S/840 PSU PCO L600	-	4000 K	120 lm/W	1,800 lm
910505101270	WT120C G2 LED40S/840 WIA ELB3 L1200	-	4000 K	121 lm/W	4,000 lm	911401837080	WT120C G2 LED25S/840 PSU PCO L1200	-	4000 K	122 lm/W	2,500 lm

CoreLine Waterproof

Order Code	Full Product Name	All-in Type	Correlated Color	Luminous Efficacy	Luminous Flux
			Temperature (Nom)	(rated) (Nom)	
911401837180	WT120C G2 LED31S/840 PSU PCO L1500	-	4000 K	128 lm/W	3,100 lm
911401837280	WT120C G2 LED37S/840 PSU PCO L1200	-	4000 K	129 lm/W	3,700 lm
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	-	4000 K	133 lm/W	5,700 lm
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	-	4000 K	131 lm/W	7,500 lm
911401814985	WT120C G2 LED27_45S/840 PSU L1200	All-in, Multi Lumen	4000 K	150 lm/W	2,700 lm
910505100036	WT120C G2 LED19S/840 PSU MDU L600	-	4000 K	116 lm/W	1,900 lm
910505100038	WT120C G2 LED19S/840 PSD L600	-	4000 K	115 lm/W	1,900 lm
911401815487	WT120C G2 LED20S/840 PSU L600	-	4000 K	156 lm/W	2,000 lm
911401815587	WT120C G2 LED40S/840 PSU L600	-	4000 K	160 lm/W	4,000 lm
911401816087	WT120C G2 LED40S/840 PSD L600	-	4000 K	160 lm/W	4,000 lm
911401823480	WT120C G2 LED19S/840 PSU L600	-	4000 K	126 lm/W	1,900 lm
911401825885	WT120C G2 LED19S/840 PSU L600 BN	-	4000 K	126 lm/W	1,900 lm
911401815085	WT120C G2 LED37_60S/840 PSU L1500	All-in, Multi Lumen	4000 K	148 lm/W	3,700 lm
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	-	4000 K	133 lm/W	3,400 lm
910505100059	WT120C G2 LED34S/840 PSU MDU L1500	-	4000 K	131 lm/W	3,400 lm
910505100061	WT120C G2 LED34S/840 PSD L1500	-	4000 K	131 lm/W	3,400 lm

Order Code	Full Product Name	All-in Type	Correlated Color	Luminous Efficacy	Luminous Flux
			Temperature (Nom)	(rated) (Nom)	
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	-	4000 K	113 lm/W	3,400 lm
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	-	4000 K	110 lm/W	3,400 lm
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	-	4000 K	135 lm/W	6,000 lm
910505100067	WT120C G2 LED60S/840 PSU MDU L1500	-	4000 K	133 lm/W	6,000 lm
910505100068	WT120C G2 LED60S/840 PSU MDU TW3 L1500	-	4000 K	133 lm/W	6,000 lm
910505100069	WT120C G2 LED60S/840 PSU WEC L1500	-	4000 K	135 lm/W	6,000 lm
910505100070	WT120C G2 LED60S/840 PSU TW1 WEC L1500	-	4000 K	136 lm/W	6,000 lm
910505100072	WT120C G2 LED60S/840 PSD L1500	-	4000 K	133 lm/W	6,000 lm
910505100073	WT120C G2 LED60S/840 PSU ELB3 L1500	-	4000 K	121 lm/W	6,000 lm
910505100076	WT120C G2 LED60S/840 PSD ELB3 L1500	-	4000 K	121 lm/W	6,000 lm
910505100077	WT120C G2 LED80S/840 PSU TW3 L1500	-	4000 K	133 lm/W	8,000 lm
910505100078	WT120C G2 LED80S/840 PSU MDU L1500	-	4000 K	131 lm/W	8,000 lm
910505100079	WT120C G2 LED80S/840 PSD L1500	-	4000 K	129 lm/W	8,000 lm
910505100080	WT120C G2 LED80S/840 PSU L1500 ELB3	-	4000 K	126 lm/W	8,000 lm
910505101271	WT120C G2 LED65S/840 WIA L1500	-	4000 K	144 lm/W	6,500 lm
910505101272	WT120C G2 LED65S/840 WIA ELB3 L1500	-	4000 K	135 lm/W	6,500 lm

CoreLine Waterproof

Order Code	Full Product Name	All-in Type	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505101274	WT120C G2 LED65S/840 WIA TW3 L1500	-	4000 K	141 lm/W	6,500 lm
910505103013	WT120C G2 LED80S/840 WIA L1500	-	4000 K	131 lm/W	8,000 lm
910505103015	WT120C G2 LED80S/840 WIA TW3 L1500	-	4000 K	133 lm/W	8,000 lm
911401535491	WT120C G2 LED34S/840 PSU TW3 L1500	-	4000 K	138 lm/W	3,400 lm
911401535591	WT120C G2 LED60S/840 PSU TW3 L1500	-	4000 K	140 lm/W	6,000 lm
911401535691	WT120C G2 LED80S/840 PSU TW3 L1500	-	4000 K	140 lm/W	8,000 lm
911401815887	WT120C G2 LED100S/840 PSU L1500	-	4000 K	160 lm/W	10,000 lm
911401815987	WT120C G2 LED120S/840 PSU L1500	-	4000 K	160 lm/W	12,000 lm
911401816387	WT120C G2 LED100S/840 PSD L1500	-	4000 K	160 lm/W	10,000 lm
911401816487	WT120C G2 LED120S/840 PSD L1500	-	4000 K	160 lm/W	12,000 lm

Order Code	Full Product Name	All-in Type	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401823680	WT120C G2 LED34S/840 PSU L1500	-	4000 K	140 lm/W	3,400 lm
911401823880	WT120C G2 LED60S/840 PSU L1500	-	4000 K	140 lm/W	6,000 lm
911401823980	WT120C G2 LED80S/840 PSU L1500	-	4000 K	140 lm/W	8,000 lm
911401824481	WT120C G2 LED34S/865 PSU L1500	-	6500 K	139 lm/W	3,400 lm
911401824581	WT120C G2 LED60S/865 PSU L1500	-	6500 K	139 lm/W	6,000 lm
911401824781	WT120C G2 LED55S/830 PSU L1500	-	3000 K	128 lm/W	5,500 lm
911401825985	WT120C G2 LED34S/840 PSU L1500 BN	-	4000 K	141 lm/W	3,400 lm
911401826085	WT120C G2 LED80S/840 PSU L1500 BN	-	4000 K	140 lm/W	8,000 lm
911401826985	WT120C G2 LED60S/840 PSU L1500 BN	-	4000 K	140 lm/W	6,000 lm

Light Technical (2/2)

Order Code	Full Product Name	Optic type
910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	Wide beam
910505100040	WT120C G2 LED27S/840 PSU MDU L1200	Wide beam
910505100042	WT120C G2 LED27S/840 PSU ELB3 L1200	Wide beam
910505100044	WT120C G2 LED27S/840 PSD L1200	Wide beam
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	Wide beam
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	Wide beam
910505100048	WT120C G2 LED40S/840 PSU MDU L1200	Wide beam
910505100049	WT120C G2 LED40S/840 PSU MDU TW3 L1200	Wide beam
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	Wide beam
910505100053	WT120C G2 LED40S/840 PSD L1200	Wide beam
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	Wide beam
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	Wide beam
910505101269	WT120C G2 LED40S/840 WIA L1200	Wide beam
910505101270	WT120C G2 LED40S/840 WIA ELB3 L1200	Wide beam
911401535291	WT120C G2 LED27S/840 PSU TW3 L1200	Beam angle 110°

Order Code	Full Product Name	Optic type
911401535391	WT120C G2 LED40S/840 PSU TW3 L1200	Beam angle 110°
911401815687	WT120C G2 LED60S/840 PSU L1200	Symmetrical
911401815787	WT120C G2 LED80S/840 PSU L1200	Symmetrical
911401816187	WT120C G2 LED60S/840 PSD L1200	Symmetrical
911401816287	WT120C G2 LED80S/840 PSD L1200	Symmetrical
911401823580	WT120C G2 LED27S/840 PSU L1200	Wide beam
911401823780	WT120C G2 LED40S/840 PSU L1200	Wide beam
911401824381	WT120C G2 LED40S/865 PSU L1200	Wide beam
911401824681	WT120C G2 LED37S/830 PSU L1200	Wide beam
911401826785	WT120C G2 LED27S/840 PSU L1200 BN	Symmetrical
911401826885	WT120C G2 LED40S/840 PSU L1200 BN	Symmetrical
911401836980	WT120C G2 LED18S/840 PSU PCO L600	Very wide beam
911401837080	WT120C G2 LED25S/840 PSU PCO L1200	Very wide beam
911401837180	WT120C G2 LED31S/840 PSU PCO L1500	Very wide beam
911401837280	WT120C G2 LED37S/840 PSU PCO L1200	Very wide beam

CoreLine Waterproof

Order Code	Full Product Name	Optic type
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	Very wide beam
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	Very wide beam
911401814985	WT120C G2 LED27_45S/840 PSU L1200	Symmetrical
910505100036	WT120C G2 LED19S/840 PSU MDU L600	Wide beam
910505100038	WT120C G2 LED19S/840 PSD L600	Wide beam
911401815487	WT120C G2 LED20S/840 PSU L600	Symmetrical
911401815587	WT120C G2 LED40S/840 PSU L600	Symmetrical
911401816087	WT120C G2 LED40S/840 PSD L600	Symmetrical
911401823480	WT120C G2 LED19S/840 PSU L600	Wide beam
911401825885	WT120C G2 LED19S/840 PSU L600 BN	Symmetrical
911401815085	WT120C G2 LED37_60S/840 PSU L1500	Symmetrical
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	Wide beam
910505100059	WT120C G2 LED34S/840 PSU MDU L1500	Wide beam
910505100061	WT120C G2 LED34S/840 PSD L1500	Wide beam
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	Wide beam
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	Wide beam
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	Wide beam
910505100067	WT120C G2 LED60S/840 PSU MDU L1500	Wide beam
910505100068	WT120C G2 LED60S/840 PSU MDU TW3 L1500	Wide beam
910505100069	WT120C G2 LED60S/840 PSU WEC L1500	Wide beam
910505100070	WT120C G2 LED60S/840 PSU TW1 WEC L1500	Wide beam
910505100072	WT120C G2 LED60S/840 PSD L1500	Wide beam
910505100073	WT120C G2 LED60S/840 PSU ELB3 L1500	Wide beam
910505100076	WT120C G2 LED60S/840 PSD ELB3 L1500	Wide beam
910505100077	WT120C G2 LED80S/840 PSU TW3 L1500	Wide beam

Order Code	Full Product Name	Optic type
910505100078	WT120C G2 LED80S/840 PSU MDU L1500	Wide beam
910505100079	WT120C G2 LED80S/840 PSD L1500	Wide beam
910505100080	WT120C G2 LED80S/840 PSU L1500 ELB3	Wide beam
910505101271	WT120C G2 LED65S/840 WIA L1500	Wide beam
910505101272	WT120C G2 LED65S/840 WIA ELB3 L1500	Wide beam
910505101274	WT120C G2 LED65S/840 WIA TW3 L1500	Wide beam
910505103013	WT120C G2 LED80S/840 WIA L1500	Wide beam
910505103015	WT120C G2 LED80S/840 WIA TW3 L1500	Wide beam
911401535491	WT120C G2 LED34S/840 PSU TW3 L1500	Beam angle 110°
911401535591	WT120C G2 LED60S/840 PSU TW3 L1500	Beam angle 110°
911401535691	WT120C G2 LED80S/840 PSU TW3 L1500	Beam angle 110°
911401815887	WT120C G2 LED100S/840 PSU L1500	Symmetrical
911401815987	WT120C G2 LED120S/840 PSU L1500	Symmetrical
911401816387	WT120C G2 LED100S/840 PSD L1500	Symmetrical
911401816487	WT120C G2 LED120S/840 PSD L1500	Symmetrical
911401823680	WT120C G2 LED34S/840 PSU L1500	Wide beam
911401823880	WT120C G2 LED60S/840 PSU L1500	Wide beam
911401823980	WT120C G2 LED80S/840 PSU L1500	Wide beam
911401824481	WT120C G2 LED34S/865 PSU L1500	Wide beam
911401824581	WT120C G2 LED60S/865 PSU L1500	Wide beam
911401824781	WT120C G2 LED55S/830 PSU L1500	Wide beam
911401825985	WT120C G2 LED34S/840 PSU L1500 BN	Symmetrical
911401826085	WT120C G2 LED80S/840 PSU L1500 BN	Symmetrical
911401826985	WT120C G2 LED60S/840 PSU L1500 BN	Symmetrical

Operating and Electrical

Order Code	Full Product Name	Power		Suitable for random switching
		Input Voltage	Consumption	
910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	220 to 240 V	21.5 W	Not applicable
910505100040	WT120C G2 LED27S/840 PSU MDU L1200	220 to 240 V	22 W	Yes
910505100042	WT120C G2 LED27S/840 PSU ELB3 L1200	220 to 240 V	26 W	Not applicable
910505100044	WT120C G2 LED27S/840 PSD L1200	220 to 240 V	22 W	Not applicable
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	220 to 240 V	27 W	Not applicable
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	220 to 240 V	30 W	Not applicable
910505100048	WT120C G2 LED40S/840 PSU MDU L1200	220 to 240 V	30.5 W	Yes

Order Code	Full Product Name	Power		Suitable for random switching
		Input Voltage	Consumption	
910505100049	WT120C G2 LED40S/840 PSU MDU TW3 L1200	220 to 240 V	30 W	Yes
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	220 to 240 V	29.5 W	Not applicable
910505100053	WT120C G2 LED40S/840 PSD L1200	220 to 240 V	30.5 W	Not applicable
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	220 to 240 V	33 W	Not applicable
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	220 to 240 V	35.5 W	Not applicable
910505101269	WT120C G2 LED40S/840 WIA L1200	220 to 240 V	30 W	Not applicable
910505101270	WT120C G2 LED40S/840 WIA ELB3 L1200	220 to 240 V	33 W	Not applicable

CoreLine Waterproof

Order Code	Full Product Name	Input Voltage	Power		Suitable for random switching
			Consumption		
911401535291	WT120C G2 LED27S/840 PSU TW3 L1200	220 to 240 V	20.5 W		Not applicable
911401535391	WT120C G2 LED40S/840 PSU TW3 L1200	220 to 240 V	28.5 W		Not applicable
911401815687	WT120C G2 LED60S/840 PSU L1200	220 to 240 V	37.5 W		No
911401815787	WT120C G2 LED80S/840 PSU L1200	220 to 240 V	50 W		No
911401816187	WT120C G2 LED60S/840 PSD L1200	220 to 240 V	37.5 W		No
911401816287	WT120C G2 LED80S/840 PSD L1200	220 to 240 V	50 W		No
911401823580	WT120C G2 LED27S/840 PSU L1200	220 to 240 V	20.5 W		Not applicable
911401823780	WT120C G2 LED40S/840 PSU L1200	220 to 240 V	28.6 W		Not applicable
911401824381	WT120C G2 LED40S/865 PSU L1200	220 to 240 V	28.5 W		Not applicable
911401824681	WT120C G2 LED37S/830 PSU L1200	220 to 240 V	28.5 W		Not applicable
911401826785	WT120C G2 LED27S/840 PSU L1200 BN	220 to 240 V	21 W		Yes
911401826885	WT120C G2 LED40S/840 PSU L1200 BN	220 to 240 V	29 W		Yes
911401836980	WT120C G2 LED18S/840 PSU PCO L600	220 to 240 V	15 W		Not applicable
911401837080	WT120C G2 LED25S/840 PSU PCO L1200	220 to 240 V	20.5 W		Not applicable
911401837180	WT120C G2 LED31S/840 PSU PCO L1500	220 to 240 V	24.3 W		Not applicable
911401837280	WT120C G2 LED37S/840 PSU PCO L1200	220 to 240 V	28.6 W		Not applicable

Order Code	Full Product Name	Input Voltage	Power		Suitable for random switching
			Consumption		
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	220 to 240 V	42.9 W		Not applicable
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	220 to 240 V	57.1 W		Not applicable
911401814985	WT120C G2 LED27_45S/840 PSU L1200	220 to 240 V	32 W		Yes
910505100036	WT120C G2 LED19S/840 PSU MDU L600	220 to 240 V	16.4 W		Yes
910505100038	WT120C G2 LED19S/840 PSD L600	220 to 240 V	16.5 W		Not applicable
911401815487	WT120C G2 LED20S/840 PSU L600	220 to 240 V	12.8 W		No
911401815587	WT120C G2 LED40S/840 PSU L600	220 to 240 V	25 W		No
911401816087	WT120C G2 LED40S/840 PSD L600	220 to 240 V	25 W		No
911401823480	WT120C G2 LED19S/840 PSU L600	220 to 240 V	15 W		Not applicable
911401825885	WT120C G2 LED19S/840 PSU L600 BN	220 to 240 V	15 W		Yes
911401815085	WT120C G2 LED37_60S/840 PSU L1500	220 to 240 V	43 W		Yes
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	220 to 240 V	25.5 W		Not applicable
910505100059	WT120C G2 LED34S/840 PSU MDU L1500	220 to 240 V	26 W		Yes
910505100061	WT120C G2 LED34S/840 PSD L1500	220 to 240 V	26 W		Not applicable
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	220 to 240 V	30 W		Not applicable
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	220 to 240 V	31 W		Not applicable
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	220 to 240 V	44.5 W		Not applicable

CoreLine Waterproof

Order Code	Full Product Name	Input Voltage	Power		Suitable for random switching
			Consumption		
910505100067	WT120C G2 LED60S/840 PSU MDU L1500	220 to 240 V	45 W		Yes
910505100068	WT120C G2 LED60S/840 PSU MDU TW3 L1500	220 to 240 V	45 W		Yes
910505100069	WT120C G2 LED60S/840 PSU WEC L1500	220 to 240 V	44.5 W		Not applicable
910505100070	WT120C G2 LED60S/840 PSU TW1 WEC L1500	220 to 240 V	44 W		Not applicable
910505100072	WT120C G2 LED60S/840 PSD L1500	220 to 240 V	45 W		Not applicable
910505100073	WT120C G2 LED60S/840 PSU ELB3 L1500	220 to 240 V	49.5 W		Not applicable
910505100076	WT120C G2 LED60S/840 PSD ELB3 L1500	220 to 240 V	49.5 W		Not applicable
910505100077	WT120C G2 LED80S/840 PSU TW3 L1500	220 to 240 V	60 W		Not applicable
910505100078	WT120C G2 LED80S/840 PSU MDU L1500	220 to 240 V	61 W		Yes
910505100079	WT120C G2 LED80S/840 PSD L1500	220 to 240 V	62 W		Not applicable
910505100080	WT120C G2 LED80S/840 PSU L1500 ELB3	220 to 240 V	63.5 W		Not applicable
910505101271	WT120C G2 LED65S/840 WIA L1500	220 to 240 V	45 W		Not applicable
910505101272	WT120C G2 LED65S/840 WIA ELB3 L1500	220 to 240 V	48 W		Not applicable
910505101274	WT120C G2 LED65S/840 WIA TW3 L1500	220 to 240 V	46 W		Not applicable
910505103013	WT120C G2 LED80S/840 WIA L1500	220-240 V	61 W		Not applicable
910505103015	WT120C G2 LED80S/840 WIA TW3 L1500	220-240 V	60 W		Not applicable

Order Code	Full Product Name	Input Voltage	Power		Suitable for random switching
			Consumption		
911401535491	WT120C G2 LED34S/840 PSU TW3 L1500	220 to 240 V	24.5 W		Not applicable
911401535591	WT120C G2 LED60S/840 PSU TW3 L1500	220 to 240 V	43 W		Not applicable
911401535691	WT120C G2 LED80S/840 PSU TW3 L1500	220 to 240 V	57 W		Not applicable
911401815887	WT120C G2 LED100S/840 PSU L1500	220 to 240 V	62 W		No
911401815987	WT120C G2 LED120S/840 PSU L1500	220 to 240 V	75 W		No
911401816387	WT120C G2 LED100S/840 PSD L1500	220 to 240 V	62 W		No
911401816487	WT120C G2 LED120S/840 PSD L1500	220 to 240 V	75 W		No
911401823680	WT120C G2 LED34S/840 PSU L1500	220 to 240 V	24.3 W		Not applicable
911401823880	WT120C G2 LED60S/840 PSU L1500	220 to 240 V	42.9 W		Not applicable
911401823980	WT120C G2 LED80S/840 PSU L1500	220 to 240 V	57.1 W		Not applicable
911401824481	WT120C G2 LED34S/865 PSU L1500	220 to 240 V	24.5 W		Not applicable
911401824581	WT120C G2 LED60S/865 PSU L1500	220 to 240 V	43 W		Not applicable
911401824781	WT120C G2 LED55S/830 PSU L1500	220 to 240 V	43 W		Not applicable
911401825985	WT120C G2 LED34S/840 PSU L1500 BN	220 to 240 V	24 W		Yes
911401826085	WT120C G2 LED80S/840 PSU L1500 BN	220 to 240 V	57 W		Yes
911401826985	WT120C G2 LED60S/840 PSU L1500 BN	220 to 240 V	43 W		Yes

Controls and Dimming

CoreLine Waterproof

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	No	-	Not applicable
910505100040	WT120C G2 LED27S/840 PSU MDU L1200	Yes	Movement and light sensor (On/Off)	Not applicable
910505100042	WT120C G2 LED27S/840 PSU ELB3 L1200	No	-	Not applicable
910505100044	WT120C G2 LED27S/840 PSD L1200	Yes	-	1%
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	Yes	-	1%
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	No	-	Not applicable
910505100048	WT120C G2 LED40S/840 PSU MDU L1200	Yes	Movement and light sensor (On/Off)	Not applicable
910505100049	WT120C G2 LED40S/840 PSU MDU TW3 L1200	Yes	Movement and light sensor (On/Off)	Not applicable
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	No	-	Not applicable
910505100053	WT120C G2 LED40S/840 PSD L1200	Yes	-	1%
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	No	-	Not applicable
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	Yes	-	1%
910505101269	WT120C G2 LED40S/840 WIA L1200	Yes	-	10%
910505101270	WT120C G2 LED40S/840 WIA ELB3 L1200	Yes	-	10%
911401535291	WT120C G2 LED27S/840 PSU TW3 L1200	No	-	Not applicable
911401535391	WT120C G2 LED40S/840 PSU TW3 L1200	No	-	Not applicable
911401815687	WT120C G2 LED60S/840 PSU L1200	No	-	-
911401815787	WT120C G2 LED80S/840 PSU L1200	No	-	-
911401816187	WT120C G2 LED60S/840 PSD L1200	Yes	-	-
911401816287	WT120C G2 LED80S/840 PSD L1200	Yes	-	-
911401823580	WT120C G2 LED27S/840 PSU L1200	No	-	Not applicable
911401823780	WT120C G2 LED40S/840 PSU L1200	No	-	Not applicable

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
911401824381	WT120C G2 LED40S/865 PSU L1200	No	-	Not applicable
911401824681	WT120C G2 LED37S/830 PSU L1200	No	-	Not applicable
911401826785	WT120C G2 LED27S/840 PSU L1200 BN	No	-	-
911401826885	WT120C G2 LED40S/840 PSU L1200 BN	No	-	-
911401836980	WT120C G2 LED18S/840 PSU PCO L600	No	-	Not applicable
911401837080	WT120C G2 LED25S/840 PSU PCO L1200	No	-	Not applicable
911401837180	WT120C G2 LED31S/840 PSU PCO L1500	No	-	Not applicable
911401837280	WT120C G2 LED37S/840 PSU PCO L1200	No	-	Not applicable
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	No	-	Not applicable
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	No	-	Not applicable
911401814985	WT120C G2 LED27_45S/840 PSU L1200	No	-	-
910505100036	WT120C G2 LED19S/840 PSU MDU L600	Yes	Movement and light sensor (On/Off)	Not applicable
910505100038	WT120C G2 LED19S/840 PSD L600	Yes	-	1%
911401815487	WT120C G2 LED20S/840 PSU L600	No	-	-
911401815587	WT120C G2 LED40S/840 PSU L600	No	-	-
911401816087	WT120C G2 LED40S/840 PSD L600	Yes	-	-
911401823480	WT120C G2 LED19S/840 PSU L600	No	-	Not applicable
911401825885	WT120C G2 LED19S/840 PSU L600 BN	No	-	-
911401815085	WT120C G2 LED37_60S/840 PSU L1500	No	-	-
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	No	-	Not applicable
910505100059	WT120C G2 LED34S/840 PSU MDU L1500	Yes	Movement and light sensor (On/Off)	Not applicable
910505100061	WT120C G2 LED34S/840 PSD L1500	Yes	-	1%
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	No	-	Not applicable

CoreLine Waterproof

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	Yes	-	1%
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	No	-	Not applicable
910505100067	WT120C G2 LED60S/840 PSU MDU L1500	Yes	Movement and light sensor (On/Off)	Not applicable
910505100068	WT120C G2 LED60S/840 PSU MDU TW3 L1500	Yes	Movement and light sensor (On/Off)	Not applicable
910505100069	WT120C G2 LED60S/840 PSU WEC L1500	No	-	Not applicable
910505100070	WT120C G2 LED60S/840 PSU TW1 WEC L1500	No	-	Not applicable
910505100072	WT120C G2 LED60S/840 PSD L1500	Yes	-	1%
910505100073	WT120C G2 LED60S/840 PSU ELB3 L1500	No	-	Not applicable
910505100076	WT120C G2 LED60S/840 PSD ELB3 L1500	Yes	-	1%
910505100077	WT120C G2 LED80S/840 PSU TW3 L1500	No	-	Not applicable
910505100078	WT120C G2 LED80S/840 PSU MDU L1500	Yes	Movement and light sensor (On/Off)	Not applicable
910505100079	WT120C G2 LED80S/840 PSD L1500	Yes	-	1%
910505100080	WT120C G2 LED80S/840 PSU L1500 ELB3	No	-	Not applicable
910505101271	WT120C G2 LED65S/840 WIA L1500	Yes	-	10%
910505101272	WT120C G2 LED65S/840 WIA ELB3 L1500	Yes	-	10%
910505101274	WT120C G2 LED65S/840 WIA TW3 L1500	Yes	-	10%

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505103013	WT120C G2 LED80S/840 WIA L1500	Yes	-	10%
910505103015	WT120C G2 LED80S/840 WIA TW3 L1500	Yes	-	10%
911401535491	WT120C G2 LED34S/840 PSU TW3 L1500	No	-	Not applicable
911401535591	WT120C G2 LED60S/840 PSU TW3 L1500	No	-	Not applicable
911401535691	WT120C G2 LED80S/840 PSU TW3 L1500	No	-	Not applicable
911401815887	WT120C G2 LED100S/840 PSU L1500	No	-	-
911401815987	WT120C G2 LED120S/840 PSU L1500	No	-	-
911401816387	WT120C G2 LED100S/840 PSD L1500	Yes	-	-
911401816487	WT120C G2 LED120S/840 PSD L1500	Yes	-	-
911401823680	WT120C G2 LED34S/840 PSU L1500	No	-	Not applicable
911401823880	WT120C G2 LED60S/840 PSU L1500	No	-	Not applicable
911401823980	WT120C G2 LED80S/840 PSU L1500	No	-	Not applicable
911401824481	WT120C G2 LED34S/865 PSU L1500	No	-	Not applicable
911401824581	WT120C G2 LED60S/865 PSU L1500	No	-	Not applicable
911401824781	WT120C G2 LED55S/830 PSU L1500	No	-	Not applicable
911401825985	WT120C G2 LED34S/840 PSU L1500 BN	No	-	-
911401826085	WT120C G2 LED80S/840 PSU L1500 BN	No	-	-
911401826985	WT120C G2 LED60S/840 PSU L1500 BN	No	-	-

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	Gray
910505100040	WT120C G2 LED27S/840 PSU MDU L1200	Gray
910505100042	WT120C G2 LED27S/840 PSU ELB3 L1200	Gray
910505100044	WT120C G2 LED27S/840 PSD L1200	Gray
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	Gray
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	Gray
910505100048	WT120C G2 LED40S/840 PSU MDU L1200	Gray
910505100049	WT120C G2 LED40S/840 PSU MDU TW3 L1200	Gray
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	Gray

Order Code	Full Product Name	Housing Color
910505100053	WT120C G2 LED40S/840 PSD L1200	Gray
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	Gray
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	Gray
910505101269	WT120C G2 LED40S/840 WIA L1200	Gray
910505101270	WT120C G2 LED40S/840 WIA ELB3 L1200	Gray
911401535291	WT120C G2 LED27S/840 PSU TW3 L1200	Gray
911401535391	WT120C G2 LED40S/840 PSU TW3 L1200	Gray
911401815687	WT120C G2 LED60S/840 PSU L1200	Grey
911401815787	WT120C G2 LED80S/840 PSU L1200	Grey

CoreLine Waterproof

Order Code	Full Product Name	Housing Color
911401816187	WT120C G2 LED60S/840 PSD L1200	Grey
911401816287	WT120C G2 LED80S/840 PSD L1200	Grey
911401823580	WT120C G2 LED27S/840 PSU L1200	Grey
911401823780	WT120C G2 LED40S/840 PSU L1200	Grey
911401824381	WT120C G2 LED40S/865 PSU L1200	Grey
911401824681	WT120C G2 LED37S/830 PSU L1200	Grey
911401826785	WT120C G2 LED27S/840 PSU L1200 BN	Grey
911401826885	WT120C G2 LED40S/840 PSU L1200 BN	Grey
911401836980	WT120C G2 LED18S/840 PSU PCO L600	Grey
911401837080	WT120C G2 LED25S/840 PSU PCO L1200	Grey
911401837180	WT120C G2 LED31S/840 PSU PCO L1500	Grey
911401837280	WT120C G2 LED37S/840 PSU PCO L1200	Grey
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	Grey
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	Grey
911401814985	WT120C G2 LED27_45S/840 PSU L1200	Grey
910505100036	WT120C G2 LED19S/840 PSU MDU L600	Grey
910505100038	WT120C G2 LED19S/840 PSD L600	Grey
911401815487	WT120C G2 LED20S/840 PSU L600	Grey
911401815587	WT120C G2 LED40S/840 PSU L600	Grey
911401816087	WT120C G2 LED40S/840 PSD L600	Grey
911401823480	WT120C G2 LED19S/840 PSU L600	Grey
911401825885	WT120C G2 LED19S/840 PSU L600 BN	Grey
911401815085	WT120C G2 LED37_60S/840 PSU L1500	Grey
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	Grey
910505100059	WT120C G2 LED34S/840 PSU MDU L1500	Grey
910505100061	WT120C G2 LED34S/840 PSD L1500	Grey
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	Grey
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	Grey
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	Grey
910505100067	WT120C G2 LED60S/840 PSU MDU L1500	Grey
910505100068	WT120C G2 LED60S/840 PSU MDU TW3 L1500	Grey

Order Code	Full Product Name	Housing Color
910505100069	WT120C G2 LED60S/840 PSU WEC L1500	Grey
910505100070	WT120C G2 LED60S/840 PSU TW1 WEC L1500	Grey
910505100072	WT120C G2 LED60S/840 PSD L1500	Grey
910505100073	WT120C G2 LED60S/840 PSU ELB3 L1500	Grey
910505100076	WT120C G2 LED60S/840 PSD ELB3 L1500	Grey
910505100077	WT120C G2 LED80S/840 PSU TW3 L1500	Grey
910505100078	WT120C G2 LED80S/840 PSU MDU L1500	Grey
910505100079	WT120C G2 LED80S/840 PSD L1500	Grey
910505100080	WT120C G2 LED80S/840 PSU L1500 ELB3	Grey
910505101271	WT120C G2 LED65S/840 WIA L1500	Grey
910505101272	WT120C G2 LED65S/840 WIA ELB3 L1500	Grey
910505101274	WT120C G2 LED65S/840 WIA TW3 L1500	Grey
910505103013	WT120C G2 LED80S/840 WIA L1500	Grey
910505103015	WT120C G2 LED80S/840 WIA TW3 L1500	Grey
911401535491	WT120C G2 LED34S/840 PSU TW3 L1500	Grey
911401535591	WT120C G2 LED60S/840 PSU TW3 L1500	Grey
911401535691	WT120C G2 LED80S/840 PSU TW3 L1500	Grey
911401815887	WT120C G2 LED100S/840 PSU L1500	Grey
911401815987	WT120C G2 LED120S/840 PSU L1500	Grey
911401816387	WT120C G2 LED100S/840 PSD L1500	Grey
911401816487	WT120C G2 LED120S/840 PSD L1500	Grey
911401823680	WT120C G2 LED34S/840 PSU L1500	Grey
911401823880	WT120C G2 LED60S/840 PSU L1500	Grey
911401823980	WT120C G2 LED80S/840 PSU L1500	Grey
911401824481	WT120C G2 LED34S/865 PSU L1500	Grey
911401824581	WT120C G2 LED60S/865 PSU L1500	Grey
911401824781	WT120C G2 LED55S/830 PSU L1500	Grey
911401825985	WT120C G2 LED34S/840 PSU L1500 BN	Grey
911401826085	WT120C G2 LED80S/840 PSU L1500 BN	Grey
911401826985	WT120C G2 LED60S/840 PSU L1500 BN	Grey

Emergency Operation (1/2)

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	-	-	-	-
910505100040	WT120C G2 LED27S/840 PSU MDU L1200	-	-	-	-
910505100042	WT120C G2 LED27S/840 PSU ELB3 L1200	No	Emergency lighting 3 hours duration basic version	500 lm	Lithium

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910505100044	WT120C G2 LED27S/840 PSD L1200	-	-	-	-
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	No	Emergency lighting 3 hours duration basic version	500 lm	Lithium
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	-	-	-	-

CoreLine Waterproof

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910505100048	WT120C G2 LED40S/840 PSU MDU L1200	-	-	-	-
910505100049	WT120C G2 LED40S/840 PSU MDU TW3 L1200	-	-	-	-
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-	-	-	-
910505100053	WT120C G2 LED40S/840 PSD L1200	-	-	-	-
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	No	Emergency lighting 3 hours duration basic version	500 lm	Lithium
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	No	Emergency lighting 3 hours duration basic version	500 lm	Lithium
910505101269	WT120C G2 LED40S/840 WIA L1200	-	-	-	-
910505101270	WT120C G2 LED40S/840 WIA ELB3 L1200	No	Emergency lighting 3 hours duration basic version	500 lm	Lithium
911401535291	WT120C G2 LED27S/840 PSU TW3 L1200	-	-	-	-
911401535391	WT120C G2 LED40S/840 PSU TW3 L1200	-	-	-	-
911401815687	WT120C G2 LED60S/840 PSU L1200	No	-	-	-
911401815787	WT120C G2 LED80S/840 PSU L1200	No	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
911401816187	WT120C G2 LED60S/840 PSD L1200	No	-	-	-
911401816287	WT120C G2 LED80S/840 PSD L1200	No	-	-	-
911401823580	WT120C G2 LED27S/840 PSU L1200	-	-	-	-
911401823780	WT120C G2 LED40S/840 PSU L1200	-	-	-	-
911401824381	WT120C G2 LED40S/865 PSU L1200	-	-	-	-
911401824681	WT120C G2 LED37S/830 PSU L1200	-	-	-	-
911401826785	WT120C G2 LED27S/840 PSU L1200 BN	-	-	-	-
911401826885	WT120C G2 LED40S/840 PSU L1200 BN	-	-	-	-
911401836980	WT120C G2 LED18S/840 PSU PCO L600	-	-	-	-
911401837080	WT120C G2 LED25S/840 PSU PCO L1200	-	-	-	-
911401837180	WT120C G2 LED31S/840 PSU PCO L1500	-	-	-	-
911401837280	WT120C G2 LED37S/840 PSU PCO L1200	-	-	-	-
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	-	-	-	-
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	-	-	-	-
911401814985	WT120C G2 LED27_45S/840 PSU L1200	-	-	-	-
910505100036	WT120C G2 LED19S/840 PSU MDU L600	-	-	-	-

CoreLine Waterproof

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910505100038	WT120C G2 LED19S/840 PSD L600	-	-	-	-
911401815487	WT120C G2 LED20S/840 PSU L600	No	-	-	-
911401815587	WT120C G2 LED40S/840 PSU L600	No	-	-	-
911401816087	WT120C G2 LED40S/840 PSD L600	No	-	-	-
911401823480	WT120C G2 LED19S/840 PSU L600	-	-	-	-
911401825885	WT120C G2 LED19S/840 PSU L600 BN	-	-	-	-
911401815085	WT120C G2 LED37_60S/840 PSU L1500	-	-	-	-
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	-	-	-	-
910505100059	WT120C G2 LED34S/840 PSU MDU L1500	-	-	-	-
910505100061	WT120C G2 LED34S/840 PSD L1500	-	-	-	-
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	No	Emergency lighting 3 hours duration basic version	500 lm	Lithium
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	No	Emergency lighting 3 hours duration basic version	500 lm	Lithium
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	-	-	-	-
910505100067	WT120C G2 LED60S/840 PSU MDU L1500	-	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910505100068	WT120C G2 LED60S/840 PSU MDU TW3 L1500	-	-	-	-
910505100069	WT120C G2 LED60S/840 PSU WEC L1500	-	-	-	-
910505100070	WT120C G2 LED60S/840 PSU TW1 WEC L1500	-	-	-	-
910505100072	WT120C G2 LED60S/840 PSD L1500	-	-	-	-
910505100073	WT120C G2 LED60S/840 PSU ELB3 L1500	No	Emergency lighting 3 hours duration basic version	500 lm	Lithium
910505100076	WT120C G2 LED60S/840 PSD ELB3 L1500	No	Emergency lighting 3 hours duration basic version	500 lm	Lithium
910505100077	WT120C G2 LED80S/840 PSU TW3 L1500	-	-	-	-
910505100078	WT120C G2 LED80S/840 PSU MDU L1500	-	-	-	-
910505100079	WT120C G2 LED80S/840 PSD L1500	-	-	-	-
910505100080	WT120C G2 LED80S/840 PSU L1500 ELB3	No	Emergency lighting 3 hours duration basic version	500 lm	Lithium
910505101271	WT120C G2 LED65S/840 WIA L1500	-	-	-	-
910505101272	WT120C G2 LED65S/840 WIA ELB3 L1500	No	Emergency lighting 3 hours duration	500 lm	Lithium

CoreLine Waterproof

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
			basic version		
910505101274	WT120C G2 LED65S/840 WIA TW3 L1500	-	-	-	-
910505103013	WT120C G2 LED80S/840 WIA L1500	-	-	-	-
910505103015	WT120C G2 LED80S/840 WIA TW3 L1500	-	-	-	-
911401535491	WT120C G2 LED34S/840 PSU TW3 L1500	-	-	-	-
911401535591	WT120C G2 LED60S/840 PSU TW3 L1500	-	-	-	-
911401535691	WT120C G2 LED80S/840 PSU TW3 L1500	-	-	-	-
911401815887	WT120C G2 LED100S/840 PSU L1500	No	-	-	-
911401815987	WT120C G2 LED120S/840 PSU L1500	No	-	-	-
911401816387	WT120C G2 LED100S/840 PSD L1500	No	-	-	-
911401816487	WT120C G2 LED120S/840 PSD L1500	No	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
911401823680	WT120C G2 LED34S/840 PSU L1500	-	-	-	-
911401823880	WT120C G2 LED60S/840 PSU L1500	-	-	-	-
911401823980	WT120C G2 LED80S/840 PSU L1500	-	-	-	-
911401824481	WT120C G2 LED34S/865 PSU L1500	-	-	-	-
911401824581	WT120C G2 LED60S/865 PSU L1500	-	-	-	-
911401824781	WT120C G2 LED55S/830 PSU L1500	-	-	-	-
911401825985	WT120C G2 LED34S/840 PSU L1500 BN	-	-	-	-
911401826085	WT120C G2 LED80S/840 PSU L1500 BN	-	-	-	-
911401826985	WT120C G2 LED60S/840 PSU L1500 BN	-	-	-	-

Emergency Operation (2/2)

Order Code	Full Product Name	Rated duration of the emergency lighting (when fully charged)
910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	-
910505100040	WT120C G2 LED27S/840 PSU MDU L1200	-
910505100042	WT120C G2 LED27S/840 PSU ELB3 L1200	3 hour(s)
910505100044	WT120C G2 LED27S/840 PSD L1200	-
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	3 hour(s)
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	-
910505100048	WT120C G2 LED40S/840 PSU MDU L1200	-
910505100049	WT120C G2 LED40S/840 PSU MDU TW3 L1200	-
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-
910505100053	WT120C G2 LED40S/840 PSD L1200	-
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	3 hour(s)

Order Code	Full Product Name	Rated duration of the emergency lighting (when fully charged)
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	3 hour(s)
910505101269	WT120C G2 LED40S/840 WIA L1200	-
910505101270	WT120C G2 LED40S/840 WIA ELB3 L1200	3 hour(s)
911401535291	WT120C G2 LED27S/840 PSU TW3 L1200	-
911401535391	WT120C G2 LED40S/840 PSU TW3 L1200	-
911401815687	WT120C G2 LED60S/840 PSU L1200	-
911401815787	WT120C G2 LED80S/840 PSU L1200	-
911401816187	WT120C G2 LED60S/840 PSD L1200	-
911401816287	WT120C G2 LED80S/840 PSD L1200	-
911401823580	WT120C G2 LED27S/840 PSU L1200	-
911401823780	WT120C G2 LED40S/840 PSU L1200	-

CoreLine Waterproof

Order Code	Full Product Name	Rated duration of the emergency lighting (when fully charged)
911401824381	WT120C G2 LED40S/865 PSU L1200	-
911401824681	WT120C G2 LED37S/830 PSU L1200	-
911401826785	WT120C G2 LED27S/840 PSU L1200 BN	-
911401826885	WT120C G2 LED40S/840 PSU L1200 BN	-
911401836980	WT120C G2 LED18S/840 PSU PCO L600	-
911401837080	WT120C G2 LED25S/840 PSU PCO L1200	-
911401837180	WT120C G2 LED31S/840 PSU PCO L1500	-
911401837280	WT120C G2 LED37S/840 PSU PCO L1200	-
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	-
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	-
911401814985	WT120C G2 LED27_45S/840 PSU L1200	-
910505100036	WT120C G2 LED19S/840 PSU MDU L600	-
910505100038	WT120C G2 LED19S/840 PSD L600	-
911401815487	WT120C G2 LED20S/840 PSU L600	-
911401815587	WT120C G2 LED40S/840 PSU L600	-
911401816087	WT120C G2 LED40S/840 PSD L600	-
911401823480	WT120C G2 LED19S/840 PSU L600	-
911401825885	WT120C G2 LED19S/840 PSU L600 BN	-
911401815085	WT120C G2 LED37_60S/840 PSU L1500	-
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	-
910505100059	WT120C G2 LED34S/840 PSU MDU L1500	-
910505100061	WT120C G2 LED34S/840 PSD L1500	-
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	3 hour(s)
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	3 hour(s)
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	-
910505100067	WT120C G2 LED60S/840 PSU MDU L1500	-
910505100068	WT120C G2 LED60S/840 PSU MDU TW3 L1500	-
910505100069	WT120C G2 LED60S/840 PSU WEC L1500	-
910505100070	WT120C G2 LED60S/840 PSU TW1 WEC L1500	-

Order Code	Full Product Name	Rated duration of the emergency lighting (when fully charged)
910505100072	WT120C G2 LED60S/840 PSD L1500	-
910505100073	WT120C G2 LED60S/840 PSU ELB3 L1500	3 hour(s)
910505100076	WT120C G2 LED60S/840 PSD ELB3 L1500	3 hour(s)
910505100077	WT120C G2 LED80S/840 PSU TW3 L1500	-
910505100078	WT120C G2 LED80S/840 PSU MDU L1500	-
910505100079	WT120C G2 LED80S/840 PSD L1500	-
910505100080	WT120C G2 LED80S/840 PSU L1500 ELB3	3 hour(s)
910505101271	WT120C G2 LED65S/840 WIA L1500	-
910505101272	WT120C G2 LED65S/840 WIA ELB3 L1500	3 hour(s)
910505101274	WT120C G2 LED65S/840 WIA TW3 L1500	-
910505103013	WT120C G2 LED80S/840 WIA L1500	-
910505103015	WT120C G2 LED80S/840 WIA TW3 L1500	-
911401535491	WT120C G2 LED34S/840 PSU TW3 L1500	-
911401535591	WT120C G2 LED60S/840 PSU TW3 L1500	-
911401535691	WT120C G2 LED80S/840 PSU TW3 L1500	-
911401815887	WT120C G2 LED100S/840 PSU L1500	-
911401815987	WT120C G2 LED120S/840 PSU L1500	-
911401816387	WT120C G2 LED100S/840 PSD L1500	-
911401816487	WT120C G2 LED120S/840 PSD L1500	-
911401823680	WT120C G2 LED34S/840 PSU L1500	-
911401823880	WT120C G2 LED60S/840 PSU L1500	-
911401823980	WT120C G2 LED80S/840 PSU L1500	-
911401824481	WT120C G2 LED34S/865 PSU L1500	-
911401824581	WT120C G2 LED60S/865 PSU L1500	-
911401824781	WT120C G2 LED55S/830 PSU L1500	-
911401825985	WT120C G2 LED34S/840 PSU L1500 BN	-
911401826085	WT120C G2 LED80S/840 PSU L1500 BN	-
911401826985	WT120C G2 LED60S/840 PSU L1500 BN	-

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3 (SVM)		Stroboscopic effect visibility measure
				per EN 61000-3-3	(SVM)	
910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	-20 to +35 °C	For mounting on easily flammable surfaces	1	1.6	1.6
910505100040	WT120C G2 LED27S/840 PSU MDU L1200	-20 to +35 °C	For mounting on easily flammable surfaces	1	1.6	1.6
910505100042	WT120C G2 LED27S/840	0 to +25 °C	For mounting on easily	1	1.6	1.6

Order Code	Full Product Name	Ambient temperature range	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3 (SVM)		Stroboscopic effect visibility measure
				per EN 61000-3-3	(SVM)	
910505100044	WT120C G2 LED27S/840 PSD L1200	-20 to +35 °C	For mounting on easily flammable surfaces	1	1.6	1.6
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	0 to +25 °C	For mounting on easily flammable surfaces	1	1.6	1.6

CoreLine Waterproof

Order Code	Full Product Name	Ambient temperature range	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	-20 to +35 °C	For mounting on easily flammable surfaces	1	1.6
910505100048	WT120C G2 LED40S/840 PSU MDU L1200	-20 to +35 °C	For mounting on easily flammable surfaces	1	1.6
910505100049	WT120C G2 LED40S/840 PSU MDU TW3 L1200	-20 to +35 °C	For mounting on easily flammable surfaces	1	1.6
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-20 to +35 °C	For mounting on easily flammable surfaces	1	1.6
910505100053	WT120C G2 LED40S/840 PSD L1200	-20 to +35 °C	For mounting on easily flammable surfaces	1	1.6
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	0 to +25 °C	For mounting on easily flammable surfaces	1	1.6
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	0 to +25 °C	For mounting on easily flammable surfaces	1	1.6
910505101269	WT120C G2 LED40S/840 WIA L1200	-20 to +35 °C	For mounting on easily flammable surfaces	1	1.6
910505101270	WT120C G2 LED40S/840 WIA ELB3 L1200	0 to +25 °C	For mounting on easily flammable surfaces	1	1.6
911401535291	WT120C G2 LED27S/840 PSU TW3 L1200	-20 to +40 °C	For mounting on easily flammable surfaces	1	1.6
911401535391	WT120C G2 LED40S/840 PSU TW3 L1200	-20 to +40 °C	For mounting on easily flammable surfaces	1	1.6

Order Code	Full Product Name	Ambient temperature range	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
911401815687	WT120C G2 LED60S/840 PSU L1200	-20 to +40 °C	For mounting on easily flammable surfaces	-	0.4
911401815787	WT120C G2 LED80S/840 PSU L1200	-20 to +40 °C	For mounting on easily flammable surfaces	-	0.4
911401816187	WT120C G2 LED60S/840 PSD L1200	-20 to +40 °C	For mounting on easily flammable surfaces	-	0.4
911401816287	WT120C G2 LED80S/840 PSD L1200	-20 to +40 °C	For mounting on easily flammable surfaces	-	0.4
911401823580	WT120C G2 LED27S/840 PSU L1200	-20 to +40 °C	For mounting on easily flammable surfaces	1	1.6
911401823780	WT120C G2 LED40S/840 PSU L1200	-20 to +40 °C	For mounting on easily flammable surfaces	1	1.6
911401824381	WT120C G2 LED40S/865 PSU L1200	-20 to +40 °C	For mounting on easily flammable surfaces	1	1.6
911401824681	WT120C G2 LED37S/830 PSU L1200	-20 to +40 °C	For mounting on easily flammable surfaces	1	1.6
911401826785	WT120C G2 LED27S/840 PSU L1200 BN	-20 to +40 °C	For mounting on easily flammable surfaces	1	0.4
911401826885	WT120C G2 LED40S/840 PSU L1200 BN	-20 to +40 °C	For mounting on easily flammable surfaces	1	0.4
911401836980	WT120C G2 LED18S/840 PSU PCO L600	-20 to +40 °C	For mounting on easily flammable surfaces	1	1.6
911401837080	WT120C G2 LED25S/840	-20 to +40 °C	For mounting on easily	1	1.6

CoreLine Waterproof

Order Code	Full Product Name	Ambient temperature range	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
	PSU PCO L1200		flammable surfaces		
911401837180	WT120C G2 LED31S/840 PSU PCO L1500	-20 to +40 °C	For mounting on easily flammable surfaces	1	1.6
911401837280	WT120C G2 LED37S/840 PSU PCO L1200	-20 to +40 °C	For mounting on easily flammable surfaces	1	1.6
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	-20 to +40 °C	For mounting on easily flammable surfaces	1	1.6
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	-20 to +40 °C	For mounting on easily flammable surfaces	1	1.6
911401814985	WT120C G2 LED27_45S/840 PSU L1200	-20 to +40 °C	For mounting on normally flammable surfaces	1	0.4
910505100036	WT120C G2 LED19S/840 PSU MDU L600	-20 to +35 °C	For mounting on easily flammable surfaces	1	1.6
910505100038	WT120C G2 LED19S/840 PSD L600	-20 to +35 °C	For mounting on easily flammable surfaces	1	1.6
911401815487	WT120C G2 LED20S/840 PSU L600	-20 to +40 °C	For mounting on easily flammable surfaces	-	0.4
911401815587	WT120C G2 LED40S/840 PSU L600	-20 to +40 °C	For mounting on easily flammable surfaces	-	0.4
911401816087	WT120C G2 LED40S/840 PSD L600	-20 to +40 °C	For mounting on easily flammable surfaces	-	0.4
911401823480	WT120C G2 LED19S/840 PSU L600	-20 to +40 °C	For mounting on easily flammable surfaces	1	1.6

Order Code	Full Product Name	Ambient temperature range	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
911401825885	WT120C G2 LED19S/840 PSU L600 BN	-20 to +40 °C	For mounting on easily flammable surfaces	1	1.6
911401815085	WT120C G2 LED37_60S/840 PSU L1500	-20 to +40 °C	For mounting on normally flammable surfaces	1	0.4
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	-20 to +35 °C	For mounting on easily flammable surfaces	1	1.6
910505100059	WT120C G2 LED34S/840 PSU MDU L1500	-20 to +35 °C	For mounting on easily flammable surfaces	1	1.6
910505100061	WT120C G2 LED34S/840 PSD L1500	-20 to +35 °C	For mounting on easily flammable surfaces	1	1.6
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	0 to +25 °C	For mounting on easily flammable surfaces	1	1.6
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	0 to +25 °C	For mounting on easily flammable surfaces	1	1.6
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	-20 to +35 °C	For mounting on easily flammable surfaces	1	1.6
910505100067	WT120C G2 LED60S/840 PSU MDU L1500	-20 to +35 °C	For mounting on easily flammable surfaces	1	1.6
910505100068	WT120C G2 LED60S/840 PSU MDU TW3 L1500	-20 to +35 °C	For mounting on easily flammable surfaces	1	1.6
910505100069	WT120C G2 LED60S/840 PSU WEC L1500	-20 to +35 °C	For mounting on easily flammable surfaces	1	1.6
910505100070	WT120C G2 LED60S/840	-20 to +35 °C	For mounting on easily	1	1.6

CoreLine Waterproof

Order Code	Full Product Name	Ambient temperature range	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
	PSU TW1		flammable		
	WEC L1500		surfaces		
910505100072	WT120C G2	-20 to +35 °C	For mounting	1	1.6
	LED60S/840		on easily		
	PSD L1500		flammable		
			surfaces		
910505100073	WT120C G2	0 to +25 °C	For mounting	1	1.6
	LED60S/840		on easily		
	PSU ELB3		flammable		
	L1500		surfaces		
910505100076	WT120C G2	0 to +25 °C	For mounting	1	1.6
	LED60S/840		on easily		
	PSD ELB3		flammable		
	L1500		surfaces		
910505100077	WT120C G2	-20 to +35 °C	For mounting	1	1.6
	LED80S/840		on easily		
	PSU TW3		flammable		
	L1500		surfaces		
910505100078	WT120C G2	-20 to +35 °C	For mounting	1	1.6
	LED80S/840		on easily		
	PSU MDU		flammable		
	L1500		surfaces		
910505100079	WT120C G2	-20 to +35 °C	For mounting	1	1.6
	LED80S/840		on easily		
	PSD L1500		flammable		
			surfaces		
910505100080	WT120C G2	0 to +25 °C	For mounting	1	1.6
	LED80S/840		on easily		
	PSU L1500		flammable		
	ELB3		surfaces		
910505101271	WT120C G2	-20 to +35 °C	For mounting	1	1.6
	LED65S/840		on easily		
	WIA L1500		flammable		
			surfaces		
910505101272	WT120C G2	0 to +25 °C	For mounting	1	1.6
	LED65S/840		on easily		
	WIA ELB3		flammable		
	L1500		surfaces		
910505101274	WT120C G2	-20 to +35 °C	For mounting	1	1.6
	LED65S/840		on easily		
	WIA TW3		flammable		
	L1500		surfaces		
910505103013	WT120C G2	-20 to +35 °C	For mounting	1	1.6
	LED80S/840		on easily		
	WIA L1500		flammable		
			surfaces		

Order Code	Full Product Name	Ambient temperature range	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910505103015	WT120C G2	-20 to +35 °C	For mounting	1	1.6
	LED80S/840		on easily		
	WIA TW3		flammable		
	L1500		surfaces		
911401535491	WT120C G2	-20 to +40 °C	For mounting	1	1.6
	LED34S/840		on easily		
	PSU TW3		flammable		
	L1500		surfaces		
911401535591	WT120C G2	-20 to +40 °C	For mounting	1	1.6
	LED60S/840		on easily		
	PSU TW3		flammable		
	L1500		surfaces		
911401535691	WT120C G2	-20 to +40 °C	For mounting	1	1.6
	LED80S/840		on easily		
	PSU TW3		flammable		
	L1500		surfaces		
911401535691	WT120C G2	-20 to +40 °C	For mounting	1	1.6
	LED80S/840		on easily		
	PSU TW3		flammable		
	L1500		surfaces		
911401815887	WT120C G2	-20 to +40 °C	For mounting	-	0.4
	LED100S/84		on easily		
	0 PSU L1500		flammable		
			surfaces		
911401815987	WT120C G2	-20 to +40 °C	For mounting	-	0.4
	LED120S/84		on easily		
	0 PSU L1500		flammable		
			surfaces		
911401816387	WT120C G2	-20 to +40 °C	For mounting	-	0.4
	LED100S/84		on easily		
	0 PSD L1500		flammable		
			surfaces		
911401816487	WT120C G2	-20 to +40 °C	For mounting	-	0.4
	LED120S/84		on easily		
	0 PSD L1500		flammable		
			surfaces		
911401823680	WT120C G2	-20 to +40 °C	For mounting	1	1.6
	LED34S/840		on easily		
	PSU L1500		flammable		
			surfaces		
911401823880	WT120C G2	-20 to +40 °C	For mounting	1	1.6
	LED60S/840		on easily		
	PSU L1500		flammable		
			surfaces		
911401823980	WT120C G2	-20 to +40 °C	For mounting	1	1.6
	LED80S/840		on easily		
	PSU L1500		flammable		
			surfaces		

CoreLine Waterproof

Order Code	Full Product Name	Ambient temperature range	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3 (SVM)	
				Stroboscopic effect visibility measure	
911401824481	WT120C G2 LED34S/865 PSU L1500	-20 to +40 °C	For mounting on easily flammable surfaces	1	1.6
911401824581	WT120C G2 LED60S/865 PSU L1500	-20 to +40 °C	For mounting on easily flammable surfaces	1	1.6
911401824781	WT120C G2 LED55S/830 PSU L1500	-20 to +40 °C	For mounting on easily flammable surfaces	1	1.6

Order Code	Full Product Name	Ambient temperature range	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3 (SVM)	
				Stroboscopic effect visibility measure	
911401825985	WT120C G2 LED34S/840 PSU L1500 BN	-20 to +40 °C	For mounting on easily flammable surfaces	1	1.6
911401826085	WT120C G2 LED80S/840 PSU L1500 BN	-20 to +40 °C	For mounting on easily flammable surfaces	1	0.4
911401826985	WT120C G2 LED60S/840 PSU L1500 BN	-20 to +40 °C	For mounting on easily flammable surfaces	1	0.4

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	(0.38,0.38)SDCM<=3
910505100040	WT120C G2 LED27S/840 PSU MDU L1200	(0.38,0.38)SDCM<=3
910505100042	WT120C G2 LED27S/840 PSU ELB3 L1200	(0.38,0.38)SDCM<=3
910505100044	WT120C G2 LED27S/840 PSD L1200	(0.38,0.38)SDCM<=3
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	(0.38,0.38)SDCM<=3
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	(0.38,0.38)SDCM<=3
910505100048	WT120C G2 LED40S/840 PSU MDU L1200	(0.38,0.38)SDCM<=3
910505100049	WT120C G2 LED40S/840 PSU MDU TW3 L1200	(0.38,0.38)SDCM<=3
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	(0.38,0.38)SDCM<=3
910505100053	WT120C G2 LED40S/840 PSD L1200	(0.38,0.38)SDCM<=3
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	(0.38,0.38)SDCM<=3
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	(0.38,0.38)SDCM<=3
910505101269	WT120C G2 LED40S/840 WIA L1200	(0.38,0.38)SDCM<=3
910505101270	WT120C G2 LED40S/840 WIA ELB3 L1200	(0.38,0.38)SDCM<=3
911401535291	WT120C G2 LED27S/840 PSU TW3 L1200	(0.38,0.38)SDCM<=3
911401535391	WT120C G2 LED40S/840 PSU TW3 L1200	(0.38,0.38)SDCM<=3
911401815687	WT120C G2 LED60S/840 PSU L1200	(0.38,0.38)SDCM≤3
911401815787	WT120C G2 LED80S/840 PSU L1200	(0.38,0.38)SDCM≤3
911401816187	WT120C G2 LED60S/840 PSD L1200	(0.38,0.38)SDCM≤3
911401816287	WT120C G2 LED80S/840 PSD L1200	(0.38,0.38)SDCM≤3
911401823580	WT120C G2 LED27S/840 PSU L1200	(0.38,0.38)SDCM<=3
911401823780	WT120C G2 LED40S/840 PSU L1200	(0.38,0.38)SDCM<=3
911401824381	WT120C G2 LED40S/865 PSU L1200	(0.31,0.32)SDCM<=3
911401824681	WT120C G2 LED37S/830 PSU L1200	(0.43,0.40)SDCM<=3
911401826785	WT120C G2 LED27S/840 PSU L1200 BN	(0.38,0.38)SDCM<=3
911401826885	WT120C G2 LED40S/840 PSU L1200 BN	(0.38,0.38)SDCM<=3
911401836980	WT120C G2 LED18S/840 PSU PCO L600	(0.38,0.38)SDCM<=3
911401837080	WT120C G2 LED25S/840 PSU PCO L1200	(0.38,0.38)SDCM<=3
911401837180	WT120C G2 LED31S/840 PSU PCO L1500	(0.38,0.38)SDCM<=3
911401837280	WT120C G2 LED37S/840 PSU PCO L1200	(0.38,0.38)SDCM<=3

Order Code	Full Product Name	Initial chromaticity
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	(0.38,0.38)SDCM<=3
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	(0.38,0.38)SDCM<=3
911401814985	WT120C G2 LED27_45S/840 PSU L1200	(0.38,0.38)SDCM<=3
910505100036	WT120C G2 LED19S/840 PSU MDU L600	(0.38,0.38)SDCM<=3
910505100038	WT120C G2 LED19S/840 PSD L600	(0.38,0.38)SDCM<=3
911401815487	WT120C G2 LED20S/840 PSU L600	(0.38,0.38)SDCM≤3
911401815587	WT120C G2 LED40S/840 PSU L600	(0.38,0.38)SDCM≤3
911401816087	WT120C G2 LED40S/840 PSD L600	(0.38,0.38)SDCM≤3
911401823480	WT120C G2 LED19S/840 PSU L600	(0.38,0.38)SDCM<=3
911401825885	WT120C G2 LED19S/840 PSU L600 BN	(0.38,0.38)SDCM<=3
911401815085	WT120C G2 LED37_60S/840 PSU L1500	(0.38,0.38)SDCM<=3
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	(0.38,0.38)SDCM<=3
910505100059	WT120C G2 LED34S/840 PSU MDU L1500	(0.38,0.38)SDCM<=3
910505100061	WT120C G2 LED34S/840 PSD L1500	(0.38,0.38)SDCM<=3
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	(0.38,0.38)SDCM<=3
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	(0.38,0.38)SDCM<=3
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	(0.38,0.38)SDCM<=3
910505100067	WT120C G2 LED60S/840 PSU MDU L1500	(0.38,0.38)SDCM<=3
910505100068	WT120C G2 LED60S/840 PSU MDU TW3 L1500	(0.38,0.38)SDCM<=3
910505100069	WT120C G2 LED60S/840 PSU WEC L1500	(0.38,0.38)SDCM<=3
910505100070	WT120C G2 LED60S/840 PSU TW1 WEC L1500	(0.38,0.38)SDCM<=3
910505100072	WT120C G2 LED60S/840 PSD L1500	(0.38,0.38)SDCM<=3
910505100073	WT120C G2 LED60S/840 PSU ELB3 L1500	(0.38,0.38)SDCM<=3
910505100076	WT120C G2 LED60S/840 PSD ELB3 L1500	(0.38,0.38)SDCM<=3
910505100077	WT120C G2 LED80S/840 PSU TW3 L1500	(0.38,0.38)SDCM<=3
910505100078	WT120C G2 LED80S/840 PSU MDU L1500	(0.38,0.38)SDCM<=3
910505100079	WT120C G2 LED80S/840 PSD L1500	(0.38,0.38)SDCM<=3
910505100080	WT120C G2 LED80S/840 PSU L1500 ELB3	(0.38,0.38)SDCM<=3
910505101271	WT120C G2 LED65S/840 WIA L1500	(0.38,0.38)SDCM<=3
910505101272	WT120C G2 LED65S/840 WIA ELB3 L1500	(0.38,0.38)SDCM<=3

CoreLine Waterproof

Order Code	Full Product Name	Initial chromaticity
910505101274	WT120C G2 LED65S/840 WIA TW3 L1500	(0.38,0.38)SDCM<=3
910505103013	WT120C G2 LED80S/840 WIA L1500	(0.38,0.38)SDCM<=3
910505103015	WT120C G2 LED80S/840 WIA TW3 L1500	(0.38,0.38)SDCM<=3
911401535491	WT120C G2 LED34S/840 PSU TW3 L1500	(0.38,0.38)SDCM<=3
911401535591	WT120C G2 LED60S/840 PSU TW3 L1500	(0.38,0.38)SDCM<=3
911401535691	WT120C G2 LED80S/840 PSU TW3 L1500	(0.38,0.38)SDCM<=3
911401815887	WT120C G2 LED100S/840 PSU L1500	(0.38,0.38)SDCM<=3
911401815987	WT120C G2 LED120S/840 PSU L1500	(0.38,0.38)SDCM<=3
911401816387	WT120C G2 LED100S/840 PSD L1500	(0.38,0.38)SDCM<=3
911401816487	WT120C G2 LED120S/840 PSD L1500	(0.38,0.38)SDCM<=3

Order Code	Full Product Name	Initial chromaticity
911401823680	WT120C G2 LED34S/840 PSU L1500	(0.38,0.38)SDCM<=3
911401823880	WT120C G2 LED60S/840 PSU L1500	(0.38,0.38)SDCM<=3
911401823980	WT120C G2 LED80S/840 PSU L1500	(0.38,0.38)SDCM<=3
911401824481	WT120C G2 LED34S/865 PSU L1500	(0.31,0.32)SDCM<=3
911401824581	WT120C G2 LED60S/865 PSU L1500	(0.31,0.32)SDCM<=3
911401824781	WT120C G2 LED55S/830 PSU L1500	(0.43,0.40)SDCM<=3
911401825985	WT120C G2 LED34S/840 PSU L1500 BN	(0.38,0.38)SDCM<=3
911401826085	WT120C G2 LED80S/840 PSU L1500 BN	(0.38,0.38)SDCM<=3
911401826985	WT120C G2 LED60S/840 PSU L1500 BN	(0.38,0.38)SDCM<=3

Product Data

Order Code	Full Product Name	Product family code
910505100039	WT120C G2 LED27S/840 PSU TW3 L1200	WT130C
910505100040	WT120C G2 LED27S/840 PSU MDU L1200	WT130C
910505100042	WT120C G2 LED27S/840 PSU ELB3 L1200	WT130C
910505100044	WT120C G2 LED27S/840 PSD L1200	WT130C
910505100045	WT120C G2 LED27S/840 PSD ELB3 L1200	WT130C
910505100047	WT120C G2 LED40S/840 PSU TW3 L1200	WT130C
910505100048	WT120C G2 LED40S/840 PSU MDU L1200	WT130C
910505100049	WT120C G2 LED40S/840 PSU MDU TW3 L1200	WT130C
910505100051	WT120C G2 LED40S/840 PSU TW1 WEC L1200	WT130C
910505100053	WT120C G2 LED40S/840 PSD L1200	WT130C
910505100054	WT120C G2 LED40S/840 PSU ELB3 L1200	WT130C
910505100057	WT120C G2 LED40S/840 PSD ELB3 L1200	WT130C
910505101269	WT120C G2 LED40S/840 WIA L1200	WT130C
910505101270	WT120C G2 LED40S/840 WIA ELB3 L1200	WT130C
911401535291	WT120C G2 LED27S/840 PSU TW3 L1200	-
911401535391	WT120C G2 LED40S/840 PSU TW3 L1200	WT130C
911401815687	WT120C G2 LED60S/840 PSU L1200	-
911401815787	WT120C G2 LED80S/840 PSU L1200	-
911401816187	WT120C G2 LED60S/840 PSD L1200	-
911401816287	WT120C G2 LED80S/840 PSD L1200	-
911401823580	WT120C G2 LED27S/840 PSU L1200	-
911401823780	WT120C G2 LED40S/840 PSU L1200	WT130C
911401824381	WT120C G2 LED40S/865 PSU L1200	-
911401824681	WT120C G2 LED37S/830 PSU L1200	-
911401826785	WT120C G2 LED27S/840 PSU L1200 BN	-
911401826885	WT120C G2 LED40S/840 PSU L1200 BN	-
911401836980	WT120C G2 LED18S/840 PSU PCO L600	-
911401837080	WT120C G2 LED25S/840 PSU PCO L1200	-
911401837180	WT120C G2 LED31S/840 PSU PCO L1500	-
911401837280	WT120C G2 LED37S/840 PSU PCO L1200	-
911401837380	WT120C G2 LED57S/840 PSU PCO L1500	-
911401837480	WT120C G2 LED75S/840 PSU PCO L1500	-
911401814985	WT120C G2 LED27_45S/840 PSU L1200	-
910505100036	WT120C G2 LED19S/840 PSU MDU L600	WT130C
910505100038	WT120C G2 LED19S/840 PSD L600	WT130C
911401815487	WT120C G2 LED20S/840 PSU L600	-
911401815587	WT120C G2 LED40S/840 PSU L600	-
911401816087	WT120C G2 LED40S/840 PSD L600	-




Order Code	Full Product Name	Product family code
911401823480	WT120C G2 LED19S/840 PSU L600	-
911401825885	WT120C G2 LED19S/840 PSU L600 BN	-
911401815085	WT120C G2 LED37_60S/840 PSU L1500	-
910505100058	WT120C G2 LED34S/840 PSU TW3 L1500	WT130C
910505100059	WT120C G2 LED34S/840 PSU MDU L1500	WT130C
910505100061	WT120C G2 LED34S/840 PSD L1500	WT130C
910505100062	WT120C G2 LED34S/840 PSU ELB3 L1500	WT130C
910505100064	WT120C G2 LED34S/840 PSD ELB3 L1500	WT130C
910505100066	WT120C G2 LED60S/840 PSU TW3 L1500	WT130C
910505100067	WT120C G2 LED60S/840 PSU MDU L1500	WT130C
910505100068	WT120C G2 LED60S/840 PSU MDU TW3 L1500	WT130C
910505100069	WT120C G2 LED60S/840 PSU WEC L1500	WT130C
910505100070	WT120C G2 LED60S/840 PSU TW1 WEC L1500	WT130C
910505100072	WT120C G2 LED60S/840 PSD L1500	WT130C
910505100073	WT120C G2 LED60S/840 PSU ELB3 L1500	WT130C
910505100076	WT120C G2 LED60S/840 PSD ELB3 L1500	WT130C
910505100077	WT120C G2 LED80S/840 PSU TW3 L1500	WT130C
910505100078	WT120C G2 LED80S/840 PSU MDU L1500	WT130C
910505100079	WT120C G2 LED80S/840 PSD L1500	WT130C
910505100080	WT120C G2 LED80S/840 PSU L1500 ELB3	WT130C
910505101271	WT120C G2 LED65S/840 WIA L1500	WT130C
910505101272	WT120C G2 LED65S/840 WIA ELB3 L1500	WT130C
910505101274	WT120C G2 LED65S/840 WIA TW3 L1500	WT130C
910505103013	WT120C G2 LED80S/840 WIA L1500	WT130C
910505103015	WT120C G2 LED80S/840 WIA TW3 L1500	WT130C
911401535491	WT120C G2 LED34S/840 PSU TW3 L1500	WT130C
911401535591	WT120C G2 LED60S/840 PSU TW3 L1500	-
911401535691	WT120C G2 LED80S/840 PSU TW3 L1500	-
911401815887	WT120C G2 LED100S/840 PSU L1500	-
911401815987	WT120C G2 LED120S/840 PSU L1500	-
911401816387	WT120C G2 LED100S/840 PSD L1500	-
911401816487	WT120C G2 LED120S/840 PSD L1500	-
911401823680	WT120C G2 LED34S/840 PSU L1500	WT130C
911401823880	WT120C G2 LED60S/840 PSU L1500	-
911401823980	WT120C G2 LED80S/840 PSU L1500	-
911401824481	WT120C G2 LED34S/865 PSU L1500	-
911401824581	WT120C G2 LED60S/865 PSU L1500	-
911401824781	WT120C G2 LED55S/830 PSU L1500	-

CoreLine Waterproof

Order Code	Full Product Name	Product family code
911401825985	WT120C G2 LED34S/840 PSU L1500 BN	-
911401826085	WT120C G2 LED80S/840 PSU L1500 BN	-

Order Code	Full Product Name	Product family code
911401826985	WT120C G2 LED60S/840 PSU L1500 BN	-




Polar Wide Diagrams



Polar Normal (separate) - WT120CI - 910505101272

Polar Normal (separate) - WT120CI - 910505100069




Polar Normal (separate) - WT120CI - 910505100036



Polar Normal (separate) - WT120CI - 910505100048

Polar Normal (separate) - WT120CI - 910505100073

Polar Normal (separate) - WT120CI - 910505100067




Polar Normal (separate) - WT120CI - 910505100042


Polar Normal (separate) - WT120CI - 910505100054

Polar Normal (separate) - WT120CI - 910505100057


Polar Wide Diagrams




Polar Normal (separate) - WT120CI - 910505100072




Polar Normal (separate) - WT120CI - 910505100079




Polar Normal (separate) - WT120CI - 910505100077




Polar Normal (separate) - WT120CI - 910505100049




Polar Normal (separate) - WT120CI - 910505100040




Polar Normal (separate) - WT120CI - 910505100045



Polar Normal (separate) - WT120CI - 910505100064




Polar Normal (separate) - WT120CI - 910505100051




Polar Normal (separate) - WT120CI - 910505100039


Polar Wide Diagrams




Polar Normal (separate) - WT120CI - 910505100061




Polar Normal (separate) - WT120CI - 910505100078




Polar Normal (separate) - WT120CI - 910505100047




Polar Normal (separate) - WT120CI - 910505100068




Polar Normal (separate) - WT120CI - 910505100080




Polar Normal (separate) - WT120CI - 910505100044



Polar Normal (separate) - WT120CI - 910505100059




Polar Normal (separate) - WT120CI - 910505100062




Polar Normal (separate) - WT120CI - 910505100076


Polar Wide Diagrams




Polar Normal (separate) - WT120CI - 910505100070




Polar Normal (separate) - WT120CI - 910505100053




Polar Normal (separate) - WT120CI - 910505101269




Polar Normal (separate) - WT120CI - 910505101271




Polar Normal (separate) - WT120CI - 910505101274




Polar Normal (separate) - WT120CI - 910505101270



Polar Normal (separate) - WT120CI - 910505100058




Polar Normal (separate) - WT120CI - 910505100038




Polar Normal (separate) - WT120CI - 910505103015


Polar Wide Diagrams




Polar Normal (separate) - WT120CI - 911401535391




Polar Normal (separate) - WT120CI - 911401535491




Polar Normal (separate) - WT120CI - 911401823680




Polar Normal (separate) - WT120CI - 911401823780




Polar Normal (separate) - WT120CI - 910505100066




Polar Normal (separate) - WT120CI - 910505103013




Polar Normal (separate) - 911401823880




Polar Normal (separate) - 911401535291




Polar Normal (separate) - 911401535591



Polar Normal (separate) - 911401535691




Polar Normal (separate) - 911401824381




Polar Normal (separate) - 911401824481

CoreLine Waterproof


Polar Wide Diagrams




Polar Normal (separate) - 911401816187




Polar Normal (separate) - 911401815887




Polar Normal (separate) - 911401816387




Polar Normal (separate) - 911401815487



Polar Normal (separate) - 911401815787



Polar Normal (separate) - 911401816487



Polar Normal (separate) - 911401815687

