CoreLine Waterproof – the clear choice for LED

CoreLine Waterproof

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Waterproof range of LED products can be used to replace traditional waterproof luminaires with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Benefits

- Up to 50% energy savings compared with TL-D
- Reliable LED technology – maintenance-free
- Direct replacement for conventional waterproof luminaires in terms of light performance, installation flexibility and length

Features

- Reliable integrated LED technology, ensuring maintenance-free installation and a long lifetime
- Can be used to replace traditional waterproof luminaires ranging from 18 to 58 W TL-D
- Wide-beam light distribution
- Diffuser with optical element ensures visual comfort
- Ceiling-mounted bracket and suspension hooks included; installation can be made vandal-proof by additional screw fixation of mounting brackets

Application

- Parking garages
- Warehouses
- General lighting

Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

Versions

CoreLine Waterproof WT120C G2 PCU -

Dimensional drawing







Product details

CoreLine Waterproof WT120C G2
PCU-7DPP

CoreLine Waterproof WT120C G2
PCU-3DPP

CoreLine Waterproof WT120C G2
PCU-10DPP

CoreLine Waterproof WT120C G2
PCU-9DPP

CoreLine Waterproof WT120C G2
PCU-12DPP

CoreLine waterproof G2 (WT120C G2),MDU, Motion Detection Unit



CoreLine Waterproof WT120C G2
PCU-2DPP



CoreLine Waterproof WT120C G2
PCU-13DPP

CoreLine Waterproof

Product details

CoreLine Waterproof WT120C G2 PCU-8DPP



CoreLine waterproof G2 (WT120C G2),MDU, Motion Detection Unit

CoreLine Waterproof WT120C G2 PCU-11DPP

CoreLine waterproof G2 (WT120C G2),Emergency lighting, TrustSight

General Information	
Driver included	Yes
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Color rendering index (CRI)	>80
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Mechanical and Housing	
Mech. impact protection code	IK08
Ingress protection code	IP65
Approval and Application	
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on easily flammable surfaces
Glow-wire test	Temperature 850 °C, duration 30 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Lamp family code	Light source replaceable
88309900	WT120C G2 LED40S/840 PSD L1200	LED40S	No
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	LED40S	No
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	LED40S	No
75428799	WT120C G2 LED60S/840 PSU L1200	-	-
84046600	WT120C G2 LED27S/840 PSU L1200	-	No
36933499	WT120C G2 LED40S/865 PSU L1200	-	No
34976399	WT120C G2 LED18S/840 PSU PCO L600	-	No
34977099	WT120C G2 LED25S/840 PSU PCO L1200	-	No
34978799	WT120C G2 LED31S/840 PSU PCO L1500	-	No
34979499	WT120C G2 LED37S/840 PSU PCO L1200	-	No
34980099	WT120C G2 LED57S/840 PSU PCO L1500	-	No
34981799	WT120C G2 LED75S/840 PSU PCO L1500	-	No
84045900	WT120C G2 LED19S/840 PSU L600	-	No
96267800	WT120C G2 LED34S/840 PSU MDU L1500	LED34S	No
88308200	WT120C G2 LED34S/840 PSD L1500	LED34S	No
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	LED34S	No
88310500	WT120C G2 LED60S/840 PSD L1500	LED60S	No
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	LED80S	No
75431799	WT120C G2 LED120S/840 PSU L1500	-	-
84049700	WT120C G2 LED60S/840 PSU L1500	-	No
40928900	WT120C G2 LED80S/840 PSU L1500	-	No
36934199	WT120C G2 LED34S/865 PSU L1500	-	No
36935899	WT120C G2 LED60S/865 PSU L1500	-	No

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
88309900	WT120C G2 LED40S/840 PSD L1200	4000 K	131 lm/W	4,000 lm	Wide beam
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	4000 K	121 lm/W	4,000 lm	Wide beam
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	4000 K	113 lm/W	4,000 lm	Wide beam
75428799	WT120C G2 LED60S/840 PSU L1200	4000 K	160 lm/W	6,000 lm	Symmetrical
84046600	WT120C G2 LED27S/840 PSU L1200	4000 K	131 lm/W	2,700 lm	Wide beam
36933499	WT120C G2 LED40S/865 PSU L1200	6500 K	140 lm/W	4,000 lm	Wide beam
34976399	WT120C G2 LED18S/840 PSU PCO L600	4000 K	120 lm/W	1,800 lm	Very wide beam
34977099	WT120C G2 LED25S/840 PSU PCO L1200	4000 K	122 lm/W	2,500 lm	Very wide beam
34978799	WT120C G2 LED31S/840 PSU PCO L1500	4000 K	128 lm/W	3,100 lm	Very wide beam
34979499	WT120C G2 LED37S/840 PSU PCO L1200	4000 K	129 lm/W	3,700 lm	Very wide beam
34980099	WT120C G2 LED57S/840 PSU PCO L1500	4000 K	133 lm/W	5,700 lm	Very wide beam
34981799	WT120C G2 LED75S/840 PSU PCO L1500	4000 K	131 lm/W	7,500 lm	Very wide beam
84045900	WT120C G2 LED19S/840 PSU L600	4000 K	126 lm/W	1,900 lm	Wide beam
96267800	WT120C G2 LED34S/840 PSU MDU L1500	4000 K	132 lm/W	3,400 lm	Wide beam
88308200	WT120C G2 LED34S/840 PSD L1500	4000 K	131 lm/W	3,400 lm	Wide beam
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	4000 K	110 lm/W	3,400 lm	Wide beam
88310500	WT120C G2 LED60S/840 PSD L1500	4000 K	133 lm/W	6,000 lm	Wide beam
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	4000 K	126 lm/W	8,000 lm	Wide beam
75431799	WT120C G2 LED120S/840 PSU L1500	4000 K	160 lm/W	12,000 lm	Symmetrical
84049700	WT120C G2 LED60S/840 PSU L1500	4000 K	140 lm/W	6,000 lm	Wide beam
40928900	WT120C G2 LED80S/840 PSU L1500	4000 K	140 lm/W	8,000 lm	Wide beam
36934199	WT120C G2 LED34S/865 PSU L1500	6500 K	139 lm/W	3,400 lm	Wide beam
36935899	WT120C G2 LED60S/865 PSU L1500	6500 K	139 lm/W	6,000 lm	Wide beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Suitable for random switching
88309900	WT120C G2 LED40S/840 PSD L1200	30.5 W	Not applicable
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	33 W	Not applicable
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	35.5 W	Not applicable
75428799	WT120C G2 LED60S/840 PSU L1200	37.5 W	No
84046600	WT120C G2 LED27S/840 PSU L1200	20.5 W	Not applicable
36933499	WT120C G2 LED40S/865 PSU L1200	28.5 W	Not applicable
34976399	WT120C G2 LED18S/840 PSU PCO L600	15 W	Not applicable
34977099	WT120C G2 LED25S/840 PSU PCO L1200	20.5 W	Not applicable
34978799	WT120C G2 LED31S/840 PSU PCO L1500	24.3 W	Not applicable
34979499	WT120C G2 LED37S/840 PSU PCO L1200	28.6 W	Not applicable
34980099	WT120C G2 LED57S/840 PSU PCO L1500	42.9 W	Not applicable
34981799	WT120C G2 LED75S/840 PSU PCO L1500	57.1 W	Not applicable

Order Code	Full Product Name	Power Consumption	Suitable for random switching
84045900	WT120C G2 LED19S/840 PSU L600	15 W	Not applicable
96267800	WT120C G2 LED34S/840 PSU MDU L1500	26 W	Yes
88308200	WT120C G2 LED34S/840 PSD L1500	26 W	Not applicable
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	31 W	Not applicable
88310500	WT120C G2 LED60S/840 PSD L1500	45 W	Not applicable
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	63.5 W	Not applicable
75431799	WT120C G2 LED120S/840 PSU L1500	75 W	No
84049700	WT120C G2 LED60S/840 PSU L1500	42.9 W	Not applicable
40928900	WT120C G2 LED80S/840 PSU L1500	57.1 W	Not applicable
36934199	WT120C G2 LED34S/865 PSU L1500	24.5 W	Not applicable
36935899	WT120C G2 LED60S/865 PSU L1500	43 W	Not applicable

Controls and Dimming

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
88309900	WT120C G2 LED40S/840 PSD L1200	Yes	-	1%
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	No	-	Not applicable
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	Yes	-	1%
75428799	WT120C G2 LED60S/840 PSU L1200	No	-	-
84046600	WT120C G2 LED27S/840 PSU L1200	No	-	Not applicable
36933499	WT120C G2 LED40S/865 PSU L1200	No	-	Not applicable
34976399	WT120C G2 LED18S/840 PSU PCO L600	No	-	Not applicable
34977099	WT120C G2 LED25S/840 PSU PCO L1200	No	-	Not applicable
34978799	WT120C G2 LED31S/840 PSU PCO L1500	No	-	Not applicable
34979499	WT120C G2 LED37S/840 PSU PCO L1200	No	-	Not applicable

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
34980099	WT120C G2 LED57S/840 PSU PCO L1500	No	-	Not applicable
34981799	WT120C G2 LED75S/840 PSU PCO L1500	No	-	Not applicable
84045900	WT120C G2 LED19S/840 PSU L600	No	-	Not applicable
96267800	WT120C G2 LED34S/840 PSU MDU L1500	No	Movement and light sensor (On/Off)	Not applicable
88308200	WT120C G2 LED34S/840 PSD L1500	Yes	-	1%
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	Yes	-	1%
88310500	WT120C G2 LED60S/840 PSD L1500	Yes	-	1%
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	No	-	Not applicable
75431799	WT120C G2 LED120S/840 PSU L1500	No	-	-

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
84049700	WT120C G2 LED60S/840 PSU L1500	No	-	Not applicable
40928900	WT120C G2 LED80S/840 PSU L1500	No	-	Not applicable

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
36934199	WT120C G2 LED34S/865 PSU L1500	No	-	Not applicable
36935899	WT120C G2 LED60S/865 PSU L1500	No	-	Not applicable

Mechanical and Housing

Order Code	Full Product Name	Housing Color
88309900	WT120C G2 LED40S/840 PSD L1200	Gray
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	Gray
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	Gray
75428799	WT120C G2 LED60S/840 PSU L1200	Grey
84046600	WT120C G2 LED27S/840 PSU L1200	Gray
36933499	WT120C G2 LED40S/865 PSU L1200	Gray
34976399	WT120C G2 LED18S/840 PSU PCO L600	Gray
34977099	WT120C G2 LED25S/840 PSU PCO L1200	Gray
34978799	WT120C G2 LED31S/840 PSU PCO L1500	Gray
34979499	WT120C G2 LED37S/840 PSU PCO L1200	Gray
34980099	WT120C G2 LED57S/840 PSU PCO L1500	Gray
34981799	WT120C G2 LED75S/840 PSU PCO L1500	Gray

Order Code	Full Product Name	Housing Color
84045900	WT120C G2 LED19S/840 PSU L600	Gray
96267800	WT120C G2 LED34S/840 PSU MDU L1500	Gray
88308200	WT120C G2 LED34S/840 PSD L1500	Gray
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	Gray
88310500	WT120C G2 LED60S/840 PSD L1500	Gray
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	Gray
75431799	WT120C G2 LED120S/840 PSU L1500	Grey
84049700	WT120C G2 LED60S/840 PSU L1500	Gray
40928900	WT120C G2 LED80S/840 PSU L1500	Gray
36934199	WT120C G2 LED34S/865 PSU L1500	Gray
36935899	WT120C G2 LED60S/865 PSU L1500	Gray

Emergency Operation (1/2)

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
88309900	WT120C G2 LED40S/840 PSD L1200	-	-	-	-
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	No	Emergency lighting 3 hours duration basic version	500 lm	Lithium
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	No	Emergency lighting 3 hours duration basic version	500 lm	Lithium
75428799	WT120C G2 LED60S/840 PSU L1200	No	-	-	-
84046600	WT120C G2 LED27S/840 PSU L1200	-	-	-	-
36933499	WT120C G2 LED40S/865 PSU L1200	-	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
34976399	WT120C G2 LED18S/840 PSU PCO L600	-	-	-	-
34977099	WT120C G2 LED25S/840 PSU PCO L1200	-	-	-	-
34978799	WT120C G2 LED31S/840 PSU PCO L1500	-	-	-	-
34979499	WT120C G2 LED37S/840 PSU PCO L1200	-	-	-	-
34980099	WT120C G2 LED57S/840 PSU PCO L1500	-	-	-	-
34981799	WT120C G2 LED75S/840 PSU PCO L1500	-	-	-	-
84045900	WT120C G2 LED19S/840 PSU L600	-	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
96267800	WT120C G2 LED34S/840 PSU MDU L1500	-	-	-	-
88308200	WT120C G2 LED34S/840 PSD L1500	-	-	-	-
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	No	Emergency lighting 3 hours duration basic version	500 lm	Lithium
88310500	WT120C G2 LED60S/840 PSD L1500	-	-	-	-
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	No	Emergency lighting 3 hours	500 lm	Lithium
75431799	WT120C G2 LED120S/840 PSU L1500	No	-	-	-
84049700	WT120C G2 LED60S/840 PSU L1500	-	-	-	-
40928900	WT120C G2 LED80S/840 PSU L1500	-	-	-	-
36934199	WT120C G2 LED34S/865 PSU L1500	-	-	-	-
36935899	WT120C G2 LED60S/865 PSU L1500	-	-	-	-

Emergency Operation (2/2)

Order Code	Full Product Name	Rated duration of the emergency lighting (when fully charged)
88309900	WT120C G2 LED40S/840 PSD L1200	-
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	3 hour(s)
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	3 hour(s)
75428799	WT120C G2 LED60S/840 PSU L1200	-
84046600	WT120C G2 LED27S/840 PSU L1200	-
36933499	WT120C G2 LED40S/865 PSU L1200	-
34976399	WT120C G2 LED18S/840 PSU PCO L600	-
34977099	WT120C G2 LED25S/840 PSU PCO L1200	-
34978799	WT120C G2 LED31S/840 PSU PCO L1500	-
34979499	WT120C G2 LED37S/840 PSU PCO L1200	-
34980099	WT120C G2 LED57S/840 PSU PCO L1500	-
34981799	WT120C G2 LED75S/840 PSU PCO L1500	-
84045900	WT120C G2 LED19S/840 PSU L600	-
96267800	WT120C G2 LED34S/840 PSU MDU L1500	-
88308200	WT120C G2 LED34S/840 PSD L1500	-
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	3 hour(s)
88310500	WT120C G2 LED60S/840 PSD L1500	-
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	3 hour(s)
75431799	WT120C G2 LED120S/840 PSU L1500	-
84049700	WT120C G2 LED60S/840 PSU L1500	-
40928900	WT120C G2 LED80S/840 PSU L1500	-
36934199	WT120C G2 LED34S/865 PSU L1500	-
36935899	WT120C G2 LED60S/865 PSU L1500	-

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
88309900	WT120C G2 LED40S/840 PSD L1200	-20 to +35 °C	1	1.6
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	0 to +25 °C	1	1.6

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	0 to +25 °C	1	1.6
75428799	WT120C G2 LED60S/840 PSU L1200	-20 to +40 °C	-	0.4
84046600	WT120C G2 LED27S/840 PSU L1200	-20 to +40 °C	1	1.6
36933499	WT120C G2 LED40S/865 PSU L1200	-20 to +40 °C	1	1.6
34976399	WT120C G2 LED18S/840 PSU PCO L600	-20 to +40 °C	1	1.6
34977099	WT120C G2 LED25S/840 PSU PCO L1200	-20 to +40 °C	1	1.6
34978799	WT120C G2 LED31S/840 PSU PCO L1500	-20 to +40 °C	1	1.6
34979499	WT120C G2 LED37S/840 PSU PCO L1200	-20 to +40 °C	1	1.6
34980099	WT120C G2 LED57S/840 PSU PCO L1500	-20 to +40 °C	1	1.6
34981799	WT120C G2 LED75S/840 PSU PCO L1500	-20 to +40 °C	1	1.6
84045900	WT120C G2 LED19S/840 PSU L600	-20 to +40 °C	1	1.6

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
96267800	WT120C G2 LED34S/840 PSU MDU L1500	-20 to +35 °C	1	1.6
88308200	WT120C G2 LED34S/840 PSD L1500	-20 to +35 °C	1	1.6
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	0 to +25 °C	1	1.6
88310500	WT120C G2 LED60S/840 PSD L1500	-20 to +35 °C	1	1.6
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	0 to +25 °C	1	1.6
75431799	WT120C G2 LED120S/840 PSU L1500	-20 to +40 °C	-	0.4
84049700	WT120C G2 LED60S/840 PSU L1500	-20 to +40 °C	1	1.6
40928900	WT120C G2 LED80S/840 PSU L1500	-20 to +40 °C	1	1.6
36934199	WT120C G2 LED34S/865 PSU L1500	-20 to +40 °C	1	1.6
36935899	WT120C G2 LED60S/865 PSU L1500	-20 to +40 °C	1	1.6

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
88309900	WT120C G2 LED40S/840 PSD L1200	(0.38,0.38)SDCM<=3
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	(0.38,0.38)SDCM<=3
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	(0.38,0.38)SDCM<=3
75428799	WT120C G2 LED60S/840 PSU L1200	(0.38,0.38) SDCM≤3
84046600	WT120C G2 LED27S/840 PSU L1200	(0.38,0.38)SDCM<=3
36933499	WT120C G2 LED40S/865 PSU L1200	(0.31,0.32)SDCM<=3
34976399	WT120C G2 LED18S/840 PSU PCO L600	(0.38,0.38)SDCM<=3
34977099	WT120C G2 LED25S/840 PSU PCO L1200	(0.38,0.38)SDCM<=3
34978799	WT120C G2 LED31S/840 PSU PCO L1500	(0.38,0.38)SDCM<=3

Order Code	Full Product Name	Initial chromaticity
34979499	WT120C G2 LED37S/840 PSU PCO L1200	(0.38,0.38)SDCM<=3
34980099	WT120C G2 LED57S/840 PSU PCO L1500	(0.38,0.38)SDCM<=3
34981799	WT120C G2 LED75S/840 PSU PCO L1500	(0.38,0.38)SDCM<=3
84045900	WT120C G2 LED19S/840 PSU L600	(0.38,0.38)SDCM<=3
96267800	WT120C G2 LED34S/840 PSU MDU L1500	(0.38,0.38)SDCM<=3
88308200	WT120C G2 LED34S/840 PSD L1500	(0.38,0.38)SDCM<=3
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	(0.38,0.38)SDCM<=3
88310500	WT120C G2 LED60S/840 PSD L1500	(0.38,0.38)SDCM<=3
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	(0.38,0.38)SDCM<=3

Order Code	Full Product Name	Initial chromaticity
75431799	WT120C G2 LED120S/840 PSU L1500	(0.38,0.38) SDCM≤3
84049700	WT120C G2 LED60S/840 PSU L1500	(0.38,0.38)SDCM<=3
40928900	WT120C G2 LED80S/840 PSU L1500	(0.38,0.38)SDCM<=3

Order Code	Full Product Name	Initial chromaticity
36934199	WT120C G2 LED34S/865 PSU L1500	(0.31,0.32)SDCM<=3
36935899	WT120C G2 LED60S/865 PSU L1500	(0.31,0.32)SDCM<=3

Product Data

Order Code	Full Product Name	Product family code
88309900	WT120C G2 LED40S/840 PSD L1200	WT130C
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	WT130C
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	WT130C
75428799	WT120C G2 LED60S/840 PSU L1200	-
84046600	WT120C G2 LED27S/840 PSU L1200	-
36933499	WT120C G2 LED40S/865 PSU L1200	-
34976399	WT120C G2 LED18S/840 PSU PCO L600	-
34977099	WT120C G2 LED25S/840 PSU PCO L1200	-
34978799	WT120C G2 LED31S/840 PSU PCO L1500	-
34979499	WT120C G2 LED37S/840 PSU PCO L1200	-
34980099	WT120C G2 LED57S/840 PSU PCO L1500	-
34981799	WT120C G2 LED75S/840 PSU PCO L1500	-

Order Code	Full Product Name	Product family code
84045900	WT120C G2 LED19S/840 PSU L600	-
96267800	WT120C G2 LED34S/840 PSU MDU L1500	WT130C
88308200	WT120C G2 LED34S/840 PSD L1500	WT130C
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	WT130C
88310500	WT120C G2 LED60S/840 PSD L1500	WT130C
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	WT130C
75431799	WT120C G2 LED120S/840 PSU L1500	-
84049700	WT120C G2 LED60S/840 PSU L1500	-
40928900	WT120C G2 LED80S/840 PSU L1500	-
36934199	WT120C G2 LED34S/865 PSU L1500	-
36935899	WT120C G2 LED60S/865 PSU L1500	-

Polar Wide Diagrams



Polar Normal (separate) - WT120CI - 910505100054



Polar Normal (separate) - WT120CI - 910505100057



Polar Normal (separate) - WT120CI - 910505100072



Polar Normal (separate) - WT120CI - 910505100064



Polar Normal (separate) - WT120CI - 910505100061



Polar Normal (separate) - WT120CI - 910505100080

Polar Wide Diagrams



Polar Normal (separate) - WT120CI - 910505100059



Polar Normal (separate) - WT120CI - 910505100053



Polar Normal (separate) - 911401823880



Polar Normal (separate) - 911401824381



Polar Normal (separate) - 911401824481



Polar Normal (separate) - 911401824581



Polar Normal (separate) - 911401823480



Polar Normal (separate) - 911401823580



Polar Normal (separate) - 911401823980



Polar Normal (separate) - 911401836980

CoreLine Waterproof

Polar Wide Diagrams



Polar Normal (separate) - 911401837080



Polar Normal (separate) - 911401837280



Polar Normal (separate) - 911401837180



Polar Normal (separate) - 911401837380



Polar Normal (separate) - 911401837480



Polar Normal (separate) - 911401815987



Polar Normal (separate) - 911401815687

© 2026 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.