



# GreenPerform Waterproof G3: A high-performance, energy-efficient waterproof batten

## GreenPerform Waterproof G3

GreenPerform Waterproof G3 is a superb choice for hard-working applications. Not only does it provide excellent optical performance, it also delivers substantial energy saving. And because it works seamlessly with IoT software like Interact, it also offers the option of customization, convenience, and data-driven insights.

### Benefits

- Excellent energy savings
- Reliable choice, long serviceability
- Suitable for extensive applications
- Interact software and platforms

### Features

- Up to 181lm/W (HE), and 160lm/W (general)
- 100,000 hours L70B50 @25°C
- IP66/IK08
- Up to -30°C ~ +60°C working temp. (HT version)
- Works with Interact IoT software and platform
- Superior optics (WB & Opal), SDCM 3

# GreenPerform Waterproof G3

## Application

- Parking Garages
- Manufacturing
- Warehouses

## Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP65 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

## Specifications

<b>Mounting type</b>	Surface
	Suspended
<b>Operating Temperature range</b>	-30 to +50°C (@PSU)
<b>Light Source</b>	LED
<b>Mains Voltage</b>	220-240V / 50-60Hz
<b>Dimming</b>	PSD: DALI
	WIA: Wireless control, compatible with Interact Pro
	PSU: non-dimmable
	DIA: Dimmable via Dali, compatible with Interact
<b>Control system input</b>	DALI/Interact
<b>Material</b>	PC
<b>Main color of the luminaire</b>	RAL7035
<b>Lumen maintenance at median useful life 50.000h</b>	L90
<b>Lumen maintenance at median useful life 100.000h</b>	L70
<b>Flicker / Pst / SVM</b>	<3.2% / 0.5 / 0.4
<b>Luminous flux</b>	Up to 10000lm
<b>Power consumption</b>	8.1W to 62.5W

<b>Luminaire efficacy</b>	Up to 181lm/W
<b>Correlated color temperature - CCT</b>	4000K
	6500K
<b>Color Rendering index - CRI</b>	81
<b>Risk Group</b>	RG0
<b>Optical cover/lens material</b>	PC
<b>Optical cover/lens finish</b>	Opal
	Clear
<b>Protection Class</b>	Class I
<b>IEC61140</b>	
<b>Mechanical impact protection</b>	IK08
<b>Ingress protection</b>	IP66
<b>Driver replaceable</b>	Yes
<b>Overall height</b>	76mm
<b>Overall length</b>	665mm
	1215mm
	1515mm
<b>Overall width</b>	80mm
<b>Installation</b>	Suspension
	Surface

## Versions



RTP-OF-WT198X






RTP-OF-WT198X



GreenPerform Waterproof EcoSet

# GreenPerform Waterproof G3

## Dimensional drawing



### Light Technical

Color rendering index (CRI) 80

### Operating and Electrical

Protection class IEC Safety class I  
 Input Voltage 220 to 240 V  
 Line Frequency 50 to 60 Hz

### Mechanical and Housing

Mech. impact protection code IK08

### Approval and Application

CE mark Yes  
 ENEC mark -  
 Flammability mark -

### General Information

Order Code	Full Product Name	Driver included	Gear	Number of gear units	Service tag
99473999	WT198C LED27S/840 PSU L1200	-	-	-	-
99474699	WT198C LED25S/840 PSU PCO L1200	-	-	-	-
99479199	WT198C LED27S/865 PSU L1200	-	-	-	-
99480799	WT198C LED25S/865 PSU PCO L1200	-	-	-	-
99482199	WT198C LED40S/840 PSU L1200	-	-	-	-
99483899	WT198C LED37S/840 PSU PCO L1200	-	-	-	-
99488399	WT198C LED40S/865 PSU L1200	-	-	-	-
99489099	WT198C LED37S/865 PSU PCO L1200	-	-	-	-
99475399	WT198C LED27S/840 PSD L1200	-	-	-	-
99481499	WT198C LED27S/865 PSD L1200	-	-	-	-
99484599	WT198C LED40S/840 PSD L1200	-	-	-	-
99490699	WT198C LED40S/865 PSD L1200	-	-	-	-
99476099	WT198C LED27S/840 PSD Es L1200	-	-	-	-

Order Code	Full Product Name	Driver included	Gear	Number of gear units	Service tag
99485299	WT198C LED40S/840 PSD Es L1200	-	-	-	-
99477799	WT198X LED27S/840 WIA L1200	-	-	-	-
99486999	WT198X LED40S/840 WIA L1200	-	-	-	-
99524899	WT198C HE LED27S/840 PSU L1200	-	-	-	-
99526299	WT198C HE LED27S/865 PSU L1200	-	-	-	-
99528699	WT198C HE LED40S/840 PSU L1200	-	-	-	-
99530999	WT198C HE LED40S/865 PSU L1200	-	-	-	-
99525599	WT198C HE LED27S/840 PSD L1200	-	-	-	-
99529399	WT198C HE LED40S/840 PSD L1200	-	-	-	-
99527999	WT198C HE LED27S/865 PSD L1200	-	-	-	-
99531699	WT198C HE LED40S/865 PSD L1200	-	-	-	-
99491399	WT198C LED60S/840 PSU L1200	-	-	-	-
99493799	WT198C LED57S/840 PSU PCO L1200	-	-	-	-
99495199	WT198C LED60S/840 PSD L1200	-	-	-	-
99500299	WT198C LED60S/865 PSU L1200	-	-	-	-
99502699	WT198C LED57S/865 PSU PCO L1200	-	-	-	-
99504099	WT198C LED60S/865 PSD L1200	-	-	-	-
99472299	WT198X LED20S/840 DIA H4 L600	-	-	-	-
99492099	WT198C LED60S/840 PSU L1500	-	-	-	-
99494499	WT198C LED57S/840 PSU PCO L1500	-	-	-	-
99501999	WT198C LED60S/865 PSU L1500	-	-	-	-
99503399	WT198C LED57S/865 PSU PCO L1500	-	-	-	-
99506499	WT198C LED80S/840 PSU L1500	-	-	-	-
99507199	WT198C LED75S/840 PSU PCO L1500	-	-	-	-
99512599	WT198C LED80S/865 PSU L1500	-	-	-	-
99513299	WT198C LED75S/865 PSU PCO L1500	-	-	-	-
99515699	WT198C LED100S/840 PSU L1500	-	-	-	-
99516399	WT198C LED94S/840 PSU PCO L1500	-	-	-	-
99521799	WT198C LED100S/865 PSU L1500	-	-	-	-
99522499	WT198C LED94S/865 PSU PCO L1500	-	-	-	-
99496899	WT198C LED60S/840 PSD L1500	-	-	-	-
99505799	WT198C LED60S/865 PSD L1500	-	-	-	-
99508899	WT198C LED80S/840 PSD L1500	-	-	-	-
99514999	WT198C LED80S/865 PSD L1500	-	-	-	-
99517099	WT198C LED100S/840 PSD L1500	-	-	-	-
99523199	WT198C LED100S/865 PSD L1500	-	-	-	-
99497599	WT198C LED60S/840 PSD Es L1500	-	-	-	-
99509599	WT198C LED80S/840 PSD Es L1500	-	-	-	-
99518799	WT198C LED100S/840 PSD Es L1500	-	-	-	-
99498299	WT198X LED60S/840 WIA L1500	-	-	-	-
99510199	WT198X LED80S/840 WIA L1500	-	-	-	-
99519499	WT198X LED100S/840 WIA L1500	-	-	-	-
99532399	WT198C HE LED60S/840 PSU L1500	-	-	-	-
99534799	WT198C HE LED60S/865 PSU L1500	-	-	-	-
99536199	WT198C HE LED80S/840 PSU L1500	-	-	-	-
99538599	WT198C HE LED80S/865 PSU L1500	-	-	-	-
99540899	WT198C HE LED100S/840 PSU L1500	-	-	-	-
99542299	WT198C HE LED100S/865 PSU L1500	-	-	-	-
99533099	WT198C HE LED60S/840 PSD L1500	-	-	-	-
99537899	WT198C HE LED80S/840 PSD L1500	-	-	-	-
99541599	WT198C HE LED100S/840 PSD L1500	-	-	-	-
99535499	WT198C HE LED60S/865 PSD L1500	-	-	-	-

Order Code	Full Product Name	Driver included	Gear	Number of gear units	Service tag
99539299	WT198C HE LED80S/865 PSD L1500	-	-	-	-
99543999	WT198C HE LED100S/865 PSD L1500	-	-	-	-
99478499	WT198X LED27S/840 DIA H4 L1200	-	-	-	-
99487699	WT198X LED40S/840 DIA H4 L1200	-	-	-	-
99499999	WT198X LED60S/840 DIA H4 L1500	-	-	-	-
99511899	WT198X LED80S/840 DIA H4 L1500	-	-	-	-
53260199	WT198X LED20S/840 L1 W L600	Yes	EB	1 unit	Yes
98248499	WT198X LED40S/840 L1 W L1200	Yes	EB	1 unit	Yes
53236699	WT198X LED60S/840 L1 W L1500	Yes	EB	1 unit	Yes
53261899	WT198X LED20S/865 L1 W L600	Yes	EB	1 unit	Yes
53243499	WT198X LED27S/865 L1 W L1200	Yes	EB	1 unit	Yes
53258899	WT198X LED40S/865 L1 W L1200	Yes	EB	1 unit	Yes
53256499	WT198X LED82S/865 L1 W L1500	Yes	EB	1 unit	Yes
53238099	WT198X LED20S/840 L1 S L600	Yes	EB	1 unit	Yes
98249199	WT198X LED60S/840 L1 S L1500	Yes	EB	1 unit	Yes
53234299	WT198X LED82S/840 L1 S L1500	Yes	EB	1 unit	Yes
53251999	WT198X LED20S/865 L1 S L600	Yes	EB	1 unit	Yes
53247299	WT198X LED82S/865 L1 S L1500	Yes	EB	1 unit	Yes
53249699	WT198X LED19S/840 L1 W PCO L600	Yes	EB	1 unit	Yes
53254099	WT198X LED26S/840 L1 W PCO L1200	Yes	EB	1 unit	Yes
53268799	WT198X LED38S/840 L1 W PCO L1200	Yes	EB	1 unit	Yes
53250299	WT198X LED19S/865 L1 W PCO L600	Yes	EB	1 unit	Yes
53264999	WT198X LED26S/865 L1 W PCO L1200	Yes	EB	1 unit	Yes
53269499	WT198X LED38S/865 L1 W PCO L1200	Yes	EB	1 unit	Yes
53263299	WT198X LED57S/865 L1 W PCO L1500	Yes	EB	1 unit	Yes
53252699	WT198X LED19S/840 L1 S PCO L600	Yes	EB	1 unit	Yes
99467899	WT198C LED12S/840 PSU L600	-	-	-	-
99468599	WT198C LED11S/840 PSU PCO L600	-	-	-	-
99469299	WT198C LED20S/840 PSU L600	-	-	-	-
99470899	WT198C LED18S/840 PSU PCO L600	-	-	-	-
99471599	WT198X LED20S/840 WIA L600	-	-	-	-
53246599	WT198X LED27S/840 L1 S L1200	Yes	EB	1 unit	Yes
51810099	WT198X LED40S/840 L1 S L1200	Yes	EB	1 unit	Yes
53265699	WT198X LED27S/865 L1 S L1200	Yes	EB	1 unit	Yes
51811799	WT198X LED40S/865 L1 S L1200	Yes	EB	1 unit	Yes
53266399	WT198X LED26S/840 L1 S PCO L1200	Yes	EB	1 unit	Yes
53259599	WT198X LED38S/840 L1 S PCO L1200	Yes	EB	1 unit	Yes
53257199	WT198X LED26S/865 L1 S PCO L1200	Yes	EB	1 unit	Yes
53235999	WT198X LED38S/865 L1 S PCO L1200	Yes	EB	1 unit	Yes

## Light Technical (1/2)

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
99473999	WT198C LED27S/840 PSU L1200	115 degree(s)	4000 K	159 lm/W	2,700 lm	99479199	WT198C LED27S/865 PSU L1200	115 degree(s)	6500 K	159 lm/W	2,700 lm
99474699	WT198C LED25S/840 PSU PCO L1200	115 degree(s)	4000 K	150 lm/W	2,550 lm	99480799	WT198C LED25S/865 PSU PCO L1200	115 degree(s)	6500 K	150 lm/W	2,550 lm

## GreenPerform Waterproof G3

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
99482199	WT198C LED40S/840 PSU L1200	115 degree(s)	4000 K	160 lm/W	4,000 lm
99483899	WT198C LED37S/840 PSU PCO L1200	115 degree(s)	4000 K	150 lm/W	3,750 lm
99488399	WT198C LED40S/865 PSU L1200	115 degree(s)	6500 K	160 lm/W	4,000 lm
99489099	WT198C LED37S/865 PSU PCO L1200	115 degree(s)	6500 K	150 lm/W	3,750 lm
99475399	WT198C LED27S/840 PSD L1200	115 degree(s)	4000 K	159 lm/W	2,700 lm
99481499	WT198C LED27S/865 PSD L1200	115 degree(s)	6500 K	159 lm/W	2,700 lm
99484599	WT198C LED40S/840 PSD L1200	115 degree(s)	4000 K	160 lm/W	4,000 lm
99490699	WT198C LED40S/865 PSD L1200	115 degree(s)	6500 K	160 lm/W	4,000 lm
99476099	WT198C LED27S/840 PSD Es L1200	115 degree(s)	4000 K	159 lm/W	2,700 lm
99485299	WT198C LED40S/840 PSD Es L1200	115 degree(s)	4000 K	160 lm/W	4,000 lm
99477799	WT198X LED27S/840 WIA L1200	115 degree(s)	4000 K	159 lm/W	2,700 lm
99486999	WT198X LED40S/840 WIA L1200	115 degree(s)	4000 K	160 lm/W	4,000 lm
99524899	WT198C HE LED27S/840 PSU L1200	115 degree(s)	4000 K	172 lm/W	2,700 lm
99526299	WT198C HE LED27S/865 PSU L1200	115 degree(s)	6500 K	172 lm/W	2,700 lm
99528699	WT198C HE LED40S/840 PSU L1200	115 degree(s)	4000 K	173 lm/W	4,000 lm
99530999	WT198C HE LED40S/865 PSU L1200	115 degree(s)	6500 K	173 lm/W	4,000 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
99525599	WT198C HE LED27S/840 PSD L1200	115 degree(s)	4000 K	172 lm/W	2,700 lm
99529399	WT198C HE LED40S/840 PSD L1200	115 degree(s)	4000 K	173 lm/W	4,000 lm
99527999	WT198C HE LED27S/865 PSD L1200	115 degree(s)	6500 K	172 lm/W	2,700 lm
99531699	WT198C HE LED40S/865 PSD L1200	115 degree(s)	6500 K	173 lm/W	4,000 lm
99491399	WT198C LED60S/840 PSU L1200	115 degree(s)	4000 K	156 lm/W	6,000 lm
99493799	WT198C LED57S/840 PSU PCO L1200	115 degree(s)	4000 K	147 lm/W	5,650 lm
99495199	WT198C LED60S/840 PSD L1200	115 degree(s)	4000 K	156 lm/W	6,000 lm
99500299	WT198C LED60S/865 PSU L1200	115 degree(s)	6500 K	156 lm/W	6,000 lm
99502699	WT198C LED57S/865 PSU PCO L1200	115 degree(s)	6500 K	147 lm/W	5,650 lm
99504099	WT198C LED60S/865 PSD L1200	115 degree(s)	6500 K	156 lm/W	6,000 lm
99472299	WT198X LED20S/840 DIA H4 L600	115 degree(s)	4000 K	143 lm/W	2,000 lm
99492099	WT198C LED60S/840 PSU L1500	115 degree(s)	4000 K	160 lm/W	6,000 lm
99494499	WT198C LED57S/840 PSU PCO L1500	115 degree(s)	4000 K	151 lm/W	5,650 lm
99501999	WT198C LED60S/865 PSU L1500	115 degree(s)	6500 K	160 lm/W	6,000 lm
99503399	WT198C LED57S/865 PSU PCO L1500	115 degree(s)	6500 K	151 lm/W	5,650 lm
99506499	WT198C LED80S/840 PSU L1500	115 degree(s)	4000 K	160 lm/W	8,000 lm

## GreenPerform Waterproof G3

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
99507199	WT198C LED75S/840 PSU PCO L1500	115 degree(s)	4000 K	151 lm/W	7,550 lm
99512599	WT198C LED80S/865 PSU L1500	115 degree(s)	6500 K	160 lm/W	8,000 lm
99513299	WT198C LED75S/865 PSU PCO L1500	115 degree(s)	6500 K	151 lm/W	7,550 lm
99515699	WT198C LED100S/840 PSU L1500	115 degree(s)	4000 K	160 lm/W	10,000 lm
99516399	WT198C LED94S/840 PSU PCO L1500	115 degree(s)	4000 K	151 lm/W	9,450 lm
99521799	WT198C LED100S/865 PSU L1500	115 degree(s)	6500 K	160 lm/W	10,000 lm
99522499	WT198C LED94S/865 PSU PCO L1500	115 degree(s)	6500 K	151 lm/W	9,450 lm
99496899	WT198C LED60S/840 PSD L1500	115 degree(s)	4000 K	160 lm/W	6,000 lm
99505799	WT198C LED60S/865 PSD L1500	115 degree(s)	6500 K	160 lm/W	6,000 lm
99508899	WT198C LED80S/840 PSD L1500	115 degree(s)	4000 K	160 lm/W	8,000 lm
99514999	WT198C LED80S/865 PSD L1500	115 degree(s)	6500 K	160 lm/W	8,000 lm
99517099	WT198C LED100S/840 PSD L1500	115 degree(s)	4000 K	160 lm/W	10,000 lm
99523199	WT198C LED100S/865 PSD L1500	115 degree(s)	6500 K	160 lm/W	10,000 lm
99497599	WT198C LED60S/840 PSD Es L1500	115 degree(s)	4000 K	160 lm/W	6,000 lm
99509599	WT198C LED80S/840 PSD Es L1500	115 degree(s)	4000 K	160 lm/W	8,000 lm
99518799	WT198C LED100S/840 PSD Es L1500	115 degree(s)	4000 K	160 lm/W	10,000 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
99498299	WT198X LED60S/840 WIA L1500	115 degree(s)	4000 K	160 lm/W	6,000 lm
99510199	WT198X LED80S/840 WIA L1500	115 degree(s)	4000 K	160 lm/W	8,000 lm
99519499	WT198X LED100S/840 WIA L1500	115 degree(s)	4000 K	160 lm/W	10,000 lm
99532399	WT198C HE LED60S/840 PSU L1500	115 degree(s)	4000 K	178 lm/W	6,000 lm
99534799	WT198C HE LED60S/865 PSU L1500	115 degree(s)	6500 K	178 lm/W	6,000 lm
99536199	WT198C HE LED80S/840 PSU L1500	115 degree(s)	4000 K	180 lm/W	8,000 lm
99538599	WT198C HE LED80S/865 PSU L1500	115 degree(s)	6500 K	180 lm/W	8,000 lm
99540899	WT198C HE LED100S/840 PSU L1500	115 degree(s)	4000 K	181 lm/W	10,000 lm
99542299	WT198C HE LED100S/865 PSU L1500	115 degree(s)	6500 K	181 lm/W	10,000 lm
99533099	WT198C HE LED60S/840 PSD L1500	115 degree(s)	4000 K	178 lm/W	6,000 lm
99537899	WT198C HE LED80S/840 PSD L1500	115 degree(s)	4000 K	180 lm/W	8,000 lm
99541599	WT198C HE LED100S/840 PSD L1500	115 degree(s)	4000 K	181 lm/W	10,000 lm
99535499	WT198C HE LED60S/865 PSD L1500	115 degree(s)	6500 K	178 lm/W	6,000 lm
99539299	WT198C HE LED80S/865 PSD L1500	115 degree(s)	6500 K	180 lm/W	8,000 lm
99543999	WT198C HE LED100S/865 PSD L1500	115 degree(s)	6500 K	181 lm/W	10,000 lm
99478499	WT198X LED27S/840 DIA H4 L1200	115 degree(s)	4000 K	150 lm/W	2,700 lm

## GreenPerform Waterproof G3

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
99487699	WT198X LED40S/840 DIA H4 L1200	115 degree(s)	4000 K	154 lm/W	4,000 lm
99499999	WT198X LED60S/840 DIA H4 L1500	115 degree(s)	4000 K	156 lm/W	6,000 lm
99511899	WT198X LED80S/840 DIA H4 L1500	115 degree(s)	4000 K	157 lm/W	8,000 lm
53260199	WT198X LED20S/840 L1 W L600	-	4000 K	136.1 lm/W	2,000 lm
98248499	WT198X LED40S/840 L1 W L1200	-	4000 K	138.4 lm/W	4,000 lm
53236699	WT198X LED60S/840 L1 W L1500	-	4000 K	137.6 lm/W	6,000 lm
53261899	WT198X LED20S/865 L1 W L600	-	6500 K	136.1 lm/W	2,000 lm
53243499	WT198X LED27S/865 L1 W L1200	-	6500 K	143.6 lm/W	2,700 lm
53258899	WT198X LED40S/865 L1 W L1200	-	6500 K	138.4 lm/W	4,000 lm
53256499	WT198X LED82S/865 L1 W L1500	-	6500 K	138.7 lm/W	8,200 lm
53238099	WT198X LED20S/840 L1 S L600	-	4000 K	136.1 lm/W	2,000 lm
98249199	WT198X LED60S/840 L1 S L1500	-	4000 K	137.6 lm/W	6,000 lm
53234299	WT198X LED82S/840 L1 S L1500	-	4000 K	138.7 lm/W	8,200 lm
53251999	WT198X LED20S/865 L1 S L600	-	6500 K	136.1 lm/W	2,000 lm
53247299	WT198X LED82S/865 L1 S L1500	-	6500 K	138.7 lm/W	8,200 lm
53249699	WT198X LED19S/840 L1 W PCO L600	-	4000 K	129.3 lm/W	1,900 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
53254099	WT198X LED26S/840 L1 W PCO L1200	-	4000 K	138.3 lm/W	2,600 lm
53268799	WT198X LED38S/840 L1 W PCO L1200	-	4000 K	131.5 lm/W	3,800 lm
53250299	WT198X LED19S/865 L1 W PCO L600	-	6500 K	129.3 lm/W	1,900 lm
53264999	WT198X LED26S/865 L1 W PCO L1200	-	6500 K	138.3 lm/W	2,600 lm
53269499	WT198X LED38S/865 L1 W PCO L1200	-	6500 K	131.5 lm/W	3,800 lm
53263299	WT198X LED57S/865 L1 W PCO L1500	-	6500 K	130.7 lm/W	5,700 lm
53252699	WT198X LED19S/840 L1 S PCO L600	-	4000 K	129.3 lm/W	1,900 lm
99467899	WT198C LED12S/840 PSU L600	115 degree(s)	4000 K	154 lm/W	1,250 lm
99468599	WT198C LED11S/840 PSU PCO L600	115 degree(s)	4000 K	142 lm/W	1,150 lm
99469299	WT198C LED20S/840 PSU L600	115 degree(s)	4000 K	154 lm/W	2,000 lm
99470899	WT198C LED18S/840 PSU PCO L600	115 degree(s)	4000 K	142 lm/W	1,850 lm
99471599	WT198X LED20S/840 WIA L600	115 degree(s)	4000 K	154 lm/W	2,000 lm
53246599	WT198X LED27S/840 L1 S L1200	-	4000 K	143.6 lm/W	2,700 lm
51810099	WT198X LED40S/840 L1 S L1200	-	4000 K	138.4 lm/W	4,000 lm
53265699	WT198X LED27S/865 L1 S L1200	-	6500 K	143.6 lm/W	2,700 lm
51811799	WT198X LED40S/865 L1 S L1200	-	6500 K	138.4 lm/W	4,000 lm

# GreenPerform Waterproof G3

Order Code	Full Product Name	Beam angle of light source	Correlated Color	Luminous Efficacy	Luminous Flux
			Temperature (Nom)	(rated) (Nom)	
53266399	WT198X LED26S/840 L1 S PCO L1200	-	4000 K	138.3 lm/W	2,600 lm
53259599	WT198X LED38S/840 L1 S PCO L1200	-	4000 K	131.5 lm/W	3,800 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color	Luminous Efficacy	Luminous Flux
			Temperature (Nom)	(rated) (Nom)	
53257199	WT198X LED26S/865 L1 S PCO L1200	-	6500 K	138.3 lm/W	2,600 lm
53235999	WT198X LED38S/865 L1 S PCO L1200	-	6500 K	131.5 lm/W	3,800 lm

## Light Technical (2/2)

Order Code	Full Product Name	Number of light	
		sources	Optic type
99473999	WT198C LED27S/840 PSU L1200	-	Very wide beam
99474699	WT198C LED25S/840 PSU PCO L1200	-	Opal
99479199	WT198C LED27S/865 PSU L1200	-	Very wide beam
99480799	WT198C LED25S/865 PSU PCO L1200	-	Opal
99482199	WT198C LED40S/840 PSU L1200	-	Very wide beam
99483899	WT198C LED37S/840 PSU PCO L1200	-	Opal
99488399	WT198C LED40S/865 PSU L1200	-	Very wide beam
99489099	WT198C LED37S/865 PSU PCO L1200	-	Opal
99475399	WT198C LED27S/840 PSD L1200	-	Very wide beam
99481499	WT198C LED27S/865 PSD L1200	-	Very wide beam
99484599	WT198C LED40S/840 PSD L1200	-	Very wide beam
99490699	WT198C LED40S/865 PSD L1200	-	Very wide beam
99476099	WT198C LED27S/840 PSD Es L1200	-	Very wide beam
99485299	WT198C LED40S/840 PSD Es L1200	-	Very wide beam
99477799	WT198X LED27S/840 WIA L1200	-	Very wide beam
99486999	WT198X LED40S/840 WIA L1200	-	Very wide beam
99524899	WT198C HE LED27S/840 PSU L1200	-	Very wide beam
99526299	WT198C HE LED27S/865 PSU L1200	-	Very wide beam
99528699	WT198C HE LED40S/840 PSU L1200	-	Very wide beam
99530999	WT198C HE LED40S/865 PSU L1200	-	Very wide beam
99525599	WT198C HE LED27S/840 PSD L1200	-	Very wide beam
99529399	WT198C HE LED40S/840 PSD L1200	-	Very wide beam
99527999	WT198C HE LED27S/865 PSD L1200	-	Very wide beam
99531699	WT198C HE LED40S/865 PSD L1200	-	Very wide beam
99491399	WT198C LED60S/840 PSU L1200	-	Very wide beam
99493799	WT198C LED57S/840 PSU PCO L1200	-	Very wide beam
99495199	WT198C LED60S/840 PSD L1200	-	Very wide beam
99500299	WT198C LED60S/865 PSU L1200	-	Very wide beam
99502699	WT198C LED57S/865 PSU PCO L1200	-	Very wide beam
99504099	WT198C LED60S/865 PSD L1200	-	Very wide beam
99472299	WT198X LED20S/840 DIA H4 L600	-	Very wide beam
99492099	WT198C LED60S/840 PSU L1500	-	Very wide beam
99494499	WT198C LED57S/840 PSU PCO L1500	-	Opal
99501999	WT198C LED60S/865 PSU L1500	-	Very wide beam
99503399	WT198C LED57S/865 PSU PCO L1500	-	Opal
99506499	WT198C LED80S/840 PSU L1500	-	Very wide beam
99507199	WT198C LED75S/840 PSU PCO L1500	-	Opal
99512599	WT198C LED80S/865 PSU L1500	-	Very wide beam

Order Code	Full Product Name	Number of light	
		sources	Optic type
99513299	WT198C LED75S/865 PSU PCO L1500	-	Opal
99515699	WT198C LED100S/840 PSU L1500	-	Very wide beam
99516399	WT198C LED94S/840 PSU PCO L1500	-	Opal
99521799	WT198C LED100S/865 PSU L1500	-	Very wide beam
99522499	WT198C LED94S/865 PSU PCO L1500	-	Opal
99496899	WT198C LED60S/840 PSD L1500	-	Very wide beam
99505799	WT198C LED60S/865 PSD L1500	-	Very wide beam
99508899	WT198C LED80S/840 PSD L1500	-	Very wide beam
99514999	WT198C LED80S/865 PSD L1500	-	Very wide beam
99517099	WT198C LED100S/840 PSD L1500	-	Very wide beam
99523199	WT198C LED100S/865 PSD L1500	-	Very wide beam
99497599	WT198C LED60S/840 PSD Es L1500	-	Very wide beam
99509599	WT198C LED80S/840 PSD Es L1500	-	Very wide beam
99518799	WT198C LED100S/840 PSD Es L1500	-	Very wide beam
99498299	WT198X LED60S/840 WIA L1500	-	Very wide beam
99510199	WT198X LED80S/840 WIA L1500	-	Very wide beam
99519499	WT198X LED100S/840 WIA L1500	-	Very wide beam
99532399	WT198C HE LED60S/840 PSU L1500	-	Very wide beam
99534799	WT198C HE LED60S/865 PSU L1500	-	Very wide beam
99536199	WT198C HE LED80S/840 PSU L1500	-	Very wide beam
99538599	WT198C HE LED80S/865 PSU L1500	-	Very wide beam
99540899	WT198C HE LED100S/840 PSU L1500	-	Very wide beam
99542299	WT198C HE LED100S/865 PSU L1500	-	Very wide beam
99533099	WT198C HE LED60S/840 PSD L1500	-	Very wide beam
99537899	WT198C HE LED80S/840 PSD L1500	-	Very wide beam
99541599	WT198C HE LED100S/840 PSD L1500	-	Very wide beam
99535499	WT198C HE LED60S/865 PSD L1500	-	Very wide beam
99539299	WT198C HE LED80S/865 PSD L1500	-	Very wide beam
99543999	WT198C HE LED100S/865 PSD L1500	-	Very wide beam
99478499	WT198X LED27S/840 DIA H4 L1200	-	Very wide beam
99487699	WT198X LED40S/840 DIA H4 L1200	-	Very wide beam
99499999	WT198X LED60S/840 DIA H4 L1500	-	Very wide beam
99511899	WT198X LED80S/840 DIA H4 L1500	-	Very wide beam
53260199	WT198X LED20S/840 L1 W L600	1	-
98248499	WT198X LED40S/840 L1 W L1200	1	-
53236699	WT198X LED60S/840 L1 W L1500	1	-
53261899	WT198X LED20S/865 L1 W L600	1	-
53243499	WT198X LED27S/865 L1 W L1200	1	-

## GreenPerform Waterproof G3

Order Code	Full Product Name	Number of light	
		sources	Optic type
53258899	WT198X LED40S/865 L1 W L1200	1	-
53256499	WT198X LED82S/865 L1 W L1500	1	-
53238099	WT198X LED20S/840 L1 S L600	1	-
98249199	WT198X LED60S/840 L1 S L1500	1	-
53234299	WT198X LED82S/840 L1 S L1500	1	-
53251999	WT198X LED20S/865 L1 S L600	1	-
53247299	WT198X LED82S/865 L1 S L1500	1	-
53249699	WT198X LED19S/840 L1 W PCO L600	1	-
53254099	WT198X LED26S/840 L1 W PCO L1200	1	-
53268799	WT198X LED38S/840 L1 W PCO L1200	1	-
53250299	WT198X LED19S/865 L1 W PCO L600	1	-
53264999	WT198X LED26S/865 L1 W PCO L1200	1	-
53269499	WT198X LED38S/865 L1 W PCO L1200	1	-
53263299	WT198X LED57S/865 L1 W PCO L1500	1	-

Order Code	Full Product Name	Number of light	
		sources	Optic type
53252699	WT198X LED19S/840 L1 S PCO L600	1	-
99467899	WT198C LED12S/840 PSU L600	-	Very wide beam
99468599	WT198C LED11S/840 PSU PCO L600	-	Opal
99469299	WT198C LED20S/840 PSU L600	-	Very wide beam
99470899	WT198C LED18S/840 PSU PCO L600	-	Opal
99471599	WT198X LED20S/840 WIA L600	-	Very wide beam
53246599	WT198X LED27S/840 L1 S L1200	1	-
51810099	WT198X LED40S/840 L1 S L1200	1	-
53265699	WT198X LED27S/865 L1 S L1200	1	-
51811799	WT198X LED40S/865 L1 S L1200	1	-
53266399	WT198X LED26S/840 L1 S PCO L1200	1	-
53259599	WT198X LED38S/840 L1 S PCO L1200	1	-
53257199	WT198X LED26S/865 L1 S PCO L1200	1	-
53235999	WT198X LED38S/865 L1 S PCO L1200	1	-

### Operating and Electrical

Order Code	Full Product Name	Power Consumption	Suitable for
			random switching
99473999	WT198C LED27S/840 PSU L1200	17 W	-
99474699	WT198C LED25S/840 PSU PCO L1200	17 W	-
99479199	WT198C LED27S/865 PSU L1200	17 W	-
99480799	WT198C LED25S/865 PSU PCO L1200	17 W	-
99482199	WT198C LED40S/840 PSU L1200	25 W	-
99483899	WT198C LED37S/840 PSU PCO L1200	25 W	-
99488399	WT198C LED40S/865 PSU L1200	25 W	-
99489099	WT198C LED37S/865 PSU PCO L1200	25 W	-
99475399	WT198C LED27S/840 PSD L1200	17 W	-
99481499	WT198C LED27S/865 PSD L1200	17 W	-
99484599	WT198C LED40S/840 PSD L1200	25 W	-
99490699	WT198C LED40S/865 PSD L1200	25 W	-
99476099	WT198C LED27S/840 PSD Es L1200	17 W	-
99485299	WT198C LED40S/840 PSD Es L1200	25 W	-
99477799	WT198X LED27S/840 WIA L1200	17 W	-
99486999	WT198X LED40S/840 WIA L1200	25 W	-
99524899	WT198C HE LED27S/840 PSU L1200	15.7 W	-
99526299	WT198C HE LED27S/865 PSU L1200	15.7 W	-
99528699	WT198C HE LED40S/840 PSU L1200	23.1 W	-
99530999	WT198C HE LED40S/865 PSU L1200	23.1 W	-
99525599	WT198C HE LED27S/840 PSD L1200	15.7 W	-
99529399	WT198C HE LED40S/840 PSD L1200	23.1 W	-
99527999	WT198C HE LED27S/865 PSD L1200	15.7 W	-
99531699	WT198C HE LED40S/865 PSD L1200	23.1 W	-
99491399	WT198C LED60S/840 PSU L1200	38.4 W	-
99493799	WT198C LED57S/840 PSU PCO L1200	38.4 W	-

Order Code	Full Product Name	Power Consumption	Suitable for
			random switching
99495199	WT198C LED60S/840 PSD L1200	38.4 W	-
99500299	WT198C LED60S/865 PSU L1200	38.4 W	-
99502699	WT198C LED57S/865 PSU PCO L1200	38.4 W	-
99504099	WT198C LED60S/865 PSD L1200	38.4 W	-
99472299	WT198X LED20S/840 DIA H4 L600	14 W	-
99492099	WT198C LED60S/840 PSU L1500	37.5 W	-
99494499	WT198C LED57S/840 PSU PCO L1500	37.5 W	-
99501999	WT198C LED60S/865 PSU L1500	37.5 W	-
99503399	WT198C LED57S/865 PSU PCO L1500	37.5 W	-
99506499	WT198C LED80S/840 PSU L1500	50 W	-
99507199	WT198C LED75S/840 PSU PCO L1500	50 W	-
99512599	WT198C LED80S/865 PSU L1500	50 W	-
99513299	WT198C LED75S/865 PSU PCO L1500	50 W	-
99515699	WT198C LED100S/840 PSU L1500	62.5 W	-
99516399	WT198C LED94S/840 PSU PCO L1500	62.5 W	-
99521799	WT198C LED100S/865 PSU L1500	62.5 W	-
99522499	WT198C LED94S/865 PSU PCO L1500	62.5 W	-
99496899	WT198C LED60S/840 PSD L1500	37.5 W	-
99505799	WT198C LED60S/865 PSD L1500	37.5 W	-
99508899	WT198C LED80S/840 PSD L1500	50 W	-
99514999	WT198C LED80S/865 PSD L1500	50 W	-
99517099	WT198C LED100S/840 PSD L1500	62.5 W	-
99523199	WT198C LED100S/865 PSD L1500	62.5 W	-
99497599	WT198C LED60S/840 PSD Es L1500	37.5 W	-

## GreenPerform Waterproof G3

Order Code	Full Product Name	Power Consumption	Suitable for random switching
99509599	WT198C LED80S/840 PSD Es L1500	50 W	-
99518799	WT198C LED100S/840 PSD Es L1500	62.5 W	-
99498299	WT198X LED60S/840 WIA L1500	37.5 W	-
99510199	WT198X LED80S/840 WIA L1500	50 W	-
99519499	WT198X LED100S/840 WIA L1500	62.5 W	-
99532399	WT198C HE LED60S/840 PSU L1500	33.8 W	-
99534799	WT198C HE LED60S/865 PSU L1500	33.8 W	-
99536199	WT198C HE LED80S/840 PSU L1500	44.4 W	-
99538599	WT198C HE LED80S/865 PSU L1500	44.4 W	-
99540899	WT198C HE LED100S/840 PSU L1500	55.1 W	-
99542299	WT198C HE LED100S/865 PSU L1500	55.1 W	-
99533099	WT198C HE LED60S/840 PSD L1500	33.8 W	-
99537899	WT198C HE LED80S/840 PSD L1500	44.4 W	-
99541599	WT198C HE LED100S/840 PSD L1500	55.1 W	-
99535499	WT198C HE LED60S/865 PSD L1500	33.8 W	-
99539299	WT198C HE LED80S/865 PSD L1500	44.4 W	-
99543999	WT198C HE LED100S/865 PSD L1500	55.1 W	-
99478499	WT198X LED27S/840 DIA H4 L1200	18 W	-
99487699	WT198X LED40S/840 DIA H4 L1200	26 W	-
99499999	WT198X LED60S/840 DIA H4 L1500	38.5 W	-
99511899	WT198X LED80S/840 DIA H4 L1500	51 W	-
53260199	WT198X LED20S/840 L1 W L600	14.7 W	Yes
98248499	WT198X LED40S/840 L1 W L1200	28.9 W	Yes
53236699	WT198X LED60S/840 L1 W L1500	43.6 W	Yes
53261899	WT198X LED20S/865 L1 W L600	14.7 W	Yes
53243499	WT198X LED27S/865 L1 W L1200	18.8 W	Yes
53258899	WT198X LED40S/865 L1 W L1200	28.9 W	Yes
53256499	WT198X LED82S/865 L1 W L1500	59.1 W	Yes
53238099	WT198X LED20S/840 L1 S L600	14.7 W	Yes
98249199	WT198X LED60S/840 L1 S L1500	43.6 W	Yes
53234299	WT198X LED82S/840 L1 S L1500	59.1 W	Yes

Order Code	Full Product Name	Power Consumption	Suitable for random switching
53251999	WT198X LED20S/865 L1 S L600	14.7 W	Yes
53247299	WT198X LED82S/865 L1 S L1500	59.1 W	Yes
53249699	WT198X LED19S/840 L1 W PCO L600	14.7 W	Yes
53254099	WT198X LED26S/840 L1 W PCO L1200	18.8 W	Yes
53268799	WT198X LED38S/840 L1 W PCO L1200	28.9 W	Yes
53250299	WT198X LED19S/865 L1 W PCO L600	14.7 W	Yes
53264999	WT198X LED26S/865 L1 W PCO L1200	18.8 W	Yes
53269499	WT198X LED38S/865 L1 W PCO L1200	28.9 W	Yes
53263299	WT198X LED57S/865 L1 W PCO L1500	43.6 W	Yes
53252699	WT198X LED19S/840 L1 S PCO L600	14.7 W	Yes
99467899	WT198C LED12S/840 PSU L600	8.1 W	-
99468599	WT198C LED11S/840 PSU PCO L600	8.1 W	-
99469299	WT198C LED20S/840 PSU L600	13 W	-
99470899	WT198C LED18S/840 PSU PCO L600	13 W	-
99471599	WT198X LED20S/840 WIA L600	13 W	-
53246599	WT198X LED27S/840 L1 S L1200	18.8 W	Yes
51810099	WT198X LED40S/840 L1 S L1200	28.9 W	Yes
53265699	WT198X LED27S/865 L1 S L1200	18.8 W	Yes
51811799	WT198X LED40S/865 L1 S L1200	28.9 W	Yes
53266399	WT198X LED26S/840 L1 S PCO L1200	18.8 W	Yes
53259599	WT198X LED38S/840 L1 S PCO L1200	28.9 W	Yes
53257199	WT198X LED26S/865 L1 S PCO L1200	18.8 W	Yes
53235999	WT198X LED38S/865 L1 S PCO L1200	28.9 W	Yes

### Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
99473999	WT198C LED27S/840 PSU L1200	Fixed	-
99474699	WT198C LED25S/840 PSU PCO L1200	Fixed	-
99479199	WT198C LED27S/865 PSU L1200	Fixed	-
99480799	WT198C LED25S/865 PSU PCO L1200	Fixed	-
99482199	WT198C LED40S/840 PSU L1200	Fixed	-
99483899	WT198C LED37S/840 PSU PCO L1200	Fixed	-
99488399	WT198C LED40S/865 PSU L1200	Fixed	-
99489099	WT198C LED37S/865 PSU PCO L1200	Fixed	-
99475399	WT198C LED27S/840 PSD L1200	DALI	-
99481499	WT198C LED27S/865 PSD L1200	DALI	-
99484599	WT198C LED40S/840 PSD L1200	DALI	-

Order Code	Full Product Name	Dimmable	Maximum dim level
99490699	WT198C LED40S/865 PSD L1200	DALI	-
99476099	WT198C LED27S/840 PSD Es L1200	DALI	-
99485299	WT198C LED40S/840 PSD Es L1200	DALI	-
99477799	WT198X LED27S/840 WIA L1200	Wireless Dim	-
99486999	WT198X LED40S/840 WIA L1200	Wireless Dim	-
99524899	WT198C HE LED27S/840 PSU L1200	Fixed	-
99526299	WT198C HE LED27S/865 PSU L1200	Fixed	-
99528699	WT198C HE LED40S/840 PSU L1200	Fixed	-
99530999	WT198C HE LED40S/865 PSU L1200	Fixed	-
99525599	WT198C HE LED27S/840 PSD L1200	DALI	-
99529399	WT198C HE LED40S/840 PSD L1200	DALI	-

# GreenPerform Waterproof G3

Order Code	Full Product Name	Dimmable	Maximum dim level
99527999	WT198C HE LED27S/865 PSD L1200	DALI	-
99531699	WT198C HE LED40S/865 PSD L1200	DALI	-
99491399	WT198C LED60S/840 PSU L1200	Fixed	-
99493799	WT198C LED57S/840 PSU PCO L1200	Fixed	-
99495199	WT198C LED60S/840 PSD L1200	DALI	-
99500299	WT198C LED60S/865 PSU L1200	Fixed	-
99502699	WT198C LED57S/865 PSU PCO L1200	Fixed	-
99504099	WT198C LED60S/865 PSD L1200	DALI	-
99472299	WT198X LED20S/840 DIA H4 L600	DALI	-
99492099	WT198C LED60S/840 PSU L1500	Fixed	-
99494499	WT198C LED57S/840 PSU PCO L1500	Fixed	-
99501999	WT198C LED60S/865 PSU L1500	Fixed	-
99503399	WT198C LED57S/865 PSU PCO L1500	Fixed	-
99506499	WT198C LED80S/840 PSU L1500	Fixed	-
99507199	WT198C LED75S/840 PSU PCO L1500	Fixed	-
99512599	WT198C LED80S/865 PSU L1500	Fixed	-
99513299	WT198C LED75S/865 PSU PCO L1500	Fixed	-
99515699	WT198C LED100S/840 PSU L1500	Fixed	-
99516399	WT198C LED94S/840 PSU PCO L1500	Fixed	-
99521799	WT198C LED100S/865 PSU L1500	Fixed	-
99522499	WT198C LED94S/865 PSU PCO L1500	Fixed	-
99496899	WT198C LED60S/840 PSD L1500	DALI	-
99505799	WT198C LED60S/865 PSD L1500	DALI	-
99508899	WT198C LED80S/840 PSD L1500	DALI	-
99514999	WT198C LED80S/865 PSD L1500	DALI	-
99517099	WT198C LED100S/840 PSD L1500	DALI	-
99523199	WT198C LED100S/865 PSD L1500	DALI	-
99497599	WT198C LED60S/840 PSD Es L1500	DALI	-
99509599	WT198C LED80S/840 PSD Es L1500	DALI	-
99518799	WT198C LED100S/840 PSD Es L1500	DALI	-
99498299	WT198X LED60S/840 WIA L1500	Wireless Dim	-
99510199	WT198X LED80S/840 WIA L1500	Wireless Dim	-
99519499	WT198X LED100S/840 WIA L1500	Wireless Dim	-
99532399	WT198C HE LED60S/840 PSU L1500	Fixed	-
99534799	WT198C HE LED60S/865 PSU L1500	Fixed	-
99536199	WT198C HE LED80S/840 PSU L1500	Fixed	-
99538599	WT198C HE LED80S/865 PSU L1500	Fixed	-
99540899	WT198C HE LED100S/840 PSU L1500	Fixed	-
99542299	WT198C HE LED100S/865 PSU L1500	Fixed	-
99533099	WT198C HE LED60S/840 PSD L1500	DALI	-
99537899	WT198C HE LED80S/840 PSD L1500	DALI	-

Order Code	Full Product Name	Dimmable	Maximum dim level
99541599	WT198C HE LED100S/840 PSD L1500	DALI	-
99535499	WT198C HE LED60S/865 PSD L1500	DALI	-
99539299	WT198C HE LED80S/865 PSD L1500	DALI	-
99543999	WT198C HE LED100S/865 PSD L1500	DALI	-
99478499	WT198X LED27S/840 DIA H4 L1200	DALI	-
99487699	WT198X LED40S/840 DIA H4 L1200	DALI	-
99499999	WT198X LED60S/840 DIA H4 L1500	DALI	-
99511899	WT198X LED80S/840 DIA H4 L1500	DALI	-
53260199	WT198X LED20S/840 L1 W L600	Wireless Dim	20%
98248499	WT198X LED40S/840 L1 W L1200	Step Dim	20%
53236699	WT198X LED60S/840 L1 W L1500	Wireless Dim	20%
53261899	WT198X LED20S/865 L1 W L600	Wireless Dim	20%
53243499	WT198X LED27S/865 L1 W L1200	Step Dim	20%
53258899	WT198X LED40S/865 L1 W L1200	Wireless Dim	20%
53256499	WT198X LED82S/865 L1 W L1500	Step Dim	20%
53238099	WT198X LED20S/840 L1 S L600	Step Dim	20%
98249199	WT198X LED60S/840 L1 S L1500	Step Dim	20%
53234299	WT198X LED82S/840 L1 S L1500	Wireless Dim	20%
53251999	WT198X LED20S/865 L1 S L600	Step Dim	20%
53247299	WT198X LED82S/865 L1 S L1500	Wireless Dim	20%
53249699	WT198X LED19S/840 L1 W PCO L600	Wireless Dim	20%
53254099	WT198X LED26S/840 L1 W PCO L1200	Wireless Dim	20%
53268799	WT198X LED38S/840 L1 W PCO L1200	Step Dim	20%
53250299	WT198X LED19S/865 L1 W PCO L600	Wireless Dim	20%
53264999	WT198X LED26S/865 L1 W PCO L1200	Step Dim	20%
53269499	WT198X LED38S/865 L1 W PCO L1200	Step Dim	20%
53263299	WT198X LED57S/865 L1 W PCO L1500	Wireless Dim	20%
53252699	WT198X LED19S/840 L1 S PCO L600	Step Dim	20%
99467899	WT198C LED12S/840 PSU L600	Fixed	-
99468599	WT198C LED11S/840 PSU PCO L600	Fixed	-
99469299	WT198C LED20S/840 PSU L600	Fixed	-
99470899	WT198C LED18S/840 PSU PCO L600	Fixed	-
99471599	WT198X LED20S/840 WIA L600	Wireless Dim	-
53246599	WT198X LED27S/840 L1 S L1200	Wireless Dim	20%
51810099	WT198X LED40S/840 L1 S L1200	Wireless Dim	20%
53265699	WT198X LED27S/865 L1 S L1200	Wireless Dim	20%
51811799	WT198X LED40S/865 L1 S L1200	Step Dim	20%
53266399	WT198X LED26S/840 L1 S PCO L1200	Step Dim	20%
53259599	WT198X LED38S/840 L1 S PCO L1200	Wireless Dim	20%
53257199	WT198X LED26S/865 L1 S PCO L1200	Step Dim	20%
53235999	WT198X LED38S/865 L1 S PCO L1200	Wireless Dim	20%

## Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Housing Color	Ingress protection code
99473999	WT198C LED27S/840 PSU L1200	Polycarbonate	Grey	IP66
99474699	WT198C LED25S/840 PSU PCO L1200	Polycarbonate	Grey	IP66

Order Code	Full Product Name	Optical cover type	Housing Color	Ingress protection code
99479199	WT198C LED27S/865 PSU L1200	Polycarbonate	Grey	IP66
99480799	WT198C LED25S/865 PSU PCO L1200	Polycarbonate	Grey	IP66

## GreenPerform Waterproof G3

Order Code	Full Product Name	Optical cover type	Housing Color	Ingress protection code
99482199	WT198C LED40S/840 PSU L1200	Polycarbonate	Grey	IP66
99483899	WT198C LED37S/840 PSU PCO L1200	Polycarbonate	Grey	IP66
99488399	WT198C LED40S/865 PSU L1200	Polycarbonate	Grey	IP66
99489099	WT198C LED37S/865 PSU PCO L1200	Polycarbonate	Grey	IP66
99475399	WT198C LED27S/840 PSD L1200	Polycarbonate	Grey	IP66
99481499	WT198C LED27S/865 PSD L1200	Polycarbonate	Grey	IP66
99484599	WT198C LED40S/840 PSD L1200	Polycarbonate	Grey	IP66
99490699	WT198C LED40S/865 PSD L1200	Polycarbonate	Grey	IP66
99476099	WT198C LED27S/840 PSD Es L1200	Polycarbonate	Grey	IP66
99485299	WT198C LED40S/840 PSD Es L1200	Polycarbonate	Grey	IP66
99477799	WT198X LED27S/840 WIA L1200	Polycarbonate	Grey	IP66
99486999	WT198X LED40S/840 WIA L1200	Polycarbonate	Grey	IP66
99524899	WT198C HE LED27S/840 PSU L1200	Polycarbonate	Grey	IP66
99526299	WT198C HE LED27S/865 PSU L1200	Polycarbonate	Grey	IP66
99528699	WT198C HE LED40S/840 PSU L1200	Polycarbonate	Grey	IP66
99530999	WT198C HE LED40S/865 PSU L1200	Polycarbonate	Grey	IP66
99525599	WT198C HE LED27S/840 PSD L1200	Polycarbonate	Grey	IP66
99529399	WT198C HE LED40S/840 PSD L1200	Polycarbonate	Grey	IP66
99527999	WT198C HE LED27S/865 PSD L1200	Polycarbonate	Grey	IP66
99531699	WT198C HE LED40S/865 PSD L1200	Polycarbonate	Grey	IP66
99491399	WT198C LED60S/840 PSU L1200	Polycarbonate	Grey	IP66
99493799	WT198C LED57S/840 PSU PCO L1200	Polycarbonate	Grey	IP66
99495199	WT198C LED60S/840 PSD L1200	Polycarbonate	Grey	IP66
99500299	WT198C LED60S/865 PSU L1200	Polycarbonate	Grey	IP66
99502699	WT198C LED57S/865 PSU PCO L1200	Polycarbonate	Grey	IP66

Order Code	Full Product Name	Optical cover type	Housing Color	Ingress protection code
99504099	WT198C LED60S/865 PSD L1200	Polycarbonate	Grey	IP66
99472299	WT198X LED20S/840 DIA H4 L600	Polycarbonate	Grey	IP66
99492099	WT198C LED60S/840 PSU L1500	Polycarbonate	Grey	IP66
99494499	WT198C LED57S/840 PSU PCO L1500	Polycarbonate	Grey	IP66
99501999	WT198C LED60S/865 PSU L1500	Polycarbonate	Grey	IP66
99503399	WT198C LED57S/865 PSU PCO L1500	Polycarbonate	Grey	IP66
99506499	WT198C LED80S/840 PSU L1500	Polycarbonate	Grey	IP66
99507199	WT198C LED75S/840 PSU PCO L1500	Polycarbonate	Grey	IP66
99512599	WT198C LED80S/865 PSU L1500	Polycarbonate	Grey	IP66
99513299	WT198C LED75S/865 PSU PCO L1500	Polycarbonate	Grey	IP66
99515699	WT198C LED100S/840 PSU L1500	Polycarbonate	Grey	IP66
99516399	WT198C LED94S/840 PSU PCO L1500	Polycarbonate	Grey	IP66
99521799	WT198C LED100S/865 PSU L1500	Polycarbonate	Grey	IP66
99522499	WT198C LED94S/865 PSU PCO L1500	Polycarbonate	Grey	IP66
99496899	WT198C LED60S/840 PSD L1500	Polycarbonate	Grey	IP66
99505799	WT198C LED60S/865 PSD L1500	Polycarbonate	Grey	IP66
99508899	WT198C LED80S/840 PSD L1500	Polycarbonate	Grey	IP66
99514999	WT198C LED80S/865 PSD L1500	Polycarbonate	Grey	IP66
99517099	WT198C LED100S/840 PSD L1500	Polycarbonate	Grey	IP66
99523199	WT198C LED100S/865 PSD L1500	Polycarbonate	Grey	IP66
99497599	WT198C LED60S/840 PSD Es L1500	Polycarbonate	Grey	IP66
99509599	WT198C LED80S/840 PSD Es L1500	Polycarbonate	Grey	IP66
99518799	WT198C LED100S/840 PSD Es L1500	Polycarbonate	Grey	IP66
99498299	WT198X LED60S/840 WIA L1500	Polycarbonate	Grey	IP66
99510199	WT198X LED80S/840 WIA L1500	Polycarbonate	Grey	IP66

## GreenPerform Waterproof G3

Order Code	Full Product Name	Optical cover type	Housing Color	Ingress protection code
99519499	WT198X LED100S/840 WIA L1500	Polycarbonate	Grey	IP66
99532399	WT198C HE LED60S/840 PSU L1500	Polycarbonate	Grey	IP66
99534799	WT198C HE LED60S/865 PSU L1500	Polycarbonate	Grey	IP66
99536199	WT198C HE LED80S/840 PSU L1500	Polycarbonate	Grey	IP66
99538599	WT198C HE LED80S/865 PSU L1500	Polycarbonate	Grey	IP66
99540899	WT198C HE LED100S/840 PSU L1500	Polycarbonate	Grey	IP66
99542299	WT198C HE LED100S/865 PSU L1500	Polycarbonate	Grey	IP66
99533099	WT198C HE LED60S/840 PSD L1500	Polycarbonate	Grey	IP66
99537899	WT198C HE LED80S/840 PSD L1500	Polycarbonate	Grey	IP66
99541599	WT198C HE LED100S/840 PSD L1500	Polycarbonate	Grey	IP66
99535499	WT198C HE LED60S/865 PSD L1500	Polycarbonate	Grey	IP66
99539299	WT198C HE LED80S/865 PSD L1500	Polycarbonate	Grey	IP66
99543999	WT198C HE LED100S/865 PSD L1500	Polycarbonate	Grey	IP66
99478499	WT198X LED27S/840 DIA H4 L1200	Polycarbonate	Grey	IP66
99487699	WT198X LED40S/840 DIA H4 L1200	Polycarbonate	Grey	IP66
99499999	WT198X LED60S/840 DIA H4 L1500	Polycarbonate	Grey	IP66
99511899	WT198X LED80S/840 DIA H4 L1500	Polycarbonate	Grey	IP66
53260199	WT198X LED20S/840 L1 W L600	Polycarbonate bowl/cover	Gray	IP65
98248499	WT198X LED40S/840 L1 W L1200	Polycarbonate bowl/cover	Gray	IP65
53236699	WT198X LED60S/840 L1 W L1500	Polycarbonate bowl/cover	Gray	IP65
53261899	WT198X LED20S/865 L1 W L600	Polycarbonate bowl/cover	Gray	IP65
53243499	WT198X LED27S/865 L1 W L1200	Polycarbonate bowl/cover	Gray	IP65
53258899	WT198X LED40S/865 L1 W L1200	Polycarbonate bowl/cover	Gray	IP65
53256499	WT198X LED82S/865 L1 W L1500	Polycarbonate bowl/cover	Gray	IP65
53238099	WT198X LED20S/840 L1 S L600	Polycarbonate bowl/cover	Gray	IP65

Order Code	Full Product Name	Optical cover type	Housing Color	Ingress protection code
98249199	WT198X LED60S/840 L1 S L1500	Polycarbonate bowl/cover	Gray	IP65
53234299	WT198X LED82S/840 L1 S L1500	Polycarbonate bowl/cover	Gray	IP65
53251999	WT198X LED20S/865 L1 S L600	Polycarbonate bowl/cover	Gray	IP65
53247299	WT198X LED82S/865 L1 S L1500	Polycarbonate bowl/cover	Gray	IP65
53249699	WT198X LED19S/840 L1 W PCO L600	Polycarbonate bowl/cover	Gray	IP65
53254099	WT198X LED26S/840 L1 W PCO L1200	Polycarbonate bowl/cover	Gray	IP65
53268799	WT198X LED38S/840 L1 W PCO L1200	Polycarbonate bowl/cover	Gray	IP65
53250299	WT198X LED19S/865 L1 W PCO L600	Polycarbonate bowl/cover	Gray	IP65
53264999	WT198X LED26S/865 L1 W PCO L1200	Polycarbonate bowl/cover	Gray	IP65
53269499	WT198X LED38S/865 L1 W PCO L1200	Polycarbonate bowl/cover	Gray	IP65
53263299	WT198X LED57S/865 L1 W PCO L1500	Polycarbonate bowl/cover	Gray	IP65
53252699	WT198X LED19S/840 L1 S PCO L600	Polycarbonate bowl/cover	Gray	IP65
99467899	WT198C LED12S/840 PSU L600	Polycarbonate	Grey	IP66
99468599	WT198C LED11S/840 PSU PCO L600	Polycarbonate	Grey	IP66
99469299	WT198C LED20S/840 PSU L600	Polycarbonate	Grey	IP66
99470899	WT198C LED18S/840 PSU PCO L600	Polycarbonate	Grey	IP66
99471599	WT198X LED20S/840 WIA L600	Polycarbonate	Grey	IP66
53246599	WT198X LED27S/840 L1 S L1200	Polycarbonate bowl/cover	Gray	IP65
51810099	WT198X LED40S/840 L1 S L1200	Polycarbonate bowl/cover	Gray	IP65
53265699	WT198X LED27S/865 L1 S L1200	Polycarbonate bowl/cover	Gray	IP65
51811799	WT198X LED40S/865 L1 S L1200	Polycarbonate bowl/cover	Gray	IP65
53266399	WT198X LED26S/840 L1 S PCO L1200	Polycarbonate bowl/cover	Gray	IP65
53259599	WT198X LED38S/840 L1 S PCO L1200	Polycarbonate bowl/cover	Gray	IP65
53257199	WT198X LED26S/865 L1 S PCO L1200	Polycarbonate bowl/cover	Gray	IP65
53235999	WT198X LED38S/865 L1 S PCO L1200	Polycarbonate bowl/cover	Gray	IP65

# GreenPerform Waterproof G3

## Approval and Application

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
99473999	WT198C LED27S/840 PSU L1200	-30 to +50 °C	-
99474699	WT198C LED25S/840 PSU PCO L1200	-30 to +50 °C	-
99479199	WT198C LED27S/865 PSU L1200	-30 to +50 °C	-
99480799	WT198C LED25S/865 PSU PCO L1200	-30 to +50 °C	-
99482199	WT198C LED40S/840 PSU L1200	-30 to +50 °C	-
99483899	WT198C LED37S/840 PSU PCO L1200	-30 to +50 °C	-
99488399	WT198C LED40S/865 PSU L1200	-30 to +50 °C	-
99489099	WT198C LED37S/865 PSU PCO L1200	-30 to +50 °C	-
99475399	WT198C LED27S/840 PSD L1200	-25 to +45 °C	-
99481499	WT198C LED27S/865 PSD L1200	-25 to +45 °C	-
99484599	WT198C LED40S/840 PSD L1200	-25 to +40 °C	-
99490699	WT198C LED40S/865 PSD L1200	-25 to +40 °C	-
99476099	WT198C LED27S/840 PSD Es L1200	-30 to +60 °C	-
99485299	WT198C LED40S/840 PSD Es L1200	-30 to +60 °C	-
99477799	WT198X LED27S/840 WIA L1200	-25 to +45 °C	-
99486999	WT198X LED40S/840 WIA L1200	-25 to +40 °C	-
99524899	WT198C HE LED27S/840 PSU L1200	-30 to +50 °C	-
99526299	WT198C HE LED27S/865 PSU L1200	-30 to +50 °C	-
99528699	WT198C HE LED40S/840 PSU L1200	-30 to +50 °C	-
99530999	WT198C HE LED40S/865 PSU L1200	-30 to +50 °C	-
99525599	WT198C HE LED27S/840 PSD L1200	-25 to +45 °C	-
99529399	WT198C HE LED40S/840 PSD L1200	-25 to +40 °C	-
99527999	WT198C HE LED27S/865 PSD L1200	-25 to +45 °C	-
99531699	WT198C HE LED40S/865 PSD L1200	-25 to +40 °C	-
99491399	WT198C LED60S/840 PSU L1200	-30 to +50 °C	-

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
99493799	WT198C LED57S/840 PSU PCO L1200	-30 to +50 °C	-
99495199	WT198C LED60S/840 PSD L1200	-25 °C to 50 °C	-
99500299	WT198C LED60S/865 PSU L1200	-30 to +50 °C	-
99502699	WT198C LED57S/865 PSU PCO L1200	-30 to +50 °C	-
99504099	WT198C LED60S/865 PSD L1200	-25 °C to 50 °C	-
99472299	WT198X LED20S/840 DIA H4 L600	-25 to +45 °C	-
99492099	WT198C LED60S/840 PSU L1500	-30 to +50 °C	-
99494499	WT198C LED57S/840 PSU PCO L1500	-30 to +50 °C	-
99501999	WT198C LED60S/865 PSU L1500	-30 to +50 °C	-
99503399	WT198C LED57S/865 PSU PCO L1500	-30 to +50 °C	-
99506499	WT198C LED80S/840 PSU L1500	-30 to +50 °C	-
99507199	WT198C LED75S/840 PSU PCO L1500	-30 to +50 °C	-
99512599	WT198C LED80S/865 PSU L1500	-30 to +50 °C	-
99513299	WT198C LED75S/865 PSU PCO L1500	-30 to +50 °C	-
99515699	WT198C LED100S/840 PSU L1500	-30 to +45 °C	-
99516399	WT198C LED94S/840 PSU PCO L1500	-30 to +45 °C	-
99521799	WT198C LED100S/865 PSU L1500	-30 to +45 °C	-
99522499	WT198C LED94S/865 PSU PCO L1500	-30 to +45 °C	-
99496899	WT198C LED60S/840 PSD L1500	-25 to +40 °C	-
99505799	WT198C LED60S/865 PSD L1500	-25 to +40 °C	-
99508899	WT198C LED80S/840 PSD L1500	-25 to +40 °C	-
99514999	WT198C LED80S/865 PSD L1500	-25 to +40 °C	-
99517099	WT198C LED100S/840 PSD L1500	-25 to +40 °C	-
99523199	WT198C LED100S/865 PSD L1500	-25 to +40 °C	-
99497599	WT198C LED60S/840 PSD Es L1500	-30 to +60 °C	-

## GreenPerform Waterproof G3

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
99509599	WT198C LED80S/840 PSD Es L1500	-30 to +60 °C	-
99518799	WT198C LED100S/840 PSD Es L1500	-30 to +50 °C	-
99498299	WT198X LED60S/840 WIA L1500	-25 to +40 °C	-
99510199	WT198X LED80S/840 WIA L1500	-25 to +40 °C	-
99519499	WT198X LED100S/840 WIA L1500	-25 to +40 °C	-
99532399	WT198C HE LED60S/840 PSU L1500	-30 to +50 °C	-
99534799	WT198C HE LED60S/865 PSU L1500	-30 to +50 °C	-
99536199	WT198C HE LED80S/840 PSU L1500	-30 to +50 °C	-
99538599	WT198C HE LED80S/865 PSU L1500	-30 to +50 °C	-
99540899	WT198C HE LED100S/840 PSU L1500	-30 to +50 °C	-
99542299	WT198C HE LED100S/865 PSU L1500	-30 to +50 °C	-
99533099	WT198C HE LED60S/840 PSD L1500	-25 to +40 °C	-
99537899	WT198C HE LED80S/840 PSD L1500	-25 to +40 °C	-
99541599	WT198C HE LED100S/840 PSD L1500	-25 to +40 °C	-
99535499	WT198C HE LED60S/865 PSD L1500	-25 to +40 °C	-
99539299	WT198C HE LED80S/865 PSD L1500	-25 to +40 °C	-
99543999	WT198C HE LED100S/865 PSD L1500	-25 to +40 °C	-
99478499	WT198X LED27S/840 DIA H4 L1200	-25 to +45 °C	-
99487699	WT198X LED40S/840 DIA H4 L1200	-25 to +40 °C	-
99499999	WT198X LED60S/840 DIA H4 L1500	-25 to +40 °C	-
99511899	WT198X LED80S/840 DIA H4 L1500	-25 to +40 °C	-
53260199	WT198X LED20S/840 L1 W L600	-20 to +45 °C	Temperature 650 °C, duration 30 s
98248499	WT198X LED40S/840 L1 W L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
53236699	WT198X LED60S/840 L1 W L1500	-20 to +45 °C	Temperature 650 °C, duration 30 s
53261899	WT198X LED20S/865 L1 W L600	-20 to +45 °C	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
53243499	WT198X LED27S/865 L1 W L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
53258899	WT198X LED40S/865 L1 W L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
53256499	WT198X LED82S/865 L1 W L1500	-20 to +45 °C	Temperature 650 °C, duration 30 s
53238099	WT198X LED20S/840 L1 S L600	-20 to +45 °C	Temperature 650 °C, duration 30 s
98249199	WT198X LED60S/840 L1 S L1500	-20 to +45 °C	Temperature 650 °C, duration 30 s
53234299	WT198X LED82S/840 L1 S L1500	-20 to +45 °C	Temperature 650 °C, duration 30 s
53251999	WT198X LED20S/865 L1 S L600	-20 to +45 °C	Temperature 650 °C, duration 30 s
53247299	WT198X LED82S/865 L1 S L1500	-20 to +45 °C	Temperature 650 °C, duration 30 s
53249699	WT198X LED19S/840 L1 W PCO L600	-20 to +45 °C	Temperature 650 °C, duration 30 s
53254099	WT198X LED26S/840 L1 W PCO L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
53268799	WT198X LED38S/840 L1 W PCO L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
53250299	WT198X LED19S/865 L1 W PCO L600	-20 to +45 °C	Temperature 650 °C, duration 30 s
53264999	WT198X LED26S/865 L1 W PCO L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
53269499	WT198X LED38S/865 L1 W PCO L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
53263299	WT198X LED57S/865 L1 W PCO L1500	-20 to +45 °C	Temperature 650 °C, duration 30 s
53252699	WT198X LED19S/840 L1 S PCO L600	-20 to +45 °C	Temperature 650 °C, duration 30 s
99467899	WT198C LED12S/840 PSU L600	-30 to +60 °C	-
99468599	WT198C LED11S/840 PSU PCO L600	-30 to +60 °C	-
99469299	WT198C LED20S/840 PSU L600	-30 to +50 °C	-
99470899	WT198C LED18S/840 PSU PCO L600	-30 to +50 °C	-
99471599	WT198X LED20S/840 WIA L600	-25 to +45 °C	-
53246599	WT198X LED27S/840 L1 S L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
51810099	WT198X LED40S/840 L1 S L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
53265699	WT198X LED27S/865 L1 S L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
51811799	WT198X LED40S/865 L1 S L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s

## GreenPerform Waterproof G3

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
53266399	WT198X LED26S/840 L1 S PCO L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
53259599	WT198X LED38S/840 L1 S PCO L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
53257199	WT198X LED26S/865 L1 S PCO L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
53235999	WT198X LED38S/865 L1 S PCO L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s

### Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
99473999	WT198C LED27S/840 PSU L1200	-	-10%,+15%
99474699	WT198C LED25S/840 PSU PCO L1200	-	-10%,+15%
99479199	WT198C LED27S/865 PSU L1200	-	-10%,+15%
99480799	WT198C LED25S/865 PSU PCO L1200	-	-10%,+15%
99482199	WT198C LED40S/840 PSU L1200	-	-10%,+15%
99483899	WT198C LED37S/840 PSU PCO L1200	-	-10%,+15%
99488399	WT198C LED40S/865 PSU L1200	-	-10%,+15%
99489099	WT198C LED37S/865 PSU PCO L1200	-	-10%,+15%
99475399	WT198C LED27S/840 PSD L1200	-	-10%,+15%
99481499	WT198C LED27S/865 PSD L1200	-	-10%,+15%
99484599	WT198C LED40S/840 PSD L1200	-	-10%,+15%
99490699	WT198C LED40S/865 PSD L1200	-	-10%,+15%
99476099	WT198C LED27S/840 PSD Es L1200	-	-10%,+15%
99485299	WT198C LED40S/840 PSD Es L1200	-	-10%,+15%
99477799	WT198X LED27S/840 WIA L1200	-	-10%,+15%
99486999	WT198X LED40S/840 WIA L1200	-	-10%,+15%
99524899	WT198C HE LED27S/840 PSU L1200	-	-10%,+15%
99526299	WT198C HE LED27S/865 PSU L1200	-	-10%,+15%
99528699	WT198C HE LED40S/840 PSU L1200	-	-10%,+15%
99530999	WT198C HE LED40S/865 PSU L1200	-	-10%,+15%
99525599	WT198C HE LED27S/840 PSD L1200	-	-10%,+15%
99529399	WT198C HE LED40S/840 PSD L1200	-	-10%,+15%
99527999	WT198C HE LED27S/865 PSD L1200	-	-10%,+15%
99531699	WT198C HE LED40S/865 PSD L1200	-	-10%,+15%
99491399	WT198C LED60S/840 PSU L1200	-	-10%,+15%
99493799	WT198C LED57S/840 PSU PCO L1200	-	-10%,+15%
99495199	WT198C LED60S/840 PSD L1200	-	-10%,+15%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
99500299	WT198C LED60S/865 PSU L1200	-	-10%,+15%
99502699	WT198C LED57S/865 PSU PCO L1200	-	-10%,+15%
99504099	WT198C LED60S/865 PSD L1200	-	-10%,+15%
99472299	WT198X LED20S/840 DIA H4 L600	-	-10%,+15%
99492099	WT198C LED60S/840 PSU L1500	-	-10%,+15%
99494499	WT198C LED57S/840 PSU PCO L1500	-	-10%,+15%
99501999	WT198C LED60S/865 PSU L1500	-	-10%,+15%
99503399	WT198C LED57S/865 PSU PCO L1500	-	-10%,+15%
99506499	WT198C LED80S/840 PSU L1500	-	-10%,+15%
99507199	WT198C LED75S/840 PSU PCO L1500	-	-10%,+15%
99512599	WT198C LED80S/865 PSU L1500	-	-10%,+15%
99513299	WT198C LED75S/865 PSU PCO L1500	-	-10%,+15%
99515699	WT198C LED100S/840 PSU L1500	-	-10%,+15%
99516399	WT198C LED94S/840 PSU PCO L1500	-	-10%,+15%
99521799	WT198C LED100S/865 PSU L1500	-	-10%,+15%
99522499	WT198C LED94S/865 PSU PCO L1500	-	-10%,+15%
99496899	WT198C LED60S/840 PSD L1500	-	-10%,+15%
99505799	WT198C LED60S/865 PSD L1500	-	-10%,+15%
99508899	WT198C LED80S/840 PSD L1500	-	-10%,+15%
99514999	WT198C LED80S/865 PSD L1500	-	-10%,+15%
99517099	WT198C LED100S/840 PSD L1500	-	-10%,+15%
99523199	WT198C LED100S/865 PSD L1500	-	-10%,+15%
99497599	WT198C LED60S/840 PSD Es L1500	-	-10%,+15%
99509599	WT198C LED80S/840 PSD Es L1500	-	-10%,+15%
99518799	WT198C LED100S/840 PSD Es L1500	-	-10%,+15%
99498299	WT198X LED60S/840 WIA L1500	-	-10%,+15%
99510199	WT198X LED80S/840 WIA L1500	-	-10%,+15%
99519499	WT198X LED100S/840 WIA L1500	-	-10%,+15%
99532399	WT198C HE LED60S/840 PSU L1500	-	-10%,+15%

# GreenPerform Waterproof G3

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
99534799	WT198C HE LED60S/865 PSU L1500	-	-10%,+15%
99536199	WT198C HE LED80S/840 PSU L1500	-	-10%,+15%
99538599	WT198C HE LED80S/865 PSU L1500	-	-10%,+15%
99540899	WT198C HE LED100S/840 PSU L1500	-	-10%,+15%
99542299	WT198C HE LED100S/865 PSU L1500	-	-10%,+15%
99533099	WT198C HE LED60S/840 PSD L1500	-	-10%,+15%
99537899	WT198C HE LED80S/840 PSD L1500	-	-10%,+15%
99541599	WT198C HE LED100S/840 PSD L1500	-	-10%,+15%
99535499	WT198C HE LED60S/865 PSD L1500	-	-10%,+15%
99539299	WT198C HE LED80S/865 PSD L1500	-	-10%,+15%
99543999	WT198C HE LED100S/865 PSD L1500	-	-10%,+15%
99478499	WT198X LED27S/840 DIA H4 L1200	-	-10%,+15%
99487699	WT198X LED40S/840 DIA H4 L1200	-	-10%,+15%
99499999	WT198X LED60S/840 DIA H4 L1500	-	-10%,+15%
99511899	WT198X LED80S/840 DIA H4 L1500	-	-10%,+15%
53260199	WT198X LED20S/840 L1 W L600	(0.38, 0.38) SDCM≤3	-10% / +10%
98248499	WT198X LED40S/840 L1 W L1200	(0.38, 0.38) SDCM≤3	-10% / +10%
53236699	WT198X LED60S/840 L1 W L1500	(0.38, 0.38) SDCM≤3	-10% / +10%
53261899	WT198X LED20S/865 L1 W L600	(0.32, 0.33) SDCM≤3	-10% / +10%
53243499	WT198X LED27S/865 L1 W L1200	(0.32, 0.33) SDCM≤3	-10% / +10%
53258899	WT198X LED40S/865 L1 W L1200	(0.32, 0.33) SDCM≤3	-10% / +10%
53256499	WT198X LED82S/865 L1 W L1500	(0.32, 0.33) SDCM≤3	-10% / +10%
53238099	WT198X LED20S/840 L1 S L600	(0.38, 0.38) SDCM≤3	-10% / +10%
98249199	WT198X LED60S/840 L1 S L1500	(0.38, 0.38) SDCM≤3	-10% / +10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
53234299	WT198X LED82S/840 L1 S L1500	(0.38, 0.38) SDCM≤3	-10% / +10%
53251999	WT198X LED20S/865 L1 S L600	(0.32, 0.33) SDCM≤3	-10% / +10%
53247299	WT198X LED82S/865 L1 S L1500	(0.32, 0.33) SDCM≤3	-10% / +10%
53249699	WT198X LED19S/840 L1 W L600	(0.38, 0.38) SDCM≤3	-10% / +10%
53254099	WT198X LED26S/840 L1 W L1200	(0.38, 0.38) SDCM≤3	-10% / +10%
53268799	WT198X LED38S/840 L1 W L1200	(0.38, 0.38) SDCM≤3	-10% / +10%
53250299	WT198X LED19S/865 L1 W L600	(0.32, 0.33) SDCM≤3	-10% / +10%
53264999	WT198X LED26S/865 L1 W L1200	(0.32, 0.33) SDCM≤3	-10% / +10%
53269499	WT198X LED38S/865 L1 W L1200	(0.32, 0.33) SDCM≤3	-10% / +10%
53263299	WT198X LED57S/865 L1 W L1500	(0.32, 0.33) SDCM≤3	-10% / +10%
53252699	WT198X LED19S/840 L1 S L600	(0.38, 0.38) SDCM≤3	-10% / +10%
99467899	WT198C LED12S/840 PSU L600	-	-10%,+15%
99468599	WT198C LED11S/840 PSU L600	-	-10%,+15%
99469299	WT198C LED20S/840 PSU L600	-	-10%,+15%
99470899	WT198C LED18S/840 PSU L600	-	-10%,+15%
99471599	WT198X LED20S/840 WIA L600	-	-10%,+15%
53246599	WT198X LED27S/840 L1 S L1200	(0.38, 0.38) SDCM≤3	-10% / +10%
51810099	WT198X LED40S/840 L1 S L1200	(0.38, 0.38) SDCM≤3	-10% / +10%
53265699	WT198X LED27S/865 L1 S L1200	(0.32, 0.33) SDCM≤3	-10% / +10%
51811799	WT198X LED40S/865 L1 S L1200	(0.32, 0.33) SDCM≤3	-10% / +10%
53266399	WT198X LED26S/840 L1 S L1200	(0.38, 0.38) SDCM≤3	-10% / +10%
53259599	WT198X LED38S/840 L1 S L1200	(0.38, 0.38) SDCM≤3	-10% / +10%
53257199	WT198X LED26S/865 L1 S L1200	(0.32, 0.33) SDCM≤3	-10% / +10%
53235999	WT198X LED38S/865 L1 S L1200	(0.32, 0.33) SDCM≤3	-10% / +10%

## GreenPerform Waterproof G3

