



GreenPerform Waterproof G3: A high-performance, energy-efficient waterproof batten

GreenPerform Waterproof G3

GreenPerform Waterproof G3 is a superb choice for hard-working applications. Not only does it provide excellent optical performance, it also delivers substantial energy saving. And because it works seamlessly with IoT software like Interact, it also offers the option of customization, convenience, and data-driven insights.

Benefits

- Excellent energy savings
- Reliable choice, long serviceability
- Suitable for extensive applications
- Interact software and platforms

Features

- Up to 181lm/W (HE), and 160lm/W (general)
- 100,000 hours L70B50 @25°C
- IP66/IK08
- Up to -30°C ~ +60°C working temp. (HT version)
- Works with Interact IoT software and platform
- Superior optics (WB & Opal), SDCM 3

GreenPerform Waterproof G3

Application

- Parking Garages
- Manufacturing
- Warehouses

Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP65 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

Specifications

Mounting type	Surface Suspended
Operating Temperature range	-30 to +50°C (@PSU)
Light Source	LED
Mains Voltage	220-240V / 50-60Hz
Dimming	PSD: DALI WIA: Wireless control, compatible with Interact Pro PSU: non-dimmable DIA: Dimmable via Dali, compatible with Interact
Control system input	DALI/Interact
Material	PC
Main color of the luminaire	RAL7035
Lumen maintenance at median useful life 50.000h	L90
Lumen maintenance at median useful life 100.000h	L70
Flicker / Pst / SVM	<3.2% / 0.5 / 0.4
Luminous flux	Up to 10000lm
Power consumption	8.1W to 62.5W

Luminaire efficacy	Up to 181lm/W
Correlated color temperature - CCT	4000K 6500K
Color Rendering index - CRI	81
Risk Group	RG0
Optical cover/lens material	PC
Optical cover/lens finish	Opal Clear
Protection Class IEC61140	Class I
Mechanical impact protection	IK08
Ingress protection	IP66
Driver replaceable	Yes
Overall height	76mm
Overall length	665mm 1215mm 1515mm
Overall width	80mm
Installation	Suspension Surface

Versions





GreenPerform Waterproof EcoSet



RTP-OF-GreenPerform-Waterproof-G3-WT198C

GreenPerform Waterproof G3

Dimensional drawing



Type	Dimension (mm)							Nr. Of Clips
	A	B	C	D	E min	E max	F	
L600		665			308	512		6
L1200	76	1215	80	38	538	1062	85	10
L1500		1515			838	1362		12

Light Technical

Color rendering index (CRI) 80

Operating and Electrical

Protection class IEC Safety class I

Input Voltage 220 to 240 V

Line Frequency 50 to 60 Hz

Mechanical and Housing

Mech. impact protection code IK08

Approval and Application

CE mark Yes

ENEC mark -

Flammability mark -

General Information

Order Code	Full Product Name	Driver included	Number of gear		Service tag
			Gear	units	
911401503947	WT198C LED27S/840 PSU L1200	-	-	-	-
911401504047	WT198C LED25S/840 PSU PCO L1200	-	-	-	-
911401504347	WT198C LED40S/840 PSU L1200	-	-	-	-
911401504447	WT198C LED37S/840 PSU PCO L1200	-	-	-	-
911401505947	WT198C LED27S/840 PSD L1200	-	-	-	-
911401506147	WT198C LED40S/840 PSD L1200	-	-	-	-
911401507547	WT198X LED27S/840 WIA L1200	-	-	-	-
911401507647	WT198X LED40S/840 WIA L1200	-	-	-	-
911401509547	WT198C HE LED27S/840 PSU L1200	-	-	-	-
911401509647	WT198C HE LED27S/865 PSU L1200	-	-	-	-
911401509747	WT198C HE LED40S/840 PSU L1200	-	-	-	-
911401509847	WT198C HE LED40S/865 PSU L1200	-	-	-	-
911401510547	WT198C HE LED27S/840 PSD L1200	-	-	-	-
911401510647	WT198C HE LED40S/840 PSD L1200	-	-	-	-
911401528247	WT198C HE LED27S/865 PSD L1200	-	-	-	-
911401528347	WT198C HE LED40S/865 PSD L1200	-	-	-	-
911401529047	WT198C LED60S/840 PSU L1200	-	-	-	-
911401529447	WT198C LED60S/865 PSU L1200	-	-	-	-
911401529547	WT198C LED57S/865 PSU PCO L1200	-	-	-	-
911401529647	WT198C LED60S/865 PSD L1200	-	-	-	-
911401504747	WT198C LED60S/840 PSU L1500	-	-	-	-
911401504847	WT198C LED57S/840 PSU PCO L1500	-	-	-	-
911401504947	WT198C LED60S/865 PSU L1500	-	-	-	-
911401505147	WT198C LED80S/840 PSU L1500	-	-	-	-

Order Code	Full Product Name	Driver included	Number of gear		Service tag
			Gear	units	
911401505247	WT198C LED75S/840 PSU PCO L1500	-	-	-	-
911401505347	WT198C LED80S/865 PSU L1500	-	-	-	-
911401506347	WT198C LED60S/840 PSD L1500	-	-	-	-
911401506547	WT198C LED80S/840 PSD L1500	-	-	-	-
911401507747	WT198X LED60S/840 WIA L1500	-	-	-	-
911401507847	WT198X LED80S/840 WIA L1500	-	-	-	-
911401509947	WT198C HE LED60S/840 PSU L1500	-	-	-	-
911401510047	WT198C HE LED60S/865 PSU L1500	-	-	-	-
911401510147	WT198C HE LED80S/840 PSU L1500	-	-	-	-
911401510247	WT198C HE LED80S/865 PSU L1500	-	-	-	-
911401510347	WT198C HE LED100S/840 PSU L1500	-	-	-	-
911401510447	WT198C HE LED100S/865 PSU L1500	-	-	-	-
911401510747	WT198C HE LED60S/840 PSD L1500	-	-	-	-
911401510847	WT198C HE LED80S/840 PSD L1500	-	-	-	-
911401510947	WT198C HE LED100S/840 PSD L1500	-	-	-	-
911401528447	WT198C HE LED60S/865 PSD L1500	-	-	-	-
911401528547	WT198C HE LED80S/865 PSD L1500	-	-	-	-
911401528647	WT198C HE LED100S/865 PSD L1500	-	-	-	-
911401551502	WT198X LED20S/840 L1 W L600	Yes	EB	1 unit	Yes
911401551702	WT198X LED40S/840 L1 W L1200	Yes	EB	1 unit	Yes
911401551802	WT198X LED60S/840 L1 W L1500	Yes	EB	1 unit	Yes
911401552002	WT198X LED20S/865 L1 W L600	Yes	EB	1 unit	Yes
911401552102	WT198X LED27S/865 L1 W L1200	Yes	EB	1 unit	Yes
911401552202	WT198X LED40S/865 L1 W L1200	Yes	EB	1 unit	Yes
911401552402	WT198X LED82S/865 L1 W L1500	Yes	EB	1 unit	Yes
911401552502	WT198X LED19S/840 L1 W PCO L600	Yes	EB	1 unit	Yes
911401552602	WT198X LED26S/840 L1 W PCO L1200	Yes	EB	1 unit	Yes
911401552702	WT198X LED38S/840 L1 W PCO L1200	Yes	EB	1 unit	Yes
911401553002	WT198X LED19S/865 L1 W PCO L600	Yes	EB	1 unit	Yes
911401553102	WT198X LED26S/865 L1 W PCO L1200	Yes	EB	1 unit	Yes
911401553202	WT198X LED38S/865 L1 W PCO L1200	Yes	EB	1 unit	Yes
911401553302	WT198X LED57S/865 L1 W PCO L1500	Yes	EB	1 unit	Yes
911401503747	WT198C LED20S/840 PSU L600	-	-	-	-
911401503847	WT198C LED18S/840 PSU PCO L600	-	-	-	-
911401507447	WT198X LED20S/840 WIA L600	-	-	-	-
911401571191	WT198X LED27S/840 L1 S L1200	Yes	EB	1 unit	Yes
911401571291	WT198X LED40S/840 L1 S L1200	Yes	EB	1 unit	Yes
911401571691	WT198X LED27S/865 L1 S L1200	Yes	EB	1 unit	Yes
911401571791	WT198X LED40S/865 L1 S L1200	Yes	EB	1 unit	Yes
911401572191	WT198X LED26S/840 L1 S PCO L1200	Yes	EB	1 unit	Yes
911401572291	WT198X LED38S/840 L1 S PCO L1200	Yes	EB	1 unit	Yes
911401572691	WT198X LED26S/865 L1 S PCO L1200	Yes	EB	1 unit	Yes
911401572791	WT198X LED38S/865 L1 S PCO L1200	Yes	EB	1 unit	Yes

Light Technical (1/2)

GreenPerform Waterproof G3

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401503947	WT198C LED27S/840 PSU L1200	115 degree(s)	4000 K	159 lm/W	2,700 lm
911401504047	WT198C LED25S/840 PSU PCO L1200	115 degree(s)	4000 K	150 lm/W	2,550 lm
911401504347	WT198C LED40S/840 PSU L1200	115 degree(s)	4000 K	160 lm/W	4,000 lm
911401504447	WT198C LED37S/840 PSU PCO L1200	115 degree(s)	4000 K	150 lm/W	3,750 lm
911401505947	WT198C LED27S/840 PSD L1200	115 degree(s)	4000 K	159 lm/W	2,700 lm
911401506147	WT198C LED40S/840 PSD L1200	115 degree(s)	4000 K	160 lm/W	4,000 lm
911401507547	WT198X LED27S/840 WIA L1200	115 degree(s)	4000 K	159 lm/W	2,700 lm
911401507647	WT198X LED40S/840 WIA L1200	115 degree(s)	4000 K	160 lm/W	4,000 lm
911401509547	WT198C HE LED27S/840 PSU L1200	115 degree(s)	4000 K	172 lm/W	2,700 lm
911401509647	WT198C HE LED27S/865 PSU L1200	115 degree(s)	6500 K	172 lm/W	2,700 lm
911401509747	WT198C HE LED40S/840 PSU L1200	115 degree(s)	4000 K	173 lm/W	4,000 lm
911401509847	WT198C HE LED40S/865 PSU L1200	115 degree(s)	6500 K	173 lm/W	4,000 lm
911401510547	WT198C HE LED27S/840 PSD L1200	115 degree(s)	4000 K	172 lm/W	2,700 lm
911401510647	WT198C HE LED40S/840 PSD L1200	115 degree(s)	4000 K	173 lm/W	4,000 lm
911401528247	WT198C HE LED27S/865 PSD L1200	115 degree(s)	6500 K	172 lm/W	2,700 lm
911401528347	WT198C HE LED40S/865 PSD L1200	115 degree(s)	6500 K	173 lm/W	4,000 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401529047	WT198C LED60S/840 PSU L1200	115 degree(s)	4000 K	156 lm/W	6,000 lm
911401529447	WT198C LED60S/865 PSU L1200	115 degree(s)	6500 K	156 lm/W	6,000 lm
911401529547	WT198C LED57S/865 PSU PCO L1200	115 degree(s)	6500 K	147 lm/W	5,650 lm
911401529647	WT198C LED60S/865 PSD L1200	115 degree(s)	6500 K	156 lm/W	6,000 lm
911401504747	WT198C LED60S/840 PSU L1500	115 degree(s)	4000 K	160 lm/W	6,000 lm
911401504847	WT198C LED57S/840 PSU PCO L1500	115 degree(s)	4000 K	151 lm/W	5,650 lm
911401504947	WT198C LED60S/865 PSU L1500	115 degree(s)	6500 K	160 lm/W	6,000 lm
911401505147	WT198C LED80S/840 PSU L1500	115 degree(s)	4000 K	160 lm/W	8,000 lm
911401505247	WT198C LED75S/840 PSU PCO L1500	115 degree(s)	4000 K	151 lm/W	7,550 lm
911401505347	WT198C LED80S/865 PSU L1500	115 degree(s)	6500 K	160 lm/W	8,000 lm
911401506347	WT198C LED60S/840 PSD L1500	115 degree(s)	4000 K	160 lm/W	6,000 lm
911401506547	WT198C LED80S/840 PSD L1500	115 degree(s)	4000 K	160 lm/W	8,000 lm
911401507747	WT198X LED60S/840 WIA L1500	115 degree(s)	4000 K	160 lm/W	6,000 lm
911401507847	WT198X LED80S/840 WIA L1500	115 degree(s)	4000 K	160 lm/W	8,000 lm
911401509947	WT198C HE LED60S/840 PSU L1500	115 degree(s)	4000 K	178 lm/W	6,000 lm
911401510047	WT198C HE LED60S/865 PSU L1500	115 degree(s)	6500 K	178 lm/W	6,000 lm

GreenPerform Waterproof G3

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401510147	WT198C HE LED80S/840 PSU L1500	115 degree(s)	4000 K	180 lm/W	8,000 lm
911401510247	WT198C HE LED80S/865 PSU L1500	115 degree(s)	6500 K	180 lm/W	8,000 lm
911401510347	WT198C HE LED100S/840 PSU L1500	115 degree(s)	4000 K	181 lm/W	10,000 lm
911401510447	WT198C HE LED100S/865 PSU L1500	115 degree(s)	6500 K	181 lm/W	10,000 lm
911401510747	WT198C HE LED60S/840 PSD L1500	115 degree(s)	4000 K	178 lm/W	6,000 lm
911401510847	WT198C HE LED80S/840 PSD L1500	115 degree(s)	4000 K	180 lm/W	8,000 lm
911401510947	WT198C HE LED100S/840 PSD L1500	115 degree(s)	4000 K	181 lm/W	10,000 lm
911401528447	WT198C HE LED60S/865 PSD L1500	115 degree(s)	6500 K	178 lm/W	6,000 lm
911401528547	WT198C HE LED80S/865 PSD L1500	115 degree(s)	6500 K	180 lm/W	8,000 lm
911401528647	WT198C HE LED100S/865 PSD L1500	115 degree(s)	6500 K	181 lm/W	10,000 lm
911401551502	WT198X LED20S/840 L1 W L600	-	4000 K	136.1 lm/W	2,000 lm
911401551702	WT198X LED40S/840 L1 W L1200	-	4000 K	138.4 lm/W	4,000 lm
911401551802	WT198X LED60S/840 L1 W L1500	-	4000 K	137.6 lm/W	6,000 lm
911401552002	WT198X LED20S/865 L1 W L600	-	6500 K	136.1 lm/W	2,000 lm
911401552102	WT198X LED27S/865 L1 W L1200	-	6500 K	143.6 lm/W	2,700 lm
911401552202	WT198X LED40S/865 L1 W L1200	-	6500 K	138.4 lm/W	4,000 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401552402	WT198X LED82S/865 L1 W L1500	-	6500 K	138.7 lm/W	8,200 lm
911401552502	WT198X LED19S/840 L1 W PCO L600	-	4000 K	129.3 lm/W	1,900 lm
911401552602	WT198X LED26S/840 L1 W PCO L1200	-	4000 K	138.3 lm/W	2,600 lm
911401552702	WT198X LED38S/840 L1 W PCO L1200	-	4000 K	131.5 lm/W	3,800 lm
911401553002	WT198X LED19S/865 L1 W PCO L600	-	6500 K	129.3 lm/W	1,900 lm
911401553102	WT198X LED26S/865 L1 W PCO L1200	-	6500 K	138.3 lm/W	2,600 lm
911401553202	WT198X LED38S/865 L1 W PCO L1200	-	6500 K	131.5 lm/W	3,800 lm
911401553302	WT198X LED57S/865 L1 W PCO L1500	-	6500 K	130.7 lm/W	5,700 lm
911401503747	WT198C LED20S/840 PSU L600	115 degree(s)	4000 K	154 lm/W	2,000 lm
911401503847	WT198C LED18S/840 PSU PCO L600	115 degree(s)	4000 K	142 lm/W	1,850 lm
911401507447	WT198X LED20S/840 WIA L600	115 degree(s)	4000 K	154 lm/W	2,000 lm
911401571191	WT198X LED27S/840 L1 S L1200	-	4000 K	143.6 lm/W	2,700 lm
911401571291	WT198X LED40S/840 L1 S L1200	-	4000 K	138.4 lm/W	4,000 lm
911401571691	WT198X LED27S/865 L1 S L1200	-	6500 K	143.6 lm/W	2,700 lm
911401571791	WT198X LED40S/865 L1 S L1200	-	6500 K	138.4 lm/W	4,000 lm
911401572191	WT198X LED26S/840 L1 S PCO L1200	-	4000 K	138.3 lm/W	2,600 lm

GreenPerform Waterproof G3

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature	Luminous Efficacy (rated)	Luminous Flux
			(Nom)	(Nom)	(Nom)
911401572291	WT198X LED38S/840 L1 S PCO L1200	-	4000 K	131.5 lm/W	3,800 lm
911401572691	WT198X LED26S/865 L1 S PCO L1200	-	6500 K	138.3 lm/W	2,600 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature	Luminous Efficacy (rated)	Luminous Flux
			(Nom)	(Nom)	(Nom)
911401572791	WT198X LED38S/865 L1 S PCO L1200	-	6500 K	131.5 lm/W	3,800 lm

Light Technical (2/2)

Order Code	Full Product Name	Number of light sources	Optic type
911401503947	WT198C LED27S/840 PSU L1200	-	Very wide beam
911401504047	WT198C LED25S/840 PSU PCO L1200	-	Opal
911401504347	WT198C LED40S/840 PSU L1200	-	Very wide beam
911401504447	WT198C LED37S/840 PSU PCO L1200	-	Opal
911401505947	WT198C LED27S/840 PSD L1200	-	Very wide beam
911401506147	WT198C LED40S/840 PSD L1200	-	Very wide beam
911401507547	WT198X LED27S/840 WIA L1200	-	Very wide beam
911401507647	WT198X LED40S/840 WIA L1200	-	Very wide beam
911401509547	WT198C HE LED27S/840 PSU L1200	-	Very wide beam
911401509647	WT198C HE LED27S/865 PSU L1200	-	Very wide beam
911401509747	WT198C HE LED40S/840 PSU L1200	-	Very wide beam
911401509847	WT198C HE LED40S/865 PSU L1200	-	Very wide beam
911401510547	WT198C HE LED27S/840 PSD L1200	-	Very wide beam
911401510647	WT198C HE LED40S/840 PSD L1200	-	Very wide beam
911401528247	WT198C HE LED27S/865 PSD L1200	-	Very wide beam
911401528347	WT198C HE LED40S/865 PSD L1200	-	Very wide beam
911401529047	WT198C LED60S/840 PSU L1200	-	Very wide beam
911401529447	WT198C LED60S/865 PSU L1200	-	Very wide beam
911401529547	WT198C LED57S/865 PSU PCO L1200	-	Very wide beam
911401529647	WT198C LED60S/865 PSD L1200	-	Very wide beam
911401504747	WT198C LED60S/840 PSU L1500	-	Very wide beam
911401504847	WT198C LED57S/840 PSU PCO L1500	-	Opal
911401504947	WT198C LED60S/865 PSU L1500	-	Very wide beam
911401505147	WT198C LED80S/840 PSU L1500	-	Very wide beam
911401505247	WT198C LED75S/840 PSU PCO L1500	-	Opal
911401505347	WT198C LED80S/865 PSU L1500	-	Very wide beam
911401506347	WT198C LED60S/840 PSD L1500	-	Very wide beam
911401506547	WT198C LED80S/840 PSD L1500	-	Very wide beam
911401507747	WT198X LED60S/840 WIA L1500	-	Very wide beam
911401507847	WT198X LED80S/840 WIA L1500	-	Very wide beam
911401509947	WT198C HE LED60S/840 PSU L1500	-	Very wide beam
911401510047	WT198C HE LED60S/865 PSU L1500	-	Very wide beam
911401510147	WT198C HE LED80S/840 PSU L1500	-	Very wide beam
911401510247	WT198C HE LED80S/865 PSU L1500	-	Very wide beam

Order Code	Full Product Name	Number of light sources	Optic type
911401510347	WT198C HE LED100S/840 PSU L1500	-	Very wide beam
911401510447	WT198C HE LED100S/865 PSU L1500	-	Very wide beam
911401510747	WT198C HE LED60S/840 PSD L1500	-	Very wide beam
911401510847	WT198C HE LED80S/840 PSD L1500	-	Very wide beam
911401510947	WT198C HE LED100S/840 PSD L1500	-	Very wide beam
911401528447	WT198C HE LED60S/865 PSD L1500	-	Very wide beam
911401528547	WT198C HE LED80S/865 PSD L1500	-	Very wide beam
911401528647	WT198C HE LED100S/865 PSD L1500	-	Very wide beam
911401551502	WT198X LED20S/840 L1 W L600	1	-
911401551702	WT198X LED40S/840 L1 W L1200	1	-
911401551802	WT198X LED60S/840 L1 W L1500	1	-
911401552002	WT198X LED20S/865 L1 W L600	1	-
911401552102	WT198X LED27S/865 L1 W L1200	1	-
911401552202	WT198X LED40S/865 L1 W L1200	1	-
911401552402	WT198X LED82S/865 L1 W L1500	1	-
911401552502	WT198X LED19S/840 L1 W PCO L600	1	-
911401552602	WT198X LED26S/840 L1 W PCO L1200	1	-
911401552702	WT198X LED38S/840 L1 W PCO L1200	1	-
911401553002	WT198X LED19S/865 L1 W PCO L600	1	-
911401553102	WT198X LED26S/865 L1 W PCO L1200	1	-
911401553202	WT198X LED38S/865 L1 W PCO L1200	1	-
911401553302	WT198X LED57S/865 L1 W PCO L1500	1	-
911401503747	WT198C LED20S/840 PSU L600	-	Very wide beam
911401503847	WT198C LED18S/840 PSU PCO L600	-	Opal
911401507447	WT198X LED20S/840 WIA L600	-	Very wide beam
911401571191	WT198X LED27S/840 L1 S L1200	1	-
911401571291	WT198X LED40S/840 L1 S L1200	1	-
911401571691	WT198X LED27S/865 L1 S L1200	1	-
911401571791	WT198X LED40S/865 L1 S L1200	1	-
911401572191	WT198X LED26S/840 L1 S PCO L1200	1	-
911401572291	WT198X LED38S/840 L1 S PCO L1200	1	-
911401572691	WT198X LED26S/865 L1 S PCO L1200	1	-
911401572791	WT198X LED38S/865 L1 S PCO L1200	1	-

Operating and Electrical

GreenPerform Waterproof G3

Order Code	Full Product Name	Power Consumption	Suitable for random switching
911401503947	WT198C LED27S/840 PSU L1200	17 W	-
911401504047	WT198C LED25S/840 PSU PCO L1200	17 W	-
911401504347	WT198C LED40S/840 PSU L1200	25 W	-
911401504447	WT198C LED37S/840 PSU PCO L1200	25 W	-
911401505947	WT198C LED27S/840 PSD L1200	17 W	-
911401506147	WT198C LED40S/840 PSD L1200	25 W	-
911401507547	WT198X LED27S/840 WIA L1200	17 W	-
911401507647	WT198X LED40S/840 WIA L1200	25 W	-
911401509547	WT198C HE LED27S/840 PSU L1200	15.7 W	-
911401509647	WT198C HE LED27S/865 PSU L1200	15.7 W	-
911401509747	WT198C HE LED40S/840 PSU L1200	23.1 W	-
911401509847	WT198C HE LED40S/865 PSU L1200	23.1 W	-
911401510547	WT198C HE LED27S/840 PSD L1200	15.7 W	-
911401510647	WT198C HE LED40S/840 PSD L1200	23.1 W	-
911401528247	WT198C HE LED27S/865 PSD L1200	15.7 W	-
911401528347	WT198C HE LED40S/865 PSD L1200	23.1 W	-
911401529047	WT198C LED60S/840 PSU L1200	38.4 W	-
911401529447	WT198C LED60S/865 PSU L1200	38.4 W	-
911401529547	WT198C LED57S/865 PSU PCO L1200	38.4 W	-
911401529647	WT198C LED60S/865 PSD L1200	38.4 W	-
911401504747	WT198C LED60S/840 PSU L1500	37.5 W	-
911401504847	WT198C LED57S/840 PSU PCO L1500	37.5 W	-
911401504947	WT198C LED60S/865 PSU L1500	37.5 W	-
911401505147	WT198C LED80S/840 PSU L1500	50 W	-
911401505247	WT198C LED75S/840 PSU PCO L1500	50 W	-
911401505347	WT198C LED80S/865 PSU L1500	50 W	-
911401506347	WT198C LED60S/840 PSD L1500	37.5 W	-
911401506547	WT198C LED80S/840 PSD L1500	50 W	-
911401507747	WT198X LED60S/840 WIA L1500	37.5 W	-
911401507847	WT198X LED80S/840 WIA L1500	50 W	-
911401509947	WT198C HE LED60S/840 PSU L1500	33.8 W	-
911401510047	WT198C HE LED60S/865 PSU L1500	33.8 W	-
911401510147	WT198C HE LED80S/840 PSU L1500	44.4 W	-

Order Code	Full Product Name	Power Consumption	Suitable for random switching
911401510247	WT198C HE LED80S/865 PSU L1500	44.4 W	-
911401510347	WT198C HE LED100S/840 PSU L1500	55.1 W	-
911401510447	WT198C HE LED100S/865 PSU L1500	55.1 W	-
911401510747	WT198C HE LED60S/840 PSD L1500	33.8 W	-
911401510847	WT198C HE LED80S/840 PSD L1500	44.4 W	-
911401510947	WT198C HE LED100S/840 PSD L1500	55.1 W	-
911401528447	WT198C HE LED60S/865 PSD L1500	33.8 W	-
911401528547	WT198C HE LED80S/865 PSD L1500	44.4 W	-
911401528647	WT198C HE LED100S/865 PSD L1500	55.1 W	-
911401551502	WT198X LED20S/840 L1 W L600	14.7 W	Yes
911401551702	WT198X LED40S/840 L1 W L1200	28.9 W	Yes
911401551802	WT198X LED60S/840 L1 W L1500	43.6 W	Yes
911401552002	WT198X LED20S/865 L1 W L600	14.7 W	Yes
911401552102	WT198X LED27S/865 L1 W L1200	18.8 W	Yes
911401552202	WT198X LED40S/865 L1 W L1200	28.9 W	Yes
911401552402	WT198X LED82S/865 L1 W L1500	59.1 W	Yes
911401552502	WT198X LED19S/840 L1 W PCO L600	14.7 W	Yes
911401552602	WT198X LED26S/840 L1 W PCO L1200	18.8 W	Yes
911401552702	WT198X LED38S/840 L1 W PCO L1200	28.9 W	Yes
911401553002	WT198X LED19S/865 L1 W PCO L600	14.7 W	Yes
911401553102	WT198X LED26S/865 L1 W PCO L1200	18.8 W	Yes
911401553202	WT198X LED38S/865 L1 W PCO L1200	28.9 W	Yes
911401553302	WT198X LED57S/865 L1 W PCO L1500	43.6 W	Yes
911401503747	WT198C LED20S/840 PSU L600	13 W	-
911401503847	WT198C LED18S/840 PSU PCO L600	13 W	-
911401507447	WT198X LED20S/840 WIA L600	13 W	-
911401571191	WT198X LED27S/840 L1 S L1200	18.8 W	Yes
911401571291	WT198X LED40S/840 L1 S L1200	28.9 W	Yes
911401571691	WT198X LED27S/865 L1 S L1200	18.8 W	Yes
911401571791	WT198X LED40S/865 L1 S L1200	28.9 W	Yes
911401572191	WT198X LED26S/840 L1 S PCO L1200	18.8 W	Yes

GreenPerform Waterproof G3

Order Code	Full Product Name	Power Consumption	Suitable for random switching
911401572291	WT198X LED38S/840 L1 S PCO L1200	28.9 W	Yes
911401572691	WT198X LED26S/865 L1 S PCO L1200	18.8 W	Yes

Order Code	Full Product Name	Power Consumption	Suitable for random switching
911401572791	WT198X LED38S/865 L1 S PCO L1200	28.9 W	Yes

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
911401503947	WT198C LED27S/840 PSU L1200	Fixed	-
911401504047	WT198C LED25S/840 PSU PCO L1200	Fixed	-
911401504347	WT198C LED40S/840 PSU L1200	Fixed	-
911401504447	WT198C LED37S/840 PSU PCO L1200	Fixed	-
911401505947	WT198C LED27S/840 PSD L1200	DALI	-
911401506147	WT198C LED40S/840 PSD L1200	DALI	-
911401507547	WT198X LED27S/840 WIA L1200	Wireless Dim	-
911401507647	WT198X LED40S/840 WIA L1200	Wireless Dim	-
911401509547	WT198C HE LED27S/840 PSU L1200	Fixed	-
911401509647	WT198C HE LED27S/865 PSU L1200	Fixed	-
911401509747	WT198C HE LED40S/840 PSU L1200	Fixed	-
911401509847	WT198C HE LED40S/865 PSU L1200	Fixed	-
911401510547	WT198C HE LED27S/840 PSD L1200	DALI	-
911401510647	WT198C HE LED40S/840 PSD L1200	DALI	-
911401528247	WT198C HE LED27S/865 PSD L1200	DALI	-
911401528347	WT198C HE LED40S/865 PSD L1200	DALI	-
911401529047	WT198C LED60S/840 PSU L1200	Fixed	-
911401529447	WT198C LED60S/865 PSU L1200	Fixed	-
911401529547	WT198C LED57S/865 PSU PCO L1200	Fixed	-
911401529647	WT198C LED60S/865 PSD L1200	DALI	-
911401504747	WT198C LED60S/840 PSU L1500	Fixed	-
911401504847	WT198C LED57S/840 PSU PCO L1500	Fixed	-
911401504947	WT198C LED60S/865 PSU L1500	Fixed	-
911401505147	WT198C LED80S/840 PSU L1500	Fixed	-
911401505247	WT198C LED75S/840 PSU PCO L1500	Fixed	-
911401505347	WT198C LED80S/865 PSU L1500	Fixed	-
911401506347	WT198C LED60S/840 PSD L1500	DALI	-
911401506547	WT198C LED80S/840 PSD L1500	DALI	-
911401507747	WT198X LED60S/840 WIA L1500	Wireless Dim	-
911401507847	WT198X LED80S/840 WIA L1500	Wireless Dim	-
911401509947	WT198C HE LED60S/840 PSU L1500	Fixed	-
911401510047	WT198C HE LED60S/865 PSU L1500	Fixed	-
911401510147	WT198C HE LED80S/840 PSU L1500	Fixed	-
911401510247	WT198C HE LED80S/865 PSU L1500	Fixed	-

Order Code	Full Product Name	Dimmable	Maximum dim level
911401510347	WT198C HE LED100S/840 PSU L1500	Fixed	-
911401510447	WT198C HE LED100S/865 PSU L1500	Fixed	-
911401510747	WT198C HE LED60S/840 PSD L1500	DALI	-
911401510847	WT198C HE LED80S/840 PSD L1500	DALI	-
911401510947	WT198C HE LED100S/840 PSD L1500	DALI	-
911401528447	WT198C HE LED60S/865 PSD L1500	DALI	-
911401528547	WT198C HE LED80S/865 PSD L1500	DALI	-
911401528647	WT198C HE LED100S/865 PSD L1500	DALI	-
911401551502	WT198X LED20S/840 L1 W L600	Wireless Dim	20%
911401551702	WT198X LED40S/840 L1 W L1200	Step Dim	20%
911401551802	WT198X LED60S/840 L1 W L1500	Wireless Dim	20%
911401552002	WT198X LED20S/865 L1 W L600	Wireless Dim	20%
911401552102	WT198X LED27S/865 L1 W L1200	Step Dim	20%
911401552202	WT198X LED40S/865 L1 W L1200	Wireless Dim	20%
911401552402	WT198X LED82S/865 L1 W L1500	Step Dim	20%
911401552502	WT198X LED19S/840 L1 W PCO L600	Wireless Dim	20%
911401552602	WT198X LED26S/840 L1 W PCO L1200	Wireless Dim	20%
911401552702	WT198X LED38S/840 L1 W PCO L1200	Step Dim	20%
911401553002	WT198X LED19S/865 L1 W PCO L600	Wireless Dim	20%
911401553102	WT198X LED26S/865 L1 W PCO L1200	Step Dim	20%
911401553202	WT198X LED38S/865 L1 W PCO L1200	Step Dim	20%
911401553302	WT198X LED57S/865 L1 W PCO L1500	Wireless Dim	20%
911401503747	WT198C LED20S/840 PSU L600	Fixed	-
911401503847	WT198C LED18S/840 PSU PCO L600	Fixed	-
911401507447	WT198X LED20S/840 WIA L600	Wireless Dim	-
911401571191	WT198X LED27S/840 L1 S L1200	Wireless Dim	20%
911401571291	WT198X LED40S/840 L1 S L1200	Wireless Dim	20%
911401571691	WT198X LED27S/865 L1 S L1200	Wireless Dim	20%
911401571791	WT198X LED40S/865 L1 S L1200	Step Dim	20%
911401572191	WT198X LED26S/840 L1 S PCO L1200	Step Dim	20%
911401572291	WT198X LED38S/840 L1 S PCO L1200	Wireless Dim	20%
911401572691	WT198X LED26S/865 L1 S PCO L1200	Step Dim	20%
911401572791	WT198X LED38S/865 L1 S PCO L1200	Wireless Dim	20%

Mechanical and Housing

GreenPerform Waterproof G3

Order Code	Full Product Name	Optical cover type	Housing Color	Ingress protection code
911401503947	WT198C LED27S/840 PSU L1200	Polycarbonate	Grey	IP66
911401504047	WT198C LED25S/840 PSU PCO L1200	Polycarbonate	Grey	IP66
911401504347	WT198C LED40S/840 PSU L1200	Polycarbonate	Grey	IP66
911401504447	WT198C LED37S/840 PSU PCO L1200	Polycarbonate	Grey	IP66
911401505947	WT198C LED27S/840 PSD L1200	Polycarbonate	Grey	IP66
911401506147	WT198C LED40S/840 PSD L1200	Polycarbonate	Grey	IP66
911401507547	WT198X LED27S/840 WIA L1200	Polycarbonate	Grey	IP66
911401507647	WT198X LED40S/840 WIA L1200	Polycarbonate	Grey	IP66
911401509547	WT198C HE LED27S/840 PSU L1200	Polycarbonate	Grey	IP66
911401509647	WT198C HE LED27S/865 PSU L1200	Polycarbonate	Grey	IP66
911401509747	WT198C HE LED40S/840 PSU L1200	Polycarbonate	Grey	IP66
911401509847	WT198C HE LED40S/865 PSU L1200	Polycarbonate	Grey	IP66
911401510547	WT198C HE LED27S/840 PSD L1200	Polycarbonate	Grey	IP66
911401510647	WT198C HE LED40S/840 PSD L1200	Polycarbonate	Grey	IP66
911401528247	WT198C HE LED27S/865 PSD L1200	Polycarbonate	Grey	IP66
911401528347	WT198C HE LED40S/865 PSD L1200	Polycarbonate	Grey	IP66
911401529047	WT198C LED60S/840 PSU L1200	Polycarbonate	Grey	IP66
911401529447	WT198C LED60S/865 PSU L1200	Polycarbonate	Grey	IP66
911401529547	WT198C LED57S/865 PSU PCO L1200	Polycarbonate	Grey	IP66
911401529647	WT198C LED60S/865 PSD L1200	Polycarbonate	Grey	IP66
911401504747	WT198C LED60S/840 PSU L1500	Polycarbonate	Grey	IP66
911401504847	WT198C LED57S/840 PSU PCO L1500	Polycarbonate	Grey	IP66
911401504947	WT198C LED60S/865 PSU L1500	Polycarbonate	Grey	IP66
911401505147	WT198C LED80S/840 PSU L1500	Polycarbonate	Grey	IP66
911401505247	WT198C LED75S/840 PSU PCO L1500	Polycarbonate	Grey	IP66

Order Code	Full Product Name	Optical cover type	Housing Color	Ingress protection code
911401505347	WT198C LED80S/865 PSU L1500	Polycarbonate	Grey	IP66
911401506347	WT198C LED60S/840 PSD L1500	Polycarbonate	Grey	IP66
911401506547	WT198C LED80S/840 PSD L1500	Polycarbonate	Grey	IP66
911401507747	WT198X LED60S/840 WIA L1500	Polycarbonate	Grey	IP66
911401507847	WT198X LED80S/840 WIA L1500	Polycarbonate	Grey	IP66
911401509947	WT198C HE LED60S/840 PSU L1500	Polycarbonate	Grey	IP66
911401510047	WT198C HE LED60S/865 PSU L1500	Polycarbonate	Grey	IP66
911401510147	WT198C HE LED80S/840 PSU L1500	Polycarbonate	Grey	IP66
911401510247	WT198C HE LED80S/865 PSU L1500	Polycarbonate	Grey	IP66
911401510347	WT198C HE LED100S/840 PSU L1500	Polycarbonate	Grey	IP66
911401510447	WT198C HE LED100S/865 PSU L1500	Polycarbonate	Grey	IP66
911401510747	WT198C HE LED60S/840 PSD L1500	Polycarbonate	Grey	IP66
911401510847	WT198C HE LED80S/840 PSD L1500	Polycarbonate	Grey	IP66
911401510947	WT198C HE LED100S/840 PSD L1500	Polycarbonate	Grey	IP66
911401528447	WT198C HE LED60S/865 PSD L1500	Polycarbonate	Grey	IP66
911401528547	WT198C HE LED80S/865 PSD L1500	Polycarbonate	Grey	IP66
911401528647	WT198C HE LED100S/865 PSD L1500	Polycarbonate	Grey	IP66
911401551502	WT198X LED20S/840 L1 W L600 bowl/cover	Polycarbonate	Gray	IP65
911401551702	WT198X LED40S/840 L1 W L1200 bowl/cover	Polycarbonate	Gray	IP65
911401551802	WT198X LED60S/840 L1 W L1500 bowl/cover	Polycarbonate	Gray	IP65
911401552002	WT198X LED20S/865 L1 W L600 bowl/cover	Polycarbonate	Gray	IP65
911401552102	WT198X LED27S/865 L1 W L1200 bowl/cover	Polycarbonate	Gray	IP65
911401552202	WT198X LED40S/865 L1 W L1200 bowl/cover	Polycarbonate	Gray	IP65

GreenPerform Waterproof G3

Order Code	Full Product Name	Optical cover type	Housing Color	Ingress protection code
911401552402	WT198X LED82S/865 L1 W L1500	Polycarbonate bowl/cover	Gray	IP65
911401552502	WT198X LED19S/840 L1 W PCO L600	Polycarbonate bowl/cover	Gray	IP65
911401552602	WT198X LED26S/840 L1 W PCO L1200	Polycarbonate bowl/cover	Gray	IP65
911401552702	WT198X LED38S/840 L1 W PCO L1200	Polycarbonate bowl/cover	Gray	IP65
911401553002	WT198X LED19S/865 L1 W PCO L600	Polycarbonate bowl/cover	Gray	IP65
911401553102	WT198X LED26S/865 L1 W PCO L1200	Polycarbonate bowl/cover	Gray	IP65
911401553202	WT198X LED38S/865 L1 W PCO L1200	Polycarbonate bowl/cover	Gray	IP65
911401553302	WT198X LED57S/865 L1 W PCO L1500	Polycarbonate bowl/cover	Gray	IP65
911401503747	WT198C LED20S/840 PSU L600	Polycarbonate	Grey	IP66
911401503847	WT198C LED18S/840 PSU PCO L600	Polycarbonate	Grey	IP66

Order Code	Full Product Name	Optical cover type	Housing Color	Ingress protection code
911401507447	WT198X LED20S/840 WIA L600	Polycarbonate	Grey	IP66
911401571191	WT198X LED27S/840 L1 S L1200	Polycarbonate bowl/cover	Gray	IP65
911401571291	WT198X LED40S/840 L1 S L1200	Polycarbonate bowl/cover	Gray	IP65
911401571691	WT198X LED27S/865 L1 S L1200	Polycarbonate bowl/cover	Gray	IP65
911401571791	WT198X LED40S/865 L1 S L1200	Polycarbonate bowl/cover	Gray	IP65
911401572191	WT198X LED26S/840 L1 S PCO L1200	Polycarbonate bowl/cover	Gray	IP65
911401572291	WT198X LED38S/840 L1 S PCO L1200	Polycarbonate bowl/cover	Gray	IP65
911401572691	WT198X LED26S/865 L1 S PCO L1200	Polycarbonate bowl/cover	Gray	IP65
911401572791	WT198X LED38S/865 L1 S PCO L1200	Polycarbonate bowl/cover	Gray	IP65

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
911401503947	WT198C LED27S/840 PSU L1200	-30 to +50 °C	-
911401504047	WT198C LED25S/840 PSU PCO L1200	-30 to +50 °C	-
911401504347	WT198C LED40S/840 PSU L1200	-30 to +50 °C	-
911401504447	WT198C LED37S/840 PSU PCO L1200	-30 to +50 °C	-
911401505947	WT198C LED27S/840 PSD L1200	-25 to +45 °C	-
911401506147	WT198C LED40S/840 PSD L1200	-25 to +40 °C	-
911401507547	WT198X LED27S/840 WIA L1200	-25 to +45 °C	-
911401507647	WT198X LED40S/840 WIA L1200	-25 to +40 °C	-
911401509547	WT198C HE LED27S/840 PSU L1200	-30 to +50 °C	-
911401509647	WT198C HE LED27S/865 PSU L1200	-30 to +50 °C	-
911401509747	WT198C HE LED40S/840 PSU L1200	-30 to +50 °C	-
911401509847	WT198C HE LED40S/865 PSU L1200	-30 to +50 °C	-

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
911401510547	WT198C HE LED27S/840 PSD L1200	-25 to +45 °C	-
911401510647	WT198C HE LED40S/840 PSD L1200	-25 to +40 °C	-
911401528247	WT198C HE LED27S/865 PSD L1200	-25 to +45 °C	-
911401528347	WT198C HE LED40S/865 PSD L1200	-25 to +40 °C	-
911401529047	WT198C LED60S/840 PSU L1200	-30 to +50 °C	-
911401529447	WT198C LED60S/865 PSU L1200	-30 to +50 °C	-
911401529547	WT198C LED57S/865 PSU PCO L1200	-30 to +50 °C	-
911401529647	WT198C LED60S/865 PSD L1200	-25 °C to 50 °C	-
911401504747	WT198C LED60S/840 PSU L1500	-30 to +50 °C	-
911401504847	WT198C LED57S/840 PSU PCO L1500	-30 to +50 °C	-
911401504947	WT198C LED60S/865 PSU L1500	-30 to +50 °C	-
911401505147	WT198C LED80S/840 PSU L1500	-30 to +50 °C	-

GreenPerform Waterproof G3

Order Code	Full Product Name	Ambient temperature	
		range	Glow-wire test
911401505247	WT198C LED75S/840 PSU PCO L1500	-30 to +50 °C	-
911401505347	WT198C LED80S/865 PSU L1500	-30 to +50 °C	-
911401506347	WT198C LED60S/840 PSD L1500	-25 to +40 °C	-
911401506547	WT198C LED80S/840 PSD L1500	-25 to +40 °C	-
911401507747	WT198X LED60S/840 WIA L1500	-25 to +40 °C	-
911401507847	WT198X LED80S/840 WIA L1500	-25 to +40 °C	-
911401509947	WT198C HE LED60S/840 PSU L1500	-30 to +50 °C	-
911401510047	WT198C HE LED60S/865 PSU L1500	-30 to +50 °C	-
911401510147	WT198C HE LED80S/840 PSU L1500	-30 to +50 °C	-
911401510247	WT198C HE LED80S/865 PSU L1500	-30 to +50 °C	-
911401510347	WT198C HE LED100S/840 PSU L1500	-30 to +50 °C	-
911401510447	WT198C HE LED100S/865 PSU L1500	-30 to +50 °C	-
911401510747	WT198C HE LED60S/840 PSD L1500	-25 to +40 °C	-
911401510847	WT198C HE LED80S/840 PSD L1500	-25 to +40 °C	-
911401510947	WT198C HE LED100S/840 PSD L1500	-25 to +40 °C	-
911401528447	WT198C HE LED60S/865 PSD L1500	-25 to +40 °C	-
911401528547	WT198C HE LED80S/865 PSD L1500	-25 to +40 °C	-
911401528647	WT198C HE LED100S/865 PSD L1500	-25 to +40 °C	-
911401551502	WT198X LED20S/840 L1 W L600	-20 to +45 °C	Temperature 650 °C, duration 30 s
911401551702	WT198X LED40S/840 L1 W L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
911401551802	WT198X LED60S/840 L1 W L1500	-20 to +45 °C	Temperature 650 °C, duration 30 s
911401552002	WT198X LED20S/865 L1 W L600	-20 to +45 °C	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature	
		range	Glow-wire test
911401552102	WT198X LED27S/865 L1 W L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
911401552202	WT198X LED40S/865 L1 W L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
911401552402	WT198X LED82S/865 L1 W L1500	-20 to +45 °C	Temperature 650 °C, duration 30 s
911401552502	WT198X LED19S/840 L1 W PCO L600	-20 to +45 °C	Temperature 650 °C, duration 30 s
911401552602	WT198X LED26S/840 L1 W PCO L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
911401552702	WT198X LED38S/840 L1 W PCO L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
911401553002	WT198X LED19S/865 L1 W PCO L600	-20 to +45 °C	Temperature 650 °C, duration 30 s
911401553102	WT198X LED26S/865 L1 W PCO L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
911401553202	WT198X LED38S/865 L1 W PCO L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
911401553302	WT198X LED57S/865 L1 W PCO L1500	-20 to +45 °C	Temperature 650 °C, duration 30 s
911401503747	WT198C LED20S/840 PSU L600	-30 to +50 °C	-
911401503847	WT198C LED18S/840 PSU PCO L600	-30 to +50 °C	-
911401507447	WT198X LED20S/840 WIA L600	-25 to +45 °C	-
911401571191	WT198X LED27S/840 L1 S L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
911401571291	WT198X LED40S/840 L1 S L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
911401571691	WT198X LED27S/865 L1 S L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
911401571791	WT198X LED40S/865 L1 S L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
911401572191	WT198X LED26S/840 L1 S PCO L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
911401572291	WT198X LED38S/840 L1 S PCO L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
911401572691	WT198X LED26S/865 L1 S PCO L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s
911401572791	WT198X LED38S/865 L1 S PCO L1200	-20 to +45 °C	Temperature 650 °C, duration 30 s

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity	Luminous flux
			tolerance
911401503947	WT198C LED27S/840 PSU L1200	-	-10%,+15%

Order Code	Full Product Name	Initial chromaticity	Luminous flux
			tolerance
911401504047	WT198C LED25S/840 PSU PCO L1200	-	-10%,+15%

GreenPerform Waterproof G3

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401504347	WT198C LED40S/840 PSU L1200	-	-10%,+15%
911401504447	WT198C LED37S/840 PSU PCO L1200	-	-10%,+15%
911401505947	WT198C LED27S/840 PSD L1200	-	-10%,+15%
911401506147	WT198C LED40S/840 PSD L1200	-	-10%,+15%
911401507547	WT198X LED27S/840 WIA L1200	-	-10%,+15%
911401507647	WT198X LED40S/840 WIA L1200	-	-10%,+15%
911401509547	WT198C HE LED27S/840 PSU L1200	-	-10%,+15%
911401509647	WT198C HE LED27S/865 PSU L1200	-	-10%,+15%
911401509747	WT198C HE LED40S/840 PSU L1200	-	-10%,+15%
911401509847	WT198C HE LED40S/865 PSU L1200	-	-10%,+15%
911401510547	WT198C HE LED27S/840 PSD L1200	-	-10%,+15%
911401510647	WT198C HE LED40S/840 PSD L1200	-	-10%,+15%
911401528247	WT198C HE LED27S/865 PSD L1200	-	-10%,+15%
911401528347	WT198C HE LED40S/865 PSD L1200	-	-10%,+15%
911401529047	WT198C LED60S/840 PSU L1200	-	-10%,+15%
911401529447	WT198C LED60S/865 PSU L1200	-	-10%,+15%
911401529547	WT198C LED57S/865 PSU PCO L1200	-	-10%,+15%
911401529647	WT198C LED60S/865 PSD L1200	-	-10%,+15%
911401504747	WT198C LED60S/840 PSU L1500	-	-10%,+15%
911401504847	WT198C LED57S/840 PSU PCO L1500	-	-10%,+15%
911401504947	WT198C LED60S/865 PSU L1500	-	-10%,+15%
911401505147	WT198C LED80S/840 PSU L1500	-	-10%,+15%
911401505247	WT198C LED75S/840 PSU PCO L1500	-	-10%,+15%
911401505347	WT198C LED80S/865 PSU L1500	-	-10%,+15%
911401506347	WT198C LED60S/840 PSD L1500	-	-10%,+15%
911401506547	WT198C LED80S/840 PSD L1500	-	-10%,+15%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401507747	WT198X LED60S/840 WIA L1500	-	-10%,+15%
911401507847	WT198X LED80S/840 WIA L1500	-	-10%,+15%
911401509947	WT198C HE LED60S/840 PSU L1500	-	-10%,+15%
911401510047	WT198C HE LED60S/865 PSU L1500	-	-10%,+15%
911401510147	WT198C HE LED80S/840 PSU L1500	-	-10%,+15%
911401510247	WT198C HE LED80S/865 PSU L1500	-	-10%,+15%
911401510347	WT198C HE LED100S/840 PSU L1500	-	-10%,+15%
911401510447	WT198C HE LED100S/865 PSU L1500	-	-10%,+15%
911401510747	WT198C HE LED60S/840 PSD L1500	-	-10%,+15%
911401510847	WT198C HE LED80S/840 PSD L1500	-	-10%,+15%
911401510947	WT198C HE LED100S/840 PSD L1500	-	-10%,+15%
911401528447	WT198C HE LED60S/865 PSD L1500	-	-10%,+15%
911401528547	WT198C HE LED80S/865 PSD L1500	-	-10%,+15%
911401528647	WT198C HE LED100S/865 PSD L1500	-	-10%,+15%
911401551502	WT198X LED20S/840 L1 W L600	(0.38, 0.38)	-10% / +10% SDCM≤3
911401551702	WT198X LED40S/840 L1 W L1200	(0.38, 0.38)	-10% / +10% SDCM≤3
911401551802	WT198X LED60S/840 L1 W L1500	(0.38, 0.38)	-10% / +10% SDCM≤3
911401552002	WT198X LED20S/865 L1 W L600	(0.32, 0.33)	-10% / +10% SDCM≤3
911401552102	WT198X LED27S/865 L1 W L1200	(0.32, 0.33)	-10% / +10% SDCM≤3
911401552202	WT198X LED40S/865 L1 W L1200	(0.32, 0.33)	-10% / +10% SDCM≤3
911401552402	WT198X LED82S/865 L1 W L1500	(0.32, 0.33)	-10% / +10% SDCM≤3
911401552502	WT198X LED19S/840 L1 W PCO L600	(0.38, 0.38)	-10% / +10% SDCM≤3
911401552602	WT198X LED26S/840 L1 W PCO L1200	(0.38, 0.38)	-10% / +10% SDCM≤3
911401552702	WT198X LED38S/840 L1 W PCO L1200	(0.38, 0.38)	-10% / +10% SDCM≤3
911401553002	WT198X LED19S/865 L1 W PCO L600	(0.32, 0.33)	-10% / +10% SDCM≤3

GreenPerform Waterproof G3

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401553102	WT198X LED26S/865 L1 W PCO L1200	(0.32, 0.33) SDCM≤3	-10% / +10%
911401553202	WT198X LED38S/865 L1 W PCO L1200	(0.32, 0.33) SDCM≤3	-10% / +10%
911401553302	WT198X LED57S/865 L1 W PCO L1500	(0.32, 0.33) SDCM≤3	-10% / +10%
911401503747	WT198C LED20S/840 PSU L600	-	-10%,+15%
911401503847	WT198C LED18S/840 PSU PCO L600	-	-10%,+15%
911401507447	WT198X LED20S/840 WIA L600	-	-10%,+15%
911401571191	WT198X LED27S/840 L1 S L1200	(0.38, 0.38) SDCM≤3	-10% / +10%
911401571291	WT198X LED40S/840 L1 S L1200	(0.38, 0.38) SDCM≤3	-10% / +10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401571691	WT198X LED27S/865 L1 S L1200	(0.32, 0.33) SDCM≤3	-10% / +10%
911401571791	WT198X LED40S/865 L1 S L1200	(0.32, 0.33) SDCM≤3	-10% / +10%
911401572191	WT198X LED26S/840 L1 S PCO L1200	(0.38, 0.38) SDCM≤3	-10% / +10%
911401572291	WT198X LED38S/840 L1 S PCO L1200	(0.38, 0.38) SDCM≤3	-10% / +10%
911401572691	WT198X LED26S/865 L1 S PCO L1200	(0.32, 0.33) SDCM≤3	-10% / +10%
911401572791	WT198X LED38S/865 L1 S PCO L1200	(0.32, 0.33) SDCM≤3	-10% / +10%

