

**PHILIPS**

**Lighting**



# Product Description

## MSR Hot Restrike

High-efficiency hot restrike metal halide lamps designed for optimum light collection

### Benefits

- High luminous efficacy
- Compact arc (5 - 20 mm)
- Excellent colour rendering
- Dimmable with a stable colour temperature

### Features

- Run-up time 2 minutes
- Frosted top of outer bulb to avoid excessively bright centre beam in open face luminaires
- Universal burning position

### Application

- Indoor and outdoor filming
- Studios and theatres
- Professional photography
- Solar simulation

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


# MSR Hot Restrike

## Versions



XPPR\_XDMSR\_0005-Product photo

## Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 575	30 mm	7.0	69 mm	71 mm	70	145 mm	43 mm	42	41 mm
HR 1CT/4			mm		mm			mm	

