



Halogen non-reflector lamps – high-quality light and easy to use

Λαμπήρας προβολής

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.

Οφέλη

- Optimal beam performance
- 100% Color Rendering Index (CRI)
- Constant light output throughout lifetime

Χαρακτηριστικά

- Distortion-free, quartz bulb and precisely defined filament position
- Lamp replacement without adjustment
- XHP version with xenon gas for maximum light output
- Flat filament available

Λαμπτήρας προβολής

Εφαρμογή


- Studio, film, theatre and disco lighting
- Slide, overhead, profile and 8/16 mm film projectors
- Microscopes
- Optical equipment
- Slide and film viewers
- Surgery lamps
- Microfilm readers
- Dental lamps
- Spectrography

Versions



XPPR_XHMPSEFF_0002-Product photo

Σχεδιάγραμμα διαστάσεων



Product	D (max)	L (min)	L (max)	L	P (max)	P	P (min)	C (max)
14623 95W	11,5 mm	31,5 mm	32,25	32	1,05 mm	1 mm	0,95	50 mm
G6.35 17V 1CT/ 10X10F			mm	mm			mm	
7158XHP 150W	11,5 mm	31,5 mm	33,25	33	1,05 mm	1 mm	0,95	50 mm
G6.35 24V 1CT/ 10X10F			mm	mm			mm	

Γενικές πληροφορίες

Βάση-κάλυμμα	G6.35
Θέση λειτουργίας	S90

Μηχανικά εξαρτήματα και Περιβλημα

Υλικό λαμπτήρα	Χαλαζίας, ανοιχτό στην υπεριώδη ακτινοβολία
----------------	---

Τεχνικά χαρακτηριστικά φωτισμού

Λαμπτήρας προβολής

Order Code	Full Product Name	Σχετική θερμοκρασία χρώματος (ονομ.)	Δείκτης χρωματικής απόδοσης (CRI)
41020750	7158XHP 150W G6.35 24V 1CT/10X10F	3450 K	100

Order Code	Full Product Name	Σχετική θερμοκρασία χρώματος (ονομ.)	Δείκτης χρωματικής απόδοσης (CRI)
42667350	14623 95W G6.35 17V 1CT/10X10F	-	-

Χαρακτηριστικά ηλεκτρικής λειτουργίας

Order Code	Full Product Name	Κατανάλωση ενέργειας
41020750	7158XHP 150W G6.35 24V 1CT/10X10F	150 W

Order Code	Full Product Name	Κατανάλωση ενέργειας
42667350	14623 95W G6.35 17V 1CT/10X10F	95 W

