# Actinic BL TL-D(K) Secura – additional safety and HACCP approval

## Actinic BL TL-D(K) Secura

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL-D(K) Secura lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. In addition, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice.

### Benefits

- Perfectly matches the eye sensitivity of houseflies and in this way attracts more insects
- Safe for use
- Good environmental choice
- No risk of glass particles

### Features

- Emits long-wave UV-A radiation in the 350-400nm range
- UV-B/UV-A ratio less than 0.1 % (UV-B 280-315nm)
- 100% lead-free
- Low mercury content
- Shatterproof sleeve

# Actinic BL TL-D(K) Secura

## Application

- Insect traps, Electronic Fly Killers (EFKs)

## Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

## Versions

XPPR_XUBTLD_0002-Product photo

Secura

## Dimensional drawing




| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|---|---|---|---|---|---|
| Actinic BL TL-DK Secura 36W/10 1SL/25 | 28 mm | 589.8 mm | 596.9 mm | 594.5 mm | 604 mm |




| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|---|---|---|---|---|---|
| Actinic BL TL-D 15W/10 Secura 1SL/25 | 28 mm | 437.4 mm | 444.5 mm | 442.1 mm | 451.6 mm |
| Actinic BL TL-D 18W/10 Secura 1SL/25 | 28 mm | 589.8 mm | 596.9 mm | 594.5 mm | 604 mm |

# Actinic BL TL-D(K) Secura

| General Information | |
|---|---|
| **Cap-Base** | G13 |

| Light Technical | |
|---|---|
| **Color Designation** | Actinic |
| **Color Code** | 10 |

| Mechanical and Housing | |
|---|---|
| **Bulb Shape** | T26 |

## Operating and Electrical

| Order Code | Full Product Name | Lamp Current (Nom) | Power Consumption |
|---|---|---|---|
| 928048201003 | Actinic BL TL-D 18W/10 Secura 1SL/25 | 0.36 A | 18 W |
| 928019801003 | Actinic BL TL-DK Secura 36W/10 1SL/25 | 0.865 A | 36 W |

| Order Code | Full Product Name | Lamp Current (Nom) | Power Consumption |
|---|---|---|---|
| 928024701029 | Actinic BL TL-D 15W/10 Secura 1SL/25 | 0.335 A | 15 W |

## Approval and Application

| Order Code | Full Product Name | Mercury (Hg) Content (Nom) |
|---|---|---|
| 928048201003 | Actinic BL TL-D 18W/10 Secura 1SL/25 | 5.0 mg |
| 928019801003 | Actinic BL TL-DK Secura 36W/10 1SL/25 | 8.0 mg |

| Order Code | Full Product Name | Mercury (Hg) Content (Nom) |
|---|---|---|
| 928024701029 | Actinic BL TL-D 15W/10 Secura 1SL/25 | 5 |

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.