PHILIPS

Lighting

Actinic BL TL-D(K) Secura – additional safety and HACCP approval

Actinic BL TL-D(K) Secura

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL-D(K) Secura lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. In addition, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice.

Benefits

- Perfectly matches the eye sensitivity of houseflies and in this way attracts more insects
- Safe for use
- Good environmental choice
- No risk of glass particles

Features

- Emits long-wave UV-A radiation in the 350-400nm range
- UV-B/UV-A ratio less than 0.1 % (UV-B 280-315nm)
- 100% lead-free
- Low mercury content
- Shatterproof sleeve

Actinic BL TL-D(K) Secura

Application

- Insect traps, Electronic Fly Killers (EFKs)

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions

XPPR_XUBTLD_0002-Product photo

Secura

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 15W/10 Secura 1SL/25	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm
Actinic BL TL-D 18W/10 Secura 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

General Information	
Cap-Base	G13
Light Technical	
Color Designation	Actinic
Color Code	10
Mechanical and Housing	
Bulb Shape	T26

Operating and Electrical

Actinic BL TL-D(K) Secura

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
928048201003	Actinic BL TL-D 18W/10 Secura 1SL/25	0.36 A	18 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
928024701029	Actinic BL TL-D 15W/10 Secura 1SL/25	0.335 A	15 W

Approval and Application

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
928048201003	Actinic BL TL-D 18W/10 Secura 1SL/25	5.0 mg

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
928024701029	Actinic BL TL-D 15W/10 Secura 1SL/25	5

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.