



## Metronomis LED – a play of light and shadow

Metronomis LED is the first post-top range in the world to offer a palette of environmental lighting effects to give projects a unique contextual or aesthetic touch. An innovative play of reflection, light and shadow creates an environmental pattern on the ground or on the bowl to create additional ambience. Four new iconic designs – with a visual and modular link to Metronomis I – are reduced to the essential elements. During the day, the discreet, transparent design blends into its context, be it contemporary or classical, while its night-time appearance is both functional and decorative. The flexible, modular Metronomis LED comes with a range of columns and a wide variety of optics and effects, enabling architects and lighting designers to create a unified, consistent lighting design that still reflects the differences in urban culture and history. Offers exceptional visual comfort while also optimizing safety

### Benefits

- Pure design and palette of lighting effects to make your city unique
- Offers exceptional visual comfort while also optimizing safety
- Complete and innovative lighting solution with a shared design identity for both mast and luminaire

### Applications

- City centers and squares
- Commercial and business centers
- Residential and architectural area

## Features

- A palette of lighting effects on the ground or on the inside or outside of the bowl makes it possible to

create different atmospheres and to give streets and cityscapes a distinctive visual touch

- Five dedicated aluminum and wooden masts – heights of 3.5 and 4 meters – enhance the pure, simplified style of the luminaires

## Versions



YHB653 METROLAT  
FLANGE PLATE



YHM652 METROLIGHT 120  
FLANGE PLATE



YHM652 METROLIGHT 120  
GROUND SECTION



YHM656 METROCONE  
FLANGE PLATE



YHM656 METROCONE  
GROUND SECTION



YHP657 METRORORIGINAL  
FLANGE PLATE



YHP657 METRORORIGINAL  
GROUND SECTION



YHP658 METROTUBE  
FLANGE PLATE

YHP685 METROTUBE  
GROUND SECTION



YHW655 METROWOOD  
FLANGE PLATE




YHW655 METROWOOD  
GROUND SECTION




YHP654 METROBASIC  
FLANGE PLATE




**Dimensional drawing**




METROBASIC - Pole with flange - 3.5 m - 76 mm - RAL color




METROBASIC - Pole with flange - 4.0 m - 76 mm - RAL color




METROCONE - Pole for embedded installation - 3.5 m - 90 mm - RAL color




METROCONE - Pole for embedded installation - 4.0 m - 90 mm - RAL color




METROCONE - Pole with flange - 3.5 m - 90 mm - RAL color




METROCONE - Pole with flange - 4.0 m - 90 mm - RAL color




METROLAT - Pole with flange - 3.5 m - 135 mm - RAL color




METROLIGHT - Pole for embedded installation - 3.5 m - 76 mm - RAL color




METROLIGHT - Pole for embedded installation - 4.0 m - 76 mm - RAL color




METROLIGHT - Pole with flange - 3.5 m - 76 mm - RAL color




METROLIGHT - Pole with flange - 4.0 m - 76 mm - RAL color




METRORIGINAL - Pole for embedded installation - 3.5 m - 135 mm - RAL color




METRORIGINAL - Pole for embedded installation - 4.0 m - 135 mm - RAL color




METRORIGINAL - Pole with flange - 3.5 m - 135 mm - RAL color




METRORIGINAL - Pole with flange - 4.0 m - 135 mm - RAL color




METROTUB - Pole for embedded installation - 3.5 m - 135 mm - RAL color




METROTUB - Pole for embedded installation - 4.0 m - 135 mm - RAL color




METROTUB - Pole with flange - 3.5 m - 135 mm - RAL color




METROTUB - Pole with flange - 4.0 m - 135 mm - RAL color




METROWOOD - Pole for embedded installation - 3.5 m - 133 mm - RAL color



METROWOOD - Pole for embedded installation - 4.0 m - 133 mm - RAL color



METROWOOD - Pole with flange - 3.5 m - 133 mm - RAL color



METROWOOD - Pole with flange - 4.0 m - 133 mm - RAL color

### Approval and Application

CE mark

Yes