

MileWide² – design meets efficiency

Many municipal authorities are embracing the benefits of contemporary outdoor lighting. These include a more attractive urban environment and increased comfort, safety and security for the public. Not to mention the positive impact on environmental protection and city branding. Together with Holscher Design, Philips has developed MileWide², the successor to the highly popular MileWide family. Featuring a range of dedicated masts and brackets, the pure, clean design of MileWide² integrates perfectly with today's and tomorrow's cityscape. With its high-quality finish and high level of lighting performance, MileWide² is suitable for a wide range of applications, ranging from traffic roads to city centers. Multi-layer optics provide a uniform light distribution and reduced glare, enabling direct replacement of HID solutions without compromising on spacing, mounting height or light quality.

Benefits

- Consistency and continuity of family design
- Complete solution with dedicated masts and brackets
- Discreet solution with clean lines radiating a strong character

Applications

- Residential streets
- Walking, cycling and running paths
- Main roads

- Motorways
- Car parks

Features

- Dedicated total solution based on clean-design, high-finish MileWide family
- Two different shapes to match different integration styles
- Different heights available – suitable for a wide range of applications
- "Plug-and-play"

Versions



YHP435 PLS-EMB CUR
4000 RAL48



YHP435 PLS-EMB CUR
6000 RAL60



YHP435 PLS-FLG CUR
4000 RAL48



YHP435 PLS-FLG CUR
6000 RAL60



YHP435 PLT-EMB CUR
6000 RAL60 48



YHP435 PLT-FLG CUR
6000 RAL60 48



YRP435 PLS-EMB CONE
4000 RAL48



YRP435 PLS-FLG CONE
4000 RAL48



YRP435 PLT-EMB CONE
6000 RAL60 48



YRP435 PLT-EMB CONE
6000 RAL60 60




YRP435 PLT-FLG CONE
6000 RAL60 48




YRP435 PLT-FLG CONE
6000 RAL60 60


Dimensional drawing




4.0 m - 70 mm




6.0 m - 80 mm




4.0 m - 70 mm




6.0 m - 80 mm




6.0 m - 80 mm




6.0 m - 80 mm




4.0 m - 70 mm




4.0 m - 70 mm




6.0 m - 80 mm



6.0 m - 80 mm




6.0 m - 80 mm



6.0 m - 80 mm

Product details



MileWide2_Bend pole.tif



MileWide2_Slend pole.tif

Approval and Application

CE mark

Yes