



# GreenPerform Waterproof Tubular WT228C

## Mounting Instruction/安装说明书



| Type/型号                        | CCT (K) | Power(W)/功率 | Lumen Output (lm)/流明输出 | Dimension /尺寸 | Energy efficiency class of light source/光源能效等级 | kg  | Voltage/电压 | Frequency/频率 |
|--------------------------------|---------|-------------|------------------------|---------------|------------------------------------------------|-----|------------|--------------|
| WT228C LED50S/840 PSU L1200 TW | 4000    | 39          | 5000                   | 1340x69x69    | D                                              | 1.2 | 220-240V~  | 50/60Hz      |
| WT228C LED50S/865 PSU L1200 TW | 6500    | 39          | 5000                   | 1340x69x69    | D                                              | 1.2 |            |              |
| WT228C LED70S/840 PSU L1500 TW | 4000    | 54          | 7000                   | 1640x69x69    | D                                              | 1.5 |            |              |
| WT228C LED39S/840 PSU L1500 TW | 4000    | 28          | 3900                   | 1640x69x69    | D                                              | 1.5 |            |              |




### Mounting distance / 安装距离

Unit (mm)


| Type | L1200   | L1500     |
|------|---------|-----------|
| L    | 700-950 | 1000-1250 |

### Installation / 安装方式

- ☒ Ceiling Mounting 吸顶安装
- ☒ Wall Mounting 墙装
- ☒ Suspended Mounting 悬吊安装







Surface Mounting / 表面安装  
shipped with products/随产品出货



Separate Accessories/悬吊附件  
911401867784 WT210Z SMS  
Could be ordered separately/需要单独购买




(X2)



### Cable Connection / 输入接线


60245 IEC57 Ø1.0-2.5mm<sup>2</sup>

Brown / 棕 — L  
Blue / 蓝 — N  
Yellow Green / 黄绿 — PE



### Inrush current / 侵入电流

|                                 | LED50S | LED70S | LED39S |
|---------------------------------|--------|--------|--------|
| Max [A]                         | 20     | 40     | 25     |
| Tref [μs]                       | 150    | 100    | 50     |
| Max. Nr of products / 最多产品数     |        |        |        |
| Drivers / MCB 16A type B [max.] | 30     | 18     | 30     |
| Drivers / MCB 10A type B [max.] | 24     | 15     | 24     |
| Drivers / MCB 16A type C [max.] | 34     | 24     | 38     |
| Drivers / MCB 10A type C [max.] | 24     | 15     | 24     |



EN

1. Do not look directly at led light for a long time to avoid physical discomfort.
2. The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
3. The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.
4. Above average concentration of sulfur affects the useful lifetime of the product.  
E.g: Light color changes from white to yellow.
5. For use in environments where an accumulation of conductive dust on the luminaire may be expected.
6. Do not install the luminaire under water.
7. Do not install the luminaire in refrigeration house.
8. This luminaire can install in ammonia environment, typically in chicken&pig farms.
9. Do not install the luminaire in the environment where vibration exists.

CN

1. 切勿长时间直视led灯具，以免产生身体不适的情况；
2. 灯具应由有资格的电工安装，接线要符合IEE电气标准或国家标准；
3. 此灯具内的光源应由制造商或其服务代理商或一个类似的有资格的人来更换；
4. 若使用环境中，硫浓度高于平均水平会影响产品的使用寿命。比如灯具颜色会从白色变成黄色；
5. 可能在灯具上会积聚导电灰尘的环境中使用；
6. 请勿将灯具安装在水下；
7. 请勿在冷库内安装灯具；
8. 该灯具可安装在有氨气的环境中，尤其适用于养鸡场和养猪场；
9. 请勿将灯具安装在振动环境中；



This marking indicates that this product should not be disposed with other household wastes. To prevent possible harm to the environment or human health from uncontrolled waste disposal, recycle it responsibly to promote the sustainable reuse of material resources. To return your used device, please use the return and collection systems or contact the retailer where the product was purchased. They can take this product for environmental safe recycling.

#### 用户资料

用户姓名: \_\_\_\_\_ (先生/女士)

产品名称: \_\_\_\_\_

产品型号: \_\_\_\_\_

出售单位及地址: \_\_\_\_\_

购买日期: 年 月 日

发票号码: \_\_\_\_\_

**PHILIPS**

Philips and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V.

昕诺飞灯具(上海)有限公司  
地址: 上海市闵行区合川路2555号1幢二楼, 邮编: 200233  
服务热线: 8008 201 201  
4009 201 201

仅限中国大陆地区

#### 昕诺飞灯具产品

##### 质保条款

本公司保证该产品在正常使用及保养下能发挥其优越性能。同时本公司将为持证用户提供一年质保服务(不含光源)。

1. 自购买日起一年内, 凡经本公司确认为正常使用情况下因产品本身质量问题导致的故障及损坏, 您将获得质保服务。

2. 此质保服务包括灯具以及灯具包含的附件、辅助装置。

3. 消费者申请质保服务时, 须提供本保修证以及有效的购买凭证。

4. 以下情况将不能享受质保服务:

1) 无生产日期、涂改生产日期或撕毁掉、调换生产日期贴纸;

2) 产品已经由非本公司授权人员拆卸、改装或修理过;

3) 超过质保有效时限的产品;

4) 正常使用引起的产品老化、磨损、划伤、掉漆等, 不影响产品的正常使用;

5) 非质量问题造成产品外壳严重损坏(包括变形、氧化、腐蚀或有严重的水渍等);

6) 使用不当引起的人为损坏, 如接不当电源、使用不当的配件、不当之安装、不依照说明书使用、错误使用或疏忽造成的损坏等;

7) 其他不可抗力因素, 如火灾、水灾、地震、高压、酸碱腐蚀、雷击浪涌等造成的损坏。

服务热线: 8008 201 201  
4009 201 201

昕诺飞灯具(上海)有限公司

仅限中国大陆地区

#### 产品中有害物质的名称及含量

12NC: 444100099181

| 部件名称            | 有害物质  |       |       |             |           |
|-----------------|-------|-------|-------|-------------|-----------|
|                 | 铅(Pb) | 汞(Hg) | 镉(Cd) | 六价铬(Cr(VI)) | 多溴联苯(PBB) |
| LED灯板/光源        | ○     | ○     | ○     | ○           | ○         |
| 驱动器(板)、铜制及电子零部件 | ×     | ○     | ○     | ○           | ○         |
| 透镜光学部件          | ○     | ○     | ○     | ○           | ○         |
| 外壳及其他零部件        | ○     | ○     | ○     | ○           | ○         |

本表格依据SJ/T 11364的规定编制。

○: 表示该有害物质在该部件所有均质材料中的含量均在GB/T 26572规定的限量要求以下。

×: 表示该有害物质至少在该部件的某一均质材料中的含量超出GB/T 26572规定的限量要求。

Applicable to China Only