


GreenUp Grid






GD309B LED Downlight/筒射灯

Mounting instructions/安装说明书






Modular Type 型号	CRI 显色指数	CCT 色温	Beam Angle 光束角	Input 输入 220-240V,50/60Hz;	Lum Dim. 灯具尺寸 L*W*H(mm)	Cut out 开孔尺寸 (mm)	Weight(kg) 重量
GD309B 3*P20 PSU-E	≥80 / ≥90	2700K 3000K 3500K 4000K 5000K	NB MB WB VWB	0.45A,60W	L270*W140*H107	255*125	2.04
GD309B 3*P20 PSR-E	≥80 / ≥90			0.48A,60W			2.04
GD309B 3*P20 PSR-E 1-10V	≥80 / ≥90			0.51A,60W			2.13
GD309B 3*P20 PSD-E	≥80 / ≥90			0.60A,60W			2.1
GD309B 3*P24 PSU-E	≥80 / ≥90			0.51A,72W			2.04
GD309B 3*P24 PSR-E	≥80 / ≥90			0.75A,72W			2.13
GD309B 3*P24 PSR-E 1-10V	≥80 / ≥90			0.75A,72W	L270*W140*H112	255*125	2.13
GD309B 3*P24 PSD-E	≥80 / ≥90			0.60A,72W			2.1
GD309B 3*P28 PSU-E	≥80 / ≥90			0.60A,84W			2.04
GD309B 3*P28 PSR-E	≥80 / ≥90			0.75A,84W			2.13
GD309B 3*P28 PSR-E 1-10V	≥80 / ≥90			0.75A,84W			2.13
GD309B 3*P28 PSD-E	≥80 / ≥90			1.02A,84W			2.28
GD309B 3*P33 PSU-E	≥80 / ≥90			0.69A,99W			2.04
GD309B 3*P33 PSR-E	≥80 / ≥90			0.75A,99W			2.13
GD309B 3*P33 PSR-E 1-10V	≥80 / ≥90			0.96A,99W			2.23
GD309B 3*P33 PSD-E	≥80 / ≥90			1.02A,99W			2.28


Dimension 组件尺寸



Following installation method is NOT allowed
请不要使用以下几种方式安装灯具




ON



Please do not use your bare hand to adjust the core
when the light is on
灯具点亮时请不要用手直接接触灯头进行调节

OFF



Turn off the power and wait for 15mins before adjust the
core with bare hand
关闭电源并静置**15**分钟后，可以手直接接触灯头进行调节



This product is for indoor use only.本产品仅限室内使用。

Please read this manual carefully before using the product.Please keep the manual for future reference.
使用本产品前，请先仔细阅读本手册。请保留本手册作为日后参照用。

The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE eleatrical regulations
or the national requirementa.灯具应由有资格的电工安装，接线要符合IEE电气标准或国家标准。

The luminaire is complied to IEC 60598-1 or GB 7000.1。
此灯具是依据IEC60598-1或国标GB 7000.1所制造。

The luminaire shall,under no circumstance,be covered with insulation matting or similar material.
此灯具不能被隔热衬垫或类似材料覆盖。

If the external flexible cable or cord of this luminaire is dnmaged,it shall be exclusively replaced by the manufacture or
his service agent or a similar qualified person in order to avoid a hazard.
如果此灯具外部软缆或软线损坏了，该线要由制造商或其服务代理商专门提供的软缆或软线更换。



The manufacturer will not be held responsible for improper usage or modification to the product.
所有不当使用或自行更改产品结构而导致损坏，生产商不负任何责任。

The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar
qualified person.
此灯具内的光源应由制造商或其服务代理商或一个有类似资格的人来更换。

In case of malfunction,please switch off the power and contact your nearest Philips dealer.
如发现异常或操作有任何问题，请务必先切断电源，然后与飞利浦经销商联系。

Maintenance 保养方法:

The corrosive atmosphere or hazardous materials such as sulfur,chlorine,phthalate,etc must be avoided during the sue and storage.
灯具避免在腐蚀性环境或者含有有害物质，例如硫化物，卤化物，邻苯二甲酸酯等环境中储存和使用。

To ensure optimum performance,please clean the product regularly(recommended twice a year).Turn off luminaire before cleaning.
为了保持灯具明亮效果，请定期（半年一次）进行清洁。灯具清洁请在切断电源情况下进行。

Do not use chemical solvents to clean the luminaire,it might damage the surface.
请不要用香蕉水等挥发性物质擦拭灯具表面，请不要对灯具喷洒任何化学药剂，否则灯具可能会变色或损坏。

产品中有害物质的名称及含量

部件名称	有害物质					
	铅 (Pb)	汞 (Hg)	镉 (Cd)	六价铬 (Cr(VI))	多溴联苯 (PBB)	多溴二苯醚 (PBDE)
LED灯板/光源	0	0	0	0	0	0
驱动器(板)，铜 制及电子零部件	×	0	0	0	0	0
透镜光学部件	0	0	0	0	0	0
外壳及其 它零部件	0	0	0	0	0	0

本表格依据SJ/T 11364的规定编制

○:表示该有害物质在该部件所有均质材料中的含量均在GB/T 26572规定的限量要求以下。

×:表示该有害物质至少在该部件的某一均质材料中的含量超出GB/T 26572规定的限量要求。