

GreenUp Track
ST306T LED Track Luminaire/轨道灯
Mounting instructions/安装说明书

GB7000 IP20 Ta 25℃ 220V-240V~ Ra ≥90											
Product Type 型号描述	CCT 色温	Beam Angle 光束角	Dimming Method 调光方式	Mounting Method 安装方式	Color 颜色	Current 电流	Power 功率	Weight 重量			
ST306T P10 PSU	3000K 4000K 5000K	16° 23° 36°	PSU	2 wires track mounting 2线 轨道安装	WHITE 白色 BLACK 黑色	0.045A	10W	0.54kg			
ST306T P20 PSU						0.09A	20W	0.57kg			
ST306T P30 PSU						0.135A	30W	0.91kg			
ST306T P40 PSU						0.18A	40W	0.91kg			
ST306T P11 PSR						0.05A	11W	0.64Kg			
ST306T P20 PSR						0.095A	20W	0.64Kg			
ST306T P28 PSR			PSR			0.126A	28W	1.05Kg			
ST306T P38 PSR						0.17A	38W	1.05Kg			
ST306T P10 PSD			PSD	4 wires track mounting 4线 轨道安装		0.045A	10W	0.62kg			
ST306T P20 PSD						0.09A	20W	0.62kg			
ST306T P30 PSD						0.135A	30W	1.01kg			
ST306T P40 PSD						0.18A	40W	1.01kg			
ST306T P11 PSR I-10V			PSR I-10V			0.047A	11W	0.64Kg			
ST306T P20 PSR I-10V						0.095A	20W	0.64Kg			
ST306T P28 PSR I-10V						0.126A	28W	1.05Kg			
ST306T P38 PSR I-10V						0.17A	38W	1.05Kg			
ST306T P38 PSR I-10V						0.17A	38W	1.05Kg			

Dimension灯具尺寸

Product Type 型号描述	L(cm)	W(cm)	H(cm)
ST306T P10 PSU ST306T P11 PSR	15	9.5	18.5
ST306T P20 PSU ST306T P20 PSR	15	9.5	18.5
ST306T P30 PSU ST306T P28 PSR	17	11.5	18.5
ST306T P40 PSU ST306T P38 PSR	17	11.5	18.5

Dimension灯具尺寸

Product Type 型号描述	L(cm)	W(cm)	H(cm)
ST306T P10 PSD ST306T P11 PSR I-10V	15	9.5	20
ST306T P20 PSD ST306T P20 PSR I-10V	15	9.5	20
ST306T P30 PSD ST306T P28 PSR I-10V	17	11.5	20
ST306T P40 PSD ST306T P38 PSR I-10V	17	11.5	20

Lamp can be rotated灯具可旋转角度

Only adjust the lighting angle when the power is off. 请在未通电时调节灯具照射角度。

0~180° rotation 旋转

Please be careful when adjusting the angle, and please stop rotate in the same direction When the lamp cap is adjusted to the stop position 调节角度时请小心操作, 当灯头调节到止位时, 切勿同方向继续旋转。

Recommended Installation Method推荐安装方式

① Track Surface Mount Installation 轨道吸顶安装

② Track Recessed Installation 轨道嵌入式安装

Min.100mm Max. 55mm

We recommended install the track on the ceiling. It is prohibited to install the track on the side wall and the ground. 建议导轨安装于天花板上, 禁止安装于侧墙及地面。

1.1 2 wires track mounting 2线轨道安装

0~350° rotation 旋转
0~180° rotation 旋转
OFF NO OFF
ON OFF

Please turn the rotary switch to "on" position before installation, Toggle switch to "off" position 安装前请把旋转开关旋转至"ON"位, 拨动开关拨到"OFF"位

1.2

Click

Put the track head into the track, turn the rotary switch to the "OFF" position, flip the switch to the "ON" position, hear the "click" that means the track head has locked into the track 将轨道头装入轨道内, 把旋转开关旋转至"OFF"位, 拨动开关拨到"ON"位, 听到"咔"一声后即代表轨道头已锁紧到轨道内

1.3

ON OFF
15 mins

Please do not use your bare hands to adjust the core when the light is on 灯具点亮时请不要用手直接接触灯头
Turn off the power and wait for 15mins before adjust the core with bare hand 关闭电源并静置15分钟后, 可以用手直接接触灯头

1.4

ON OFF

Turn the rotary switch to the "ON" position, flip the switch to the "OFF" position, downward to pull out the track 把旋转开关旋转至"ON"位, 拨动开关拨到"OFF"位, 向下即可拔出轨道

2.1

4 wires track mounting

4线轨道安装

0~220° rotation

旋转

The wiring of the track strip must match this, otherwise the light will be damaged

导轨条的接线必须与此匹配, 否则灯会损坏

0~180° rotation

旋转

4 wires track mounting

4线轨道安装

-I -10V

L D2

N DI

+I -10V

L

N

D2/-I -10V

DI/+I -10V

2.2

Adjust the axis as shown above and push the track head into the track

调整轴位如上图所示, 把轨道头推进轨道内

2.3

ON

OFF

15 mins

Please do not use your bare hands to adjust the core when the light is on

灯具点亮时请不要用手直接接触灯头

Turn off the power and wait for 15mins before adjust the core with bare hand

关闭电源并静置15分钟后, 可以用手直接接触灯头

2.4

Pull the switch downward to pull out the track

拨动开关, 向下即可拔出轨道

Following installation method is NOT allowed

请不要使用以下几种方式安装灯具

>5°

⚠

⚡

⚠

⚡

Please read this manual carefully before using the product. Please keep the manual for future reference.

使用本产品前, 请先仔细阅读本手册。请保留本手册作为日后参照用。

The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.

灯具应由有资格的电工安装, 接线要符合IEE电气标准或国家标准。

The luminaire is complied to IEC 60598-1 or GB 7000.1

此灯具是依据IEC 60598-1 或国标GB 7000.1所制造。

The luminaire shall, under no circumstance, be covered with insulation matting or similar material.

灯具不能被隔热衬垫或类似材料覆盖。

If the external flexible cable or cord of this luminaire is damaged, it shall be exclusively replaced by the manufacture or his service agent or a similar qualified person in order to avoid a hazard.

如果此灯具外部软缆或软线损坏了, 该线要由制造商或其服务代理商专门提供的软缆或软线更换。

The manufacturer will not take responsibility caused by improper use or self modifications of the product.

所有不当使用或自行更改产品结构而导致损坏, 生产商不负任何责任。

In case of malfunction, please switch off the power and contact your nearest Philips dealer.

如发现异常或操作有任何问题, 请务必先切断电源, 然后与飞利浦经销商联系。

Indoor use only.

本灯具仅限室内使用。

Basic insulation has been provided between LV supply and control conductors.

LV电源和控制导体之间是基本绝缘。

Turn off the power supply before checking, installation or moving.

检查, 安装或移动灯具之前, 必须切断电源。

Maintenance 保养方法:

The corrosive atmosphere or hazardous materials such as sulfur, chlorine, phthalate, etc must be avoided during the use and storage.

灯具避免在腐蚀性环境或者含有有害物质, 例如硫化物, 卤化物, 联苯二甲酸酯等环境中存储和使用。

To ensure optimum performance, please clean the product regularly (recommended twice a year). Turn off luminaire before cleaning.

为了保持灯具明亮效果, 请定期(半年一次)进行清洁。灯具清洁请在切断电源情况下进行。

Do not use chemical solvents to clean the luminaire, it might damage the surface.

请不要用香蕉水等挥发物质擦拭灯具表面, 请不要对灯具喷洒任何化学药剂, 否则灯具可能会变色或损坏。

Warning: The light source and parts of this lamp are not replaceable. When the light source and parts the end of their life, the whole lamp should be replaced.

警告: 此灯具的光源和零部件是不可替换的; 当光源和零部件到其寿终时, 应替换整个灯具!

产品中有害物质的名称及含量						
部件名称	有害物质					
	铅 (Pb)	汞 (Hg)	镉 (Cd)	六价铬 (Cr(VI))	多溴联苯 (PBB)	多溴二苯醚 (PBDE)
LED灯板/光源	○	○	○	○	○	○
驱动器(板)、铜制及电子零部件	×	○	○	○	○	○
透镜光学部件	○	○	○	○	○	○
外壳及其他零部件	○	○	○	○	○	○

本表格依据SJ/T 11364的规定编制

○ : 表示该有害物质在该部件所有均质材料中的含量均在GB/T 26572规定的限量要求以下。

× : 表示该有害物质至少在该部件的某一均质材料中的含量超过GB/T 26572规定的限量要求。

EN

ID

VN

TH

RU

UA

KZ

AR

⚠

⚡

This marking indicates that this product should not be disposed with other household wastes throughout the EU. To prevent possible harm to the environment or human health from uncontrolled waste disposal, recycle it responsibly to promote the sustainable reuse of material resources. To return your used device, please use the return and collection systems or contact the retailer where the product was purchased. They can take this product for environmental safe recycling.

Simbol di samping menunjukkan bahwa produk ini tidak boleh dibuang bersama dengan limbah rumah tangga lainnya di seluruh wilayah Uni Eropa. Untuk mencegah bahaya kerusakan lingkungan atau kesehatan manusia dari pembuangan limbah yang tidak terkontrol, lakukan daur ulang secara bertanggung jawab dalam rangka terus mempromosikan penggunaan kembali bahan tak terpakai. Untuk mengembalikan produk bekas pakai, silakan gunakan sistem layanan pengumpulan dan pengembalian yang tersedia atau hubungi toko tempat anda membeli produk ini. Pihak toko bersedia mengambil produk bekas pakai untuk mendukung kegiatan daur-ulang yang aman. Dấu hiệu này thể hiện sản phẩm này không nên được xử lý chung với các chất thải gia đình khác trong khu vực liên minh Châu Âu. Để ngăn ngừa tác hại có thể có cho môi trường hoặc sức khỏe con người từ chất thải không kiểm soát được, hãy tái chế một cách có trách nhiệm để thúc đẩy việc tái sử dụng bền vững các nguồn tài nguyên. এই চিহ্নটি স্পষ্ট করে দেয় যে এই পণ্যটি ইউরোপের অন্যান্য পরিবারের বর্জ্যের সাথে মিশিয়ে ফেলা যাবে না। পরিবেশের ক্ষতি হওয়া বা মানুষের স্বাস্থ্যের ক্ষতি হওয়ার ঝুঁকি কমাতে পণ্যটিকে পুনর্ব্যবহার করা উচিত। পণ্যটি ফেরত দেওয়ার জন্য বা পণ্যটি পরিবেশবান্ধবভাবে পুনর্ব্যবহার করার জন্য দায়িত্বশীলভাবে ব্যবহার করে পণ্যটি ফেরত দেওয়া বা সংগ্রহের ব্যবস্থা ব্যবহার করুন। Данная маркировка указывает на то, что в странах ЕС настоящее изделие нельзя утилизировать вместе с другими бытовыми отходами. Во избежание причинения вреда окружающей среде или здоровью людей данный прибор подлежит сдаче на переработку. Чтобы отправить светильник на переработку, используйте системы сбора перерабатываемых материалов или обратитесь вна предприятие розничной торговли, через которое был приобретен данный осветительный прибор. Розничный магазин может принять данный товар для последующей его отправки на безопасную для окружающей среды переработку. Дана маркировка вказує на те, що в країнах ЄС даний продукт заборонено викидати разом з іншими побутовими відходами. Щоб уникнути загрози шкоди довкіллю або здоров'ю людей, даний прилад підлягає здачі на переробку. Щоб відправити світильник на переробку, використовуйте системи збору для переробки матеріалів або зверніться до підприємства роздрібної торгівлі, через яке був придбаний даний освітлювальний прилад. Роздрібний магазин може прийняти даний товар для подальшої його відправки на безпечну для навколишнього середовища переробку. Коршаған ортаға немесе адамдардың денсаулығына зиян келтірмеу үшін, нақты құралды қайта өңдеуге тапсыру қажет. Шамшарқыты қайта өңдеуге жіберу үшін, қайта өңделетін материалдарды жинау жүйелерін пайдаланңыз немесе осы жарықтандыру құралын сатып алған бөлшек сауда кәсіпорнына жүгініңіз. Бөлшек сауда дүкені қоршаған орта үшін қауіпсіз қайта өңдеуге жөнелту үшін бұл тауарды қабылдауы мүмкін.

هذه العلامة تشير إلى أن هذا المنتج لا ينبغي التخلص منه مع النفايات المنزلية الأخرى في جميع أنحاء الاتحاد الأوروبي. لمنع أي ضرر ممكن بالبيئة أو بصحة الإنسان من التخلص غير المناسب مع النفايات، نوصي بإعادة تدويره بشكل مسؤول لتشجيع إعادة استخدام موارد الخامات. لإعادة جهازك للاستخدام، يرجى استخدام نظم الإعادة والتجميع أو الاتصال بمتاجر التجزئة حيث تم شراء المنتج. ويمكن أن يأخذ هذا المنتج لإعادة التدوير البيئي الآمن.

GreenUp Magnetic Flex

ST307Z 附件/Accessory Mounting instructions/安装说明书

GB7000 Max. 40℃ Min. -20℃ Ta 25℃																			
Product Type 型号描述	Mounting Method 安装方式	Color 颜色	Voltage 电压	Power 功率	Weight(kg) 重量														
ST307Z SM L1000	Magnetic track installation 磁吸安装系统	Black 砂黑	24V 48V	/	1.16														
ST307Z SM L2000					2.32														
ST307Z RS L1000					1.41														
ST307Z RS L2000					2.82														
ST307Z IECP					0.029														
ST307Z LECP					0.07														
ST307Z driver connection module					0.044														
ST307Z SM LCP					0.097														
ST307Z SMVLCP					0.064														
ST307Z RS LCP		0.115																	
ST307Z RSVLCP		0.085																	
ST307Z 150W I-10V driver		White 白色	24V	150W	0.36														
ST307Z 150W PSU driver		Black 砂黑	48V		0.41														
ST307Z I-10V controller		White 白色	/	/	0.187														
<table><tr><th>Dimension产品尺寸</th><th>Product Type/型号</th><th>L(cm)</th><th>W(cm)</th><th>H(cm)</th></tr><tr><td rowspan="2">Surface mounted track rail 明装导轨</td><td>ST307Z SM L1000</td><td>100</td><td>2.73</td><td>5.3</td></tr><tr><td>ST307Z SM L2000</td><td>200</td><td>2.73</td><td>5.3</td></tr></table>						Dimension产品尺寸	Product Type/型号	L(cm)	W(cm)	H(cm)	Surface mounted track rail 明装导轨	ST307Z SM L1000	100	2.73	5.3	ST307Z SM L2000	200	2.73	5.3
Dimension产品尺寸	Product Type/型号	L(cm)	W(cm)	H(cm)															
Surface mounted track rail 明装导轨	ST307Z SM L1000	100	2.73	5.3															
	ST307Z SM L2000	200	2.73	5.3															
<table><tr><th>Dimension产品尺寸</th><th>Product Type/型号</th><th>L(cm)</th><th>W(cm)</th><th>H(cm)</th></tr><tr><td rowspan="2">Recessed track rail 暗装导轨</td><td>ST307Z RS L1000</td><td>100</td><td>3.05</td><td>5.3</td></tr><tr><td>ST307Z RS L2000</td><td>200</td><td>3.05</td><td>5.3</td></tr></table>						Dimension产品尺寸	Product Type/型号	L(cm)	W(cm)	H(cm)	Recessed track rail 暗装导轨	ST307Z RS L1000	100	3.05	5.3	ST307Z RS L2000	200	3.05	5.3
Dimension产品尺寸	Product Type/型号	L(cm)	W(cm)	H(cm)															
Recessed track rail 暗装导轨	ST307Z RS L1000	100	3.05	5.3															
	ST307Z RS L2000	200	3.05	5.3															
<table><tr><th>Dimension产品尺寸</th><th>Product Type/型号</th><th>L(cm)</th><th>W(cm)</th><th>H(cm)</th></tr><tr><td rowspan="2">Surface mounted horizontal corner 明装式水平转角</td><td>ST307Z SM LCP</td><td>8.6</td><td>8.6</td><td>5.3</td></tr><tr><td>ST307Z SMVLCP</td><td>8.6</td><td>2.65</td><td>8.6</td></tr></table>						Dimension产品尺寸	Product Type/型号	L(cm)	W(cm)	H(cm)	Surface mounted horizontal corner 明装式水平转角	ST307Z SM LCP	8.6	8.6	5.3	ST307Z SMVLCP	8.6	2.65	8.6
Dimension产品尺寸	Product Type/型号	L(cm)	W(cm)	H(cm)															
Surface mounted horizontal corner 明装式水平转角	ST307Z SM LCP	8.6	8.6	5.3															
	ST307Z SMVLCP	8.6	2.65	8.6															
<table><tr><th>Dimension产品尺寸</th><th>Product Type/型号</th><th>L(cm)</th><th>W(cm)</th><th>H(cm)</th></tr><tr><td rowspan="2">Recessed horizontal corner 暗装式水平转角</td><td>ST307Z RS LCP</td><td>8.6</td><td>8.6</td><td>5.3</td></tr><tr><td>ST307Z RS VLCP</td><td>8.6</td><td>3.1</td><td>8.6</td></tr></table>						Dimension产品尺寸	Product Type/型号	L(cm)	W(cm)	H(cm)	Recessed horizontal corner 暗装式水平转角	ST307Z RS LCP	8.6	8.6	5.3	ST307Z RS VLCP	8.6	3.1	8.6
Dimension产品尺寸	Product Type/型号	L(cm)	W(cm)	H(cm)															
Recessed horizontal corner 暗装式水平转角	ST307Z RS LCP	8.6	8.6	5.3															
	ST307Z RS VLCP	8.6	3.1	8.6															
<table><tr><th>Dimension产品尺寸</th><th>Product Type/型号</th><th>L(cm)</th><th>W(cm)</th><th>H(cm)</th></tr><tr><td rowspan="2">Surface mounted vertical corner 明装式垂直转角</td><td>ST307Z SM LCP</td><td>8.6</td><td>8.6</td><td>5.3</td></tr><tr><td>ST307Z SMVLCP</td><td>8.6</td><td>2.65</td><td>8.6</td></tr></table>						Dimension产品尺寸	Product Type/型号	L(cm)	W(cm)	H(cm)	Surface mounted vertical corner 明装式垂直转角	ST307Z SM LCP	8.6	8.6	5.3	ST307Z SMVLCP	8.6	2.65	8.6
Dimension产品尺寸	Product Type/型号	L(cm)	W(cm)	H(cm)															
Surface mounted vertical corner 明装式垂直转角	ST307Z SM LCP	8.6	8.6	5.3															
	ST307Z SMVLCP	8.6	2.65	8.6															
<table><tr><th>Dimension产品尺寸</th><th>Product Type/型号</th><th>L(cm)</th><th>W(cm)</th><th>H(cm)</th></tr><tr><td rowspan="2">Recessed vertical corner 暗装式垂直转角</td><td>ST307Z RS LCP</td><td>8.6</td><td>8.6</td><td>5.3</td></tr><tr><td>ST307Z RS VLCP</td><td>8.6</td><td>3.1</td><td>8.6</td></tr></table>						Dimension产品尺寸	Product Type/型号	L(cm)	W(cm)	H(cm)	Recessed vertical corner 暗装式垂直转角	ST307Z RS LCP	8.6	8.6	5.3	ST307Z RS VLCP	8.6	3.1	8.6
Dimension产品尺寸	Product Type/型号	L(cm)	W(cm)	H(cm)															
Recessed vertical corner 暗装式垂直转角	ST307Z RS LCP	8.6	8.6	5.3															
	ST307Z RS VLCP	8.6	3.1	8.6															
<table><tr><th>Dimension产品尺寸</th><th>Product Type/型号</th><th>L(cm)</th><th>W(cm)</th><th>H(cm)</th></tr><tr><td>Type I connection module I型连接模块</td><td>ST307Z IECP</td><td>14.3</td><td>1.9</td><td>1.8</td></tr></table>						Dimension产品尺寸	Product Type/型号	L(cm)	W(cm)	H(cm)	Type I connection module I型连接模块	ST307Z IECP	14.3	1.9	1.8				
Dimension产品尺寸	Product Type/型号	L(cm)	W(cm)	H(cm)															
Type I connection module I型连接模块	ST307Z IECP	14.3	1.9	1.8															
<table><tr><th>Dimension产品尺寸</th><th>Product Type/型号</th><th>L(cm)</th><th>W(cm)</th><th>H(cm)</th></tr><tr><td>Type L connection module L型连接模块</td><td>ST307Z LECP</td><td>32</td><td>1.9</td><td>1.8</td></tr></table>						Dimension产品尺寸	Product Type/型号	L(cm)	W(cm)	H(cm)	Type L connection module L型连接模块	ST307Z LECP	32	1.9	1.8				
Dimension产品尺寸	Product Type/型号	L(cm)	W(cm)	H(cm)															
Type L connection module L型连接模块	ST307Z LECP	32	1.9	1.8															

Dimension产品尺寸

Product Type/型号	L(cm)	W(cm)	H(cm)
ST307Z driver connection module	35.5	1.9	1.8

Power connection module
电源接电模块

Dimension产品尺寸

Product Type/型号	L(cm)	W(cm)	H(cm)
ST307Z 150W I-I0V driver	26.8	4.5	3.05

150W driver (24V)
150W电源(24V)

Dimension产品尺寸

Product Type/型号	L(cm)	W(cm)	H(cm)
ST307Z 150W PSU driver	30.8	2.26	4.7

150W driver (48V)
150W电源(48V)

Dimension产品尺寸

Product Type/型号	L(cm)	W(cm)	H(cm)
ST307Z I-I0V controller	8.6	8.6	4.7

I-I0V dimmer
I-I0V调光器

1.1 Surface mounted track rail
明装导轨

Hole distance
孔距离

Φ 6mm

Hole distance is 820mm
孔距离为820mm
Surface mounted track rail -2 holes for 1m
明装导轨-1米的打孔数量为2
Surface mounted track rail -4 holes for 2m
明装导轨-2米的打孔数量为4

Recessed track rail
暗装导轨

Installation according to the actual board
thickness selection
安装时根据实际木板厚度选择
Installation card slot and installation
direction
安装卡槽位及安装方向

Installation mode one
安装模式一
Upper and lower board locking mounting plate (board thickness not
more than 12mm)
上下层木板锁紧安装片(木板厚度不大于12mm)
(The short side of the mounting piece is facing upwards, and the fixing
slot is clamped into the top slot)
(安装片短边朝上，固定槽卡入最顶部卡槽)

Installation mode two
安装模式二
Straight board直接固定木板
(The short side of the mounting piece faces down, and the fixing slot
is inserted into the bottom slot)
(安装片短边朝下，固定槽卡入最底部卡槽)

2

Grooves in the ceiling have a width of 36mm
在天花板上开槽槽的宽度为36mm
NOTE/注意:
Surface mounted track rail does not need slotting
明装导轨不需开槽

3 Stitching way
拼接方式

Horizontal corner
水平转角

Vertical corner
垂直转角

M6x8 Round head screw
圆头螺钉

Rail connection piece
导轨连接片

Track rail
导轨

Signify Luminares (Shanghai) Co., Ltd.
Address: 2F, Building 1, No. 2555, Hechuan Road, Minhang District, SH, P.R. China Postalcode: 200233
昕诺飞灯具（上海）有限公司
地址：上海市闵行区合川路2555号1幢2楼
邮编：200233

Data subject to change without notice

PHILIPS

Philips and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V

