

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Electronic controlgear for LED modules

Name and address of the applicant

Signify Netherlands B.V.
High Tech Campus 48 Eindhoven 5656 AE
Netherlands

Name and address of the manufacturer

Signify Netherlands B.V.
High Tech Campus 48 Eindhoven 5656 AE
Netherlands

Name and address of the factory

Note: When more than one factory, please report on page 2☐ Additional information on page 2

Ratings and principal characteristics

Input: 220-240 V, 50/60 Hz, 0,11-0,2 A; 186-250 V, 0 Hz, 0,13-0,23 A.
Output: 0,5 -1,05 A, 20-36 W.

Trademark / Brand (if any)


Philips

Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

Xitanium 36W/m 0.3-1.05A 54V S TD 230V, Xitanium 36W/m 0.3-1.05A 54V I TD 230V, Xitanium 20W/m 0.15-0.5A 54V S TD 230V, Xitanium 20W/m 0.15-0.5A 54V I TD 230V

Additional information (if necessary may also be reported on page 2)

See CB test report No.3500336.732 for complete model/type reference

☐ Additional information on page 2

A sample of the product was tested and found to be in conformity with

IEC 61347-1:2015, IEC 61347-1:2015/AMD1:2017, IEC 61347-2-13:2014, IEC 61347-2-13:2014/AMD1:2016

As shown in the Test Report Ref. No. which forms part of this Certificate

3500336.732

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
Arnhem, 6825 MJ
Netherlands

Date: 2022-12-15

Signature: Matilde Tonsi

