



High performance and integrated style, all in one luminaire

Gardco LED Wall Sconce 161 is an enlarged and enhanced version of the 121, providing performance capability up to that of a 400W metal halide wall sconce, while using considerably less energy. Designed for mounting heights from 15 to 20 feet, the 161 offers exceptional performance, allowing a reduction in the total pole requirements on a site. The styling of the 161 also complements the PureForm site luminaires. The sloped surface ribs of its die cast aluminum housing create a distinctly unique aesthetic element, while performing important functions in the Gardco thermal management system.

161 LED Wall Sconce




- Exceptional performance can reduce pole requirements on a site.
- Motion response and control options are available for additional energy savings.
- Performance is equivalent to 400W HID while consuming significantly less energy.
- Advanced LED optical system with full cutoff minimizes glare and light trespass.
- All 161 luminaires equipped with NW or CW LED types are DesignLights Consortium® qualified.

Ordering guide

Luminaire	Number of LEDs	Drive Current	LED Color Generation	Distributions	Voltage	Dimming Control ⁴	Electrical	Options	Finish
161								WS	
161 LED wall sconce	46L² 46 LEDs (1 module)	600 600mA	NW-G2 Neutral White 4000K, 70 CRI Generation 2	2 IES Type 2	120 120V	DD 0-10V Dimming Driver ²	Fusing F1 Single (120, 277, 347VAC) ⁵ F2 Double (208, 240, 480VAC) ⁵ F3 Canadian Double Pull (208, 240, 480VAC)	WS Surface mount conduit feed junction box	Textured
	92L 92 LEDs (2 modules)	600 600mA 800 800mA	CW-G2 Cool White 5700K, 70 CRI Generation 2 WW-G2 Warm White 3000K, 70 CRI Generation 2	3 IES Type 3 4 IES Type 4	208 208V 240 240V 277 277V 347 347V 480 480V UNV 120-277V AC HVU 347-480V AC	DCC Dual Circuit Control ¹ DynaDimmer: Automatic Profile Dimming CS50 Safety 50% Dimming, 7 hours ^{1,2,3} CM50 Median 50% Dimming, 8 hours ^{1,2,3} CE50 Economy 50% Dimming, 9 hours ^{1,2,3} DA50 All Night 50% Dimming ^{1,2,3}			

1. Not available with Dimming Driver (DD) option.
2. Not available with Dual Circuit Control (DCC) option.
3. Available in 120-277V or UNV only.
4. Not available with 480V.
5. Must specify specific input voltage.

Dimensions



Lumen range: 10,245 – 27,302

Wattage range: 91-242W

Efficacy range: 102-121Lm/W

Weight: 40 lbs (18.15 kg)

Note: Mounting plate center is located in the center of the luminaire width and 3.5" (8.89cm) above the luminaire bottom (lens down position). Splices must be made in the J-box (by others). Mounting plate must be secured by max. 5/16" (.79cm) diameter bolts (by others) structurally to the wall.

Prior to ordering, consult specification sheets on gardcolighting.com for the most current information, notes, and exclusions.

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

