

GreenSpace surface mounted high lumen/LED明装筒灯

Mounting instruction/ 安装说明

44410007991

| | | | | | | |
|-------------------|--|-------------|--|--|--------------------------|--|
| GB 7000 | | IP65 | | | $t_a 35^{\circ}\text{C}$ | |
|-------------------|--|-------------|--|--|--------------------------|--|

| Type Number 产品型号 | LEDs 颗粒数 | Lum.Power 功率 | Lamp Power 功率 | Voltage 电压 | Frequency 频率 | Class 灯具类别 | | lpeak (A) | Duration (μs) | MCB Type B 16A | |
|---------------------|-------------|-----------------|------------------|---------------|-----------------|---------------|-----|--------------|-------------------------------|-------------------|--|
| DN397C LED12 PSU | 105 | 102W | 93W | 220-240 V | 50/60 Hz | I | 4.7 | 46 | 440 | 11 | |
| DN397C LED12 PSD | 105 | 102W | 93W | 220-240 V | 50/60 Hz | I | 6.2 | 53 | 300 | 8 | |

| Dimension 灯具尺寸 | D (mm) | H (mm) |
|----------------|------------|--------|
| DN397C PSU | $\Phi 220$ | 236 |
| DN397C PSD | $\Phi 220$ | 361 |

1 在天花板上按图示尺寸，先开一个40mm的出线孔，再安装4个M6膨胀锚栓（锚栓另购，承重 > 50Kg）。
On the ceiling, make one hole for the Input wire (Min D40mm). Then install four M6 expansion anchors (not included, weight capacity > 50Kg).

2 用螺钉将安装盘固定在天花板上。（螺钉另购）
Fix the **Installation plate** on the ceiling with four M6 Screws (not included)
把灯具挂在安全绳上
Hang the luminaire with the **safety chain**

3 Connect entry cable 连接电源线
Please connect the cable to the terminal box (IP65 or above), then place the terminal box into the ceiling. (not included)
请使用IP65以上的接线盒,接线完成后将接线盒放置到天花内,飞利浦不提供接线盒。

PSU_Version

PSD_Version

The cable of the luminaire should use "Y" type connection. It should be maintained by professional electrician.
灯具电源线使用Y型连接,电源线损坏需专业人士更换。

4

Make the luminaire into **Installation plate**, and rotate anti-clockwise.
将灯具装到安装盘上,并逆时针旋转。

5

To make sure the Luminaire can rotated in right place
请确保灯具旋转到位



1. The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
灯具应由有资格的电工安装，接线要符合IEE 电气标准或国家标准。
2. The luminaire is complied to IEC 60598-1 ed.8 or GB 7000.1-2007.
此灯具是依据IEC60598-1 ed.8 或国标GB 7000.1-2007所制造。
3. Do not switch on before complete installation.
接线过程中，切勿通电。
4. The light source of this luminaire is not replaceable; when the light source reaches its end of life the whole luminaire shall be replaced
灯具中光源不可更换；当灯具寿命终结时，请更换整个灯具。
5. If the external flexible cable or cord of this luminaire is damaged, it shall be exclusively replaced by the manufacturer or his service agent or a similar qualified person in order to avoid hazard.
如果此灯具外部软电缆或软线发生损坏，该线要由制造商或其服务代理商或一个有资格的人更换，以避免发生危险。



This marking indicates that this product should not be disposed with other household wastes throughout the EU. To prevent possible harm to the environment or human health from uncontrolled waste disposal, recycle it responsibly to promote the sustainable reuse of material resources. To return your used device, please use the return and collection systems or contact the retailer where the product was purchased. They can take this product for environmental safe recycling.