

**HADCO**

Urban



**Comfort and  
adaptability  
you can afford**



# Designed to fit

When it comes to decorative outdoor lighting, aesthetics, and performance should go hand in hand. You want the latest technology, but you also need to consider adaptability, visual comfort, and your budget.

Now you can future-proof your lighting without compromising on aesthetic or price. **Hadco TownView LED post top** is an affordable, high-quality lighting solution designed to make the transition from HID to LED as seamless as possible. It's highly adaptable, featuring a variety of style, performance, and mounting options that will fit perfectly with the style of your town or neighborhood. We also offer glare control thanks to a variety of panels and lens choices that ensure visual comfort.



## Value that shines through

It's easy to see the benefits. With TownView, you get a decorative outdoor lighting solution with exceptional performance, historical style, and long-term adaptability.

### **Easily adaptable to your needs**

with features that enhance visual comfort and increase citizen and driver satisfaction.

### **Lower maintenance costs and improve efficiency**

with advanced technology, artfully incorporated into the classic design.

### **Aesthetics is never an afterthought**

with the variety of style options available.

### **Enjoy an affordable, high-quality product**

with future-proof capabilities at the forefront of its design.

# Maintaining a legacy

Change is a good thing—but some traditions are worth holding onto. TownView comes with plenty of style options so your new LED lighting will seamlessly blend in with the legacy luminaires already in place.



**TVPC-A-S**

TownView arm mount with visual comfort panels and square roof.



**TVPC-S3-S**

TownView with visual comfort panels, small post top fitter and square roof

# Make your style your own

Each application has its own look and feel that you shouldn't have to sacrifice in the name of technology. TownView allows you to preserve that special character with a wide range of decorative features, including:

- Square or curved roof styles
- Decorative arm mount
- Post top with large or small mounting fitters
- Visual comfort or ribbed panels
- Open-style cage with or without comfort lens



# Quality where it counts

Decorative lighting may put the focus on style. But we know that what's under the roof is just as important. No matter what features and options you choose, all TownView models are built to provide a high-quality solution that ensures adaptability for years to come

## Comfort first

Enhance livability in your neighborhood and improve satisfaction of your residents by controlling brightness with visual comfort options.

## Asset management

Our exclusive Service Tag uses a unique QR code system to provide easy access to product information and installation location. TownView luminaires are also compatible with Interact City and other connected lighting solutions for easy management, measurement, and monitoring of your street lighting.

## Future-proof

All TownView models come controls-ready out of the box, with a dimming driver and 7-pin receptacle. So, whether you're looking to upgrade your technology today, tomorrow, or in the future, your lighting will be ready.

## Easily accessible

Maintenance and service are simple with TownView's tool-less latch, hinged roof, hands free access to wiring, and FAWS location.



# Adapt to your view

TownView decorative outdoor lighting is designed to work in a variety of different applications, with adaptable features and options to fit your specific needs. Here are just a few examples of how people are using TownView:



## Visual comfort panel

### Downtown main street

Decorative lighting that provides charming historic style that is comfortable to look at.



## Visual comfort lens

### Residential neighborhood

A main lighting source that offers safety, security, and visual comfort.



## Vertical ribbed panel

### Park or campus setting

Improved light levels with increased vertical illumination.



## Without lens

### Storefronts and office buildings

Maximum light levels for a sense of safety and security.



# TownView

## Features and options

### 1 Roof options

Hinged roof available in curved or square roof styles.

### 3 Panel options

Panel options provide a traditional style. The vertical ribbed panel provides a clear look during the day and performance at night while the visual comfort panel reduces glare and provides a soft glow at night.

### 5 Twist-lock receptacle

The standard tool less rotatable 7-pin NEMA twist lock receptacle facilitates connected lighting solutions that can quickly and easily be upgraded in the future.



### 7 Fitter options

Small fitter available in 2 3/8", 3" or 4" OD.  
Large fitter available in 3" or 4" OD.

### 2 Lens options

Visual Comfort internal lens helps to reduce glare and pixelization while providing a modern open style.

### 4 Tool less latch

Easy access to the driver, surge protector, FAWS option, wiring area, panels and lens options.

### 6 Wiring cover access to terminal block

Quick access to wiring inside the cover. Optional terminal block location for the smaller fitter.



### 8 Arm mount option

Optional arm mount available in square roof only.

### Hinged roof hands free

Hinges open and provides hands free access. No tools required to access the driver and optical area for installation or future upgrades.



### Optional sensor ready receptacle

Optional ZD4I certified fixture (TVLN-32 only) includes D4i certified DALI driver and SR receptacle providing adaptability now or in the future.



### Drivers

The dimming driver (0-10V) is standard, D4i certified DALI driver is optional, enabling it to be combined with additional controls, now or in the future.




### Optional field adjustable wattage selector

Optional field adjustable wattage selector (FAWS) switch can be operated even while wearing Lineman's gloves, providing the ability to change wattage in the field.




# Technical information


## Dimensions



## Luminaire options



## Future ready options




**D4ID**  
D4i certified  
DALI driver

**ZD4I**  
Zhaga-D4i certified  
fixture includes D4i  
certified DALI driver and  
SR sensor receptacle

Prior to ordering,  
consult specification  
sheets on  
[lightingproducts.signify.com](https://lightingproducts.signify.com) for the most  
current information,  
notes, and exclusions.

# Future Ready Connected Solutions

## Designed for smart cities



### TownView Standard

- 0-10V dimming driver.
- 7-pin toolless rotatable receptacle enables future connectivity.
- Service Tag and data migration simplifies data collection and asset management.

### Add Interact City Node

- Delivers connected lighting system with full visibility and control of lighting from a centralized dashboard.
- Remotely manage, monitor and control lighting assets.
- [interact-lighting.com/en-us/what-is-possible/interact-city](http://interact-lighting.com/en-us/what-is-possible/interact-city)

### D4i Certified DALI Driver Option

- DALI functionality.
- Plus next generation extended DALI-2 functionality with power and data.
- Backwards DALI compatibility..

### ZD4i Certified Luminaire Option

- TVLN-32 only.
- Includes D4i certified DALI driver and SR 4-pin Zhaga Book 18 socket.
- Sensor ready luminaire enabling greater connectivity in the future – just plug in sensors when ready.



## Service Tag

### Allows for easy serviceability

Thanks to the Service Tag placed on all TownView luminaires (extra labels included) – standard and no charge, each product is uniquely identifiable by simply scanning a QR code. Information for each specific luminaire configuration can be accessed using a simple handheld device like a smartphone or tablet. This Service Tag feature enables your installation and maintenance process to become faster, easier and more cost effective. For more details visit: [signify.com/global/service-tag](http://signify.com/global/service-tag)

## Ready to make the switch?

See how you can future-proof your lighting without compromising on aesthetic or price with Hadco TownView LED luminaires. Contact your local Sales Representative for more information or to schedule a personalized demonstration, or visit:



[hadco.com/TownView TVLN, TVLC](http://hadco.com/TownView TVLN, TVLC)



[hadco.com/TownView TVPC, TVPR](http://hadco.com/TownView TVPC, TVPR)

# GENLYTE SOLUTIONS

a  [Signify](#) business

© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

PHc-1803BR TownView brochure 12/25

Signify North America Corporation  
400 Crossing Blvd, Suite 600  
Bridgewater, NJ 08807  
Telephone 800-555-0500

All trademarks are owned by Signify Holding or their respective owners.

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone 800-668-9008

[www.genlyte.com](#)