
### LIGHTOLIER

by (s) ignify

**Downlighting** 

LyteCaster LED

**L4/L5/L6** 4", 5", 6" round & square



# Defining general purpose LED downlights

LyteCaster LED downlight and adjustable luminaires provide comfortable, quality illumination. LyteCaster's shallow frame height fits into tight plenum spaces and the adaptable design makes it a versatile lighting option.

#### **Benefits**

- Frame construction: The frame is includes 90° swivel mounting bar points and offset holes for applications close to joints for easy installation.
- Shallow luminaire height: The shallow 3.5" luminaire height saves plenum space making it ideal in residential and light commercial installations.
- Modular and innovative light engine: An interchangeable and upgradeable modular light engine provides easy install.
- LyteCaster LED with warm glow effect (2700K- 2200K): Provides characteristics of an incandescent lamp when dimmed and is an alternative to a BR30 65W incandescent.
- Adjustable gimbal design: Low cost solution for slope ceiling and wall washing applications.
- Wet location listed: No need for special lens design. Great for bathrooms and shower installations.
- Remodeler kit: Ideal for renovation spaces.







## L4/L5/L6 LyteCaster LED

### Round & Square aperture downlighting

- The 4" round delivers 650 & 1000lm, and 4" square delivers 850lm.
- The 5" round delivers 1000 & 15000lm, and 5" square delivers 1000lm.
- The 6" round delivers 1500 & 2000lm, and 6" square delivers 1500lm.
- The 5" round is also available with warm glow effect and delivers 700lm.



#### **Features**

Efficacy: up to 90 lm/w Lumens: 650 & 2000 Watts: 7W - 20 W CRI: 80 & 90 (min) CCT: 2700K, 3000K, 3500K, 4000K

Volts: 120V, 120V/277V
Dimming: 0-10V & ELV
Lifetime: 50,000 hrs
Labels: IC rated, cULus
damp location listed,
ENERGY STAR® certified.
Warranty: 5 year limited

Frame Complete luminaire = Frame + Light Engine + Trim (match series and lumens with light engine)

example: L5S15AE1VA

example: L5S15927VA

Series	Lumens		Housing*	Dimming/Voltage/Version	
L4R LyteCaster LED 4" round	- 650lm	<b>10</b> 1000lm	A New construction w/screws	E1VA	
L5R LyteCaster LED 5" round	- 1000lm	<b>15</b> 1500lm	AN New construction w/nails  R Remodeler	ELV / 120V / Version A Z10UVA 0-10V / Universal 120V-277V / Version A	
L6R LyteCaster LED 6" round	- 1500lm	<b>20</b> 2000lm	R Remodeler		
L4S LyteCaster LED 4" square		<b>10</b> 850lm	A New construction w/screws		
L5S LyteCaster LED 5" square		<b>15</b> 1000lm	AN New construction w/nails		
L6S LyteCaster LED 6" square		<b>20</b> 1500lm			
L5R LyteCaster LED 5" round	- 700lm		Same as above ("A" or "AN")	EWG1 ELV & Triac / 120V	
		<b>07</b> 700lm	R Remodeler	/ warm glow effect	

Light engine	Select frame and trim (downlights)
--------------	------------------------------------

Series	Lumens		CRI/CC	T/Version
L4R LyteCaster LED 4" round	- 650lm	<b>10</b> 1000lm	827VA	80CRI / 2700K / Version A
L5R LyteCaster LED 5" round	- 1000lm	<b>15</b> 1500lm		80CRI / 3000K / Version A 80CRI / 3500K / Version A
L6R LyteCaster LED 6" round	- 1500lm	<b>20</b> 2000lm		80CRI / 4000K / Version A
L4S LyteCaster LED 4" square		<b>10</b> 850lm	927VA	90CRI / 2700K / Version A
L5S LyteCaster LED 5" square		<b>15</b> 1000lm		
L6S LyteCaster LED 6" square		<b>20</b> 1500lm	1	
L5R LyteCaster LED 5" round		<b>07</b> 700lm	8WG	80CRI / 2700K - 2200K / WarmGlow

Trim	3-part system (downlights)	OR	Light Engin & Trim	2-part system (adjustables)	example: L5SDD

Series	Shape/Style	Type/Finish (downlight) or Lumen, CRI/CCT, Finish (adjustable)
L4 LyteCaster LED 4" L5 LyteCaster LED 5" L6 LyteCaster LED 6"	R Round downlight S Square downlight	DD Open downlight / Clear diffuse (white flange) DW Open downlight / White (white flange) BW Baffle downlight / White (white flange)
L4 LyteCaster LED 4"	RA Round adjustable	06WVA 650lm, (CRI/CCT), White (white flange)/Version A 10WVA 1000lm, (CRI/CCT), White (white flange)/Version A
L5 LyteCaster LED 5"	RA Round adjustable	10WVA 1000lm, (CRI/CCT), White (white flange)/Version A 15WVA 500lm, (CRI/CCT), White (white flange)/Version A
L6 LyteCaster LED 6"	RA Round adjustable	15WVA 1500lm, (CRI/CCT), White (white flange)/Version A 20WVA 2000lm, (CRI/CCT), White (white flange)/Version A

<sup>\*</sup> New construction (NC) and remodeler housings are AirSeal IC.

Note: See specification sheets L4R, L4S, L5R, L5S, L6R, L6S for additional drawings and technical information.



Visit Signify.com/warranties for more information on Signify's standard 5-year limited warranty.

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.



2019 Signify Holding. All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereor is disclaimed. All trademarks are owned by Signify Holding or their respective owners.

Signify North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Telephone 855-486-2216 signify Canada Ltd. 181 Hillmount Road, Markham, ON, Canada L6C 2S3 Salanhona 800-668-9008