LIGHTOLIER

by (s) ignify

Downlighting

Retrofit Downlight LED

RD Round



An LED retrofit as easy as snap and click

Lightolier Retrofit Downlight LED is easy to install and will save you lots of time and frustration on the job site. This is an affordable solution for new construction or remodeling.

Benefits

- Utilizes existing frames to make replacing old downlighting and upgrading to LED, a truly easy task.
- Flexible springs allow for installation without tools.
- Contemporary and simple design with baffle trim.
- Uniform LED light with glare-reduction filter, means a more comfortable space.
- · Long lifetime will reduce your future maintenance.
- The product is dimmable with TRIAC/ELV dimmers.









RD Retrofit Downlight LED

Round aperture downlighting



Efficacy: up to 100 lm/w Lumens: 900 & 1400 Watts: 12 W (4") 15 W (5/6")

CRI: 90 (min) **CCT**: 3000 K

Volts: 120V (50/60 Hz)
Dimming: Triac & ELV
Lifetime: 42,000 hrs
Labels: AirSeal, IC rated,
ROHS & Title24 compliant,
cULus wet location listed
(covered ceilings only),
ENERGY STAR® certified.
Warranty: 5 year limited




Your go-to LED replacement solution. Whether you have a commercial, institutional or residential space that needs an energy-saving upgrade, the Retrofit Downlight will be the fast and cost-effective answer.

Fixture example: RD4R089301W


Series	Size/Shape	Lumens	CRI/CCT	Voltage	Finish
RD Retrofit Downlight	4R 4" Round	08 900 lm	930 90CRI/ 3000K	1 120V	W White (matte)
	6R 6" Round	12 1400 lm			

Dimensions





Retrofit Downlight 5"



You will love how hassle-free this fixture is, with a quick connect plug and medium base socket adapter included, you may not even need to open your toolbox.



Visit Signify.com/warranties for more information on Signify's standard 5-year limited warranty.

See specification sheet FD for additional drawings and technical information.

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.



2019 Signify Holding. All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereor is disclaimed. All trademarks are owned by Signify Holding or their respective owners.

Signify North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Telephone 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3