

# LIGHTOLIER

by  Signify

Downlighting

LyteProfile LED

SL Shower light 3"



## Experience the change, see the difference... again, and again

Architectural showerlight provides the right illumination and the safety you need in wet locations.

### Benefits

LyteProfile's showerlight is not just a modification to the downlight product, it was purposefully designed with wet locations in mind. The non-conductive flush mount lens with pre-installed gasket takes the worry out of wet location safety. It also reflects the lustrous architectural look and lighting performance that you've come to expect in all of the LyteProfile 3" downlights.



# SL LyteProfile LED

## Shower light 3" downlight



### Features

- Apertures:** 3" round
- Finish:** Matte white flange with diffuse lens
- Reflectors:** Suitable for use with any finish.
- Lumens:** 500-1500lm (3")
- Construction:** Non-conductive flush mount lens with pre-installed gasket
- Installation:** One-piece reflector and lens allows for similar installation as standard trims\*
- Labels:** cULus wet location
- Warranty:** 5 year

### Frame

example: 3RAS

Series	Installation	Voltage/Options
<b>3R</b>		
<b>3R</b> 3" Round	<b>N</b> New construction	<ul style="list-style-type: none"> <li>— Universal (120V/277V)</li> <li><b>EM</b> Emergency (see pg 2 for details &amp; limitations)<sup>1</sup></li> <li><b>LC</b> Chicago Plenum</li> <li><b>3</b> 347V (not compatible with ELV dimming)</li> <li><b>3IP</b> 347V with Interact Pro (for 0-10V engine only)<sup>2</sup></li> <li><b>IP</b> Interact Pro ready (for 0-10V engine only)<sup>2</sup></li> </ul>
	<b>A</b> AirSeal IC (1000lm max)	<ul style="list-style-type: none"> <li>— Universal (120V/277V)</li> <li><b>S</b> Shallow (120V/277V)<sup>3</sup></li> </ul>

### Engine / Trim

example: P3RDL10930CLZ10US

Series	Style	Lumens	CRI	CCT
<b>P3R</b>			<b>9</b>	
<b>P3R</b> LyteProfile LED 3" Round	<ul style="list-style-type: none"> <li><b>DL</b> Downlight</li> <li><b>LW</b> Lensed Wall Wash<sup>4</sup></li> <li><b>SL</b> Shower light<sup>4</sup> (w/non-conductive trim and lens)</li> </ul>	<ul style="list-style-type: none"> <li><b>05</b> 500lm</li> <li><b>10</b> 1000lm</li> <li><b>15</b> 1500lm<sup>5</sup></li> </ul>	<b>9</b> 90CRI	<ul style="list-style-type: none"> <li><b>27</b> 2700K</li> <li><b>30</b> 3000K</li> <li><b>35</b> 3500K</li> <li><b>40</b> 4000K</li> </ul>
		<b>10</b> 1000lm	<b>9</b> 90CRI	<b>D2W</b> 3000K-1800K <sup>6</sup>

### Engine / Trim (continued)

Reflector	Flange	Dimming / Voltage	Plenum
<b>CL</b> Specular clear	— White (matte)	<b>Z10U</b> 0-10V 1% / Universal (120V/277V/347V)	— Spun aluminum
<b>CC</b> Comfort clear	<b>P</b> Matching reflector	<b>LU</b> Lutron PEQ0 / Universal (120V/277V/347V) (Dim to 0.1%) <sup>7</sup>	<b>S</b> Shallow cast aluminum <sup>3</sup>
<b>CD</b> Comfort clear diffuse			
<b>BK</b> Black (matte)		<b>E1</b> Electronic low voltage / 120V	
<b>WH</b> White (matte)	— White (matte)		

### Accessories

<b>SWZDT</b>	SpaceWise wireless controller w/dwell time functionality (compatible with 0-10V, see SWZDT spec sheet)
<b>SRAINT</b>	InterAct Office Accessory (for use with Lightolier UniFrame 0-10V products)

\* Wet location rated shower light is applicable in any installation requiring dead front trims, interior or exterior non-corrosive applications, or where a diffused lens at the ceiling is required.



Visit [Signify.com/warranties](http://Signify.com/warranties) for more information on Signify's standard 5-year limited warranty.

- Emergency (EM) frame includes emergency battery with ceiling and reflector mountable test switch. Requires above ceiling access. Ceiling mount test switch only.
- InterAct Pro requires above ceiling access.
- Must order shallow IC frame, shallow engine / shallow trim for complete shallow assembly.
- Lensed wall washers and shower lights have a 1000lm limit in non-IC configuration and 500lm limit in IC configurations.
- The 1500lm (15) option is not available with standard Airseal IC frame (3RA-).
- Dim to Warm configurations are for Non-IC frames only.
- Not compatible with Shallow (S) configurations.

See specification sheet P3R for additional drawings and technical information.

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

