

# LIGHTOLIER

by  Signify

Downlighting

LyteProfile LED

P3R/P3S Round & Square



## Your lighting toolbox has expanded once again

Introducing more of a good thing with the LyteProfile 3" aperture downlight, wall wash and adjustable accent

Your lighting project decisions are now even easier. We've expanded the LyteProfile family to 3-inch square and round options so you can achieve consistent illumination and smooth installation for simple or complex projects. Enjoy one-stop shopping with the reliability and quality of the LyteProfile family. You can never have too much of a good thing.

### All luminaires feature:

- Designed for challenging ceilings and shallow plenum height.\*
- Light output 500 to 1500 lumens.
- Four different color temperature options.
- Dim-to-warm optional.
- Plug & play easy-install two part system.

\* Non-IC versions are 4.5" tall and IC versions are 3.5" tall.




interact  
ready.

# P3R/P3S LyteProfile LED


## Round and Square 3" aperture downlights




Round Downlight & Lensed wall wash



Round Adjustable accent



Square Downlight & Lensed wall wash



Square Adjustable accent

### Features

**Aperture:** 3" round/square  
**Efficacy:** up to 100lm/w  
**Lumens:** 500-1500  
**Watts:** 7-20W  
**Volts:** 120-277V, 347V  
 (50/60Hz)

**CRI:** 90 (min)  
**CCT:** 2700-4000K  
**Dimming:** 0-10V, ELV  
**Lifetime:** 56,000 hrs (L70)  
**Warranty:** 5 year

### Round styles



Lensed wall wash, Downlight & Adjustable accent

All shown with Comfort clear reflector and Polished flange

### Square styles



Lensed wall wash, Downlight & Adjustable accent

All shown with Comfort clear reflector and Polished flange

### Finishes



Specular clear



Comfort clear



Comfort clear diffuse



White



Black



Visit [Signify.com/warranties](http://Signify.com/warranties) for more information on Signify's standard 5-year limited warranty.



Tool-free installation using modular quick connect technology

See P3R & P3S specification sheets for additional drawings and technical information.

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.



© 2019 Signify Holding. All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. All trademarks are owned by Signify Holding or their respective owners.

Signify North America Corporation  
 200 Franklin Square Drive,  
 Somerset, NJ 08873  
 Telephone 855-486-2216

Signify Canada Ltd.  
 281 Hillmount Road,  
 Markham, ON, Canada L6C 2S3  
 Telephone 800-668-9008