



# Pure, polished, precision...

The ultimate family of cylinders for all your layers of light

You told us you needed beautiful lighting with a high level of fit, finish and flexibility to overcome the challenges posed by exposed ceilings in retail and hospitality environments. You asked for a complete multi-mount family with easy installation for compressed timelines in office and hotel spaces.

You wanted choice including direct/indirect, downlight, wall wash and adjustable accent combined with a myriad of mounting choices that include solid or cable pendant, wall mount, ceiling mount, dual cable mount and stem mount. Lightolier listened, and we are stoked to bring you Calculite precision cylinders... everything you asked for and more.

## Designed with designers in mind

- The largest array of cylinder options in the US market.
- Available in RAL colors or white, aluminum, and black finishes.
- Complementary design and finish to OmniSpot track family.
- Line expansion provides simplest choice to specify projects.
- Full line of downlights, wall wash, and accents.
- Wide distribution allows for greater spacing.
- Suspended cable mount provides independent control of direct and indirect light
- Expands on 2SDCM color consistency between Calculite and OmniSpot families.

# C3C Calculite

## 3" Cylinder (round aperture)

### Features

**Lumens:** up to 2000  
**CRI:** 90 (min)  
**CCT:** 2700K-4000K  
 & D2W options  
**Lifetime:** 50,000hrs (L70)  
**Warranty:** 5 year



### Fixture

example: C3CPSA15940Z10UA

Series	Mounting	Style	Lumens	CRI/CCT	Dimming/Voltage	Finish
<b>C3C</b>						
C3C Calculite 3" Cylinder	PCS Pendant w/Cable 6' power/cord <sup>5</sup> PCM Pendant w/Cable 12' power/cord <sup>5</sup> PCL Pendant w/Cable 20' power/cord <sup>5</sup>	DL Downlight <sup>2</sup>	13 1250lm	9D2W 90 CRI/3000K-1800K	L01U Lutron PEQ EcoSystem 0.1% / Unv (120/277V)	A Aluminum B Black (matte) W White (matte) RAL RAL Color <sup>6</sup> (std code)
			15 1485lm	9D2W 90 CRI/3000K-1800K	Z10U 0-10V 1% / Unv (120/277V) ELV1 ELV (120V) / Unv (120/277V)	
			10 1000lm 15 1500lm 20 2000lm <sup>4</sup>	927 90 CRI/2700K 930 90 CRI/3000K 935 90 CRI/3500K 940 90 CRI/4000K	Z10U 0-10V 1% / Unv (120/277V) ELV1 ELV (120V) / Unv (120/277V) L01U Lutron PEQ EcoSystem 0.1% / Unv (120/277V)	
	PS Pendant w/Stem <sup>1</sup> S Surface	A Adjustable Accent <sup>2</sup>	15 1500lm	9D2W 90 CRI/3000K-1800K	Z10U 0-10V 1% / Unv (120/277V) ELV1 ELV (120V) / Unv (120/277V) L01U Lutron PEQ EcoSystem 0.1% / Unv (120/277V)	A Aluminum B Black (matte) W White (matte) RAL RAL Color <sup>6</sup> (std code)
			10 1000lm 15 1500lm 20 2000lm <sup>4</sup>	927 90 CRI/2700K 930 90 CRI/3000K 935 90 CRI/3500K 940 90 CRI/4000K		
	PS Pendant w/Stem <sup>1</sup> S Surface W Wall	DL Downlight <sup>2</sup>	13 1250lm	9D2W 90 CRI/3000K-1800K	L01U Lutron PEQ EcoSystem 0.1% / Unv (120/277V)	A Aluminum B Black (matte) W White (matte) RAL RAL Color <sup>6</sup> (std code)
			15 1485lm	9D2W 90 CRI/3000K-1800K	Z10U 0-10V 1% / Unv (120/277V) ELV1 ELV (120V) / Unv (120/277V)	
		WW Wall Wash	15 1500lm	9D2W 90 CRI/3000K-1800K	Z10U 0-10V 1% / Unv (120/277V) ELV1 ELV (120V) / Unv (120/277V) L01U Lutron PEQ EcoSystem 0.1% / Unv (120/277V)	
			10 1000lm 15 1500lm 20 2000lm <sup>4</sup>	927 90 CRI/2700K 930 90 CRI/3000K 935 90 CRI/3500K 940 90 CRI/4000K		
	W Wall	UDW Up/Down Wall Wash <sup>3</sup>	15 1500lm 20 2000lm 30 3000lm	927 90 CRI/2700K 930 90 CRI/3000K 935 90 CRI/3500K 940 90 CRI/4000K	Z10U 0-10V 1% / Unv (120/277V) ELV1 ELV (120V) / Unv (120/277V) L01U Lutron PEQ EcoSystem 0.1% / Unv (120/277V) (not available for 3000lm)	A Aluminum B Black (matte) W White (matte) RAL RAL Color <sup>6</sup> (std code)
			(lumens shown divide equally up & down)			
	W Wall	UD Direct/ Indirect <sup>2,3</sup>	10 1000lm 20 2000lm	927 90 CRI/2700K 930 90 CRI/3000K 935 90 CRI/3500K 940 90 CRI/4000K	Z10U 0-10V 1% / Unv (120/277V) ELV1 ELV (120V) / Unv (120/277V)	A Aluminum B Black (matte) W White (matte) RAL RAL Color <sup>6</sup> (std code)
			(lumens shown divide equally up & down)			
	SUS Suspended 6' power/cord SUM Suspended 12' power/cord SUL Suspended 20' power/cord	UD Direct/ Indirect <sup>2,3</sup>	20 2000lm 30 3000lm	927 90 CRI/2700K 930 90 CRI/3000K 935 90 CRI/3500K 940 90 CRI/4000K	Z10U 0-10V 1% / Unv (120/277V) ELV1 ELV (120V) / Unv (120/277V)	A Aluminum B Black (matte) W White (matte) RAL RAL Color <sup>6</sup> (std code)
			(lumens shown divide equally up & down)			

- Pendant Stem (PS) mountings need to be ordered with a suspended stem kit accessory for pendants.
- Downlight (DL) and Suspended Direct/Indirect (SU,UD) styles need to be ordered with one Reflector.  
Wall Mount Direct/Indirect (WUD) styles need to be ordered with two Reflectors.
- Nominal lumens shown is total luminaire, divided equally up and down.  
Up and down for WUDW & WUD styles are controlled on a single circuit.  
SU,UD styles are controlled on separate circuits.
- Available in white (W) or black (B) finishes only with Z10 or ELV1 dimming only.
- PCS/PCM/PCL mounting includes cable with matching finish to cylinder. RAL cylinder finish will be with a black cable.
- RAL standard colors can be specified upon request. Add RAL standard code to (RALxxxxx).

**Note: Please reference C3C specification sheet for more information on Reflectors, Optics and Accessories.**



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

**GENLYTE**  
**SOLUTIONS**  
 a @signify business

Signify North America Corp.  
 400 Crossing Blvd, Suite 600  
 Bridgewater, NJ 08807  
 Telephone: 800-555-0050

Signify Canada Ltd.  
 281 Hillmount Road,  
 Markham, ON, Canada L6C 2S3  
 Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.