

LIGHTOLIER
by  **Signify**

Downlighting

Calculite

C2 2" Round & Square



It may be small, but it is mighty

Calculite by Lightolier now includes a 2" aperture downlight allowing for even more options within the Calculite family for dressing the space.

Calculite 2" family includes

- Downlight, Wall Wash and Adjustable Accent
- Round and Square apertures
- 3 lumen packages: 600lm, 900lm, and 1500lm
- 4 CRI/CCT options: 90CRI & 2700/3000/3500/4000K
- Universal dimming driver: 0-10V/ELV/TE

For further details and availability, please contact your authorized representative.

© 2021 Signify Holding. All rights reserved.



www.lightolier.com

C2 Calculite 2"

Round & Square Downlight, Wall Wash, Adjustable Accent



Features

- **Lumens:** 600/900/1500
- **CRI:** 90 (min)
- **CCT:** 2700K - 4000K
- **Shape:** Round & Square
- **Styles:** Downlight, Wall Wash, Adj. Accent
- **Dimming:** Lutron PEQ 0.1% and 0-10V/ELV/TE/UNV
- **Voltage:** 120/277V
- **Trims:** 50° Cutoff die cast
- **Frames:** Remodeler (std), New Construction non-IC & AirSeal/IC/LC

Energy Star & CEC
Title 24/JA8 certified

Engine

Complete luminaire = Engine + Trim

example: C2RA06927SPUPZLS6010

Series ¹	Style	Lumen	CRI/CCT	Beams	Dimming/Voltage	Flange	Options	
C2R	Calculite 2" Round	A Adjustable Accent	06 600lm 09 900lm 15 1500lm	927 2700K 930 3000K 935 3500K 940 4000K	NS Narrow SP Spot NF Narrow Flood FL Flood	UPZU 0-10V 1% ELV 3% Triac 3% LU Lutron PEQ 100% - 0.1% Unv (120/277V)	F Flangeless ³	MesoOptics⁴ — Symmetrical soft focus LS6010 Linear spread 60x10 ASY21 Asymmetrical 21° beam angle ASY8 Asymmetrical 8° beam angle Hex Cell Louver HCL 2" hex cell louver

Trim

example: C2RAWT

Series	Style	Finish (painted)	Flange (finish)	Options
C2R	Calculite 2" Round	A Adjustable Accent	BT Textured Black BZ Bronze D Aluminum Diffuse CD Clear Diffuse (applied finish)	— White (matte) P Polished ² (aperture matching) F Flangeless ²
C2S	Calculite 2" Square	DL Downlight LW Lensed Wall Wash ²	WT Textured White	F Flangeless ² WL Wet Location ⁵

1. Standard light engine may be used as a remodeler. Optional traditional frame-in kits are available.
2. Order Lensed Wall Wash light engine (LW) only with the Flood (FL) beam option.
3. Flangeless code must be used for both light engine and trim (mud-in ring is integral with light engine).
4. Not available on wall wash light engine.
5. Available only with Downlight (DL) configurations.

Accessories (order & install separately)

Field Installed TIR Optics (for Downlight & Accent only)

CA2NSSFR	15° TIR reflector
CA2SPSFR	19° TIR reflector
CA2NFSFR	30° TIR reflector
CA2FLSFR	55° TIR reflector

Accent Accessories

CL2HCL	2" hex cell louver
---------------	--------------------

MesoOptics Accessories (for Downlight & Accent only)

CA2RSYM	Symmetrical
CA2RLS6010	60x10 linear spread
CA2RAS21	21° bend angle
CA2RAS8	8° bend angle

Accessories

SWZDT	SpaceWise wireless controller with dwell time functionality (order with UPZ dimming option only)
--------------	--



Visit [Signify.com/warranties](https://www.signify.com/warranties) for more information on Signify's standard 5-year limited warranty.



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.