

# PHILIPS

LED lamps

A19 lamps




---

## No matter the application, get the right light

**The new simplified portfolio of Philips A19 lamps** provides a wide variety of features such as dimming and 3-way. Omni-directional light and various color temperatures make sure you always have the right light at the right budget. Ideal for decorative and ambient lighting in retail outlets, hotels, restaurants, government buildings, and multi-unit residences.

# Philips A19 LED lamps



A19 Contractor-grade (dimmable)  
Available May 2024

A19 Contractor-grade (non-dimmable)  
Available September 2024




## Ordering, electrical and technical data (Subject to change without notice)

Product No. (6nc)	Model No. (12nc)	Description	Base	Watts (W)	Lumens (lm)	Volts (V)	CRI (min)	CCT (K)	Lifetime <sup>1</sup> (hrs)	Material	Legend
<b>A19 Contractor-grade (dimmable) Available May 2024</b>											
D	589606	929003750964	5A19/CNG/827/FR/P/E26/D 12/1CT	E26	40	450	120	80	2700	15000	Plastic A <b>NEW</b>
D	589614	929003751064	5A19/CNG/830/FR/P/E26/D 12/1CT	E26	40	450	120	80	3000	15000	Plastic A <b>NEW</b>
D	589622	929003751164	5A19/CNG/840/FR/P/E26/D 12/1CT	E26	40	450	120	80	4000	15000	Plastic A <b>NEW</b>
D	589630	929003751264	5A19/CNG/850/FR/P/E26/D 12/1CT	E26	40	450	120	80	5000	15000	Plastic A <b>NEW</b>
D	581751	929003579504	8A19/CNG/827/FR/P/E26/D 4/4CT	E26	60	0	120	80	2700	15000	Plastic A <b>Phase out</b>
D	589648	929003579564	8.8A19/CNG/827/FR/P/E26/D 12/1CT	E26	60	800	120	80	2700	15000	Plastic A <b>NEW</b>
D	581769	929003584804	8A19/CNG/830/FR/P/E26/D 4/4CT	E26	60	0	120	80	3000	15000	Plastic A <b>Phase out</b>
D	589663	929003584864	8.8A19/CNG/830/FR/P/E26/D 12/1CT	E26	60	800	120	80	3000	15000	Plastic A <b>NEW</b>
D	581777	929003584904	8A19/CNG/840/FR/P/E26/D 4/4CT	E26	60	0	120	80	4000	15000	Plastic A <b>Phase out</b>
D	589671	929003584964	8.8A19/CNG/840/FR/P/E26/D 12/1CT	E26	60	800	120	80	4000	15000	Plastic A <b>NEW</b>
D	581785	929003579604	8A19/CNG/850/FR/P/E26/D 4/4CT	E26	60	0	120	80	5000	15000	Plastic A <b>Phase out</b>
D	589655	929003579664	8.8A19/CNG/850/FR/P/E26/D 12/1CT	E26	60	800	120	80	5000	15000	Plastic A <b>NEW</b>
D	589689	929003751764	11A19/CNG/827/FR/P/E26/D 12/1CT	E26	75	1100	120	80	2700	15000	Plastic B <b>NEW</b>
D	589697	929003751864	11A19/CNG/830/FR/P/E26/D 12/1CT	E26	75	1100	120	80	3000	15000	Plastic B <b>NEW</b>
D	589705	929003751964	11A19/CNG/840/FR/P/E26/D 12/1CT	E26	75	1100	120	80	4000	15000	Plastic B <b>NEW</b>
D	589713	929003752064	11A19/CNG/850/FR/P/E26/D 12/1CT	E26	75	1100	120	80	5000	15000	Plastic B <b>NEW</b>
D	581801	929003585004	14A19/CNG/827/FR/P/E26/D 4/4CT	E26	100	1500	120	80	2700	15000	Plastic C <b>Phase out</b>
D	589721	929003585064	14A19/CNG/827/FR/P/E26/D 12/1CT	E26	100	1500	120	80	2700	15000	Plastic C <b>NEW</b>
D	581827	929003585104	14A19/CNG/830/FR/P/E26/D 4/4CT	E26	100	1500	120	80	3000	15000	Plastic C <b>Phase out</b>
D	589739	929003585164	14A19/CNG/830/FR/P/E26/D 12/1CT	E26	100	1500	120	80	3000	15000	Plastic C <b>NEW</b>
D	581835	929003585204	14A19/CNG/840/FR/P/E26/D 4/4CT	E26	100	1500	120	80	4000	15000	Plastic C <b>Phase out</b>
D	589747	929003585264	14A19/CNG/840/FR/P/E26/D 12/1CT	E26	100	1500	120	80	4000	15000	Plastic C <b>NEW</b>
D	581868	929003585304	14A19/CNG/850/FR/P/E26/D 4/4CT	E26	100	1500	120	80	5000	15000	Plastic C <b>Phase out</b>
D	589754	929003585364	14A19/CNG/850/FR/P/E26/D 12/1CT	E26	100	1500	120	80	5000	15000	Plastic C <b>NEW</b>
<b>A19 Contractor-grade (non-dimmable) Available September 2024</b>											
D	565119	929003004804	8.5A19/LED/927/FR/P/ND 4/1FB	E26		800	120	90	2700	11000	Plastic A <b>Phase out</b>
D	588939	929002311364	9A19/CNG/827/FR/P/E26/ND 4/1CT	E26	60	0	120	90	2700	15000	Plastic A <b>NEW</b>
D	565127	929003004904	8.5A19/LED/930/FR/P/ND 4/1FB	E26		800	120	90	3000	11000	Plastic A <b>Phase out</b>
D	589977	929002475464	9A19/CNG/830/FR/P/E26/ND 4/1CT	E26	60	0	120	90	3000	15000	Plastic A <b>NEW</b>
D	565135	929003005004	8.5A19/LED/950/FR/P/ND 4/1FB	E26		800	120	90	5000	11000	Plastic A <b>Phase out</b>
D	588947	929002311464	9A19/CNG/850/FR/P/E26/ND 4/1CT	E26	60	0	120	90	5000	15000	Plastic A <b>NEW</b>
D	565143	929003005104	10A19/LED/927/FR/P/ND 4/1FB	E26		1000	120	90	2700	11000	Plastic B <b>Phase out</b>
D	588897	929002311564	10A19/CNG/827/FR/P/E26/ND 4/1CT	E26	75	0	120	90	2700	15000	Plastic B <b>NEW</b>
D	565150	929003005204	10A19/LED/930/FR/P/ND 4/1FB	E26		1000	120	90	3000	11000	Plastic B <b>Phase out</b>
D	588905	929003798364	10A19/CNG/830/FR/P/E26/ND 4/1CT	E26	75	1000	120	80	3000	15000	Plastic B <b>NEW</b>
D	565168	929003005304	10A19/LED/950/FR/P/ND 4/1FB	E26		1000	120	90	5000	11000	Plastic B <b>Phase out</b>
D	588913	929002311664	10A19/CNG/850/FR/P/E26/ND 4/1CT	E26	75	0	120	90	5000	15000	Plastic B <b>NEW</b>
D	565176	929003005404	13.5A19/LED/927/FR/P/ND 4/1FB	E26		1500	120	90	2700	11000	Plastic C <b>Phase out</b>
D	588953	929002311764	14A19/CNG/827/FR/P/E26/ND 4/1CT	E26	100	0	120	90	2700	15000	Plastic C <b>NEW</b>
D	565184	929003005504	13.5A19/LED/930/FR/P/ND 4/1FB	E26		1500	120	90	3000	11000	Plastic C <b>Phase out</b>
D	588921	929003798464	14A19/CNG/830/FR/P/E26/ND 4/1CT	E26	100	1500	120	80	3000	15000	Plastic C <b>NEW</b>
D	565192	929003005604	13.5A19/LED/950/FR/P/ND 4/1FB	E26		1500	120	90	5000	11000	Plastic C <b>Phase out</b>
D	588961	929002311864	14A19/CNG/850/FR/P/E26/ND 4/1CT	E26	100	0	120	90	5000	15000	Plastic C <b>NEW</b>

1. Tested to B50 L70 requirement. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70). Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed. Warranty is based off of 15,000 hour claim.

D = Damp loc. E = Enclosed suitable

# Philips A19 LED lamps



A19 CorePro T20 (dimmable)  
A19 MasterClass Warm-Glow  
Available September 2024



## Ordering, electrical and technical data (Subject to change without notice)

Product No. (6nc)	Model No. (12nc)	Description	Base	Watts (W)	Lumens (lm)	Volts (V)	CRI (min)	CCT (K)	Lifetime <sup>1</sup> (hrs)	Material	Lgd	
<b>A19 CorePro T20 (dimmable)</b>											<b>Available September 2024</b>	
D	550400	929002035704	5A19/PER/927/P/E26/DIM 6/1FB T20	E26	40	450	120	90	2700	25000	Plastic	Phase out
D	550400	929002035704	5A19/COR/927/FR/P/E26/DIM/T20 6/1CT	E26	40	450	120	90	2700	25000	Plastic	NEW
D	550434	929002036104	8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT	E26	60	800	120	90	2700	25000	Plastic	
D	550442	929002036204	8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT	E26	60	800	120	90	3000	25000	Plastic	
D	545897	929002032304	8.8A19/COR/940/FR/P/E26/DIM/T20 6/1CT	E26	60	800	120	90	4000	25000	Plastic	
D	550459	929002036304	8.8A19/COR/950/FR/P/E26/DIM/T20 6/1CT	E26	60	800	120	90	5000	25000	Plastic	
D	561035	929002385204	12.2A19/COR/927/FR/P/E26/DIM/T20 6/1CT	E26	75	1100	120	90	2700	25000	Plastic	
D	561043	929002385304	12.2A19/COR/930/FR/P/E26/DIM/T20 6/1CT	E26	75	1100	120	90	3000	25000	Plastic	
D	561050	929002385404	12.2A19/COR/940/FR/P/E26/DIM/T20 6/1CT	E26	75	1100	120	90	4000	25000	Plastic	
D	560994	929002285204	12.2A19/COR/950/FR/P/E26/DIM/T20 6/1CT	E26	75	1100	120	90	5000	25000	Plastic	
D E	561068	929002385504	16A19/PER/927/P/E26/DIM 6/1FB T20	E26	100	1600	120	90	2700	15000	Plastic	Phase out
D	588681	929003784604	16A19/COR/927/FR/P/E26/DIM/T20 6/1CT	E26	100	1500	120	90	2700	25000	Plastic	NEW
D E	561076	929002385604	16A19/PER/930/P/E26/DIM 6/1FB T20	E26	100	1600	120	90	3000	15000	Plastic	Phase out
D	588673	929003784704	16A19/COR/930/FR/P/E26/DIM/T20 6/1CT	E26	100	1500	120	90	3000	25000	Plastic	NEW
D E	561456	929002385704	16A19/PER/940/P/E26/DIM 6/1FB T20	E26	100	1600	120	90	4000	15000	Plastic	Phase out
D	588665	929003784804	16A19/COR/940/FR/P/E26/DIM/T20 6/1CT	E26	100	1500	120	90	4000	25000	Plastic	NEW
D E	561019	929002285304	16A19/PER/950/P/E26/DIM 6/1FB T20	E26	100	1600	120	90	5000	15000	Plastic	Phase out
D	588657	929003784904	16A19/COR/950/FR/P/E26/DIM/T20 6/1CT	E26	100	1500	120	90	5000	25000	Plastic	NEW
<b>A19 MasterClass Warm-Glow</b>											<b>Available September 2024</b>	
D	479428	929001940704	5A19/MAS/927-22/FR/P/E26/T20 6/1CT	E26	40	450	120	90	2200-2700	25000	Plastic	NEW
D	479444	929001940904	8.8A19/MAS/927-22/FR/P/E26/T20 6/1CT	E26	60	800	120	90	2200-2700	25000	Plastic	NEW
D	561000	929002285404	12.2A19/MAS/927-22/FR/P/E26/T20 6/1CT	E26	75	1100	120	90	2200-2700	25000	Plastic	NEW
D	588780	929003784504	16A19/MAS/927-22/FR/P/E26/T20 6/1CT	E26	100	1500	120	90	2200-2700	25000	Plastic	NEW
<b>A21</b>											<b>Available now</b>	
D	571497	929002343033	29A21/PER/827/FR/P/E26/WG/HO 4/1PF	E26	150	2610	120	80	2200-2700	15000	Plastic	E
D E	558684	929002327634	16A21/PER/930/P/GU24/DIM 4/1FB T20	GU24	100	1600	120	90	3000	15000	Plastic	D
D	571521	929002285133	18.5A21/PER/927/FR/P/E26/3WAY/T20 4/1PF 3-Way	E26	150-100-50	2600-1600-800	120	90	2700	15000	Plastic	F

1. Tested to B50 L70 requirement. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70). Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed. Warranty is based off of 15,000 hour claim.

D = Damp loc. E = Enclosed suitable

For more information on Philips' limited warranty please visit [www.philips.com/warranties](http://www.philips.com/warranties).



© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.



Signify North America Corp.  
400 Crossing Boulevard,  
Bridgewater, NJ 08807  
Telephone 800-555-0050

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.