

PHILIPS

LED lamps


A19 lamps



No matter the application, get the right light

The new simplified portfolio of Philips A19 lamps provides a wide variety of features such as dimming, 3-Way & Color-Selectable. Omni-directional light and various color temperatures make sure you always have the right light at the right budget. Ideal for decorative and ambient lighting in retail outlets, hotels, restaurants, government buildings, and multi-unit residences.

Philips A19 LED lamps



Ordering, electrical and technical data (Subject to change without notice)

6NC	12NC	Description	Volts (V)	Watts (W)	Equiva- lent	CRI (min)	CCT (K)	Lifetime (Hrs)	Lumens (lm)	T20 Status	Material	Leg- end
Contractor Grade Dimmable A19 Lamps (E26)												
D 589606	929003750964	5A19/CNG/827/FR/P/E26/D 12/1CT	120	5	40	80	2700	15,000	450	No	Plastic	A
D 589614	929003751064	5A19/CNG/830/FR/P/E26/D 12/1CT	120	5	40	80	3000	15,000	450	No	Plastic	A
D 589622	929003751164	5A19/CNG/840/FR/P/E26/D 12/1CT	120	5	40	80	4000	15,000	450	No	Plastic	A
D 589630	929003751264	5A19/CNG/850/FR/P/E26/D 12/1CT	120	5	40	80	5000	15,000	450	No	Plastic	A
D 589648	929003579564	8.8A19/CNG/827/FR/P/E26/D 12/1CT	120	8.8	60	80	2700	15,000	800	No	Plastic	A
D 589663	929003584864	8.8A19/CNG/830/FR/P/E26/D 12/1CT	120	8.8	60	80	3000	15,000	800	No	Plastic	A
D 589671	929003584964	8.8A19/CNG/840/FR/P/E26/D 12/1CT	120	8.8	60	80	4000	15,000	800	No	Plastic	A
D 589655	929003579664	8.8A19/CNG/850/FR/P/E26/D 12/1CT	120	8.8	60	80	5000	15,000	800	No	Plastic	A
D 589689	929003751764	11A19/CNG/827/FR/P/E26/D 12/1CT	120	11	75	80	2700	15,000	1100	No	Plastic	B
D 589697	929003751864	11A19/CNG/830/FR/P/E26/D 12/1CT	120	11	75	80	3000	15,000	1100	No	Plastic	B
D 589705	929003751964	11A19/CNG/840/FR/P/E26/D 12/1CT	120	11	75	80	4000	15,000	1100	No	Plastic	B
D 589713	929003752064	11A19/CNG/850/FR/P/E26/D 12/1CT	120	11	75	80	5000	15,000	1100	No	Plastic	B
D 589721	929003585064	14A19/CNG/827/FR/P/E26/D 12/1CT	120	14	100	80	2700	15,000	1500	No	Plastic	C
D 589739	929003585164	14A19/CNG/830/FR/P/E26/D 12/1CT	120	14	100	80	3000	15,000	1500	No	Plastic	C
D 589747	929003585264	14A19/CNG/840/FR/P/E26/D 12/1CT	120	14	100	80	4000	15,000	1500	No	Plastic	C
D 589754	929003585364	14A19/CNG/850/FR/P/E26/D 12/1CT	120	14	100	80	5000	15,000	1500	No	Plastic	C
Contractor Grade Non-Dimmable A19 Lamps (E26)												
D 588939	929002311364	9A19/CNG/827/FR/P/E26/ND 4/1CT	120	9	60	80	2700	15,000	800	No	Plastic	A
D 589977	929002475464	9A19/CNG/830/FR/P/E26/ND 4/1CT	120	9	60	80	3000	15,000	800	No	Plastic	A
D 588947	929002311464	9A19/CNG/850/FR/P/E26/ND 4/1CT	120	9	60	80	5000	15,000	800	No	Plastic	A
D 588897	929002311564	10A19/CNG/827/FR/P/E26/ND 4/1CT	120	10	75	80	2700	15,000	1000	No	Plastic	B
D 588905	929003798364	10A19/CNG/830/FR/P/E26/ND 4/1CT	120	10	75	80	3000	15,000	1000	No	Plastic	B
D 588913	929002311664	10A19/CNG/850/FR/P/E26/ND 4/1CT	120	10	75	80	5000	15,000	1000	No	Plastic	B
D 588953	929002311764	14A19/CNG/827/FR/P/E26/ND 4/1CT	120	14	100	80	2700	15,000	1500	No	Plastic	C
D 588921	929003798464	14A19/CNG/830/FR/P/E26/ND 4/1CT	120	14	100	80	3000	15,000	1500	No	Plastic	C
D 588961	929002311864	14A19/CNG/850/FR/P/E26/ND 4/1CT	120	14	100	80	5000	15,000	1500	No	Plastic	C
CorePro Dimmable T20 A19 Lamps (E26)												
D 550400	929002035704	5A19/COR/927/FR/P/E26/DIM/T20 6/1CT	120	5	40	90	2700	25,000	450	Yes	Plastic	A
D 550434	929002036104	8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT	120	8.8	60	90	2700	25,000	800	Yes	Plastic	A
D 550442	929002036204	8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT	120	8.8	60	90	3000	25,000	800	Yes	Plastic	A
D 545897	929002032304	8.8A19/COR/940/FR/P/E26/DIM/T20 6/1CT	120	8.8	60	90	4000	25,000	800	Yes	Plastic	A
D 550459	929002036304	8.8A19/COR/950/FR/P/E26/DIM/T20 6/1CT	120	8.8	60	90	5000	25,000	800	Yes	Plastic	A
D 561035	929002385204	12.2A19/COR/927/FR/P/E26/DIM/T20 6/1CT	120	12.2	75	90	2700	25,000	1100	Yes	Plastic	B
D 561043	929002385304	12.2A19/COR/930/FR/P/E26/DIM/T20 6/1CT	120	12.2	75	90	3000	25,000	1100	Yes	Plastic	B
D 561050	929002385404	12.2A19/COR/940/FR/P/E26/DIM/T20 6/1CT	120	12.2	75	90	4000	25,000	1100	Yes	Plastic	B
D 560994	929002285204	12.2A19/COR/950/FR/P/E26/DIM/T20 6/1CT	120	12.2	75	90	5000	25,000	1100	Yes	Plastic	B
D 588681	929003784604	14A19/COR/927/FR/P/E26/DIM/T20 6/1CT	120	14	100	90	2700	25,000	1500	Yes	Plastic	C
D 588673	929003784704	14A19/COR/930/FR/P/E26/DIM/T20 6/1CT	120	14	100	90	3000	25,000	1500	Yes	Plastic	C
D 588665	929003784804	14A19/COR/940/FR/P/E26/DIM/T20 6/1CT	120	14	100	90	4000	25,000	1500	Yes	Plastic	C
D 588657	929003784904	14A19/COR/950/FR/P/E26/DIM/T20 6/1CT	120	14	100	90	5000	25,000	1500	Yes	Plastic	C

Philips A19 LED lamps



Ordering, electrical and technical data (Subject to change without notice)

6NC	12NC	Description	Volts (V)	Watts (W)	Equiva- lent	CRI (min)	CCT (K)	Lifetime (Hrs)	Lumens (lm)	T20 Status	Material	Leg- end	
MasterClass WarmGlow Dimmable A19 Lamps (E26)													
D	479428	929001940704	5A19/MAS/927-22/FR/P/E26/T20 6/1CT	120	5	40	90	2700-2200	25,000	450	Yes	Plastic	-
D	479444	929001940904	8.8A19/MAS/927-22/FR/P/E26/T20 6/1CT	120	8.8	60	90	2700-2200	25,000	800	Yes	Plastic	-
D	561000	929002285404	12.2A19/MAS/927-22/FR/P/E26/T20 6/1CT	120	12.2	75	90	2700-2200	25,000	1100	Yes	Plastic	-
D	588780	929003784504	14A19/MAS/927-22/FR/P/E26/T20 6/1CT	120	14	100	90	2700-2200	25,000	1500	Yes	Plastic	-
MasterClass Multi-CCT Dimmable A19 Lamps (E26)													
D	610857	929003620334	8A19/COR/DipS/5CCT/FR/P/E26/DIM/T20 1CT	120	8	60	90	2700/3000/ 3500/4000/5000	15,000	800	Yes	Plastic	G
D	610865	929003620434	14A19/COR/DipS/5CCT/FR/P/E26/DIM/T20 1CT	120	14	100	90	2700/3000/ 3500/4000/5000	15,000	1500	Yes	Plastic	G
A21 lamps													
D	571497	929002343033	29A21/PER/827/FR/P/E26/WG/HO 4/1PF	120	29	150	80	2700/2200	15,000	2610	Out of scope	Plastic	E
D	558684	929002327634	16A21/PER/930/P/GU24/DIM 4/1FB T20	120	16	100	90	3000	15,000	1600	Yes	Plastic	D
D	571521	929002285133	18.5A21/PER/927/FR/P/E26/3WAY/T20 4/1PF	120	18.5	150/100/ 50	90	2700	15,000	2600/ 1600/ 800	Yes	Plastic	F

1. Tested to B50 L70 requirement. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70). Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed. Warranty is based off of 15,000 hour claim.

D = Suitable for damp locations E = Enclosed suitable

For more information on Philips' limited warranty please visit www.philips.com/warranties.



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.



Signify North America Corp.
400 Crossing Boulevard,
Bridgewater, NJ 08807
Telephone 800-555-0050

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.