PIERLITE®

IPART VEET

BWP ECO Weatherproof Batten Gen2

BWPECO202ECS

- Lockable stainless steel clip
- Wide Body
- Easy installation with large terminal block, 20mm cable gland and one optional knock-out in the body



COLOUR SELECT

Performance

System Power	18W
Exit Lumen	2500lm, 2100lm, 2100lm
Efficacy	138lm/W, 116lm/W, 116lm/W
CCT	4000K, 3000K, 6000K
CRI	80
Operating Temperature	0 to 40
MacAdam Steps	5SDCM
Ingress Protection Rating	IP65
Impact Rating	IK08
Beam Angle	100°
Warranty	3 Years
Lifetime	54,000hrs (L70/B50)


Physical


Dimensions	L655 x W130 x H92 mm
Diffuser	Polycarbonate
Luminaire Colour	Grey (Light)
Weight	1kg
Luminaire Material	Plastic (Polycarbonate)
Driver Location	Integrated
Finish	UV Stabilised
Installation	Surface Mounting

Electrical

Dimming	Non - Dimmable
Voltage	240V
Line Voltage Frequency	50Hz
Inrush Current	10.2A
Line Current	0.08A
Electrical Rating	Class 1

Line Drawings





Product Images



*Rated LED design life where stated is based upon application of Pierlite's operating and maintenance guidelines; see pierlite.com.au. Actual product life may vary dependent upon frequency of maintenance and product application. Due to continual product improvement, information is subject to change without notification. standard Terms and Conditions apply

PM 8:33:22 2026-08-25