PIERLITE®

IPART VEET

BWP ECO Weatherproof Batten Gen2

BWPECO404ECSLS

- High efficay with up to 130lm/w
- Select colour temperature from 3000K/4000K/6000K
- Select lumen output from 20W/27W/33W/40W



LUMEN SELECT™ | COLOUR SELECT

Performance

System Power	40W, 33W, 27W, 20W
Exit Lumen	5200lm, 4200lm, 3600lm, 2500lm
Tuneable CCT	N/AK to N/A K
CCT	4000K, 3000K, 6000K
CRI	80
Operating Temperature	0 to 40
MacAdam Steps	5SDCM
Ingress Protection Rating	IP65
Impact Rating	IK08
Beam Angle	100°
Warranty	3 Years
Lifetime	54,000hrs (L70/B50)

Physical

Dimensions	L1265 x W130 x H92 mm
Diffuser	Polycarbonate
Luminaire Colour	Grey (Light)
Weight	1.9kg
Luminaire Material	Plastic (Polycarbonate)
Driver Location	Integrated
Finish	UV Stabilised
Installation	Surface Mounting


Emergency

Emergency Version	No

Electrical

Dimming	Non - Dimmable
Voltage	240V
Line Voltage Frequency	50Hz
Inrush Current	12.3A
Line Current	0.19A
Electrical Rating	Class 1

Line Drawings



Product Images



*Rated LED design life where stated is based upon application of Pierlite's operating and maintenance guidelines; see pierlite.com.au. Actual product life may vary dependent upon frequency of maintenance and product application. Due to continual product improvement, information is subject to change without notification. standard Terms and Conditions apply

PM 8:33:33 2026-08-25