# Director 2 Exit Light

## DIRLEDPDSL

- Wall & Ceiling mount,complete with replaceable lithium iron phosphate (LiFeP04) battery
- Manual test and maintained emergency exit
- Also available in DALI version




## Performance

| | |
|---|---|
| System Power | 4.6W |
| Exit Lumen | 220lm |
| Efficacy | 48lm/W |
| Operating Temperature | 0 to 40 |
| Ingress Protection Rating | IP20 |
| Warranty | 3 Years |
| Lifetime | 50,000hrs (L70/B50) |

## Physical

| | |
|---|---|
| Dimensions | L380 x W160 x H220 mm |
| Diffuser | Acrylic |
| Luminaire Colour | White |
| Weight | 1.3kg |
| Luminaire Material | Plastic (Acrylic) |
| Driver Location | Integrated |
| Finish | White |
| Installation | Ceiling Surface Mounted |

## Emergency

| | |
|---|---|
| Option | Maintained |
| Testing System | Self Test |
| Battery Voltage | 3.2V |
| Battery Capacity | 1500mA |
| Emergency Mode Wattage | 4.6W |
| Emergency Mode Lumen | 48lm |
| Classification | C0/C180: D10 & C90/C270: D10 |
| Battery Charge | 4hr |
| Viewing Distance | 24m |


## Electrical

| | |
|---|---|
| Voltage | 240V |
| Electrical Rating | Class 2 |

## AS/NZS 2293.1:2018 Classification Table

| ALLOWABLE LUMINAIRE MOUNTING HEIGHT (M) | LUMINAIRE MAXIMUM SPACING FOR EACH PLAN (M) | |
|---|---|---|
| | C0/180 | C90/C270 |
| 2.1 | 7.8 | 8.5 |
| 2.4 | 8 | 8.8 |
| 2.7 | 8.1 | 8.9 |

## Line Drawings




(Ceiling Mount)

## Accessories

| | |
|---|---|
| BATPK1500/1L11 | LiFePO4, battery pack 1 CELL3.2V 1500mAh |

*Rated LED design life where stated is based upon application of Pierlite's operating and maintenance guidelines; see pierlite.com.au. Actual product life may vary dependent upon frequency of maintenance and product application. Due to continual product improvement, information is subject to change without notification.
standard Terms and Conditions apply



Pierlite is a division of Signify Innovations Australia Pty Ltd