Director 2 Exit Light

DIRLEDPSSL

- Wall & Ceiling mount,complete with replaceable lithium iron phosphate (LiFeP04) battery
- Manual test and maintained emergency exit
- Also available in DALI version



Performance

System Power	4.6W
Exit Lumen	220lm
Efficacy	48lm/W
Operating Temperature	0 to 40
Ingress Protection Rating	IP20
Warranty	3 Years
Lifetime	50,000hrs (L70/B50)

Physical

Dimensions	L380 x W110 x H160 mm
Diffuser	Acrylic
Luminaire Colour	White
Weight	1.3kg
Luminaire Material	Plastic (Acrylic)
Driver Location	Integrated
Finish	White
Installation	Wall Surface Mounted

Emergency

Option	Maintained
Testing System	Self Test
Battery Capacity	1500mA
Emergency Mode Wattage	4.6W
Emergency Mode Lumen	48lm
Classification	C0:D6.3C90/C270:D5
Viewing Distance	24m

Electrical

Voltage	240V
Electrical Rating	Class 2


Accessories

BATPK1500/1L11	LiFePO4, battery pack 1 CELL3.2V 1500mAh

AS/NZS 2293.1:2018 Classification Table

ALLOWABLE LUMINAIRE MOUNTING HEIGHT (M)	LUMINAIRE MAXIMUM SPACING FOR EACH PLAN (M)			
	C0	C90	C180	C270
2.1	3.7	4.1	0	4.1
2.4	0	4.1	0	4.1
2.7	0	0	0	0

Line Drawings



Product Images



*Rated LED design life where stated is based upon application of Pierlite's operating and maintenance guidelines; see pierlite.com.au. Actual product life may vary dependent upon frequency of maintenance and product application. Due to continual product improvement, information is subject to change without notification. standard Terms and Conditions apply