EcoSet Sensor

ECOSETSENSPIR

- Maximum LED Load 1000W
- 2-in-1 surface and recessed mounting PIR sensor with daylight switching
- Smart timer with delay time options (2/5/15/30 min)



Performance

System Power	1.2W
Operating Temperature	0 to 40
Ingress Protection Rating	IP20
Warranty	5 Years
Lifetime	50,000hrs (L70/B10)

Physical

Dimensions	L94 x W94 x H37.80 mm
Cutout Diameter	85mm
Luminaire Colour	White
Weight	0.14kg
Luminaire Material	Plastic (Polycarbonate)
Installation	Surface Mount/Recessed Mount


Sensor

Sensor Type	PIR

Electrical

Voltage	240V
Line Voltage Frequency	50Hz/60Hz
Electrical Rating	Class II

Line Drawings



Product Images



Product Images



*Rated LED design life where stated is based upon application of Pierlite's operating and maintenance guidelines; see pierlite.com.au. Actual product life may vary dependent upon frequency of maintenance and product application. Due to continual product improvement, information is subject to change without notification. standard Terms and Conditions apply

PM 9:16:47 2026-08-25