Guardian 2 Emergency Floodlight

GRLED7FL-L

- Versatile non-maintained LED emergency flood light compliant to AS/NZS2293
- Surface mounted (wall and ceiling) white finish
- IP20 as standard; weatherproof enclosure available with IP65 certification



Performance

System Power	4W
Exit Lumen	616lm
Efficacy	100lm/W
CCT	4000K
CRI	80
Operating Temperature	0 to 40
Ingress Protection Rating	IP20
Warranty	3 Years
Lifetime	50,000hrs (L70/B50)


Physical

Dimensions	L350 x W80 x H80 mm
Reflector	Plastic (Polycarbonate)
Diffuser	Polycarbonate
Luminaire Colour	White
Weight	1kg
Luminaire Material	Plastic (Polycarbonate)
Driver Location	Integrated
Finish	White
Installation	Ceiling or Wall Mounting


Emergency

Emergency Version	Yes
Option	Non Maintained
Battery	LiFePO4
Battery Voltage	6.4V
Battery Capacity	3200mA
Emergency Mode Wattage	4W
Emergency Mode Lumen	456lm
Battery Charge	2hr

Line Drawings



Product Images




Electrical

Dimming	Non - Dimmable
Voltage	240V
Inrush Current	30A
Inrush Current Duration	20µs
Line Current	0.04A
Electrical Rating	Class 2


Accessories

GRWPENCL	GUARDIAN LED WEATHERPROOF IP65 ENCLOSURE
DGLCEM3200/2L12	Battery LiFePO4 2Cell 6.4V 3200mAh (2HR)

Line Drawings



PRODUCT CODE: GRLED7FL-L



IP65 ENCLOSURE CODE: GRWPENCL

Product Images





*Rated LED design life where stated is based upon application of Pierlite's operating and maintenance guidelines; see pierlite.com.au. Actual product life may vary dependent upon frequency of maintenance and product application. Due to continual product improvement, information is subject to change without notification.
standard Terms and Conditions apply