Nipper Batten Gen2

NIPBAT404ECSLSG2

- Designed with a wide 130mm width base to easily replace old and energy consuming twin fluorescent battens.
- Flicker free LED driver built-in for increased visual acuity and comfort.
- Option for emergency with Lithium Iron Phosphate Battery 2.5W @ 313lm available



LUMEN SELECT | COLOUR SELECT

Performance

System Power	36W, 30W, 25W, 20W
Exit Lumen	4000lm, 4400lm, 3800lm, 3500lm, 3000lm, 3300lm, 2400lm, 2600lm
Efficacy	110lm/W
CCT	4000K, 5000K, 6500K
CRI	80
Operating Temperature	0 to 40
MacAdam Steps	5SDCM
Ingress Protection Rating	IP20
Beam Distribution	Symmetric
Warranty	5 Years
Lifetime	54,000hrs (L80/B50) @40 ºC


Physical

Dimensions	L1230 x W130 x H74 mm
Diffuser	Polycarbonate
Luminaire Colour	White
Weight	2.1kg
Luminaire Material	Steel (Mild)
Driver Location	Integrated
Finish	Powder Coated
Installation	Surface Mounting

Electrical

Voltage	240V
Line Voltage Frequency	50Hz/60Hz
Inrush Current	17A
Inrush Current Duration	140µs
Line Current	0.16A
Electrical Rating	Class I

Line Drawings



Product Images

*Rated LED design life where stated is based upon application of Pierlite's operating and maintenance guidelines; see pierlite.com.au. Actual product life may vary dependent upon frequency of maintenance and product application. Due to continual product improvement, information is subject to change without notification. standard Terms and Conditions apply

PM 9:11:49 2026-08-25