# OBL MINI LED Batten

## OBL600

- Made with UV resistant polycarbonate body for durability and long product lifetime
- Comes with a frosted opal diffuser for that comfortable and clean ambience.
- Built in 3-way switch for quick and easy adjustment of light levels



LUMEN SELECT | COLOUR SELECT

### Performance

| | |
|---|---|
| System Power | 15W, 10W |
| Exit Lumen | 1680lm, 1000lm |
| Efficacy | 112lm/W, 100lm/W |
| CCT | 4000K, 3000K |
| CRI | 80 |
| Operating Temperature | 0 to 45 |
| Ingress Protection Rating | IP44 |
| Beam Distribution | Asymmetric |
| Warranty | 3 Years |
| Lifetime | 54,000hrs (L70/B50) |


### Physical

| | |
|---|---|
| Dimensions | L595 x W60 x H70.70 mm |
| Diffuser | Opal |
| Luminaire Colour | White |
| Weight | 0.40kg |
| Luminaire Material | Plastic (Polycarbonate) |
| Driver Location | Integrated |
| Finish | Powder Coated |
| Installation | Surface Mounting |

### Electrical

| | |
|---|---|
| Dimming | Non - Dimmable |
| Voltage | 240V |
| Line Voltage Frequency | 50Hz |
| Inrush Current | 5A |
| Inrush Current Duration | 350µs |
| Line Current | 0.09A |
| Electrical Rating | Class II |

### Line Drawings




### Product Images



## Product Images





*Rated LED design life where stated is based upon application of Pierlite's operating and maintenance guidelines; see pierlite.com.au. Actual product life may vary dependent upon frequency of maintenance and product application. Due to continual product improvement, information is subject to change without notification.
standard Terms and Conditions apply



Pierlite is a division of Signify Innovations Australia Pty Ltd