OBL MINI LED Batten

OBL900

- Made with UV resistant polycarbonate body for durability and long product lifetime
- Comes with a frosted opal diffuser for that comfortable and clean ambience.
- Built in 3-way switch for quick and easy adjustment of light levels



LUMEN SELECT | COLOUR SELECT

Performance

System Power	20W, 20W
Exit Lumen	2100lm, 2000lm
Efficacy	105lm/W, 100lm/W
CCT	4000K, 3000K
CRI	80
Operating Temperature	0 to 45
Ingress Protection Rating	IP44
Beam Distribution	Asymmetric
Warranty	3 Years
Lifetime	54,000hrs (L70/B50)


Physical

Dimensions	L895 x W60 x H70.70 mm
Diffuser	Opal
Luminaire Colour	White
Weight	0.57kg
Luminaire Material	Plastic (Polycarbonate)
Driver Location	Integrated
Finish	Powder Coated
Installation	Surface Mounting

Electrical

Dimming	Non - Dimmable
Voltage	240V
Inrush Current	5A
Inrush Current Duration	350µs
Line Current	0.11A
Electrical Rating	Class II

Line Drawings



Product Images



Product Images





*Rated LED design life where stated is based upon application of Pierlite's operating and maintenance guidelines; see pierlite.com.au. Actual product life may vary dependent upon frequency of maintenance and product application. Due to continual product improvement, information is subject to change without notification.
standard Terms and Conditions apply