PIERLITE®

IPART

Orion Oyster Gen3

ORN23W3/4/6KDG3



- Comes with a removable trim and a pleasant opal diffuser for even light distribution
- Using a robust metal base for excellent heat dissipation and longer service life
- Colour Select: 3000K, 4000K and 6000K and Lumen Select. Phase Dimmable

LUMEN SELECT™ | COLOUR SELECT

Performance

System Power	23W, 16W
Exit Lumen	2000lm, 1900lm, 1300lm, 1400lm
Efficacy	95lm/W
CCT	4000K, 6000K, 3000K
CRI	80
Operating Temperature	0 to 40
Ingress Protection Rating	IP54
Beam Angle	100°
Warranty	3 Years
Lifetime	54,000hrs (L70/B50)


Physical

Dimensions	Ø350 x H80 mm
Diffuser	PMMA
Luminaire Colour	White
Weight	0.75kg
Luminaire Material	Steel (Mild)
Driver Location	Integrated
Finish	Powder Coated
Installation	Surface Mounting

Electrical

Dimming	Phase
Voltage	240V
Inrush Current	3.1A
Inrush Current Duration	188µs
Line Current	0.10A
Electrical Rating	Class 1

Line Drawings



Product Images



Product Images



*Rated LED design life where stated is based upon application of Pierlite's operating and maintenance guidelines; see pierlite.com.au. Actual product life may vary dependent upon frequency of maintenance and product application. Due to continual product improvement, information is subject to change without notification. standard Terms and Conditions apply