Pathfinder ECO Emergency Light

PFLED-ECO

- Recessed mount white finish
- Easy installation flex and plug included
- Non Maintained Emergency operation



Performance

System Power	1.5W
Exit Lumen	217lm
Efficacy	144lm/W
CCT	6500K
CRI	70
Operating Temperature	0 to 40
Ingress Protection Rating	IP20
Warranty	3 Years
Lifetime	50,000hrs (L70/B50)

Physical

Dimensions	Ø140 x H34 mm
Cutout Diameter	75mm
Luminaire Colour	White
Weight	0.36kg
Luminaire Material	Plastic (Polycarbonate)
Driver Location	Remote
Finish	Matt White
Installation	Recessed


Emergency

Emergency Version	Yes
Option	Non Maintained
Testing System	Manual
Battery	LiFePO4
Battery Voltage	3.2V
Battery Capacity	1500mA
Emergency Mode Wattage	1.5W
Emergency Mode Lumen	217lm
Classification	C0/C180:D40 & C90/C270 : D40
Battery Charge	2hr

AS/NZS 2293.1:2018 Classification Table

ALLOWABLE LUMINAIRE MOUNTING HEIGHT (M)	LUMINAIRE MAXIMUM SPACING FOR EACH PLAN (M)		
	C0	C90/C270	C180
2.1	11.5	11.5	11.5
2.4	13.2	13.2	13.2
2.7	14.8	14.8	14.8
3	16.5	16.5	16.5
3.3	18.1	18.1	18.1
3.6	19.5	19.5	19.5
4	20.1	20.1	20.1
4.5	20.7	20.7	20.7
5	21.2	21.2	21.2
6	22.1	22.1	22.1
7	22.6	22.6	22.6

Line Drawings



Product Images




Electrical

Voltage	240V
Line Voltage Frequency	50Hz
Inrush Current	10A
Line Current	0.03A
Electrical Rating	Class II

Accessories

PFSKIT-L2	PATHFINDER 2 D80 SURFACEKIT WHITE
FFLEDVK	FFLEDVK CEIL MNT VANDAL KIT

Line Drawings



Accessories



PFSKIT-L2

*Rated LED design life where stated is based upon application of Pierlite's operating and maintenance guidelines; see pierlite.com.au. Actual product life may vary dependent upon frequency of maintenance and product application. Due to continual product improvement, information is subject to change without notification. standard Terms and Conditions apply

Pierlite is a division of Signify Innovations Australia Pty Ltd