Sirroco Wall Light

RWL27/30/40BLK

- Selectable wattage (7W / 12W / 17W / 22W) for adaptable lumen output
- DIP-switch selectable CCT (2700K / 3000K / 4000K) for on-site flexibility
- IP65 & IK10 rated – weatherproof and impact resistant for demanding environments



LUMEN SELECT | COLOUR SELECT

Performance

System Power	22W, 17W, 12W, 7W
Exit Lumen	1940lm, 1570lm, 1180lm, 710lm, 1940lm, 1590lm, 1190lm, 1820lm, 1500lm, 1130lm, 670lm
Efficacy	88lm/W
CCT	2700K, 3000K, 4000K
CRI	90
Operating Temperature	-20 to +40
MacAdam Steps	5SDCM
Ingress Protection Rating	IP65
Impact Rating	IK10
Beam Angle	130°
Warranty	5 Years
Lifetime	54,000hrs (L80/B10) @40 ºC


Physical

Dimensions	L250 x W250 x H62 mm
Luminaire Colour	Black
Weight	1.2kg
Luminaire Material	Aluminium
Driver Location	Integrated
Finish	Powder Coated
Installation	Surface Mounting

Electrical

Voltage	240V
Line Voltage Frequency	50Hz/60Hz
Inrush Current	8A
Inrush Current Duration	100µs
Line Current	0.09A
Surge protection	Yes
Electrical Rating	Class I

Line Drawings



Product Images



Product Images







