# Slimline Batten

## SLBAT202ECSLS



- Made with durable low profile metal housing with frosted opal diffuser for uniform illumination.
- Energy efficient and highly reliable up to 100Lm/W and 54,000hrs lifetime.
- Built-in flicker free LED driver for increased visual comfort.

LUMEN SELECT | COLOUR SELECT

### Performance

| | |
|---|---|
| System Power | 20W, 17W, 14W |
| Exit Lumen | 1900lm, 1700lm, 1450lm, 2200lm, 1600lm, 2000lm, 1800lm, 1550lm |
| Efficacy | 95lm/W |
| CCT | 4000K, 5000K, 6500K |
| CRI | 80 |
| Operating Temperature | 0 to 40 |
| UGR Design | 25 |
| MacAdam Steps | 5SDCM |
| Ingress Protection Rating | IP20 |
| Warranty | 3 Years |
| Lifetime | 54,000hrs (L70/B50) |


### Physical

| | |
|---|---|
| Dimensions | L630 x W90 x H44 mm |
| Luminaire Colour | White |
| Weight | 0.39kg |
| Driver Location | Integrated |
| Finish | White |
| Installation | Surface Mounting |

### Electrical

| | |
|---|---|
| Dimming | Non - Dimmable |
| Voltage | 240V |
| Line Voltage Frequency | 50Hz |
| Inrush Current | 14A |
| Inrush Current Duration | 120µs |
| Line Current | 0.09A |
| Surge protection | Yes |
| Electrical Rating | Class 1 |

### Line Drawings




### Product Images



*Rated LED design life where stated is based upon application of Pierlite's operating and maintenance guidelines; see pierlite.com.au. Actual product life may vary dependent upon frequency of maintenance and product application. Due to continual product improvement, information is subject to change without notification. standard Terms and Conditions apply



Pierlite is a division of Signify Innovations Australia Pty Ltd