Slimline Batten

SLBAT505ECSLS



- Made with durable low profile metal housing with frosted opal diffuser for uniform illumination.
- Energy efficient and highly reliable up to 100Lm/W and 54,000hrs lifetime.
- Built-in flicker free LED driver for increased visual comfort.

LUMEN SELECT | COLOUR SELECT

Performance

System Power	50W, 41W, 35W
Exit Lumen	5200lm, 5800lm, 5200lm, 4600lm, 3900lm, 5000lm, 4600lm, 4200lm, 3900lm
Efficacy	110lm/W
CCT	4000K, 5000K, 6500K
CRI	80
Operating Temperature	0 to 40
UGR Design	25
MacAdam Steps	5SDCM
Ingress Protection Rating	IP20
Warranty	3 Years
Lifetime	54,000hrs (L70/B50)


Physical

Dimensions	L1530 x W90 x H44 mm
Luminaire Colour	White
Weight	0.91kg
Driver Location	Integrated
Finish	White
Installation	Surface Mounting

Electrical

Dimming	Non - Dimmable
Voltage	240V
Inrush Current	25A
Inrush Current Duration	135µs
Line Current	0.22A
Surge protection	Yes
Electrical Rating	Class 1

Line Drawings



Product Images

*Rated LED design life where stated is based upon application of Pierlite's operating and maintenance guidelines; see pierlite.com.au. Actual product life may vary dependent upon frequency of maintenance and product application. Due to continual product improvement, information is subject to change without notification. standard Terms and Conditions apply

Pierlite is a division of Signify Innovations Australia Pty Ltd